

Metallic Systems

SS Conduit

Technical Characteristics

Conforms to	BSI Kitemark KM-35161 Low voltage directive Inherent Low Fire Hazard (ILFH)
-------------	---

Approvals and Standards	  
-------------------------	---

Degree of mechanical protection	Very high flexibility & fatigue life
---------------------------------	--------------------------------------

Degree of protection	IP40 - with type S fittings
----------------------	-----------------------------

UV protection	Very High
---------------	-----------

Finish	Natural material
--------	------------------

Application	Indoors / Outdoors - Corrosive environments
-------------	---

Normal operating temperature range	Application	Min Temp	Max Temp
	Static	- 50°C	+350°C
	Dynamic	- 45°C	+250 °C

For use with - Fitting range	Adaptasteel - Type A , B , E , and F
------------------------------	--

Fire performance	Test Standard	Performance Rating	(See Fire testing data for fire performance overview)
	EN45545	ILFH	
	NFF16-101	ILFH	
	LUL-1085	ILFH	
	BS6855	ILFH	
	DIN 5510-2	ILFH	

Testing data	Click or See pages 3 & 4
--------------	--

Type of material	Stainless Steel - AISI 316 grade
------------------	----------------------------------




Metallic Systems

SS Conduit



Technical & Dimensional Data

Conduit size metric (mm)	10	12	16	20	25	32	40	50	63	75
Conduit size US trade (inches)	1/4"	5/16"	3/8"	1/2"	3/4"	1"	1 1/4"	1 1/2"	2"	2 1/2"
Part code	SS	SS	SS	SS	SS	SS	-	-	-	-
Coil length (m)	25/50	10/25/50	10/25/50	10/25/50	10/25/50	10/25	-	-	-	-
A - Outside diameter (mm)	9.0	13.0	16.0	20.5	25.0	32.0	-	-	-	-
B - Inside diameter (mm)	6.8	10.3	13.0	16.9	21.4	28.1	-	-	-	-
C - Static bend radius (mm)	25	30	35	45	55	60	-	-	-	-
Average weight (KG/100m)	10	11.6	18.2	23.6	28	46	-	-	-	-
For ordering code add coil length to part code - e.g SS25/25M										



Metallic Systems

SS Conduit



BS EN 61386 Clarification

	Fitting	Compression	Impact	Min temp	Max temp	bending	electrical	IP solids	IP water	Corrosion	Tensile	Non-flame Propagating	Suspended load
SS	S (A)	4	4	5	6	4	0	4	0	4	4	1	5

Mechanical Properties

Test Type	Methods / Standards	Requirements	Value
Crush Strength @ 23°C	IEC61386-1	<25% crush >90% recovery	>1250N class4
Crush Strength @ 23 °C	AFX norm C1989	10% Crush, Instantaneous Value	2200N
Impact Strength @ 23 °C	IEC61386-1	No Cracks <20% deformation	>20J
Impact Strength @ -45 °C	IEC61386-1	No Cracks. <20% deformation	>6J
Tensile Strength	IEC61386-1	With S Type Fitting	>1000N class 4
Tensile Strength	AFX norm T1987	Ultimate pull-out of S-Type Fitting	1700N
Dynamic Bend radius @ -45 °C	IEC61386-23	5000 cycles minimum	4xOD

Thermal Properties

Test Type	Methods / Standards	Requirements	Value
Minimum Temperature	IEC61386-23	Dynamic 5000 cycles	-45°C
Maximum Temperature	IEC61386-23	Dynamic 5000 cycles	250°C
Minimum Static		Permanent Use	-60°C
Maximum Static		Permanent Use	350°C

Chemical Resistance Chart

Key:

Suitable :



Limited Suitability :



Unsuitable :



Not Tested :



● Astm No.1	● Diesel oil	● Methyl Bromide	● Sulphur Dioxide (Gas)
● Astm No.2	● Diethylamine	● MEK	● Sulphuric Acid (10%)
● Astm No.3	● Ethanol	● Nitric Acid (10%)	● Sulphuric Acid (70%)
● Acetic Acid (10%)	● Ether	● Nitric Acid (70%)	● Toluene
● Acetone	● Ethylamine	● Oxalic Acid	● Transformer Oil
● Aluminium Chloride	● Ethylene Glycol	● Ozone (Gas)	● 1,1,1-Trichloroethane
● Aniline	● Ethyl Ethanoate	● Paraffin oil	● Trichloroethylene
● Benzaldehyde	● Freon 32	● Petrol	● Turpentine
● Benzene	● Hydrochloric Acid (10%)	● Phenol	● Vegetable Oil
● Carbon tetrachloride	● Hydrochloric Acid (36%)	● Sea Water	● Vinyl Acetate
● Chlorine water	● Hydrogen Peroxide (35%)	● Silver Nitrate	● Water
● Chloroform	● Hydrogen Peroxide (87%)	● Skydrol	● White Spirit
● Citric Acid	● Lactic Acid	● Sodium Chloride	● Zinc Chloride
● Copper Sulphate	● Lubricating oil	● Sodium Hydroxide (10%)	
● Cresol	● Methanol	● Sodium Hydroxide (60%)	

The information above is given as a guide only and is based on published technical data and experience. The chemical resistance of the above products is dependant on factors such as chemical exposure, concentration of the chemical and temperature. The above chemicals are valid for a temperature of 23°C. Use of the above table is at the users own discretion and risk. Those using it must satisfy themselves that their application presents no health and safety risks. The end user should assess compatibility with their application and contact Thomas & Betts for further information.

ADHERENCE TO THE CURRENT WIRING REGULATIONS BS7671 OR NEC WIRING REGULATIONS (FOR USA) IS STRONGLY ADVISED.

MINIMUM BEND RADIUS FOR FLEXING IS DEPENDANT UPON MINIMUM TEMPERATURE, BENDING FREQUENCY AND CHEMICAL ENVIRONMENT.

Cable Management Products Ltd.

CMG House - Station Road - Coleshill - B46 1HT - United Kingdom

Tel: +44(0)1675 468 222 - Fax: +44(0)1675 464 930

Technical Support e-mail: cmg.conduitsystems@abb.com - www.adaptaflex.co.uk

Metallic Systems

SS Conduit



Flammability

Test Type	Method / Standard	Requirement	Result	Unit
Oxygen Index	ISO 4589-2	% Oxygen to support combustion	ILFH	%
Glow Wire Rating	IEC 60695	No Ignition to Extinguish with 30s	ILFH	°C
Flammability	UL94	Vertical (V0, V2) or Horizontal (HB)	ILFH	
Flammability	IEC 61386-1	1Kw Burner @ 45°	ILFH	Pass/Fail
FTI	ISO 4589-3		ILFH	

Smoke

Test Type	Method / Standard	Requirement	Result	Unit
Smoke Density	ATS1000	In flaming mode <100 @ 4 mins	ILFH	
Smoke Density	ATS1000	In non flaming mode <100 @ 4 mins	ILFH	
Smoke Density	BS6853	A <0.02	ILFH	
Smoke Density	ASTM E-662	Flaming mode Ds Max	ILFH	
Smoke Density	ISO - 5659-2	Ds Max	ILFH	

Toxicity

Test Type	Method / Standard	Requirement	Result	Unit
Halogen Free	LUL	<0.5%	ILFH	Yes/No
Phosphorous Free	LUL	<0.5%	ILFH	Yes/No
Sulphur Free	LUL	<0.5%	ILFH	Yes/No
NFX 70-100	NFX70 - 100 1 / 2	CIT _{NLP}	ILFH	N/A

Fire Performance Overview

Property	Low Fire Hazard	Enhanced Low Fire Hazard	Super Low Fire Hazard	Inherent Low Fire Hazard
Property Oxygen Index ISO4589 BS6853 Smoke Density 3m ³ Zero Halogen Zero Phosphorus Zero Sulphur NFF16-102 EN45545-2	 LFH 32% ≥ OI ≥ 28% 0.02 ≤ A _s ≤ 0.03 ✓ ✓ ✓ I3F2 HL2	 EFLH OI ≥ 32% 0.0005 ± A _s ≤ 0.02 ✓ ✓ ✓ I2F2 HL3	 SLFH OI ≥ 32% A _s ≤ 0.005 ✓ ✓ ✓ I2F1 HL3	 ILFH Inherent Low Fire Hazard i.e Type , S, SS Metallic Conduit & Fit- tings

Pre Test Conditions

Duration	Standard	Temperature	Relative Humidity
168 (Hours)	EN50086/IEC61386	23 (°C)	50 (%)

Cable Management Products Ltd.

CMG House - Station Road - Coleshill - B46 1HT - United Kingdom

Tel: +44(0)1675 468 222 - Fax: +44(0)1675 464 930

Technical Support e-mail: cmg.conduitsystems@abb.com - www.adaptaflex.co.uk