

# Metallic Systems

## SPL Fitting Type A



### Technical Characteristics

Conforms to BSI Kitemark KM-35161  
CE mark to the Low Voltage Directive  
Inherent Low Fire Hazard

Approvals and Standards



Degree of mechanical protection

Very High

Degree of protection

IP67 - with all [Adaptasteel](#) liquid tight conduit in the series

UV protection

Very High

Fitting characteristics

Straight fitting - Fixed external male thread

Application

For insertion into knockouts using a locknut

Normal operating temperature range

Application	Min Temp	Max Temp
Static	- 65°C	+150°C
Dynamic	- 45°C	+150°C

For use with - Conduit series

Type [SPL](#), [SPL-EF](#), [SPLHC](#) & [SPUL](#)

Fire performance

**Test Standard**

**Performance Rating**

Not Rated

Not Rated

Testing data

Click or see page [4](#)

Type of material

Nickel Plated Brass, Co-Polyester seal - Nylon inserts

Image




# Metallic Systems

## SPL Fitting Type A



### Dimensional Data

Part No	Thread A	Nominal Dimensions (mm)				Nominal Conduit - $\varnothing$ F (mm)
		B	C	D	E	
SPL10/M16/A	M16 x 1.0	10.	18.0	18.0	5.7	18.0
SPL12/M16/A	M16 x 1.5	13.0	18.0	20.6	8.6	20.6
SPL16/M16/A	M16 x 1.5	13.0	20.0	22.0	10.3	24.0
SPL16/M20/A	M20 x 1.5	13.5	20.0	24.0	10.3	24.0
SPL20/M20/A	M20 x 1.5	15.0	22.0	25.4	14.3	24.0
SPL25/M25/A	M25 x 1.5	17.0	28.0	32.0	17.6	27.0
SPL32/M32/A	M32 x 1.5	19.0	34.0	38.0	24.0	34.0



**Cable Management Products Ltd.**

CMG House - Station Road - Coleshill - B46 1HT - United Kingdom

Tel: +44(0)1675 468 222 - Fax: +44(0)1675 464 930

Technical Support e-mail: [cmg.conduitsystems@abb.com](mailto:cmg.conduitsystems@abb.com) - [www.adaptaflex.com](http://www.adaptaflex.com)

The Company's policy is one of continuous improvement and reserves the right to change specifications at any time without prior notice.


# Metallic Systems

## SPL Fitting Type A



### Dimensional Data

Part No	Thread A	Nominal Dimensions (mm)				F (mm)
		B	C	D	E	
SPL10/PG7/A	PG7	10.0	18.0	17.0	5.7	18.0
SPL12/PG9/A	PG9	13.0	18.0	20.6	8.1	20.6
SPL16/PG11/A	PG11	13.0	20.0	24.0	10.3	24.0
SPL16/PG13/A	PG13.5	13.5	20.0	24.0	10.3	24.0
SPL20/PG16/A	PG16	15.0	22.0	25.4	14.3	27.0
SPL25/PG21/A	PG21	17.0	28.0	34.0	17.6	34.0
SPL32/PG29/A	PG29	19.0	34.0	42.0	24.0	42.0
SPL40/PG36/A	PG36	20.0	38.0	52.0	33.0	52.0
SPL50/PG42/A	PG42	24.0	43.0	60.0	38.5	60.0
SPL63/PG48/A	PG48	28.0	56.0	70.0	50.0	70.0



**Cable Management Products Ltd.**

CMG House - Station Road - Coleshill - B46 1HT - United Kingdom

Tel: +44(0)1675 468 222 - Fax: +44(0)1675 464 930

Technical Support e-mail: [cmg.conduitsystems@abb.com](mailto:cmg.conduitsystems@abb.com) - [www.adaptaflex.com](http://www.adaptaflex.com)

# Metallic Systems

## SPL Fitting Type A



### Chemical Resistance Chart

<b>Key:</b>	●	Astm No.1	●	Diesel oil	●	Methyl Bromide	●	Sulphur Dioxide (Gas)
	●	Astm No.2	●	Diethylamine	●	MEK	●	Sulphuric Acid (10%)
	●	Astm No.3	●	Ethanol	●	Nitric Acid (10%)	●	Sulphuric Acid (70%)
	●	Acetic Acid (10%)	●	Ether	●	Nitric Acid (70%)	●	Toluene
	●	Acetone	●	Ethylamine	●	Oxalic Acid	●	Transformer Oil
	●	Aluminium Chloride	●	Ethylene Glycol	●	Ozone (Gas)	●	1,1,1-Trichloroethane
	●	Aniline	●	Ethyl Ethanoate	●	Paraffin oil	●	Trichloroethylene
	●	Benzaldehyde	●	Freon 32	●	Petrol	●	Turpentine
	●	Benzene	●	Hydrochloric Acid (10%)	●	Phenol	●	Vegetable Oil
	●	Carbon tetrachloride	●	Hydrochloric Acid (36%)	●	Sea Water	●	Vinyl Acetate
	●	Chlorine water	●	Hydrogen Peroxide (35%)	●	Silver Nitrate	●	Water
	●	Chloroform	●	Hydrogen Peroxide (87%)	●	Skydrol	●	White Spirit
	●	Citric Acid	●	Lactic Acid	●	Sodium Chloride	●	Zinc Chloride
	●	Copper Sulphate	●	Lubricating oil	●	Sodium Hydroxide (10%)		
	●	Cresol	●	Methanol	●	Sodium Hydroxide (60%)		

The information above is given as a guide only and is based on published technical data and experience. The chemical resistance of the above products is dependant on factors such as chemical exposure, concentration of the chemical and temperature. The above chemicals are valid for a temperature of 23°C. Use of the above table is at the users own discretion and risk. Those using it must satisfy themselves that their application presents no health and safety risks. The end user should assess compatibility with their application and contact Thomas & Betts for further information.

ADHERENCE TO THE CURRENT WIRING REGULATIONS BS7671 OR NEC WIRING REGULATIONS (FOR USA) IS STRONGLY ADVISED.

MINIMUM BEND RADIUS FOR FLEXING IS DEPENDANT UPON MINIMUM TEMPERATURE, BENDING FREQUENCY AND CHEMICAL ENVIRONMENT.

### Thread Data

Metric	Standard thread conforming to EN60423 & BS3643			PG	German Standard thread conforming to DIN40430		
	Ext Thread Outside Diameter	Int Thread Inside Diameter	Pitch		Thread Size	Ext Thread Outside Diameter	Int Thread Inside Diameter
M10	10.0	8.9	1.0	PG7	12.5	11.3	1.27
M12	12.0	10.4	1.5	PG9	15.2	13.9	1.41
M16	16.0	14.4	1.5	PG11	18.6	17.3	1.41
M20	20.0	18.4	1.5	PG13.5	20.4	19.1	1.41
M25	25.0	23.4	1.5	PG16	22.5	21.2	1.41
M32	32.0	30.4	1.5	PG21	28.3	26.8	1.59
M40	40.0	38.4	1.5	PG29	37.0	35.5	1.59
M50	50.0	48.4	1.5	PG36	47.0	45.5	1.59
M63	63.0	61.4	1.5	PG42	54.0	52.2	1.59
M75	75.0	73.4	1.5	PG48	59.3	57.8	1.59

**Cable Management Products Ltd.**

CMG House - Station Road - Coleshill - B46 1HT - United Kingdom

Tel: +44(0)1675 468 222 - Fax: +44(0)1675 464 930

Technical Support e-mail: [cmg.conduitsystems@abb.com](mailto:cmg.conduitsystems@abb.com) - [www.adaptaflex.com](http://www.adaptaflex.com)