

## YPS Y-piece

### External conduit fitting



#### External Y-piece

Asymmetrical 3 junction fittings allow a variety of conduit size variations. These fittings are designed to snap together over all types of slit and unslit conduit, maintaining maximum conduit bore.



YPS / YPH External Y-piece

|  | Part No.   | TempGuard Part No. | Conduit size (NC) |    |    | Conduit size (NW) |     |     | Nominal dimensions (mm) |      |      |      |      |
|--|------------|--------------------|-------------------|----|----|-------------------|-----|-----|-------------------------|------|------|------|------|
|  |            |                    | A                 | B  | C  | A                 | B   | C   | D                       | E    | F    | G    | H    |
|  | YPS060606* | YPH060606*         | 06                | 06 | 06 | 4.5               | 4.5 | 4.5 | 55.0                    | 37.0 | 10.0 | 10.0 | 10.0 |
|  | YPS080808  | YPH080808          | 08                | 08 | 08 | 7.5               | 7.5 | 7.5 | 55.0                    | 37.0 | 10.0 | 10.0 | 10.0 |
|  | YPS080812  | YPH080812          | 08                | 08 | 12 | 7.5               | 7.5 | 10  | 55.0                    | 37.0 | 10.0 | 10.0 | 10.0 |
|  | YPS081208  | YPH081208          | 08                | 12 | 08 | 7.5               | 10  | 7.5 | 55.0                    | 37.0 | 10.0 | 10.0 | 10.0 |
|  | YPS101010  | YPH101010          | 10                | 10 | 10 | 8.5               | 8.5 | 8.5 | 55.0                    | 37.0 | 10.0 | 10.0 | 10.0 |
|  | YPS120808  | YPH120808          | 12                | 08 | 08 | 10                | 7.5 | 7.5 | 55.0                    | 37.0 | 10.0 | 10.0 | 10.0 |
|  | YPS120810  | YPH120810          | 12                | 08 | 10 | 10                | 7.5 | 8.5 | 55.0                    | 37.0 | 10.0 | 10.0 | 10.0 |
|  | YPS120812  | YPH120812          | 12                | 08 | 12 | 10                | 7.5 | 10  | 55.0                    | 37.0 | 10.0 | 10.0 | 10.0 |
|  | YPS121010  | YPH121010          | 12                | 10 | 10 | 10                | 8.5 | 8.5 | 55.0                    | 37.0 | 10.0 | 10.0 | 10.0 |
|  | YPS121208  | YPH121208          | 12                | 12 | 08 | 10                | 10  | 7.5 | 55.0                    | 37.0 | 10.0 | 10.0 | 10.0 |
|  | YPS121210  | YPH121210          | 12                | 12 | 10 | 10                | 10  | 8.5 | 55.0                    | 37.0 | 10.0 | 10.0 | 10.0 |
|  | YPS121212  | YPH121212          | 12                | 12 | 12 | 10                | 10  | 10  | 55.0                    | 37.0 | 10.0 | 10.0 | 10.0 |
|  | YPS160812  | YPH160812          | 16                | 08 | 12 | 13                | 7.5 | 10  | 55.0                    | 37.0 | 10.0 | 10.0 | 10.0 |
|  | YPS161010  | YPH161010          | 16                | 10 | 10 | 13                | 8.5 | 8.5 | 55.0                    | 40.0 | 10.0 | 10.0 | 10.0 |
|  | YPS161208  | YPH161208          | 16                | 12 | 08 | 13                | 10  | 7.5 | 55.0                    | 40.0 | 10.0 | 10.0 | 10.0 |
|  | YPS161210  | YPH161210          | 16                | 12 | 10 | 13                | 10  | 8.5 | 55.0                    | 40.0 | 10.0 | 10.0 | 10.0 |
|  | YPS161212  | YPH161212          | 16                | 12 | 12 | 13                | 10  | 10  | 55.0                    | 40.0 | 10.0 | 10.0 | 10.0 |
|  | YPS161608  | YPH161608          | 16                | 16 | 08 | 13                | 13  | 7.5 | 55.0                    | 40.0 | 10.0 | 10.0 | 10.0 |
|  | YPS161610  | YPH161610          | 16                | 16 | 10 | 13                | 13  | 8.5 | 55.0                    | 40.0 | 10.0 | 10.0 | 10.0 |
|  | YPS161612  | YPH161612          | 16                | 16 | 12 | 13                | 13  | 10  | 55.0                    | 40.0 | 10.0 | 10.0 | 10.0 |
|  | YPS200808  | YPH200808          | 20                | 08 | 08 | 17                | 7.5 | 7.5 | 43.0                    | 37.0 | 12.0 | 10.0 | 10.0 |
|  | YPS201208  | YPH201208          | 20                | 12 | 08 | 17                | 10  | 7.5 | 43.0                    | 37.0 | 12.0 | 10.0 | 10.0 |
|  | YPS201210  | YPH201210          | 20                | 12 | 10 | 17                | 10  | 8.5 | 43.0                    | 37.0 | 12.0 | 10.0 | 10.0 |
|  | YPS201212  | YPH201212          | 20                | 12 | 12 | 17                | 10  | 10  | 43.0                    | 37.0 | 12.0 | 10.0 | 10.0 |
|  | YPS201608  | YPH201608          | 20                | 16 | 08 | 17                | 13  | 7.5 | 43.0                    | 37.0 | 12.0 | 10.0 | 10.0 |
|  | YPS201612  | YPH201612          | 20                | 16 | 12 | 17                | 13  | 10  | 48.0                    | 40.0 | 12.0 | 10.0 | 10.0 |
|  | YPS201616  | YPH201616          | 20                | 16 | 16 | 17                | 13  | 13  | 48.0                    | 40.0 | 12.0 | 10.0 | 10.0 |
|  | YPS202008  | YPH202008          | 20                | 20 | 08 | 17                | 17  | 7.5 | 56.0                    | 45.0 | 12.0 | 10.0 | 10.0 |
|  | YPS202010  | YPH202010          | 20                | 20 | 10 | 17                | 17  | 8.5 | 58.0                    | 45.0 | 12.0 | 12.0 | 10.0 |
|  | YPS202012  | YPH202012          | 20                | 20 | 12 | 17                | 17  | 10  | 58.0                    | 45.0 | 12.0 | 12.0 | 10.0 |
|  | YPS202016  | YPH202016          | 20                | 20 | 16 | 17                | 17  | 13  | 64.0                    | 48.0 | 12.0 | 12.0 | 10.0 |
|  | YPS252020  | YPH252020          | 25                | 20 | 20 | 22                | 17  | 17  | 54.0                    | 49.0 | 10.0 | 12.0 | 12.0 |
|  | YPS252508  | YPH252508          | 25                | 25 | 08 | 22                | 22  | 7.5 | 67.0                    | 56.0 | 10.0 | 12.0 | 10.0 |
|  | YPS252510  | YPH252510          | 25                | 25 | 10 | 22                | 22  | 8.5 | 67.0                    | 56.0 | 10.0 | 13.0 | 10.0 |
|  | YPS252512  | YPH252512          | 25                | 25 | 12 | 22                | 22  | 10  | 67.0                    | 56.0 | 10.0 | 13.0 | 10.0 |
|  | YPS252516  | YPH252516          | 25                | 25 | 16 | 22                | 22  | 13  | 67.0                    | 56.0 | 10.0 | 13.0 | 10.0 |
|  | YPS252520  | YPH252520          | 25                | 25 | 20 | 22                | 22  | 17  | 77.0                    | 60.0 | 10.0 | 13.0 | 12.0 |

\*Item supplied as kit with x3 insertable reducer.

## YPS Y-piece

### External conduit fitting (continued)

|                                                                                    | Part No.  | TempGuard<br>Part No. | Conduit size<br>(NC) |    |    | Conduit size<br>(NW) |    |     | Nominal Dimensions<br>(mm) |       |      |      |      |
|------------------------------------------------------------------------------------|-----------|-----------------------|----------------------|----|----|----------------------|----|-----|----------------------------|-------|------|------|------|
|                                                                                    |           |                       | A                    | B  | C  | A                    | B  | C   | D                          | E     | F    | G    | H    |
|   | YPS252525 | YPH252525             | 25                   | 25 | 25 | 22                   | 22 | 22  | 91.0                       | 67.0  | 10.0 | 13.0 | 13.0 |
|                                                                                    | YPS282012 | YPH282012             | 28                   | 20 | 12 | 23                   | 17 | 10  | 54.0                       | 49.0  | 10.0 | 13.0 | 10.0 |
|  | YPS282016 | YPH282016             | 28                   | 20 | 16 | 23                   | 17 | 13  | 54.0                       | 49.0  | 10.0 | 12.0 | 10.0 |
|                                                                                    | YPS282020 | YPH282020             | 28                   | 20 | 20 | 23                   | 17 | 17  | 54.0                       | 49.0  | 10.0 | 12.0 | 12.0 |
|                                                                                    | YPS282512 | YPH282512             | 28                   | 25 | 12 | 23                   | 22 | 10  | 67.0                       | 56.0  | 10.0 | 12.0 | 10.0 |
|                                                                                    | YPS282520 | YPH282520             | 28                   | 25 | 20 | 23                   | 22 | 17  | 77.0                       | 60.0  | 10.0 | 13.0 | 12.0 |
|                                                                                    | YPS282525 | YPH282525             | 28                   | 25 | 25 | 23                   | 22 | 22  | 91.0                       | 67.0  | 10.0 | 13.0 | 13.0 |
|                                                                                    | YPS282808 | YPH282808             | 28                   | 28 | 08 | 23                   | 23 | 7.5 | 67.0                       | 56.0  | 10.0 | 13.0 | 10.0 |
|                                                                                    | YPS282812 | YPH282812             | 28                   | 28 | 12 | 23                   | 23 | 10  | 67.0                       | 56.0  | 10.0 | 13.0 | 10.0 |
|                                                                                    | YPS282816 | YPH282816             | 28                   | 28 | 16 | 23                   | 23 | 13  | 67.0                       | 56.0  | 10.0 | 13.0 | 10.0 |
|                                                                                    | YPS282820 | YPH282820             | 28                   | 28 | 20 | 23                   | 23 | 17  | 77.0                       | 60.0  | 10.0 | 13.0 | 12.0 |
|                                                                                    | YPS282825 | YPH282825             | 28                   | 28 | 25 | 23                   | 23 | 22  | 91.0                       | 67.0  | 12.0 | 13.0 | 13.0 |
|                                                                                    | YPS282828 | YPH282828             | 28                   | 28 | 28 | 23                   | 23 | 23  | 91.0                       | 67.0  | 12.0 | 13.0 | 13.0 |
|                                                                                    | YPS322516 | YPH322516             | 32                   | 25 | 16 | 29                   | 22 | 13  | 100.0                      | 75.0  | 12.0 | 13.0 | 10.0 |
|                                                                                    | YPS322520 | YPH322520             | 32                   | 25 | 20 | 29                   | 22 | 17  | 100.0                      | 76.0  | 12.0 | 13.0 | 12.0 |
|                                                                                    | YPS322525 | YPH322525             | 32                   | 25 | 25 | 29                   | 22 | 22  | 100.0                      | 79.0  | 12.0 | 13.0 | 13.0 |
|                                                                                    | YPS322532 | YPH322532             | 32                   | 25 | 32 | 29                   | 22 | 29  | 100.0                      | 82.0  | 12.0 | 13.0 | 13.0 |
|                                                                                    | YPS323216 | YPH323216             | 32                   | 32 | 16 | 29                   | 29 | 13  | 100.0                      | 75.0  | 12.0 | 13.0 | 10.0 |
|                                                                                    | YPS323220 | YPH323220             | 32                   | 32 | 20 | 29                   | 29 | 17  | 100.0                      | 76.0  | 12.0 | 13.0 | 12.0 |
|                                                                                    | YPS323225 | YPH323225             | 32                   | 32 | 25 | 29                   | 29 | 22  | 100.0                      | 79.0  | 12.0 | 13.0 | 13.0 |
|                                                                                    | YPS323232 | YPH323232             | 32                   | 32 | 32 | 29                   | 29 | 29  | 100.0                      | 82.0  | 13.0 | 13.0 | 13.0 |
|                                                                                    | YPS403212 | YPH403212             | 40                   | 32 | 12 | 36                   | 29 | 10  | 133.0                      | 91.0  | 15.0 | 12.0 | 10.0 |
|                                                                                    | YPS403216 | YPH403216             | 40                   | 32 | 16 | 36                   | 29 | 13  | 133.0                      | 92.0  | 15.0 | 12.0 | 10.0 |
|                                                                                    | YPS403225 | YPH403225             | 40                   | 32 | 25 | 36                   | 29 | 22  | 133.0                      | 92.0  | 15.0 | 12.0 | 12.0 |
|                                                                                    | YPS403228 | YPH403228             | 40                   | 32 | 28 | 36                   | 29 | 23  | 133.0                      | 92.0  | 15.0 | 12.0 | 12.0 |
|                                                                                    | YPS404012 | YPH404012             | 40                   | 40 | 12 | 36                   | 36 | 10  | 135.0                      | 93.0  | 15.0 | 15.0 | 10.0 |
|                                                                                    | YPS404016 | YPH404016             | 40                   | 40 | 16 | 36                   | 36 | 13  | 135.0                      | 93.0  | 15.0 | 15.0 | 10.0 |
|                                                                                    | YPS404025 | YPH404025             | 40                   | 40 | 25 | 36                   | 36 | 22  | 135.0                      | 93.0  | 15.0 | 15.0 | 12.0 |
|                                                                                    | YPS404028 | YPH404028             | 40                   | 40 | 28 | 36                   | 36 | 23  | 135.0                      | 93.0  | 15.0 | 15.0 | 12.0 |
|                                                                                    | YPS404032 | YPH404032             | 40                   | 40 | 32 | 36                   | 36 | 29  | 135.0                      | 96.0  | 15.0 | 15.0 | 12.0 |
|                                                                                    | YPS404040 | YPH404040             | 40                   | 40 | 40 | 36                   | 36 | 36  | 135.0                      | 100.0 | 15.0 | 15.0 | 15.0 |

## TPS T-piece

### External conduit fitting



#### External T-piece

3 junction fittings allow a variety of conduit size variations. These fittings are designed to snap together over all types of slit and unslit conduit, maintaining maximum conduit bore.


TPS / TPH External T-piece

|  | Part No.   | TempGuard Part No. | Conduit size (NC) |    |    | Conduit size (NW) |     |     | Nominal dimensions (mm) |      |      |      |      |      |
|--|------------|--------------------|-------------------|----|----|-------------------|-----|-----|-------------------------|------|------|------|------|------|
|  |            |                    | A                 | B  | C  | A                 | B   | C   | D                       | E    | F    | G    | H    | I    |
|  | TPS060606* | TPH060606*         | 06                | 06 | 06 | 4.5               | 4.5 | 4.5 | 45.2                    | 31.1 | 17.0 | 10.0 | 10.0 | 10.0 |
|  | TPS080808  | TPH080808          | 08                | 08 | 08 | 7.5               | 7.5 | 7.5 | 45.2                    | 31.1 | 17.0 | 10.0 | 10.0 | 10.0 |
|  | TPS081208  | TPH081208          | 08                | 12 | 08 | 7.5               | 10  | 7.5 | 45.2                    | 31.1 | 17.0 | 10.0 | 10.0 | 10.0 |
|  | TPS081612  | TPH081612          | 08                | 16 | 12 | 7.5               | 13  | 10  | 45.2                    | 31.1 | 17.0 | 10.0 | 10.0 | 10.0 |
|  | TPS100808  | TPH100808          | 10                | 08 | 08 | 8.5               | 7.5 | 7.5 | 45.2                    | 31.1 | 17.0 | 10.0 | 10.0 | 10.0 |
|  | TPS100810  | TPH100810          | 10                | 08 | 10 | 8.5               | 7.5 | 8.5 | 45.2                    | 31.1 | 17.0 | 10.0 | 10.0 | 10.0 |
|  | TPS101010  | TPH101010          | 10                | 10 | 10 | 8.5               | 8.5 | 8.5 | 45.2                    | 31.1 | 17.0 | 10.0 | 10.0 | 10.0 |
|  | TPS101012  | TPH101012          | 10                | 10 | 12 | 8.5               | 8.5 | 13  | 45.2                    | 31.1 | 17.0 | 10.0 | 10.0 | 10.0 |
|  | TPS120808  | TPH120808          | 12                | 08 | 08 | 10                | 7.5 | 7.5 | 45.2                    | 31.1 | 17.0 | 10.0 | 10.0 | 10.0 |
|  | TPS120812  | TPH120812          | 12                | 08 | 12 | 10                | 7.5 | 10  | 45.2                    | 31.1 | 17.0 | 10.0 | 10.0 | 10.0 |
|  | TPS121010  | TPH121210          | 12                | 10 | 10 | 10                | 8.5 | 8.5 | 45.2                    | 31.1 | 17.0 | 10.0 | 10.0 | 10.0 |
|  | TPS121012  | TPH121012          | 12                | 10 | 12 | 10                | 8.5 | 10  | 45.2                    | 31.1 | 17.0 | 10.0 | 10.0 | 10.0 |
|  | TPS121208  | TPH121208          | 12                | 12 | 08 | 10                | 10  | 7.5 | 45.2                    | 31.1 | 17.0 | 10.0 | 10.0 | 10.0 |
|  | TPS121210  | TPH121210          | 12                | 12 | 10 | 10                | 10  | 7.5 | 45.2                    | 31.1 | 17.0 | 10.0 | 10.0 | 10.0 |
|  | TPS121212  | TPH121212          | 12                | 12 | 12 | 10                | 10  | 10  | 45.2                    | 31.1 | 17.0 | 10.0 | 10.0 | 10.0 |
|  | TPS121612  | TPH121612          | 12                | 16 | 12 | 10                | 13  | 10  | 45.2                    | 31.1 | 21.0 | 10.0 | 10.0 | 10.0 |
|  | TPS160808  | TPH160808          | 16                | 08 | 08 | 13                | 7.5 | 7.5 | 49.1                    | 34.8 | 21.0 | 10.0 | 10.0 | 10.0 |
|  | TPS160812  | TPH160812          | 16                | 08 | 12 | 13                | 7.5 | 10  | 49.1                    | 34.8 | 21.0 | 10.0 | 10.0 | 10.0 |
|  | TPS160816  | TPH160816          | 16                | 08 | 16 | 13                | 7.5 | 13  | 49.1                    | 34.8 | 21.0 | 10.0 | 10.0 | 10.0 |
|  | TPS161012  | TPH161012          | 16                | 10 | 12 | 13                | 8.5 | 10  | 49.1                    | 34.8 | 21.0 | 10.0 | 10.0 | 10.0 |
|  | TPS161016  | TPH161016          | 16                | 10 | 16 | 13                | 8.5 | 13  | 49.1                    | 34.8 | 21.0 | 10.0 | 10.0 | 10.0 |
|  | TPS161212  | TPH161212          | 16                | 12 | 12 | 13                | 10  | 10  | 49.1                    | 34.8 | 21.0 | 10.0 | 10.0 | 10.0 |
|  | TPS161216  | TPH161216          | 16                | 12 | 16 | 13                | 10  | 13  | 49.1                    | 34.8 | 21.0 | 10.0 | 10.0 | 10.0 |
|  | TPS161608  | TPH161608          | 16                | 16 | 08 | 13                | 13  | 7.5 | 49.1                    | 34.8 | 21.0 | 10.0 | 10.0 | 10.0 |
|  | TPS161612  | TPH161612          | 16                | 16 | 12 | 13                | 13  | 10  | 49.1                    | 34.8 | 21.0 | 10.0 | 10.0 | 10.0 |
|  | TPS161616  | TPH161616          | 16                | 16 | 16 | 13                | 13  | 13  | 49.1                    | 34.8 | 21.0 | 10.0 | 10.0 | 10.0 |
|  | TPS162012  | TPH162012          | 16                | 20 | 12 | 13                | 17  | 10  | 49.1                    | 34.8 | 21.0 | 10.0 | 10.0 | 10.0 |
|  | TPS162016  | TPH162016          | 16                | 20 | 16 | 13                | 17  | 13  | 49.1                    | 34.8 | 21.0 | 10.0 | 10.0 | 10.0 |
|  | TPS200816  | TPH200816          | 20                | 08 | 16 | 17                | 7.5 | 13  | 56.5                    | 41.0 | 26.0 | 12.0 | 10.0 | 10.0 |
|  | TPS200820  | TPH200820          | 20                | 08 | 20 | 17                | 7.5 | 17  | 56.5                    | 41.0 | 26.0 | 12.0 | 10.0 | 12.0 |
|  | TPS201016  | TPH201016          | 20                | 10 | 16 | 17                | 8.5 | 13  | 56.5                    | 41.0 | 26.0 | 12.0 | 10.0 | 10.0 |
|  | TPS201020  | TPH201020          | 20                | 10 | 20 | 17                | 8.5 | 17  | 56.5                    | 41.0 | 26.0 | 12.0 | 10.0 | 12.0 |
|  | TPS201216  | TPH201216          | 20                | 12 | 16 | 17                | 10  | 13  | 56.5                    | 41.0 | 26.0 | 12.0 | 10.0 | 10.0 |
|  | TPS201220  | TPH201220          | 20                | 12 | 20 | 17                | 10  | 17  | 56.5                    | 41.0 | 26.0 | 12.0 | 10.0 | 12.0 |
|  | TPS201612  | TPH201612          | 20                | 16 | 12 | 17                | 13  | 10  | 56.5                    | 41.0 | 26.0 | 12.0 | 10.0 | 10.0 |
|  | TPS201616  | TPH201616          | 20                | 16 | 16 | 17                | 13  | 13  | 56.5                    | 41.0 | 26.0 | 12.0 | 10.0 | 10.0 |
|  | TPS201620  | TPH201620          | 20                | 16 | 20 | 17                | 13  | 17  | 56.5                    | 41.0 | 26.0 | 12.0 | 10.0 | 12.0 |

\*Item supplied as kit with x3 insertable reducer.

## TPS T-piece

### External conduit fitting (continued)

|                                                                                   | Part No.  | TempGuard<br>Part No. | Conduit size<br>(NC) |    |    | Conduit size<br>(NW) |     |    | Nominal dimensions<br>(mm) |      |      |      |      |      |
|-----------------------------------------------------------------------------------|-----------|-----------------------|----------------------|----|----|----------------------|-----|----|----------------------------|------|------|------|------|------|
|                                                                                   |           |                       | A                    | B  | C  | A                    | B   | C  | D                          | E    | F    | G    | H    | I    |
|  | TPS202012 | TPH202012             | 20                   | 20 | 12 | 17                   | 17  | 10 | 56.5                       | 41.0 | 26.0 | 12.0 | 12.0 | 10.0 |
|                                                                                   | TPS202016 | TPH202016             | 20                   | 20 | 16 | 17                   | 17  | 13 | 56.5                       | 41.0 | 26.0 | 12.0 | 12.0 | 10.0 |
|                                                                                   | TPS202020 | TPH202020             | 20                   | 20 | 20 | 17                   | 17  | 17 | 56.5                       | 41.0 | 26.0 | 12.0 | 12.0 | 12.0 |
|                                                                                   | TPS202516 | TPH202516             | 20                   | 25 | 16 | 17                   | 22  | 13 | 64.5                       | 48.5 | 33.0 | 12.0 | 13.0 | 10.0 |
|                                                                                   | TPS250820 | TPH250820             | 25                   | 08 | 20 | 22                   | 7.5 | 17 | 64.5                       | 48.5 | 33.0 | 13.0 | 10.0 | 12.0 |
|                                                                                   | TPS250825 | TPH250825             | 25                   | 08 | 25 | 22                   | 7.5 | 22 | 64.5                       | 48.5 | 33.0 | 13.0 | 10.0 | 13.0 |
|                                                                                   | TPS251025 | TPH251025             | 25                   | 10 | 25 | 22                   | 8.5 | 22 | 64.5                       | 48.5 | 33.0 | 13.0 | 10.0 | 13.0 |
|                                                                                   | TPS251220 | TPH251220             | 25                   | 12 | 20 | 22                   | 10  | 17 | 64.5                       | 48.5 | 33.0 | 13.0 | 10.0 | 12.0 |
|                                                                                   | TPS251225 | TPH251225             | 25                   | 12 | 25 | 22                   | 10  | 22 | 64.5                       | 48.5 | 33.0 | 13.0 | 10.0 | 13.0 |
|                                                                                   | TPS251620 | TPH251620             | 25                   | 16 | 20 | 22                   | 13  | 17 | 64.5                       | 48.5 | 33.0 | 13.0 | 12.0 | 12.0 |
|                                                                                   | TPS251625 | TPH251625             | 25                   | 16 | 25 | 22                   | 13  | 22 | 64.5                       | 48.5 | 33.0 | 13.0 | 12.0 | 13.0 |
|                                                                                   | TPS252020 | TPH252020             | 25                   | 20 | 20 | 22                   | 17  | 17 | 64.5                       | 48.5 | 33.0 | 13.0 | 13.0 | 12.0 |
|                                                                                   | TPS252025 | TPH252025             | 25                   | 20 | 25 | 22                   | 17  | 22 | 64.5                       | 48.5 | 33.0 | 13.0 | 13.0 | 13.0 |
|                                                                                   | TPS252520 | TPH252520             | 25                   | 25 | 20 | 22                   | 22  | 17 | 64.5                       | 48.5 | 33.0 | 13.0 | 10.0 | 12.0 |
|                                                                                   | TPS252525 | TPH252525             | 25                   | 25 | 25 | 22                   | 22  | 22 | 64.5                       | 48.5 | 33.0 | 13.0 | 10.0 | 13.0 |
|                                                                                   | TPS280820 | TPH280820             | 28                   | 08 | 20 | 23                   | 7.5 | 17 | 64.5                       | 48.5 | 33.0 | 13.0 | 10.0 | 12.0 |
|                                                                                   | TPS280828 | TPH280828             | 28                   | 08 | 28 | 23                   | 7.5 | 23 | 64.5                       | 48.5 | 33.0 | 13.0 | 10.0 | 13.0 |
|                                                                                   | TPS281020 | TPH281020             | 28                   | 10 | 20 | 23                   | 8.5 | 17 | 64.5                       | 48.5 | 33.0 | 13.0 | 10.0 | 12.0 |
|                                                                                   | TPS281028 | TPH281028             | 28                   | 10 | 28 | 23                   | 8.5 | 23 | 64.5                       | 48.5 | 33.0 | 13.0 | 10.0 | 13.0 |
|                                                                                   | TPS281220 | TPH281220             | 28                   | 12 | 20 | 23                   | 10  | 17 | 64.5                       | 48.5 | 33.0 | 13.0 | 10.0 | 13.0 |
|                                                                                   | TPS281225 | TPH281225             | 28                   | 12 | 25 | 23                   | 10  | 22 | 64.5                       | 48.5 | 33.0 | 13.0 | 10.0 | 12.0 |
|                                                                                   | TPS281228 | TPH281228             | 28                   | 12 | 28 | 23                   | 10  | 23 | 64.5                       | 48.5 | 33.0 | 13.0 | 10.0 | 13.0 |
|                                                                                   | TPS281620 | TPH281620             | 28                   | 16 | 20 | 23                   | 13  | 17 | 64.5                       | 48.5 | 33.0 | 13.0 | 10.0 | 12.0 |
|                                                                                   | TPS281625 | TPH281625             | 28                   | 16 | 25 | 23                   | 13  | 22 | 64.5                       | 48.5 | 33.0 | 13.0 | 10.0 | 13.0 |
|                                                                                   | TPS281628 | TPH281628             | 28                   | 16 | 28 | 23                   | 13  | 23 | 64.5                       | 48.5 | 33.0 | 13.0 | 10.0 | 13.0 |
|                                                                                   | TPS282020 | TPH282020             | 28                   | 20 | 20 | 23                   | 17  | 17 | 64.5                       | 48.5 | 33.0 | 13.0 | 12.0 | 12.0 |
|                                                                                   | TPS282025 | TPH282025             | 28                   | 20 | 25 | 23                   | 17  | 22 | 64.5                       | 48.5 | 33.0 | 13.0 | 12.0 | 13.0 |
|                                                                                   | TPS282028 | TPH282028             | 28                   | 20 | 28 | 23                   | 17  | 23 | 64.5                       | 48.5 | 33.0 | 13.0 | 12.0 | 13.0 |
|                                                                                   | TPS282525 | TPH282525             | 28                   | 25 | 25 | 23                   | 22  | 22 | 64.5                       | 48.5 | 33.0 | 13.0 | 13.0 | 13.0 |
|                                                                                   | TPS282528 | TPH282528             | 28                   | 25 | 28 | 23                   | 22  | 23 | 64.5                       | 48.5 | 33.0 | 13.0 | 13.0 | 13.0 |
|                                                                                   | TPS282828 | TPH282828             | 28                   | 28 | 28 | 23                   | 23  | 23 | 64.5                       | 48.5 | 33.0 | 13.0 | 13.0 | 13.0 |