



MVI Fault Interrupter	Cooper EF - Relay	30-600 Ampere
MINIMUM TRIPPING AND TOTAL CLEARING TIME-CURRENT CHARACTERISTIC CURVES		
Notes: 1. Tested per C37.60 2. Accuracy is equal to +/- 10% of the current or time which ever is greater. 3. Minimum power up current: 15 Amperes 4. Curves are applicable to the operating range of -40°C to +65°C.	5. CT current sensing capability range: 10 -10,000 amperes RMS 6. Curves and trips are set using a personal computer or a control panel 7. The total clearing time-current characteristics curves represent the total time required to detect and interrupt the fault current 8. This curve in its entirety, including the title block, should be printed on a 11"x 17" sheet in order to conform with the C37.41 curve presentation standard (5.6 cm/decade).	Copper EF Relay 30-600 Ampere
	 Route 24, Hackettstown NJ, 07840 (908) 852-1122 FAX (908) 813-2091	Issue Date: August 30, 2007 Reference number: MVI-TCC-06