

E 232 STAIRCASE LIGHTING TIME-DELAY SWITCHES

# E 232 E-8/230N Installation manual

E 232 E-8/230N Installation Manual Document ID: 9AKK108468A5386

Revision: A 2023-08-24

#### **Disclaimer**

The information in this document is subject to change without notice and should not be construed as a commitment by ABB STOTZ-KONTAKT GmbH. ABB STOTZ-KONTAKT GmbH assumes no responsibility for any errors that may appear in this document.

In no event shall ABB STOTZ-KONTAKT GmbH be liable for direct, indirect, special, incidental, or consequential damages of any nature or kind arising from the use of this document, nor shall ABB STOTZ-KONTAKT GmbH be liable for incidental or consequential damages arising from use of any software or hardware described in this document.

### Copyrights

This document and parts thereof must not be reproduced or copied without written permission from ABB STOTZ-KONTAKT GmbH, and the contents thereof must not be imparted to a third party nor used for any unauthorized purpose. The software or hardware described in this document is furnished under a license and may be used, copied, or disclosed only in accordance with the terms of such license.

© Copyright 2023 ABB STOTZ-KONTAKT GmbH. All rights reserved.

#### **Trademarks**

ABB STOTZ-KONTAKT GmbH is a registered trademark of the ABB Group. All other brand or product names mentioned in this document may be trademarks or registered trademarks of their respective holders.


#### Contact

ABB STOTZ-KONTAKT GmbH Eppelheimer Str. 82 69123 Heidelberg Germany



Warning! Installation by person with electrotechnical expertise only.


# 1. Connection diagram: 3 conductors




## Tightening torque and stripping length



# 2. Connection diagram: 4 conductors



## Tightening torque and stripping length



2/3

# 3. Technical data

## E 232E-8/230N

=	
Time range (stepless)	0.5 – 20 min. stepless
Control voltage 230 V AC	
Universal voltage in addition	8 240 V AC/DC
Glow lamp load	150 mA
3/4 conductor operated	automatically
Resettable	
Steady-light switch	
Advance warning acc. DIN 18015-2	
Long-time range of 60 min.	
Multi-functional (10 functions)	
Maximum pulse duration	10 s
Rated voltage	240 V AC
Rated Frequency	50 / 60 Hz
Control voltage range	0.85 1.1 Un
Powerloss	6 VA
Rated switching capacity	16 A, 230 V AC
Rated insulation voltage U <sub>i</sub>	4 kV
Filament lamps	2,300 W
Halogen lamps	2,300 W
Fluorescent lamps series compensated / uncorrected	2,300 VA
Fluorescent lamps inductive or capacitive	2,300 VA
Fluorescent lamps shunt compensated	400 VA (42 μF)
Electronic controlgear	9x7 W, 7x11 W,
	7x20 W, 7x23 W
Inductive load (cos φ = 0.6/230 V AC)	2,300
LED lamp load (<2W)	20W
LED lamp load (2-8W)	180 W
LED lamp load (>8W)	180 W
Contact material	AgSnO2
Contact gap	< 3 mm
Mech. serviceable life	> 107
Serviceable life at rated load, cos φ =1	> 2x105
Serviceable life at rated load, $\cos \phi = 0.6$	> 4x104
Max. terminal cross-section	13 mm²
Max. conductor cross-section	4 mm²
ON duration	100%
Ambient temperature	-25 °C to + 50 °C
Housing and insulation material	heat resistant, self-extinguishing thermoplast
Control current at 230 V AC	26 mA
Minimum command duration	20 ms