
PRODUCT BROCHURE

Cyberex® SuperSwitch®GT

200–1200A digital disconnect switch
Supporting the smart grid installation



SuperSwitch®GT

Cyberex® is proud to introduce the three phase SuperSwitch®GT, for integrating distributed energy sources with electrical power utility grids. The SuperSwitch®GT protects critical loads on any micro grid from power quality anomalies on the utility grid by instantly isolating it to provide reliable power.



Front view of SuperSwitch®GT



Why SuperSwitch®GT

- Protects micro grid from utility outage
- Protects utility from faults on the micro grid
- IEEE1547 protection – under/over voltage, under/over frequency and unintentional islanding protection
- Provides power quality function that has an adjustable over and under peak voltage level with an adjustable response time delay
- Detects instantaneous (fault) current
- Offers the capability to accept external open commands
- Enhanced monitoring of voltage, frequency, and phase difference at the DG side and utility side and will connect when conditions are within limits.
- Automatic calculation of the power flow for the unintentional islanding protection required per IEEE 1547
- Backed by world class service support.



Technical specifications

General

- 200–1200A
- 480 VAC, 3-phase, 3 or 4-wire (neutral not switched), 60Hz
- Exceeds ITIC requirements by disconnecting from failing utility in under 20ms
- Load protection with smooth, instantaneous transfer between micro and utility grid protection events, IEEE 1547 events, and power quality events.
- Automatic sensing and control automatic separation of microgrid and utility grid during system problem and reconnection back to the utility grid when the utility system is normal
- Offers synchronism check
- Based on silicon controlled rectifier (SCR) technology
- Offers necessary series protection to clear any internal faults caused by component failures
- Normal rating is 220% of the system rated voltage per IEEE 1547 Section 4.1.8.3.
- Communications capabilities through relays and modbus RTU (RS485) or modbus TCP/IP
- Easy interface to a SCADA system via modbus RTU (RS485) or modbus TCP/IP
- Optional NEMA 3R enclosure

Analog data provided

- kW
- kVAR
- PF
- RMS phase voltages
- RMS phase currents
- Symmetrical components

Digital data provided

- Switch open
- Switch closed
- Switch bypassed
- Auto mode selected
- Manual mode selected

The SuperSwitch®GT offers the following GUI controls

- **Local** – will connect and reconnect when conditions are within limits.
- **Off** – is disconnected and semiconductors are de-energized.
- **Remote** – accepts “connect” and “disconnect” commands from an external control system. If the connect command is given it will connect and disconnect when conditions are within limits of the SuperSwitch®GT internal controls.

Standards conformance

The SuperSwitch®GT shall operate in conformance with the following applicable standards:

- IEEE 1547 – standard for interconnecting distributed resources with electric power systems)
- ITIC

Order fulfillment

Prior to receipt of the confirmed order, the approval drawings set will contain the following information

- Physical arrangement and outline dimensions of equipment and equipment base details
- Weight of each shipping section
- Location in plan and elevation of incoming and outgoing terminals
- Space available for entrance of conduits
- Location in plan and elevation of all ground terminals
- Complete list and rating of all equipment devices to be furnished
- Single line diagram
- Complete interconnection diagrams for all internal and field wiring
- Complete details showing locations of all bus with bolting details
- Complete details for enclosures showing bolting details between sections
- Grid tie switch operating system description
- List of recommended spare parts

SuperSwitch®GT can be customized to meet various application needs. Therefore, we require the following with a request for quote:

- Basic specifications and one line
- Application and components involved such as wind, solar, DG etc.
- Site specifics
- Any special coordination or testing needs

Power Protection

5900 Eastport Boulevard
Richmond, VA 23231-4453 USA
Tel: +1 800 292 3739
Fax: +1 804 236 4047

abb.com

Additional information

We reserve the right to make technical changes to the product and to the information in this document without notice. The agreed conditions at the time of the order shall apply. ABB assumes no responsibility for any errors or omissions that may appear in this document. We reserve all rights in this document and in the information contained therein. Without prior written approval from ABB, reproduction, disclosure to third parties or use of any information, in whole or in part, is strictly forbidden.

© Copyright 2018 Thomas and Betts Power Solutions, LLC. All rights reserved.
Specifications subject to change without notice.

