



Ref. Certif. No.

CN45489

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT  
(IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

AC Contactor

Name and address of the applicant

ABB France  
3 Rue Jean Perrin CS 90009 69687 Chassieu Cedex, France

Name and address of the manufacturer

ABB France  
3 Rue Jean Perrin CS 90009 69687 Chassieu Cedex, France

Name and address of the factory

ABB Bulgaria EOOD - Rakovski branch  
Industrial Zone, Plovdiv District, Rakovski Municipality, 4150  
RAKOVSKI BULGARIA

Note: When more than one factory, please report on page 2

Ratings and principal characteristics

See the Appendix

Trademark (if any)

ABB

Customer's Testing Facility (CTF) Stage used

Model / Type Ref.

AF45, AF50, AF63, AF75

Additional information (if necessary may also be reported on page 2)

A sample of the product was tested and found to be in conformity with

IEC 60947-4-1:2009(3rd Edition) + AMD 1:2012

As shown in the Test Report Ref. No. which forms part of this Certificate

00901-CB2018CQC-080713

This CB Test Certificate is issued by the National Certification Body

CHINA QUALITY CERTIFICATION CENTRE

Section 9, No. 188 Nansihuan Xilu, Beijing 100070 P. R. China  
Tel: +86-10-83886666 Fax: +86-10-83886282  
website: <http://www.cqc.com.cn>

Date: Dec.13,2018

Signature:

Lu Mei



CB 0049106



AF45, AF50, AF63, AF75  
Uimp:8kV;  
Ui:1000V;  
Ith:AF45 ,AF50:100A, AF63:125A, AF75:125A;  
AF45-22/40:  
AC-1:Ue/Ie:690V/100A;  
AC-3,AC-4:Ue/Ie:220-230-240V/40A,380-400/415/440V/37A,  
500V/33A,690V/25A;  
AF50-30:  
AC-1:Ue/Ie:690V/100A;  
AC-3,AC-4:Ue/Ie:220-230-240V/53A,380-400/415V/50A,  
440/500V/45A,690V/35A;  
AC-8a:Ue/Ie:400V/63A;  
AF50-40:  
AC-1:Ue/Ie:690V/100A;  
AC-3,AC-4:Ue/Ie:220-230-240V/53A,380-400/415V/50A,  
440/500V/45A,690V/35A;  
AF63:  
AC-1:Ue/Ie:690V/115A;  
AC-3,AC-4:Ue/Ie:220-230-240/380-400/415/440V/65A,  
500V/55A,690V/43A;  
AC-8a:Ue/Ie:400V/85A;  
AF75-30:  
AC-1:Ue/Ie:690V/125A;  
AC-3,AC-4:Ue/Ie:220-230-240/380-400/415V/75A,  
440V/70A,500V/65A,690V/46A;  
AC-8a:Ue/Ie:400V/95A;  
AF75-22/40:  
AC-1:Ue/Ie:690V/125A;  
AC-3,AC-4:Ue/Ie:220-230-240/380-400/415V/75A,  
440V/70A,500V/65A,690V/46A;

Page 1 of 2

Additional information (if necessary)

Date: Dec.13,2018

Signature:



Lu Mei

3P,4P;

Us:20-60VDC,48-130VAC/DC 50/60Hz,100-250VAC/DC 50/60Hz;

IP10;

Auxiliary Circuits:(CAL5)

Ith:16A;

AC-15:Ue/Ie:24~127V/6A, 220~240V/4A, 380~440V/3A, 500~690V/2A;

DC-13:Ue/Ie:24V/6A, 48V/2.8A, 72V/1A, 110~125V/0.55A, 220~250V/0.3A;

1NO1NC

Page 2 of 2

Additional information (if necessary)

Date: Dec.13,2018

Signature:



Lu Mei