

产品认证证书

II型自愿认证

证书编号: CQC2016010302853938

发证日期: 2021年02月01日

有效期至: 2031年02月01日

委托人名称 ABB Oy
及注册地址 Muottitie 2A FI-65320 VAASA, Finland

制造商名称 ABB Oy
及注册地址 Muottitie 2A FI-65320 VAASA, Finland

生产企业名称 ABB Oy
及生产地址 Muottitie 2A FI-65320 VAASA, Finland

产品名称和系列、规格、型号 隔离开关
OT100G, OT125G, OT160G, 详见附件

产品标准和技术要求 GB/T 14048.3-2017

认证模式 型式试验+初始工厂检查+获证后监督

上述产品符合 CQC12-000001-2020 认证规则的要求, 特发此证。

证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

可通过扫描下方二维码或登录国家认监委网站 (www.cnca.gov.cn) 查验证书信息



授权签字人:

主任:

陈昕 陆楠

中国质量认证中心



<http://www.cqc.com.cn>

中国·北京·南四环西路188号9区 100070

电话: +86 10 83886666

C(2) 0005121

PRODUCT CERTIFICATION

TYPE II CQC CERTIFICATION

CERTIFICATE NO.: CQC2016010302853938

Valid from: Feb.01,2021

Valid until: Feb.01,2031

NAME AND REGISTERED ADDRESS OF THE APPLICANT ABB Oy
Muottitie 2A FI-65320 VAASA, Finland

NAME AND REGISTERED ADDRESS OF THE MANUFACTURER ABB Oy
Muottitie 2A FI-65320 VAASA, Finland

NAME AND LOCATION OF THE FACTORY ABB Oy
Muottitie 2A FI-65320 VAASA, Finland

PRODUCT NAME, MODEL AND SPECIFICATION Switch-Disconnecter
OT100G_, OT125G_, OT160G_ See the appendix

THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS GB/T 14048.3-2017

TYPE OF CERTIFICATION SCHEMES Type testing of product + initial factory inspection + follow up factory inspection

This is to certify that the above mentioned product(s) complies with the requirements of certification rules of CQC12-000001-2020.

The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

The certificate information is available through the QR code below or CNCA's website: www.cnca.gov.cn



SIGNED BY:

陈昕

PRESIDENT:

陆楠

CHINA QUALITY CERTIFICATION CENTRE



<http://www.cqc.com.cn>

Section 9, No.188, Nansihuan Xilu, Beijing 100070 P.R.China

Tel: +86 10 83886666

C(2) 0005121

产品认证证书

II型自愿认证

附 录

证书编号: CQC2016010302853938

第 1 页 共 3 页

纸 号: 5121

OT100G_, OT125G_, OT160G_

Uimp: 12kV(OT100G, OT125G, OT160G), 6kV(OT100GM, OT125GM, OT160GM);

Ui: 1000V(OT100G, OT125G, OT160G), 690V(OT100GM, OT125GM, OT160GM);

OT100G: Ith: 100A; Ie: 100A; Ue: 690V;

OT100GM: Ith: 100A; Ie: 100A; Ue: 415V;

OT125G: Ith: 125A; Ie: 125A; Ue: 690V;

OT125GM: Ith: 125A; Ie: 125A; Ue: 415V;

OT160G: Ith: 160A; Ie: 160A; Ue: 690V;

OT160GM: Ith: 160A; Ie: 160A; Ue: 415V;

Icw: 4kA/1s, 7kA/0.25s;

Icm: 12kA/690V;

Iq: 100kA/500V, 50kA/690V;

使用类别: AC-21A, AC-22A, AC-23A;

极数: 2P, 3P, 4P;

适用频率: 50/60Hz;

IP20(仅对前面板)

注: 此附录与证书同时使用时有效。



中国质量认证中心

产品认证证书

II型自愿认证


附 录

证书编号: CQC2016010302853938

第 2 页 共 3 页

纸 号: 5121

型号解释:



注: 此附录与证书同时使用时有效。

附件



中国质量认证中心

产品认证证书

II型自愿认证

附录

证书编号: CQC2016010302853938

第 3 页 共 3 页

纸 号: 5121

OT	160	G	30	K	
					Included accessories 包含附件 P = Pistol handle 带手枪式手柄 K = Direct handle 带直接安装手柄 Blank = Basic switch 不带手柄和轴
					Number of poles and placing of the operating mechanism 极数及操作机构位置 03 = 3 poles, operating mechanism at the left end of the switch 03 = 3 极(操作机构在开关左端) 04 = 4 poles, operating mechanism at the left end of the switch 04 = 4 极(操作机构在开关左端) 30 = 3 poles, operating mechanism at the right end of the switch 03 = 3 极(操作机构在开关右端) 40 = 4 poles, operating mechanism at the right end of the switch 40 = 4 极(操作机构在开关右端)
					Mounting 安装方式 G = IEC, UL, Base& DIN-rail mounting G = IEC, UL 标准, 底板和 DIN 导轨安装 GT = IEC, UL, Door mounting GT = IEC, UL 标准, 门上安装 GM = IEC, Base& DIN-rail mounting, AC-22A 415V GM = IEC 标准, 底板和 DIN 导轨安装, AC-22A 415V
					Switch size 电流等级(A) 100, 125 & 160
					Switch disconnecter 隔离开关

注：此附录与证书同时使用时有效。



中国质量认证中心