
 TECHNICAL DATA SHEET

Wire connector, Twist-on 933 series

For solid and stranded wire combinations

marrette®


Twist-on wire connector for connection of copper conductors inside junction box. For residential and commercial applications.

Certifications / Standards:


Material:

- Cap: Polypropylene (PP)
- Spring: copper plated steel

Conformance:



- CSA File No. LR6591
- UL File No. E9809, control nb. 424H

Ratings:

- Indoor use only
- Temp. Rating: 105°C (221°F) maximum
- Voltage:
 - Building wire 600 Volt maximum
 - Signs and Fixtures 1000 Volt maximum
- Wire: #22 to #8, solid and/or stranded unless noted otherwise, cu/cu only

Connection type:

- Twist-on



Approved for following copper-copper wire combinations (solid/stranded - unless specified)

1 #22 + 1 to 5 #20	1 #20 + 1 to 4 #18	1 #18 + 1 to 5 #16	1 #16 + 1 to 4 #14	1 #14 + 1 to 4 #12	1 #12 + 1 to 2 #10	1 #10 + 1 #8 Strd.
1 #22 + 1 to 5 #18	1 #20 + 1 to 4 #16	1 #18 + 1 to 4 #14	1 #16 + 1 to 4 #12	1 #14 + 1 to 2 #10	1 #12 + 1 #8 Strd.	1 to 2 #10
1 #22 + 1 to 5 #16	1 #20 + 1 to 4 #14	1 #18 + 1 to 4 #12	1 #16 + 1 to 2 #10	1 #14 + 1 #8 Strd.	1 to 4 #12	3 # 10 solid only
2 #22 + 1 to 4 #20	2 to 4 #20	1 #18 + 1 to 2 #10	2 to 6 #16	1 to 5 #14	2 #12 + 1 #10	
2 #22 + 1 to 4 #18	2 #20 + 1 to 3 # 18	2 to 6 #18	2 #16 + 1 to 4 #14	2 #14 + 1 to 3 #12	2 #12 + 1 #8 Strd.	
2 #22 + 1 to 4 #16	2 #20 + 1 to 3 # 16	2 #18 + 1 to 4 #16	2 #16 + 1 to 3 #12	2 #14 + 1 to 2 #10	3 #12 + 1 #10	
3 #22 + 1 to 3 #20	2 #20 + 1 to 3 # 14	2 #18 + 1 to 4 #14	2 #16 + 1 to 2 #10	2 #14 + 1 #8 Strd.		
3 #22 + 1 to 3 #18	3 #20 + 1 to 2 #18	2 #18 + 1 to 3 #12	2 #16 + 1 #8 Strd.	3 #14 + 1 to 2 #12		
3 #22 + 1 to 4 #16	3 #20 + 1 to 2 #16	2 #18 + 1 to 2 #10	3 #16 + 1 to 3 #14	3 #14 + 1 #10		
3 to 4 #22	3 #20 + 1 to 2 #14	3 #18 + 1 to 3 #16	3 #16 + 1 to 2 #12	3 #14 + 1 #8 Strd.		
4 #22 + 1 to 2 #20	4 #20 + 1 to 2 #18	3 #18 + 1 to 3 #14	3 #16 + 1 to 2 #10	4 #14 + 1 #12		
4 #22 + 1 to 2 #18	4 #20 + 1 to 2 #16	3 #18 + 1 to 3 #12	3 #16 + 1 #8 Strd.	4 #14 + 1 #10		
4 #22 + 1 to 2 #16	4 #20 + 1 to 2 #14	3 #18 + 1 to 2 #10	4 #16 + 1 to 2 #14			
5 to 6 #22 Solid only	5 to 6 #20 Solid only	4 #18 + 1 to 2 #16	4 #16 + 1 to 2 #12			
		4 #18 + 1 to 2 #14	4 #16 + 1 #10			
		4 #18 + 1 to 2 #12	4 #16 + 1 #8 Strd.			
		4 #18 + 1 #10	5 #16 + 1 # 14			
		5 #18 + 1 #16	5 #16 + 1 # 10			
		5 #18 + 1 #14				
		5 #18 + 1 #12				

Note: Product must be installed in accordance with applicable national and local electrical codes.