

### TECHNICAL DATA SHEET

# Terminals, lipped blade Vinyl-insulated, double crimp

## Spec-Kon<sup>®</sup>



#### Features:

- Easy entry double crimp
- · Corrosive resistant plating
- Color coded to wire size range

#### Maximum rating:

- 75°C Max
- 600 volts

Copper conductors only

Vinyl-insulated lipped blade terminals for wire termination of copper conductors ranging from 0.5mm<sup>2</sup> to 6mm<sup>2</sup>

#### Certifications / Standards:



#### **Application tool:**

• ERG9004

#### Conforms to:

• IEC 60352-2

#### Materials / Finishes:

- Copper t erminal
- Electro-Tin plated
- Vinyl insulation

Drawing	Part no:	Wire size range (mm²)	Color	Dimensions (mm)				Crimping tool
				L	F	w	D	
	LB1.5-3VDC	0.5 - 1.5	Red 📕	25.7	16.8	3.0	4.3	ERG9004
	LB1.5-46VDC	0.5 - 1.5	Red	25.7	16.8	4.6	4.3	
	LB2.5-3VDC	1.5 - 2.5	Blue	25.7	16.8	3.0	4.8	
	LB2.5-46VDC	1.5 - 2.5	Blue	25.7	16.8	4.6	4.8	
	LB6-3VDC	4.0 - 6.0	Yellow	30.2	17.2	3.0	6.7	
	LB6-46VDC	4.0 - 6.0	Yellow	30.2	17.2	4.6	6.7	

Note: Products must be installed in accordance with applicable national and local electrical codes.

tnb.abb.com (US/Latin America) tnb.ca.abb.com (Canada) abb.com

We reserve the right to make technical changes or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB does not accept any responsibility whatsoever for potential errors or possible lack of information in this document.

We reserve all rights in this document and in the subject matter and illustrations contained therein. Any reproduction - in whole or in part - is forbidden without prior written consent of ABB. Copyright© 2019 ABB. All rights reserved.