

TECHNICAL DATA SHEET - INTERACTIVE PDF

Fittings, Series 6300SST, Type A

Liquid-tight fitting

T&B Liquidtight Systems



Liquid-tight Type A stainless steel fittings for use in corrosive and caustic wash down applications

Certifications / Standards:



3-Part Specification 26 05 33.24 End User Tools

Features & Benefits:

- Meets UL 514B for liquid tight fittings
- Trade sizes from ½" to 1 ¼" (16mm to 35mm)
- Available in straight version
- NPT threads
- Provided with a captive O-ring seal and steel locknut
- Ideal for use in highly corrosive environments

Applications:

- Designed to provide a liquid-tight and dust-tight connection between the fittings, conduits and enclosure
- For use in outdoor or indoor locations, and exposed to continuous or intermittent moisture
- Used to connect flexible liquid-tight Type A conduit to boxes or enclosures
- Typical applications include raceway for general purpose industrial and commercial construction, machine OEMs, panel builders, indoor and outdoor installations

Conforms to:

- UL 514B
- File: E23018

Material

- Body: Type 304 stainless steel
- Gland: Type 304 stainless steel
- Locknut: Type 304 stainless steel
- · O-ring: Neoprene
- · Sealing ring: Santropene

Fittings, Series 6300SST, Type A | Technical data sheet - Interactive PDF | TDS000628 A

Series 6300SST Type A stainless steel fittings

Product selection								
Drawing	Part no.			Trade Size	NPT thread	Α	В	Weight
		Inches	Metric	ISO BS EN	Size	inches (mm)	inches (mm)	lbs (kg)
B H	6302SST	1/2"	16 mm	20 mm	1/2"	1 1/16" (36.3)	2 3/32" (53.3)	0.38 (0.17)
	6303SST	3/4"	21 mm	25 mm	3/4"	1 ²³ / ₃₂ " (43.7)	2 %16" (64.8)	0.63 (0.28)
	6304SST	1"	27 mm	32 mm	1"	2" (50.8)	2 19/32" (66.0)	0.81 (0.37)
	6305SST	1 1/4"	35 mm	40 mm	1 1/4"	2 1/8" (73.2)	3 3/32" (78.7)	1.66 (0.75)

Note: Product must be installed in accordance with applicable national and local electrical codes.