

TECHNICAL DATA SHEET

# Terminals, bullet disconnects

# Nylon fully-insulated, double crimp

# Spec-Kon®



Nylon fully-insulated bullet disconnects for wire termination of copper conductors ranging from 0.5mm<sup>2</sup> to 6mm<sup>2</sup>

## **Certifications / Standards:**



#### Features:

- · Easy entry double crimp
- Fully Insulated
- Corrosive resistant plating
- Color coded to wire size range

#### Maximum rating:

- 105°C Max
- 600 volts
- Copper conductors only

# Application tool:

• ERG9003

### Conforms to:

• IEC 60352-2

### Materials / Finishes:

- · Brass disconnect
- · Electro-Tin plated
- · Nylon insulation

Drawing W	Part no:	Wire size range (mm²)	Color	Dimensions (mm)				Crimping tool
				L	F	w	D	
	FIBD1.5-4NDC	0.5-1.5	Red 📕	26.2	8.5	4.0	3.8	ERG9003
	FIBD2.5-4NDC	1.5-2.5	Blue 📕	26.2	8.5	4.0	4.7	

tnb.abb.com (US/Latin America) tnb.ca.abb.com (Canada) abb.com We reserve the right to make technical changes or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB does not accept any responsibility whatsoever for potential errors or possible lack of information in this document.

We reserve all rights in this document and in the subject matter and illustrations contained therein. Any reproduction – in whole or in part – is forbidden without prior written consent of ABB.

Copyright© 2019 ABB. All rights reserved.