

NKCR.E48139 Auxiliary Devices

[Page Bottom](#)

Auxiliary Devices

[See General Information for Auxiliary Devices](#)

ABB STOTZ-KONTAKT GMBH
EPPELHEIMER STR 82
69123 HEIDELBERG, GERMANY

E48139



Trademark and/or Tradename: **ABB**

Investigated to ANSI /UL 508

Accessories, I/O modules Model(s) DX111, DX122, VI150, VI155

Accessories, mechanical resets Model(s) 1TGB100038

Accessories, mechanical resets, terminal adapters Model(s) DB140E, DB145E, DB16E, DB45E, DB80E

Accessories, single mounting kits Model(s) DB16, DB42

Auxiliary devices, electronic relays, open type Model(s) GHC followed by 105 or 106, followed by 0201, followed by R0001, R0002, R0003, R0004, R0005 or R0006.

Auxiliary devices, open type Model(s) K6 or KC6 followed by 40E, 31Z or 22Z, followed by 1.4, 1.7, 2.4 or 2.48.

Auxiliary devices, overload relay, open-type Model(s) GHC 461 02 01 R0004, GHC 461 02 02 R0004, GHC 461 02 03 R0004, GHC 461 02 04 R0004, GHC 461 02 05 R0004, GHC 461 02 06 R0004, GHC 461 02 07 R0004, GHC 461 02 08 R0004, GHC 461 02 09 R0004, GHC 461 02 10 R0004, GHC 461 02 11 R0004, GHC 461 02 12 R0004, GHC 461 10 01 R0001, GHC 461 10 01 R0003, GHC 461 10 01 R0004, GHC 461 10 02 R0001, GHC 461 10 02 R0003, GHC 461 10 02 R0004, GHC 461 10 03 R0001, GHC 461 10 03 R0003, GHC 461 10 03 R0004, GHC 461 1304 R0001, GHC 461 1304 R0002, GHC 461 1304 R0003, GHC 461 1304 R0004

GHC 462 00, followed by 01, 02, 03, 04, 05, 06, 07, 08, 09, 10 or 11, followed by R0001, R0003 or R0004.

GHC 462 10, followed by 02, 03 or 04, followed by R0001, R0003 or R0004.

GHC 463 0001 R0001, GHC 463 0001 R0002, GHC 463 0001 R0003, GHC 463 0001 R0004, GHC 464 0101 R0001, GHC 464 0101 R0003, GHC 464 0101 R0004, GHC 465 0101 R0001, GHC 465 0101 R0003, GHC 465 0101 R0004

GHC, followed by 105 or 106, followed by 0201, 0301, 1201 or 1301, followed by R0011, R0012, R0013, R0014, R0015 or R0016.

UMC22, UMC100 may be followed by additional suffixes.

Auxiliary devices, overload relays, open type Class 10 devices Model(s) T16, TA40 or TF42, followed by 0.13, 0.17, 0.23, 0.31, 0.41, 0.55, 0.74, 1.0, 1.3, 1.7, 2.3, 3.1, 4.2, 5.7, 7.6, 10, 13, 16, 20, 24, 29, 35 or 38 (20, 24, 29, 35 and 38 only for TF and TA).

Auxiliary switches Model(s) CA6 or CAF6 followed by -11K, 11E, -02 or 11M-20, followed by E, K, M or N.

Interface units auxiliary devices, open type Model(s) 95.049-052, 95.087-091, 95.095-109, 95.136-141, 96.053, 96.079, 96.080, 98.018, 98.028, 98.029

Open-Type, Overload Relays Model(s) Type TF140DU 90, TF140DU 110, TF140DU 135 and TF140DU 142.

Overload relays, electronic, open type Model(s) E140DU, E16DU 0.32, E16DU 1.0, E16DU 18.9, E16DU 2.7, E16DU 6.3, E200DU, E320DU, E45DU 30, E45DU 45, E500DU, E800DU, E80DU, EF146, EF19 0.32, EF19 1.0, EF19 18.9, EF19 2.7, EF19 6.3, EF205, EF370, EF45 30, EF45 45, EF96

Overload relays, open-type Model(s) 1SAZ411201R1001, 1SAZ411201R1002, T900DU375, T900DU500, T900DU650, T900DU850, T900SU375, T900SU500, T900SU650, T900SU850, TA110DU110, TA110DU90, TA200DU110, TA200DU135, TA200DU150, TA200DU175, TA200DU200, TA200DU90, TA450DU105, TA450DU140, TA450DU185, TA450DU235, TA450DU310, TA450DU400, TA450DU60, TA450DU80, TA450SU105, TA450SU140, TA450SU185, TA450SU235, TA450SU310, TA450SU400, TA450SU60, TA450SU80

Overload relays, open-type, Class 10 Model(s) T80DU42 may be followed by -M, T80DU52 may be followed by -M, T80DU63 may be followed by -M, T80DU80 may be followed by -M

TA42DU followed by 18-42A, may be followed by -M

TA75DU followed by 25-80A may be followed by -M

TA80DU42, TA80DU52, TA80DU63, TA80DU80

Overload relays, open-type, Class 20 Model(s) TA42DU followed by 18-42A, may be followed by -M

TA75DU followed by 25-80A may be followed by -M

TA80DU42, TA80DU52, TA80DU63

TA80DU80 followed by 42, 52, 63, or 80, may be followed by -M

Terminal block adapters, open type Model(s) AB200, AB25/25, AB25/32, AB80, DB200, DB80, GJZ420 1110 R001

Transformer modules Model(s) P30 thru P80 followed by 102, 111, 120, 202, 211, 220, 302, 311, 320, 402, 411 or 420.

Investigated to ANSI /UL 60947-1 and ANSI /UL 60947-4-1A

Accessory Mounting Kit Model(s) DB65, DB96

Accessory,mechanical resets, terminal adapters Model(s) DB19EF

Open type, Electronic overload relays Model(s) EF460, EF750

Open type, Thermal overload relays Model(s) Model TF96 followed by 51, 60, 68, 78, 87 or 96

TF65 followed by 28, 33, 40, 47, 53, 60 or 67

Overload relays, electronic, open type Model(s) EF65-56, EF65-70

Overload relays, open-type Model(s) T25DU.16, T25DU.25, T25DU.4, T25DU.63, T25DU1.0, T25DU1.4, T25DU1.8, T25DU11, T25DU14, T25DU19, T25DU2.4, T25DU25, T25DU3.1, T25DU32, T25DU4.0, T25DU5.0, T25DU6.5, T25DU8.5

Overload relays, open-type, Class 10 Model(s) TA25DU.16, may be followed by -M, TA25DU.25, may be followed by -M, TA25DU.4, may be followed by -M, TA25DU.63, may be followed by -M, TA25DU1.0, may be followed by -M, TA25DU1.4, may be followed by -M, TA25DU1.8, may be followed by -M, TA25DU11, may be followed by -M, TA25DU14, may be followed by -M, TA25DU19, may be followed by -M, TA25DU2.4, may be followed by -M, TA25DU25, may be followed by -M, TA25DU3.1, may be followed by -M, TA25DU32, may be followed by -M, TA25DU4.0, may be followed by -M, TA25DU5.0, may be followed by -M, TA25DU6.5, may be followed by -M, TA25DU8.5, may be followed by -M

Overload relays, open-type, Class 20 Model(s) TA25DU1.8, may be followed by -M, TA25DU11, may be followed by -M, TA25DU14, may be followed by -M, TA25DU19, may be followed by -M, TA25DU2.4, may be followed by -M, TA25DU25, may be followed by -M, TA25DU3.1, may be followed by -M, TA25DU32, may be followed by -M, TA25DU4.0, may be followed by -M, TA25DU5.0, may be followed by -M, TA25DU6.5, may be followed by -M, TA25DU8.5, may be followed by -M

Terminal block adapters Model(s) DX25, may be followed by -M

Terminal block adapters, open type Model(s) DB25/25A, may be followed by -M, DB25/32A, may be followed by -M

Last Updated on 2014-07-09

[Questions?](#)

[Print this page](#)

[Terms of Use](#)

[Page Top](#)

© 2014 UL LLC

When the UL Leaf Mark is on the product, or when the word "Environment" is included in the UL Mark, please search the [UL Environment database](#) for additional information regarding this product's certification.

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL's Follow-Up Service. Only those products bearing the UL Mark should be considered to be Certified and covered under UL's Follow-Up Service. Always look for the Mark on the product.

UL permits the reproduction of the material contained in the Online Certification Directory subject to the following conditions: 1. The Guide Information, Assemblies, Constructions, Designs, Systems, and/or Certifications (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from the Online Certifications Directory with permission from UL" must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "© 2014 UL LLC".