

CATALOG

# FuseWELD®

## Exothermic welding system



---

**Thomas & Betts is now ABB Installation Products, but our long legacy of quality products and innovation remains the same. From connectors that help wire buildings on Earth to cable ties that help put machines in space, we continue to work every day to make, market, design and sell products that provide a smarter, safer and more reliable flow of electricity, from source to socket.**

---

# Table of contents


004–008	<b>Overview</b>
009	<b>Earth points</b>
010–019	<b>Cable to cable</b>
020–023	<b>Cable to ground rod</b>
024–026	<b>Cable to rebar</b>
027–043	<b>Cable to steel surface and pipe</b>
044–047	<b>Cable to bar</b>
048–053	<b>Bar to bar</b>
054–057	<b>Bar to steel surface</b>
058–059	<b>Tools and accessories</b>
060–062	<b>Sure Shot® molds</b>
063–076	<b>Cross reference</b>
077–083	<b>Technical reference</b>
084–090	<b>Index</b>

# Exothermic welding system

## The Blackburn® exothermic welding process

The Blackburn exothermic welding process is a simple, self-contained method of forming high-quality electrical connections.

- 1 Mold
- 2 Crucible
- 3 Tap hole
- 4 Weld cavity
- 5 and 6 The conductors to be joined
- 7 Steel retaining disc
- 8 Weld powder
- 9 Starting powder



The compact process requires no external power or heat source, making it completely portable. Connections are made inside a semi-permanent graphite mold using the high-temperature reaction of powdered copper oxide and aluminum.

Exothermic welding equipment is used by some of the world's most demanding customers. ABB is one of the only manufacturers that can offer exothermic welding, as well as compression and bolted connectors for grounding applications.



### This is how it works

The mold (1) features a crucible (2), a tap hole (3) and a weld cavity (4). The conductors (5 and 6) to be joined are located in the weld cavity as shown, and the mold is closed. A steel retaining disc (7) is located in the bottom of the crucible to retain the weld powder (8) and starting powder (9), which are poured in on top.

Ignited with a spark gun, the starting powder sets off an exothermic reaction in the weld powder, reducing it to molten copper alloy. This instantaneously melts the retaining disc, and flows down the tap hole to the weld cavity, where it partially melts the conductors before cooling to leave a fusion weld of great mechanical and electrical integrity.




## How to use this catalog

Refer to the pictorial index at the beginning of each catalog section to determine the type of connection that you wish to make. Turn to the relevant page, and study the table. There is an illustration for each connection type, and each table provides the following information:

- **The weld powder size required:** unless otherwise stated, one weld powder is required for each connection made.
- **The mold required:** the mold part number to the left shows precisely what the mold can do, and indicates its cost.
- **The handle clamp required:** handle clamps relate directly to mold price keys. For example, handle clamp hcpk4 is for use with price key 4 molds.
- **Mold price key:** this relates to the size of graphite block used to manufacture the mold, and determines its price. The simplest and smallest molds have the lowest price key numbers.
- **Sleeves required:** stranded conductors of #6 awg or less require sleeves, which prevent burning of the strands, and improve the mechanical strength of the connection.
- **Packing:** molds for connecting stranded conductors to reinforcing bar (cre type) require sealing with packing.
- **Mold sealing compound:** required when making connections to steel surfaces and pipes. Requirement is indicated by a statement at the foot of the table.

## Mold part number

**Example:**



## Exothermic welding system

### The Blackburn® exothermic welding connection

The majority of Blackburn connections have at least twice the cross sectional area of the conductors being joined, and an equivalent or greater current carrying capacity.



Because the connection is a fusion of high conductivity, high copper content alloy, it will withstand repeated fault currents, and will not loosen in the way that mechanical connectors can.

Corrosion resistance is exceptional, too, due to the alloy's very high copper content (in excess of 90%).

#### Standards compliance

A representative range of Blackburn connections has been successfully tested in accordance with the requirements of IEEE 837-1989 – standard for qualifying permanent connections used in substation grounding.

Testing in accordance with UL and CSA. Contact ABB technical services at 888-862-3289 for listings and certificates.

- 1 Handle clamp
- 2 File card brush
- 3 Cable brush
- 4 Mold scraper
- 5 Retaining discs
- 6 Flint gun
- 7 Mold brush
- 8 Mold
- 9 Powder boxes
- 10 Cartridges

## Blackburn equipment and accessories

### **Weld powders**

Blackburn weld powders are contained in plastic cartridges, and are packed in plastic boxes of 10 or 20, depending on their size. Different joints require different powder sizes, and the size relates to the powder's nominal weight in grams.

The weld powder packaging also contains retaining discs and starting powder. The retaining discs are contained in a separate bag within the box. The starting powder is compacted into the bottom of the cartridge, underneath the weld powder, and is released by tapping the cartridge base firmly.

Blackburn weld powders are suitable for making connections from copper to copper and from copper to steel.

### **Molds**

Blackburn graphite molds are dedicated to producing one type of connection. With care, they should be capable of producing up to 75 connections each. Mold size and complexity varies, and is denoted by a price key, from one upwards.

Each mold carries a tag which gives the mold part number, the weld powder size for use with the mold and the conductor sizes for which it is intended.

### **Handle clamps**

Handle clamps provide a means of both handling the mold, and also of clamping the mold halves together (or of clamping the mold to the surface to which a connection is to be made).

### **Standard tools**


A flint gun is required to start the reaction. Cleaning tools for conductors, surfaces and molds include:

**Cable brush** – For cleaning cables and other circular conductors such as rods.

**Mold scraper** – For removing slag from the mold crucible, after firing.

**Mold brush** – For final mold cleaning.


**File card brush** – For cleaning conductors and surfaces.



# Exothermic welding system


## How to make a Blackburn® exothermic connection

—  
01 Position the clean conductors in the mold after making sure the mold is dry, by pre-heating or making a test joint.




01

—  
02 Place the metal retaining disc in the bottom of the mold crucible.




02

—  
03 Pour the powder into the crucible, spreading some starting powder onto the mold edge.



03

—  
04 Close the lid, and ignite with the flint gun from the side, firing the spark onto the starting powder.



04

—  
05 The reaction takes place safely inside the mold.



05


—  
06 Once the joint is finished, the mold should be cleaned using a mold scraper and brush ready for the next joint.





06

## Exothermic welding system


### Four-hole earth points

Diagrams	Cat. no.	A Hole size (in.)	B dia. (in.)	C (in.)	D (in.)	E (in.)	F (in.)
	GPC110	4 x $\frac{5}{16}$ UNC x $\frac{9}{16}$	$\frac{27}{64}$	2	3	$2\frac{1}{2}$	$1\frac{13}{32}$
	GPC111	As GPC110, with a pre-welded 20" long tail of 2/0 AWG PVC-insulated cable.					


### Two-hole earth points

Diagrams	Cat. no.	B Conductor type dia. (in.)	C (in.)	D (in.)	E (in.)	F (in.)
<b>Complete with front plate</b>						
	GPC115	1" x $\frac{1}{8}$ " Tape or 2/0 AWG cable	$\frac{27}{64}$	2	$3\frac{1}{8}$	$2\frac{3}{16}$
	GPC116	As GPC115, with a pre-welded 20" long tail of 2/0 AWG PVC-insulated cable.				
	GPC120	1" x $\frac{1}{8}$ " Tape or $\frac{5}{16}$ " dia. solid	$\frac{27}{64}$	2	$3\frac{1}{8}$	$2\frac{3}{16}$
	GPC121	As GPC120, with a pre-welded 20" long tail of 2/0 AWG PVC-insulated cable.				
<b>Without front plate</b>						
	GPC125	2 x $\frac{5}{16}$ UNC x $\frac{1}{2}$ "	$\frac{27}{64}$	2	$3\frac{1}{8}$	$2\frac{3}{16}$
	GPC126	As GPC125, with a pre-welded 20" long tail of 2/0 AWG PVC-insulated cable.				

### One-hole earth points

Diagrams	Cat. no.	A Hole size (in.)	B dia. (in.)	C (in.)	D (in.)	E (in.)
<b>Complete with front plate</b>						
	GPC100	1 x $\frac{5}{16}$ UNC x $\frac{5}{8}$	$\frac{27}{64}$	$2\frac{3}{16}$	$3\frac{1}{8}$	$1\frac{3}{8}$
	GPC101	1 x $\frac{3}{8}$ UNC x $\frac{5}{8}$	$\frac{27}{64}$	$2\frac{3}{16}$	$3\frac{1}{8}$	$1\frac{3}{8}$
	GPC105	As GPC100, with a pre-welded 20" long tail of 2/0 AWG PVC-insulated cable.				
	GPC106	As GPC101, with a pre-welded 20" long tail of 2/0 AWG PVC-insulated cable.				

### Static earth receptacle







Diagrams	Cat. no.	B dia. (in.)	C (in.)	D (in.)	E (in.)
	GRX005	$\frac{27}{64}$	$1\frac{1}{2}$	$3\frac{3}{8}$	$2\frac{11}{16}$

## Exothermic welding system

Cable to cable quick reference

- 01 CC1  
See page 11
- 02 CC2  
See page 12
- 03 CC4  
See page 14
- 04 CC6  
See page 16
- 05 CC7  
See page 17
- 06 CC11  
See page 19

**Below represents our standard range. Other types can be produced to order.**




## Exothermic welding system

CC1 cable to cable

- Stranded conductor
- Solid circular conductor

**CC1 cable to cable**

Diagram	Cat. no.	Wire size (A) AWG or kcmil	Welding powder size	Handle clamp type	Sleeve	Std. ctn.
	CC1-3-#3	3	32BKB	HCPK3	-	1
	CC1-3-#2	2	32BKB	HCPK3	-	1
	CC1-3-#2S	2 solid	32BKB	HCPK3	-	1
	CC1-3-#1	1	32BKB	HCPK3	-	1
	CC1-3-#1S	1 solid	32BKB	HCPK3	-	1
	CC1-4-1/0	1/0	45BKB	HCPK4	-	1
	CC1-4-1/0S	1/0 solid	45BKB	HCPK4	-	1
	CC1-4-2/0	2/0	65BKB	HCPK4	-	1
	CC1-4-3/0	3/0	90BKB	HCPK4	-	1
	CC1-4-4/0	4/0	90BKB	HCPK4	-	1
	CC1-4-4/0S	4/0 solid	90BKB	HCPK4	-	1
	CC1-4-250K	250	115BKB	HCPK4	-	1
	CC1-4-300K	300	115BKB	HCPK4	-	1
	CC1-4-350K	350	150BKB	HCPK4	-	1
	CC1-4-500K	500	200BKB	HCPK4	-	1
	CC1-5-750K	750	2 x 150BKB	HCPK5	-	1
	CC1-5-1000K	1000	2 x 200BKB	HCPK5	-	1




## Exothermic welding system

CC2 cable to cable

- Stranded conductor
- Solid circular conductor


—  
CC2 cable to cable

Diagram	Cat. no.	Wire size (A) AWG or kcmil	Wire size (B) AWG or kcmil	Welding powder size	Handle clamp type	Sleeve	Std. ctn.
	CC2-4-#4#4	4	4	32BKB	HCPK4	—	1
	CC2-4-#2S#2	2 solid	2	45BKB	HCPK4	—	1
	CC2-4-#2S#2S		2 solid	45BKB	HCPK4	—	1
	CC2-4-#2S#4		4	45BKB	HCPK4	—	1
	CC2-4-#2#2	2	2	45BKB	HCPK4	—	1
	CC2-4-#2#2S		2 solid	45BKB	HCPK4	—	1
	CC2-4-#2#4		4	45BKB	HCPK4	—	1
	CC2-4-#1#1	1	1	45BKB	HCPK4	—	1
	CC2-4-#1#2		2	45BKB	HCPK4	—	1
	CC2-4-#1#2S		2 solid	45BKB	HCPK4	—	1
	CC2-4-#1#4		4	45BKB	HCPK4	—	1
	CC2-4-1/01/0	1/0	1/0	90BKB	HCPK4	—	1
	CC2-4-1/0#1		1	45BKB	HCPK4	—	1
	CC2-4-1/0#2		2	45BKB	HCPK4	—	1
	CC2-4-1/0#2S		2 solid	45BKB	HCPK4	—	1
	CC2-4-1/0#4		4	45BKB	HCPK4	—	1
	CC2-4-2/02/0	2/0	2/0	90BKB	HCPK4	—	1
	CC2-4-2/01/0		1/0	90BKB	HCPK4	—	1
	CC2-4-2/0#1		1	45BKB	HCPK4	—	1
	CC2-4-2/0#2		2	45BKB	HCPK4	—	1
	CC2-4-2/0#2S		2 solid	45BKB	HCPK4	—	1
	CC2-4-2/0#4		4	45BKB	HCPK4	—	1
	CC2-4-3/03/0	3/0	3/0	115BKB	HCPK4	—	1
	CC2-4-3/02/0		2/0	90BKB	HCPK4	—	1
	CC2-4-3/01/0		1/0	90BKB	HCPK4	—	1
	CC2-4-3/0#1		1	45BKB	HCPK4	—	1
	CC2-4-3/0#2		2	45BKB	HCPK4	—	1
	CC2-4-3/0#2S		2 solid	45BKB	HCPK4	—	1
	CC2-4-3/0#4		4	45BKB	HCPK4	—	1
	CC2-4-4/04/0	4/0	4/0	150BKB	HCPK4	—	1
	CC2-4-4/03/0		3/0	115BKB	HCPK4	—	1
	CC2-4-4/02/0		2/0	90BKB	HCPK4	—	1
	CC2-4-4/01/0		1/0	90BKB	HCPK4	—	1
	CC2-4-4/0#1		1	90BKB	HCPK4	—	1
	CC2-4-4/0#2		2	90BKB	HCPK4	—	1
	CC2-4-4/0#2S		2 solid	90BKB	HCPK4	—	1
	CC2-4-4/0#4		4	90BKB	HCPK4	—	1
	CC2-4-250K250K	250	250	150BKB	HCPK4	—	1
	CC2-4-250K4/0		4/0	150BKB	HCPK4	—	1
	CC2-4-250K4/0		3/0	150BKB	HCPK4	—	1
	CC2-4-250K2/0		2/0	90BKB	HCPK4	—	1
	CC2-4-250K1/0		1/0	90BKB	HCPK4	—	1
	CC2-4-250K#1		1	90BKB	HCPK4	—	1
	CC2-4-250K#2		2	90BKB	HCPK4	—	1
	CC2-4-250K#2S		2 solid	90BKB	HCPK4	—	1
	CC2-4-250K#4		4	90BKB	HCPK4	—	1

## Exothermic welding system

CC2 cable to cable (continued)

### CC2 cable to cable

Diagram	Cat. no.	Wire size (A) AWG or kcmil	Wire size (B) AWG or kcmil	Welding powder size	Handle clamp type	Sleeve	Std. ctn.
	CC2-4-300K300K	300	300	200BKB	HCPK4	-	1
	CC2-4-300K250K		250	150BKB	HCPK4	-	1
	CC2-4-300K4/0		4/0	150BKB	HCPK4	-	1
	CC2-4-300K3/0		3/0	150BKB	HCPK4	-	1
	CC2-4-300K2/0		2/0	90BKB	HCPK4	-	1
	CC2-4-300K1/0		1/0	90BKB	HCPK4	-	1
	CC2-4-300K#1		1	90BKB	HCPK4	-	1
	CC2-4-300K#2		2	90BKB	HCPK4	-	1
	CC2-4-300K#2S		2 solid	90BKB	HCPK4	-	1
	CC2-4-300K#4		4	90BKB	HCPK4	-	1
	CC2-4-350K350K	350	350	200BKB	HCPK4	-	1
	CC2-4-350K300K		300	200BKB	HCPK4	-	1
	CC2-4-350K250K		250	200BKB	HCPK4	-	1
	CC2-4-350K4/0		4/0	150BKB	HCPK4	-	1
	CC2-4-350K3/0		3/0	150BKB	HCPK4	-	1
	CC2-4-350K2/0		2/0	90BKB	HCPK4	-	1
	CC2-4-350K1/0		1/0	90BKB	HCPK4	-	1
	CC2-4-350K#1		1	90BKB	HCPK4	-	1
	CC2-4-350K#2		2	90BKB	HCPK4	-	1
	CC2-4-350K#4		4	90BKB	HCPK4	-	1
	CC2-4-500K500K	500	500	2 X 150BKB	HCPK4	-	1
	CC2-4-500K350K		350	200BKB	HCPK4	-	1
	CC2-4-500K300K		300	200BKB	HCPK4	-	1
	CC2-4-500K250K		250	200BKB	HCPK4	-	1
	CC2-4-500K4/0		4/0	150BKB	HCPK4	-	1
	CC2-4-500K2/0		2/0	90BKB	HCPK4	-	1
	CC2-4-500K1/0		1/0	90BKB	HCPK4	-	1
	CC2-4-500K#1		1	90BKB	HCPK4	-	1
	CC2-4-500K#2		2	90BKB	HCPK4	-	1
	CC2-4-500K#4		4	90BKB	HCPK4	-	1
	CC2-5-750K750K	750	750	2 X 250BKB	HCPK5	-	1
	CC2-5-750K500K		500	2 X 200BKB	HCPK5	-	1
	CC2-4-750K350K		350	250BKB	HCPK4	-	1
	CC2-4-750K300K		300	200BKB	HCPK4	-	1
	CC2-4-750K250K		250	200BKB	HCPK4	-	1
	CC2-4-750K4/0		4/0	150BKB	HCPK4	-	1
	CC2-4-750K2/0		2/0	150BKB	HCPK4	-	1
	CC2-4-750K1/0		1/0	150BKB	HCPK4	-	1
	CC2-5-1000K1000K	1000	1000	2 X 250BKB	HCPK5	-	1
	CC2-5-1000K750K		750	2 X 250BKB	HCPK5	-	1
	CC2-5-1000K500K		500	2 X 200BKB	HCPK5	-	1
	CC2-4-1000K350K		350	250BKB	HCPK4	-	1
	CC2-4-1000K300K		300	200BKB	HCPK4	-	1
	CC2-4-1000K250K		250	200BKB	HCPK4	-	1
	CC2-4-1000K4/0		4/0	150BKB	HCPK4	-	1
	CC2-4-1000K2/0		2/0	150BKB	HCPK4	-	1
	CC2-4-1000K1/0		1/0	150BKB	HCPK4	-	1


## Exothermic welding system

CC4 cable to cable

- Stranded conductor
- Solid circular conductor

**CC4 cable to cable**

Diagram	Cat. no.	Wire size (A) AWG or kcmil	Wire size (B) AWG or kcmil	Welding powder size	Handle clamp type	Sleeve	Std. ctn.
	CC4-4-#4#4	4	4	45BKB	HCPK4	-	1
	CC4-4-#2#2	2	2	65BKB	HCPK4	-	1
	CC4-4-#2#4		4	65BKB	HCPK4	-	1
	CC4-4-#2S#2S	2 solid	2 solid	65BKB	HCPK4	-	1
	CC4-4-#1#1	1	1	65BKB	HCPK4	-	1
	CC4-4-#1#2		2	65BKB	HCPK4	-	1
	CC4-4-#1#4		4	65BKB	HCPK4	-	1
	CC4-4-1/01/0	1/0	1/0	90BKB	HCPK4	-	1
	CC4-4-1/0#1		1	90BKB	HCPK4	-	1
	CC4-4-1/0#2		2	90BKB	HCPK4	-	1
	CC4-4-1/0#4		4	90BKB	HCPK4	-	1
	CC4-4-2/02/0	2/0	2/0	115BKB	HCPK4	-	1
	CC4-42/01/0		1/0	115BKB	HCPK4	-	1
	CC4-4-2/0#1		1	115BKB	HCPK4	-	1
	CC4-4-2/0#2		2	115BKB	HCPK4	-	1
	CC4-4-3/03/0	3/0	3/0	115BKB	HCPK4	-	1
	CC4-4-3/02/0		2/0	150BKB	HCPK4	-	1
	CC4-4-3/01/0		1/0	115BKB	HCPK4	-	1
	CC4-4-3/0#1		1	115BKB	HCPK4	-	1
	CC4-4-3/0#2		2	115BKB	HCPK4	-	1
	CC4-4-4/04/0	4/0	4/0	200BKB	HCPK4	-	1
	CC4-4-4/03/0		3/0	200BKB	HCPK4	-	1
	CC4-4-4/02/0		2/0	150BKB	HCPK4	-	1
	CC4-4-4/01/0		1/0	150BKB	HCPK4	-	1
	CC4-4-4/0#1		1	115BKB	HCPK4	-	1
	CC4-4-4/0#2		2	115BKB	HCPK4	-	1
	CC4-4-250K250K	250	250	200BKB	HCPK4	-	1
	CC4-4-250K4/0		4/0	200BKB	HCPK4	-	1
	CC4-4-250K3/0		3/0	200BKB	HCPK4	-	1
	CC4-4-250K2/0		2/0	150BKB	HCPK4	-	1
	CC4-4-250K1/0		1/0	150BKB	HCPK4	-	1
	CC4-4-250K#1		1	115BKB	HCPK4	-	1
	CC4-4-250K#2		2	115BKB	HCPK4	-	1




## Exothermic welding system

CC4 cable to cable (continued)

### CC4 cable to cable

Diagram	Cat. no.	Wire size (A) AWG or kcmil	Wire size (B) AWG or kcmil	Welding powder size	Handle clamp type	Sleeve	Std. ctn.
	CC4-4-300K300K	300	300	250BKB	HCPK4	-	1
	CC4-4-300K250K		250	250BKB	HCPK4	-	1
	CC4-4-300K4/0		4/0	200BKB	HCPK4	-	1
	CC4-4-300K3/0		3/0	200BKB	HCPK4	-	1
	CC4-4-300K2/0		2/0	150BKB	HCPK4	-	1
	CC4-4-300K1/0		1/0	150BKB	HCPK4	-	1
	CC4-4-300K#1		1	115BKB	HCPK4	-	1
	CC4-4-300K#2		2	115BKB	HCPK4	-	1
	CC4-4-350K350K	350	350	250BKB	HCPK4	-	1
	CC4-4-350K300K		300	250BKB	HCPK4	-	1
	CC4-4-4350K250K		250	250BKB	HCPK4	-	1
	CC4-4-350K4/0		4/0	200BKB	HCPK4	-	1
	CC4-4-350K3/0		3/0	200BKB	HCPK4	-	1
	CC4-4-350K2/0		2/0	200BKB	HCPK4	-	1
	CC4-4-350K1/0		1/0	200BKB	HCPK4	-	1
	CC4-4-350K#1		1	150BKB	HCPK4	-	1
	CC4-4-350K#2		2	150BKB	HCPK4	-	1
	CC4-5-500K500K	500	500	2 x 250BKB	HCPK5	-	1
	CC4-5-500K350K		350	2 x 200BKB	HCPK5	-	1
	CC4-5-500K300K		300	2 x 200BKB	HCPK5	-	1
	CC4-5-500K250K		250	2 x 150BKB	HCPK5	-	1
	CC4-5-500K4/0		4/0	2 x 150BKB	HCPK5	-	1
	CC4-5-500K3/0		3/0	2 x 150BKB	HCPK5	-	1
	CC4-4-500K2/0		2/0	250BKB	HCPK4	-	1
	CC4-4-500K1/0		1/0	250BKB	HCPK4	-	1



## Exothermic welding system

CC6 cable to cable


### CC6 cable to cable

Cat. no.	Wire size (A) AWG or kcmil	Wire size (B) AWG or kcmil	Welding powder size	Handle clamp type	Sleeve	Std. ctn.
CC6-4-#4#4	4	4	45BKB	HCPK4	-	1
CC6-4-#2#2	2	2	65BKB	HCPK4	-	1
CC6-4-#2#4		4	65BKB	HCPK4	-	1
CC6-4-#2S#2S	2 solid	2 solid	65BKB	HCPK4	-	1
CC6-4-#1#1	1	1	65BKB	HCPK4	-	1
CC6-4-#1#2		2	65BKB	HCPK4	-	1
CC6-4-#1#4		4	65BKB	HCPK4	-	1
CC6-4-1/01/0	1/0	1/0	90BKB	HCPK4	-	1
CC6-4-1/0#1		1	90BKB	HCPK4	-	1
CC6-4-1/0#2		2	90BKB	HCPK4	-	1
CC6-4-1/0#4		4	90BKB	HCPK4	-	1
CC6-4-2/02/0	2/0	2/0	115BKB	HCPK4	-	1
CC6-42/01/0		1/0	115BKB	HCPK4	-	1
CC6-4-2/0#1		1	115BKB	HCPK4	-	1
CC6-4-2/0#2		2	115BKB	HCPK4	-	1
CC6-4-3/03/0	3/0	3/0	115BKB	HCPK4	-	1
CC6-4-3/02/0		2/0	150BKB	HCPK4	-	1
CC6-4-3/01/0		1/0	115BKB	HCPK4	-	1
CC6-4-3/0#1		1	115BKB	HCPK4	-	1
CC6-4-3/0#2		2	115BKB	HCPK4	-	1
CC6-4-4/04/0	4/0	4/0	200BKB	HCPK4	-	1
CC6-4-4/03/0		3/0	200BKB	HCPK4	-	1
CC6-4-4/02/0		2/0	150BKB	HCPK4	-	1
CC6-4-4/01/0		1/0	150BKB	HCPK4	-	1
CC6-4-4/0#1		1	115BKB	HCPK4	-	1
CC6-4-4/0#2		2	115BKB	HCPK4	-	1

- Stranded conductor
- Solid circular conductor

Cat. no.	Wire size (A) AWG or kcmil	Wire size (B) AWG or kcmil	Welding powder size	Handle clamp type	Sleeve	Std. ctn.
CC6-4-250K250K	250	250	200BKB	HCPK4	-	1
CC6-4-250K4/0		4/0	200BKB	HCPK4	-	1
CC6-4-250K3/0		3/0	200BKB	HCPK4	-	1
CC6-4-250K2/0		2/0	150BKB	HCPK4	-	1
CC6-4-250K1/0		1/0	150BKB	HCPK4	-	1
CC6-4-250K#1		1	115BKB	HCPK4	-	1
CC6-4-250K#2		2	115BKB	HCPK4	-	1
CC6-4-300K300K	300	300	250BKB	HCPK4	-	1
CC6-4-300K250K		250	250BKB	HCPK4	-	1
CC6-4-300K4/0		4/0	200BKB	HCPK4	-	1
CC6-4-300K3/0		3/0	200BKB	HCPK4	-	1
CC6-4-300K2/0		2/0	150BKB	HCPK4	-	1
CC6-4-300K1/0		1/0	150BKB	HCPK4	-	1
CC6-4-300K#1		1	115BKB	HCPK4	-	1
CC6-4-300K#2		2	115BKB	HCPK4	-	1
CC6-4-350K350K	350	350	250BKB	HCPK4	-	1
CC6-4-350K300K		300	250BKB	HCPK4	-	1
CC6-4-4350K250K		250	250BKB	HCPK4	-	1
CC6-4-350K4/0		4/0	200BKB	HCPK4	-	1
CC6-4-350K3/0		3/0	200BKB	HCPK4	-	1
CC6-4-350K2/0		2/0	200BKB	HCPK4	-	1

Diagram



## Exothermic welding system

CC7 cable to cable


### CC7 cable to cable

Cat. no.	Wire size (A) AWG or kcmil	Wire size (B) AWG or kcmil	Welding powder size	Handle clamp type	Sleeve	Std. ctn.
CC7-4-#4#4	4	4	32BKB	HCPK4	-	1
CC7-4-#4#6		6	32BKB	HCPK4	2 X sleeve #6	1
CC7-4-#4#6S		6 solid	32BKB	HCPK4	2 X sleeve #6S	1
CC7-4-#4#8		8	32BKB	HCPK4	2 X sleeve #8	1
CC7-4-#2S#2	2 solid	2	65BKB	HCPK4	-	1
CC7-4-#2S#2S		2 solid	65BKB	HCPK4	-	1
CC7-4-#2S#4		4	65BKB	HCPK4	-	1
CC7-4-#2S#6		6	45BKB	HCPK4	2 X sleeve #6	1
CC7-4-#2S#6S		6 solid	45BKB	HCPK4	2 X sleeve #6S	1
CC7-4-#2S#8		8	45BKB	HCPK4	2 X sleeve #8	1
CC7-4-#2S#8S		8 solid	45BKB	HCPK4	2 X sleeve #8S	1
CC7-4-#2#2	2	2	65BKB	HCPK4	-	1
CC7-4-#2#4		4	65BKB	HCPK4	-	1
CC7-4-#2#6		6	45BKB	HCPK4	2 X sleeve #6	1
CC7-4-#2#6S		6 solid	45BKB	HCPK4	2 X sleeve #6S	1
CC7-4-#2#8		8	45BKB	HCPK4	2 X sleeve #8	1
CC7-4-#2#8S		8 solid	45BKB	HCPK4	2 X sleeve #8S	1
CC7-4-#1S#1	1 solid	1	65BKB	HCPK4	-	1
CC7-4-#1S#2		2	65BKB	HCPK4	-	1
CC7-4-#1S#2S		2 solid	65BKB	HCPK4	-	1
CC7-4-#1S#4		4	65BKB	HCPK4	-	1
CC7-4-#1S#6		6	65BKB	HCPK4	2 X sleeve #6	1
CC7-4-#1S#6S		6 solid	65BKB	HCPK4	2 X sleeve #6S	1
CC7-4-#1S#8		8	45BKB	HCPK4	2 X sleeve #8	1
CC7-4-#1S#8S		8 solid	45BKB	HCPK4	2 X sleeve #8S	1
CC7-4-#1#1	1	1	65BKB	HCPK4	-	1
CC7-4-#1#1S		1 solid	65BKB	HCPK4	-	1
CC7-4-#1#2		2	65BKB	HCPK4	-	1
CC7-4-#1#2S		2 solid	65BKB	HCPK4	-	1
CC7-4-#1#4		4	65BKB	HCPK4	-	1
CC7-4-#1#6		6	65BKB	HCPK4	2 X sleeve #6	1
CC7-4-#1#6S		6 solid	65BKB	HCPK4	2 X sleeve #6S	1
CC7-4-#1#8		8	45BKB	HCPK4	2 X sleeve #8	1
CC7-4-#1#8S		8 solid	45BKB	HCPK4	2 X sleeve #8S	1

- Stranded conductor
- Solid circular conductor

Cat. no.	Wire size (A) AWG or kcmil	Wire size (B) AWG or kcmil	Welding powder size	Handle clamp type	Sleeve	Std. ctn.
CC7-4-1/0S1/0	1/0 solid	1/0	90BKB	HCPK4	-	1
CC7-4-1/0S1/OS		1/0 solid	90BKB	HCPK4	-	1
CC7-4-1/0S#1		1	65BKB	HCPK4	-	1
CC7-4-1/0S#1S		1 solid	65BKB	HCPK4	-	1
CC7-4-1/0S#2		2	65BKB	HCPK4	-	1
CC7-4-1/0S#2S		2 solid	65BKB	HCPK4	-	1
CC7-4-1/0S#4		4	65BKB	HCPK4	-	1
CC7-4-1/0S#6		6	65BKB	HCPK4	2 X sleeve #6	1
CC7-4-1/0S#6S		6 solid	65BKB	HCPK4	2 X sleeve #6S	1
CC7-4-1/0S#8		8	65BKB	HCPK4	2 X sleeve #8	1
CC7-4-1/0S#8S		8 solid	65BKB	HCPK4	2 X sleeve #8S	1
CC7-4-1/01/0	1/0	1/0	90BKB	HCPK4	-	1
CC7-4-1/01/OS		1/0 solid	90BKB	HCPK4	-	1
CC7-4-1/0#1		1	65BKB	HCPK4	-	1
CC7-4-1/0#1S		1 solid	65BKB	HCPK4	-	1
CC7-4-1/0#2		2	65BKB	HCPK4	-	1
CC7-4-1/0#2S		2 solid	65BKB	HCPK4	-	1
CC7-4-1/0#4		4	65BKB	HCPK4	-	1
CC7-4-1/0#6		6	65BKB	HCPK4	2 x sleeve #6	1
CC7-4-1/0#6S		6 solid	65BKB	HCPK4	2 x sleeve #6S	1
CC7-4-1/0#8		8	65BKB	HCPK4	2 x sleeve #8	1

Diagram



## Exothermic welding system

CC7 cable to cable (continued)


### CC7 cable to cable

Cat. no.	Wire size (A) AWG or kcmil	Wire size (B) AWG or kcmil	Welding powder size	Handle clamp type	Sleeve	Std. ctn.
CC7-4-1/0#8S	1/0	8 solid	65BKB	HCPK4	2 X sleeve #8S	1
CC7-4-2/02/0	2/0	2/0	115BKB	HCPK4	-	1
CC7-4-2/01/0		1/0	115BKB	HCPK4	-	1
CC7-4-2/01/OS		1/0 solid	115BKB	HCPK4	-	1
CC7-4-2/0#1		1	90BKB	HCPK4	-	1
CC7-4-2/0#1S		1 solid	90BKB	HCPK4	-	1
CC7-4-2/0#2		2	90BKB	HCPK4	-	1
CC7-4-2/0#4		4	90BKB	HCPK4	-	1
CC7-4-2/0#6		6	90BKB	HCPK4	2 X sleeve #6	1
CC7-4-2/0#6S		6 solid	90BKB	HCPK4	2 X sleeve #6S	1
CC7-4-2/0#8		8	65BKB	HCPK4	2 X sleeve #8	1
CC7-4-2/0#8S		8 solid	65BKB	HCPK4	2 X sleeve #8S	1
CC7-4-3/03/0	3/0	3/0	150BKB	HCPK4	-	1
CC7-4-3/02/0		2/0	150BKB	HCPK4	-	1
CC7-4-3/01/0		1/0	115BKB	HCPK4	-	1
CC7-4-3/01/OS		1/0 solid	115BKB	HCPK4	-	1
CC7-4-3/0#1		1	115BKB	HCPK4	-	1
CC7-4-3/0#15		1 solid	115BKB	HCPK4	-	1
CC7-4-3/0#2		2	115BKB	HCPK4	-	1
CC7-4-3/0#2S		2 solid	115BKB	HCPK4	-	1
CC7-4-3/0#4		4	115BKB	HCPK4	-	1
CC7-4-3/0#6		6	90BKB	HCPK4	2 X sleeve #6	1
CC7-4-3/0#6S		6 solid	90BKB	HCPK4	2 X sleeve #6S	1
CC7-4-3/0#8		8	90BKB	HCPK4	2 X sleeve #8	1
CC7-4-3/0#8S		8 solid	90BKB	HCPK4	2 X sleeve #8S	1

- Stranded conductor
- Solid circular conductor

Cat. no.	Wire size (A) AWG or kcmil	Wire size (B) AWG or kcmil	Welding powder size	Handle clamp type	Sleeve	Std. ctn.
CC7-4-4/0S4/0	4/0 solid	4/0	200BKB	HCPK4	-	1
CC7-4-4/0S4/0S		4/0 solid	200BKB	HCPK4	-	1
CC7-4-4/0S3/0			3/0	200BKB	HCPK4	-
CC7-4-4/0S2/0			2/0	150BKB	HCPK4	-
CC7-4-4/0S1/0			1/0	150BKB	HCPK4	-
CC7-4-4/0S1/0S		1/0 solid	150BKB	HCPK4	-	1
CC7-4-4/0S#1			1	150BKB	HCPK4	-
CC7-4-4/0S#1S		1 solid	150BKB	HCPK4	-	1
CC7-4-4/0S#2			2	150BKB	HCPK4	-
CC7-4-4/0S#2S		2 solid	150BKB	HCPK4	-	1
CC7-4-4/0S#4			4	150BKB	HCPK4	-
CC7-4-4/0S#6			6	90BKB	HCPK4	2 X sleeve #6
CC7-4-4/0S#6S		6 solid	90BKB	HCPK4	2 X sleeve #6S	1
CC7-4-4/0S#8			8	90BKB	HCPK4	2 X sleeve #8
CC7-4-4/0S#8S		8 solid	90BKB	HCPK4	2 X sleeve #8S	1
CC7-4-4/04/0	4/0	4/0	200BKB	HCPK4	-	1
CC7-4-4/04/0S		4/0 solid	200BKB	HCPK4	-	1
CC7-4-4/03/0			3/0	200BKB	HCPK4	-
CC7-4-4/02/0			2/0	150BKB	HCPK4	-
CC7-4-4/01/0			1/0	150BKB	HCPK4	-
CC7-4-4/01/0S		1/0 solid	150BKB	HCPK4	-	1
CC7-4-4/0#1			1	150BKB	HCPK4	-
CC7-4-4/0#1S		1 solid	150BKB	HCPK4	-	1
CC7-4-4/0#2			2	150BKB	HCPK4	-
CC7-4-4/0#2S		2 solid	150BKB	HCPK4	-	1
CC7-4-4/0#4			4	150BKB	HCPK4	-
CC7-4-4/0#6			6	90BKB	HCPK4	2 X sleeve #6
CC7-4-4/0#6S		6 solid	90BKB	HCPK4	2 X sleeve #6S	1
CC7-4-4/0#8			8	90BKB	HCPK4	2 X sleeve #8
CC7-4-4/0#8S		8 solid	90BKB	HCPK4	2 X sleeve #8S	1

Diagram



## Exothermic welding system

CC11 cable to cable


### CC11 cable to cable

Cat. no.	Wire size (A) AWG or kcmil	Wire size (B) AWG or kcmil	Welding powder size	Handle clamp type	Std. Sleeve ctn.
CC11-7-#6S#6S	6 solid	6 solid	32BKB	HCPK7	4 x 1 sleeve #6S
CC11-7-#6#6	6	6	45BKB	HCPK7	4 x 1 sleeve #6
CC11-7-#4#4	4	4	65BKB	HCPK7	- 1
CC11-7-#2#2	2	2	90BKB	HCPK7	- 1
CC11-7-#2#4		4	65BKB	HCPK7	- 1
CC11-7-#2S#2S	2 solid	2 solid	90BKB	HCPK7	- 1
CC11-7-#1#1	1	1	115BKB	HCPK7	- 1
CC11-7-#1#2		2	90BKB	HCPK7	- 1
CC11-7-#1#4		4	90BKB	HCPK7	- 1
CC11-7-1/01/0	1/0	1/0	150BKB	HCPK7	- 1
CC11-7-1/0#1		1	150BKB	HCPK7	- 1
CC11-7-1/0#2		2	115BKB	HCPK7	- 1
CC11-7-1/0#4		4	115BKB	HCPK7	- 1
CC11-7-2/02/0	2/0	2/0	200BKB	HCPK7	- 1
CC11-7-2/01/0		1/0	200BKB	HCPK7	- 1
CC11-7-2/0#1		1	150BKB	HCPK7	- 1
CC11-7-2/0#2		2	150BKB	HCPK7	- 1
CC11-7-3/03/0	3/0	3/0	250BKB	HCPK7	- 1
CC11-7-3/02/0		2/0	200BKB	HCPK7	- 1
CC11-7-3/01/0		1/0	200BKB	HCPK7	- 1
CC11-7-3/0#1		1	150BKB	HCPK7	- 1
CC11-7-3/0#2		2	150BKB	HCPK7	- 1
CC11-7-4/04/0	4/0	4/0	250BKB	HCPK7	- 1
CC11-7-4/03/0		3/0	250BKB	HCPK7	- 1
CC11-7-4/02/0		2/0	200BKB	HCPK7	- 1
CC11-7-4/01/0		1/0	200BKB	HCPK7	- 1
CC11-7-4/0#1		1	150BKB	HCPK7	- 1
CC11-7-4/0#2		2	150BKB	HCPK7	- 1
CC11-7-250K250K	250	250 2 x 150BKB	HCPK7	- 1	
CC11-7-250K4/0		4/0 2 x 150BKB	HCPK7	- 1	
CC11-7-250K3/0		3/0 2 x 150BKB	HCPK7	- 1	
CC11-7-250K2/0		2/0 250BKB	HCPK7	- 1	
CC11-7-250K1/0		1/0 250BKB	HCPK7	- 1	
CC11-7-250K#1		1 200BKB	HCPK7	- 1	
CC11-7-250K#2		2 150BKB	HCPK7	- 1	

- Stranded conductor
- Solid circular conductor

Cat. no.	Wire size (A) AWG or kcmil	Wire size (B) AWG or kcmil	Welding powder size	Handle clamp type	Std. Sleeve ctn.
CC11-8-300K300K	300	300 2 x 200BKB	HCPK8	- 1	
CC11-8-300K250K		250 2 x 200BKB	HCPK8	- 1	
CC11-7-300K4/0		4/0 2 x 150BKB	HCPK7	- 1	
CC11-7-300K3/0		3/0 2 x 150BKB	HCPK7	- 1	
CC11-7-300K2/0		2/0 250BKB	HCPK7	- 1	
CC11-7-300K1/0		1/0 250BKB	HCPK7	- 1	
CC11-7-300K#1		1 200BKB	HCPK7	- 1	
CC11-7-300K#2		2 150BKB	HCPK7	- 1	
CC11-8-350K350K	350	350 2 x 250BKB	HCPK8	- 1	
CC11-8-350K300K		300 2 x 250BKB	HCPK8	- 1	
CC11-8-350K250K		250 2 x 250BKB	HCPK8	- 1	
CC11-8-350K4/0		4/0 2 x 200BKB	HCPK8	- 1	
CC11-8-350K3/0		3/0 2 x 200BKB	HCPK8	- 1	
CC11-7-350K2/0		2/0 2 x 150BKB	HCPK7	- 1	
CC11-7-350K1/0		1/0 250BKB	HCPK7	- 1	
CC11-7-350K#1		1 200BKB	HCPK7	- 1	
CC11-7-350K#2		2 200BKB	HCPK7	- 1	
CC11-8-500K500K	500	500 3 x 250BKB	HCPK8	- 1	
CC11-8-500K350K		350 3 x 200BKB	HCPK8	- 1	
CC11-8-500K300K		300 3 x 200BKB	HCPK8	- 1	
CC11-8-500K250K		250 2 x 250BKB	HCPK8	- 1	
CC11-8-500K4/0		4/0 2 x 250BKB	HCPK8	- 1	
CC11-8-500K3/0		3/0 2 x 250BKB	HCPK8	- 1	
CC11-8-500K2/0		2/0 2 x 200BKB	HCPK8	- 1	
CC11-8-500K1/0		1/0 2 x 150BKB	HCPK8	- 1	

Diagram




## Exothermic welding system

Cable to ground rod quick reference


—  
01 CR1  
See page 21

—  
02 CR2  
See page 22


—  
03 CR3  
See page 23



—  
01



—  
02



—  
03

## Exothermic welding system

### CR1 cable to ground rod


#### CR1 cable to ground rod

Cat. no.	Rod size (A) in.	Wire size (B) AWG or kcmil	Welding powder size	Handle clamp type	Std. Sleeve ctn.
CR1-3-500#6	½ nominal diameter	6	65BKB	HCPK3	sleeve #6 1
CR1-3-500#6S	actual shank dia.	6 solid	65BKB	HCPK3	sleeve #6S 1
CR1-3-500#4	0.476	4	65BKB	HCPK3	- 1
CR1-3-500#4S	0.476	4 solid	45BKB	HCPK3	- 1
CR1-3-500#2	(Non-UL rod)	2	65BKB	HCPK3	- 1
CR1-3-500#2S	2 solid	65BKB	HCPK3	- 1	
CR1-4-500#1	1	65BKB	HCPK4	- 1	
CR1-4-5001/0	1/0	90BKB	HCPK4	- 1	
CR1-4-5001/OS	1/0 solid	90BKB	HCPK4	- 1	
CR1-4-5002/0	2/0	90BKB	HCPK4	- 1	
CR1-4-5003/0	3/0	90BKB	HCPK4	- 1	
CR1-4-5004/0	4/0	90BKB	HCPK4	- 1	
CR1-4-500250K	250	90BKB	HCPK4	- 1	
CR1-4-500300K	300	90BKB	HCPK4	- 1	
CR1-3-500L#6	½ true diameter	6	45BKB	HCPK3	1 x sleeve #6 1
CR1-3-500L#6S	actual shank dia.	6 solid	45BKB	HCPK3	1 x sleeve #6S 1
CR1-3-500L#4	0.502 (UL rod)	4	45BKB	HCPK3	- 1
CR1-3-500L#4S	4 solid	45BKB	HCPK3	- 1	
CR1-3-500L#2	2	65BKB	HCPK3	- 1	
CR1-3-500L#2S	2 solid	65BKB	HCPK3	- 1	
CR1-4-500L#1	1	65BKB	HCPK4	- 1	
CR1-4-500L1/0	1/0	90BKB	HCPK4	- 1	
CR1-4-500L1/OS	1/0 solid	90BKB	HCPK4	- 1	
CR1-4-500L2/0	2/0	90BKB	HCPK4	- 1	
CR1-4-500L3/0	3/0	90BKB	HCPK4	- 1	
CR1-4-500L4/0	4/0	90BKB	HCPK4	- 1	
CR1-4-500L250K	250	90BKB	HCPK4	- 1	
CR1-4-500L300K	300	90BKB	HCPK4	- 1	

- Stranded conductor
- Solid circular conductor

Cat. no.	Rod size (A) in.	Wire size (B) AWG or kcmil	Welding powder size	Handle clamp type	Std. Sleeve ctn.
CR1-3-625#6	½ nominal diameter	6	65BKB	HCPK3	1 x sleeve #6 1
CR1-3-625#6S	actual shank dia.	6 solid	65BKB	HCPK3	1 x sleeve #6S 1
CR1-3-625#4	0.560	4	65BKB	HCPK3	- 1
CR1-3-625#4S	4 solid	65BKB	HCPK3	- 1	
CR1-4-625#2	2	65BKB	HCPK4	- 1	
CR1-4-625#2S	2 solid	65BKB	HCPK4	- 1	
CR1-4-625#1	1	65BKB	HCPK4	- 1	
CR1-4-6251/0	1/0	90BKB	HCPK4	- 1	
CR1-4-6251/OS	1/0 solid	90BKB	HCPK4	- 1	
CR1-4-6252/0	2/0	90BKB	HCPK4	- 1	
CR1-4-6253/0	3/0	90BKB	HCPK4	- 1	
CR1-4-6254/0	4/0	90BKB	HCPK4	- 1	
CR1-4-625250K	250	90BKB	HCPK4	- 1	
CR1-4-625300K	300	115BKB	HCPK4	- 1	
CR1-4-625350K	350	115BKB	HCPK4	- 1	
CR1-4-625500K	500	150BKB	HCPK4	- 1	
CR1-3-750#6	¾ nominal diameter	6	32BKB	HCPK3	1 x sleeve #6 1
CR1-3-750#6S	actual shank dia.	6 solid	32BKB	HCPK3	1 x sleeve #6S 1
CR1-3-750#4	0.678	4	45BKB	HCPK3	- 1
CR1-3-750#4S	4 solid	45BKB	HCPK3	- 1	
CR1-4-750#2	2	90BKB	HCPK4	- 1	
CR1-4-750#2S	2 solid	90BKB	HCPK4	- 1	
CR1-4-750#1	1	90BKB	HCPK4	- 1	
CR1-4-7501/0	1/0	90BKB	HCPK4	- 1	
CR1-4-7501/OS	1/0 solid	90BKB	HCPK4	- 1	
CR1-4-7502/0	2/0	90BKB	HCPK4	- 1	
CR1-4-7503/0	3/0	90BKB	HCPK4	- 1	
CR1-4-7504/0	4/0	90BKB	HCPK4	- 1	
CR1-4-750250K	250	90BKB	HCPK4	- 1	
CR1-4-750300K	300	115BKB	HCPK4	- 1	
CR1-4-750350K	350	115BKB	HCPK4	- 1	
CR1-4-750500K	500	150BKB	HCPK4	- 1	

Diagram



For connections to threaded rods, remove top threaded section.

## Exothermic welding system

### CR2 cable to ground rod


#### CR2 cable to ground rod

- Stranded conductor
- Solid circular conductor

Cat. no.	Rod size (A) in.	Wire size (B) AWG or kcmil	Welding powder	Handle type	Handle sleeve	Std. ctn.
CR2-3-500#6	½ nominal diameter	6	65BKB	HCPK3	Sleeve #6	1
CR2-3-500#6S	actual shank dia. 0.476	6 solid	65BKB	HCPK3	Sleeve #6S	1
CR2-3-500#4	(Non-UL rod)	4	65BKB	HCPK3	—	1
CR2-3-500#4S		4 solid	65BKB	HCPK3	—	1
CR2-4-500#2		2	90BKB	HCPK3	—	1
CR2-4-500#2S		2 solid	90BKB	HCPK3	—	1
CR2-4-500#1		1	90BKB	HCPK4	—	1
CR2-4-5001/0		1/0	90BKB	HCPK4	—	1
CR2-4-5001/0S		1/0 solid	90BKB	HCPK4	—	1
CR2-4-5002/0		2/0	90BKB	HCPK4	—	1
CR2-4-5003/0		3/0	115BKB	HCPK4	—	1
CR2-4-5004/0		4/0	115BKB	HCPK4	—	1
CR2-4-500250K		250	150BKB	HCPK4	—	1
CR2-4-500300K		300	200BKB	HCPK4	—	1
CR2-3-500L#6	½ true diameter	6	65BKB	HCPK3	Sleeve #6	1
CR2-3-500L#6S	actual shank dia. 0.502	6 solid	65BKB	HCPK3	Sleeve #6S	1
CR2-3-500L#4	(UL rod)	4	65BKB	HCPK3	—	1
CR2-3-500L#4S		4 solid	65BKB	HCPK3	—	1
CR2-4-500L#2		2	90BKB	HCPK3	—	1
CR2-4-500L#2S		2 solid	90BKB	HCPK3	—	1
CR2-4-500L#1		1	90BKB	HCPK4	—	1
CR2-4-500L1/0		1/0	90BKB	HCPK4	—	1
CR2-4-500L1/0S		1/0 solid	90BKB	HCPK4	—	1
CR2-4-500L2/0		2/0	90BKB	HCPK4	—	1
CR2-4-500L3/0		3/0	115BKB	HCPK4	—	1
CR2-4-500L4/0		4/0	115BKB	HCPK4	—	1
CR2-4-500L250K		250	150BKB	HCPK4	—	1
CR2-4-500L300K		300	200BKB	HCPK4	—	1

Cat. no.	Rod size (A) in.	Wire size (B) AWG or kcmil	Welding powder	Handle type	Handle sleeve	Std. ctn.
CR2-3-625#6	⅜ nominal diameter	6	32BKB	HCPK3	Sleeve #6	1
CR2-3-625#6S	actual shank dia. 0.560	6 solid	32BKB	HCPK3	Sleeve #6S	1
CR2-3-625#4		4	32BKB	HCPK3	—	1
CR2-3-625#4S		4 solid	32BKB	HCPK3	—	1
CR2-4-625#2		2	90BKB	HCPK4	—	1
CR2-4-625#2S		2 solid	90BKB	HCPK4	—	1
CR2-4-625#1		1	90BKB	HCPK4	—	1
CR2-4-6251/0		1/0	90BKB	HCPK4	—	1
CR2-4-6251/0S		1/0 solid	115BKB	HCPK4	—	1
CR2-4-6252/0		2/0	115BKB	HCPK4	—	1
CR2-4-6253/0		3/0	115BKB	HCPK4	—	1
CR2-4-6254/0		4/0	115BKB	HCPK4	—	1
CR2-4-625250K		250	150BKB	HCPK4	—	1
CR2-4-625300K		300	200BKB	HCPK4	—	1
CR2-4-625350K		350	200BKB	HCPK4	—	1
CR2-4-625500K		500	250BKB	HCPK4	—	1
CR2-3-750#6	¾ nominal diameter	6	65BKB	HCPK3	Sleeve #6	1
CR2-3-750#6S	actual shank dia. 0.678	6 solid	65BKB	HCPK3	Sleeve #6S	1
CR2-3-750#4		4	65BKB	HCPK3	—	1
CR2-3-750#4S		4 solid	65BKB	HCPK3	—	1
CR2-4-750#2		2	90BKB	HCPK4	—	1
CR2-4-750#2S		2 solid	90BKB	HCPK4	—	1
CR2-4-750#1		1	90BKB	HCPK4	—	1
CR2-4-7501/0		1/0	115BKB	HCPK4	—	1
CR2-4-7501/0S		1/0 solid	115BKB	HCPK4	—	1
CR2-4-7502/0		2/0	115BKB	HCPK4	—	1
CR2-4-7503/0		3/0	115BKB	HCPK4	—	1
CR2-4-7504/0		4/0	115BKB	HCPK4	—	1
CR2-4-750250K		250	150BKB	HCPK4	—	1
CR2-4-750300K		300	200BKB	HCPK4	—	1
CR2-4-750350K		350	200BKB	HCPK4	—	1
CR2-4-750500K		500	250BKB	HCPK4	—	1

Diagram



For connections to threaded rods, remove top threaded section.

## Exothermic welding system

### CR3 cable to ground rod


- Stranded conductor
- Solid circular conductor

#### CR3 cable to ground rod

Cat. no.	Rod size (A) in.	Wire size (B) AWG or kcmil	Welding powder size	Handle clamp type	Sleeve	Std. ctn.
CR3-9-5001/0	½ nominal diameter	1/0	115BKB	HCPK4 and frame 1	—	1
CR3-9-5001/0S	actual shank dia. 0.476	1/0 solid	115BKB	HCPK4 and frame 1	—	1
CR3-9-5002/0	(Non-UL® rod)	2/0	115BKB	HCPK4 and frame 1	—	1
CR3-9-5003/0		3/0	150BKB	HCPK4 and frame 1	—	1
CR3-9-5004/0		4/0	150BKB	HCPK4 and frame 1	—	1
CR3-9-500250K		250	150BKB	HCPK4 and frame 1	—	1
CR3-9-500300K		300	200BKB	HCPK4 and frame 1	—	1
CR3-9-500L1/0	½ nominal diameter	1/0	115BKB	HCPK4 and frame 1	—	1
CR3-9-500L1/0S	actual shank dia. 0.502 (UL rod)	1/0 solid	115BKB	HCPK4 and frame 1	—	1
CR3-9-500L2/0		2/0	115BKB	HCPK4 and frame 1	—	1
CR3-9-500L3/0		3/0	150BKB	HCPK4 and frame 1	—	1
CR3-9-500L4/0		4/0	150BKB	HCPK4 and frame 1	—	1
CR3-9-500L250K		250	150BKB	HCPK4 and frame 1	—	1
CR3-9-500300K		300	200BKB	HCPK4 and frame 1	—	1

Cat. no.	Rod size (A) in.	Wire size (B) AWG or kcmil	Welding powder size	Handle clamp type	Sleeve	Std. ctn.
CR3-9-6251/0	½ nominal diameter	1/0	115BKB	HCPK4 and frame 1	—	1
CR3-9-6251/0S	actual shank dia. 0.560	1/0 solid	115BKB	HCPK4 and frame 1	—	1
CR3-9-6252/0		2/0	115BKB	HCPK4 and frame 1	—	1
CR3-9-6253/0		3/0	150BKB	HCPK4 and frame 1	—	1
CR3-9-6254/0		4/0	150BKB	HCPK4 and frame 1	—	1
CR3-9-625250K		250	150BKB	HCPK4 and frame 1	—	1
CR3-9-625300K		300	200BKB	HCPK4 and frame 1	—	1
CR3-9-625350K		350	250BKB	HCPK4 and frame 1	—	1
CR3-10-625500K		500	2 x HCPK5 and 200BKB	HCPK5 and frame 2	—	1
CR3-9-7501/0	¾ nominal diameter	1/0	115BKB	HCPK5 and frame 2	—	1
CR3-9-7501/0S	actual shank dia. 0.678	1/0 solid	115BKB	HCPK4 and frame 1	—	1
CR3-9-7502/0		2/0	115BKB	HCPK4 and frame 1	—	1
CR3-9-7503/0		3/0	115BKB	HCPK4 and frame 1	—	1
CR3-9-7504/0		4/0	115BKB	HCPK4 and frame 1	—	1
CR3-9-750250K		250	200BKB	HCPK4 and frame 1	—	1
CR3-9-750300K		300	200BKB	HCPK4 and frame 1	—	1
CR3-10-750350K		350	2 x HCPK5 and 150BKB	HCPK5 and frame 2	—	1
CR3-10-750500K		500	2 x HCPK5 and 250BKB	HCPK5 and frame 2	—	1

Diagram



For connections to threaded rods, remove top threaded section.

## Exothermic welding system


Cable to rebar quick reference

—  
01 CRE1  
See page 25


—  
02 CRE3  
See page 25

—  
03 CRE4  
See page 26


—  
04 CRE6  
See page 26




—  
01



—  
02



—  
03



—  
04


## Exothermic welding system

CRE1 and CRE3 cable to rebar

- Stranded conductor
- Solid circular conductor

CRE1 cable to rebar


Diagram	Cat. no.	Rebar size (A)	Wire size (B) AWG or kcmil	Welding powder size	Handle clamp type	Sleeve	Packing	Std. ctn.
	CRE1-4-#43R	3	4	32BKB	HCPK4	–	None	1
	CRE1-4-#2S3R		2 solid	45BKB	HCPK4	–	None	1
	CRE1-4-#23R		2	45BKB	HCPK4	–	None	1
	CRE1-4-#13R		1	65BKB	HCPK4	–	None	1
	CRE1-4-1/03R		1/0	90BKB	HCPK4	–	None	1
	CRE1-4-2/03R		2/0	90BKB	HCPK4	–	None	1
	CRE1-4-3/03R		3/0	115BKB	HCPK4	–	None	1
	CRE1-3-#4Z	4-7	4	32BKB	HCPK3B	–	Pack-A	1
	CRE1-3-#2SZ		2 solid	45BKB	HCPK3B	–	Pack-A	1
	CRE1-3-#2Z		2	45BKB	HCPK3B	–	Pack-A	1
	CRE1-3-#1Z		1	65BKB	HCPK3B	–	Pack-A	1
	CRE1-3-1/0Z		1/0	90BKB	HCPK3B	–	Pack-A	1
	CRE1-3-2/0Z		2/0	90BKB	HCPK3B	–	Pack-A	1
	CRE1-3-3/0Z		3/0	115BKB	HCPK3B	–	Pack-A	1
	CRE1-3-4/0Z		4/0	115BKB	HCPK3B	–	Pack-A	1
	CRE1-3-#4Y	8-11	4	32BKB	HCPK3B	–	Pack-A	1
	CRE1-3-#2SY		2 solid	45BKB	HCPK3B	–	Pack-A	1
	CRE1-3-#2Y		2	45BKB	HCPK3B	–	Pack-A	1
	CRE1-3-#1Y		1	65BKB	HCPK3B	–	Pack-A	1
	CRE1-3-1/0Y		1/0	90BKB	HCPK3B	–	Pack-A	1
	CRE1-3-2/0Y		2/0	90BKB	HCPK3B	–	Pack-A	1
	CRE1-3-3/0Y		3/0	115BKB	HCPK3B	–	Pack-A	1
	CRE1-3-4/0Y		4/0	115BKB	HCPK3B	–	Pack-A	1



- Stranded conductor
- Solid circular conductor

CRE3 cable to rebar

Diagram	Cat. no.	Rebar size (A)	Wire size (B) AWG or kcmil	Welding powder size	Handle clamp type	Sleeve	Packing	Std. ctn.
	CRE3-3-#4Z	4-7	4	90BKB	HCPK3A	–	Pack-A	1
	CRE3-3-#2SZ		2 solid	90BKB	HCPK3A	–	Pack-A	1
	CRE3-3-#2Z		2	90BKB	HCPK3A	–	Pack-A	1
	CRE3-4-#1Z		1	115BKB	HCPK3A	–	Pack-A	1
	CRE3-4-1/0Z		1/0	115BKB	HCPK3A	–	Pack-A	1
	CRE3-4-2/0Z		2/0	115BKB	HCPK3A	–	Pack-A	1
	CRE3-4-3/0Z		3/0	150BKB	HCPK3A	–	Pack-A	1
	CRE3-4-4/0Z		4/0	150BKB	HCPK3A	–	Pack-A	1
	CRE3-3-#4Y	8-11	4	90BKB	HCPK3A	–	Pack-A	1
	CRE3-3-#2SY		2 solid	90BKB	HCPK3A	–	Pack-A	1
	CRE3-3-#2Y		2	90BKB	HCPK3A	–	Pack-A	1
	CRE3-4-#1Y		1	115BKB	HCPK3A	–	Pack-A	1
	CRE3-4-1/0Y		1/0	115BKB	HCPK3A	–	Pack-A	1
	CRE3-4-2/0Y		2/0	115BKB	HCPK3A	–	Pack-A	1
	CRE3-4-3/0Y		3/0	150BKB	HCPK3A	–	Pack-A	1
	CRE3-4-4/0Y		4/0	150BKB	HCPK3A	–	Pack-A	1



## Exothermic welding system

CRE4 and CRE6 cable to rebar

- Stranded conductor
- Solid circular conductor

—  
CRE4 cable to rebar

Diagram	Cat. no.	Rebar size (A)	Wire size (B) AWG or kcmil	Welding powder size	Handle clamp type	Cradle	Sleeve	Packing ctn.	Std.
	CRE4-3-#4Z	4-7		4	65BKB	HCPK3B	HCPK3BMOD	–	Pack-A 1
	CRE4-3-#2SZ		2 solid	90BKB	HCPK3B	HCPK3BMOD	–	Pack-A 1	
	CRE4-3-#2Z		2	90BKB	HCPK3B	HCPK3BMOD	–	Pack-A 1	
	CRE4-3-#1Z		1	90BKB	HCPK3B	HCPK3BMOD	–	Pack-A 1	
	CRE4-3-1/OZ		1/0	115BKB	HCPK3B	HCPK3BMOD	–	Pack-A 1	
	CRE4-3-2/OZ		2/0	115BKB	HCPK3B	HCPK3BMOD	–	Pack-A 1	
	CRE4-3-3/OZ		3/0	115BKB	HCPK3B	HCPK3BMOD	–	Pack-A 1	
	CRE4-3-4/OZ		4/0	115BKB	HCPK3B	HCPK3BMOD	–	Pack-A 1	
	CRE4-3-#4Y	8-11		4	65BKB	HCPK3B	HCPK3BMOD	–	Pack-A 1
	CRE4-3-#2SY		2 solid	90BKB	HCPK3B	HCPK3BMOD	–	Pack-A 1	
	CRE4-3-#2Y		2	90BKB	HCPK3B	HCPK3BMOD	–	Pack-A 1	
	CRE4-3-#1Y		1	90BKB	HCPK3B	HCPK3BMOD	–	Pack-A 1	
	CRE4-3-1/OY		1/0	115BKB	HCPK3B	HCPK3BMOD	–	Pack-A 1	
	CRE4-3-2/OY		2/0	115BKB	HCPK3B	HCPK3BMOD	–	Pack-A 1	
	CRE4-3-3/OY		3/0	115BKB	HCPK3B	HCPK3BMOD	–	Pack-A 1	
	CRE4-3-4/OY		4/0	115BKB	HCPK3B	HCPK3BMOD	–	Pack-A 1	

- Stranded conductor
- Solid circular conductor

—  
CRE6 cable to rebar

Diagram	Cat. no.	Rebar size (A)	Wire size (B) AWG or kcmil	Welding powder size	Handle clamp type	Sleeve	Packing ctn.	Std.	
	CRE6-3-#4Z	4-7		4	65BKB	HCPK3A	–	Pack-A 1	
	CRE6-3-#2SZ		2 solid	65BKB	HCPK3A	–	Pack-A 1		
	CRE6-3-#2Z		2	65BKB	HCPK3A	–	Pack-A 1		
	CRE6-3-#1Z		1	90BKB	HCPK3A	–	Pack-A 1		
	CRE6-4-1/OZ		1/0	115BKB	HCPK3A	–	Pack-A 1		
	CRE6-4-2/OZ		2/0	115BKB	HCPK3A	–	Pack-A 1		
	CRE6-4-3/OZ		3/0	150BKB	HCPK3A	–	Pack-A 1		
	CRE6-4-4/OZ		4/0	150BKB	HCPK3A	–	Pack-A 1		
	CRE6-3-#4Y	8-11		4	65BKB	HCPK3A	–	Pack-A 1	
	CRE6-3-#2SY		2 solid	65BKB	HCPK3A	–	Pack-A 1		
	CRE6-3-#2Y		2	65BKB	HCPK3A	–	Pack-A 1		
	CRE6-3-#1Y		1	90BKB	HCPK3A	–	Pack-A 1		
	CRE6-4-1/OY		1/0	115BKB	HCPK3A	–	Pack-A 1		
	CRE6-4-2/OY		2/0	115BKB	HCPK3A	–	Pack-A 1		
	CRE6-4-3/OY		3/0	150BKB	HCPK3A	–	Pack-A 1		
	CRE6-4-4/OY		4/0	150BKB	HCPK3A	–	Pack-A 1		

## Exothermic welding system

Cable to steel surface and pipe quick reference

—  
01 CS1  
See page 28

—  
02 CS2  
See page 28

—  
03 CS3  
See page 29

—  
04 CS4  
See page 31

—  
05 CS7  
See page 33

—  
06 CS8  
See page 35

—  
07 CS9  
See page 35













—  
08 CS25  
See page 36

—  
09 CS27  
See page 38

—  
10 CS31  
See page 40

—  
11 CS32  
See page 42

—  
12 CS34  
See page 43



—  
01—  
02—  
03—  
04—  
05—  
06—  
07—  
08—  
09—  
10—  
11—  
12

## Exothermic welding system

CS1 and CS2 cable to steel surface and pipe – For flat surfaces

- Stranded conductor
- Solid circular conductor



—  
CS1 cable to steel surface and pipe – For flat surfaces

Diagrams	Cat. no.	Wire size (A) AWG or kcmil	Welding powder size	Handle clamp type	Sleeve	Std. ctn.
	CS1-4-1/0	1/0	90BKB	HCPK4	–	1
	CS1-4-2/0	2/0	90BKB	HCPK4	–	1
	CS1-4-3/0	3/0	115BKB	HCPK4	–	1
	CS1-4-4/0	4/0	115BKB	HCPK4	–	1
	CS1-4-250K	250	115BKB	HCPK4	–	1
	CS1-4-300K	300	150BKB	HCPK4	–	1
	CS1-4-350K	350	200BKB	HCPK4	–	1
	CS1-4-500K	500	200BKB	HCPK4	–	1
	CS1-4-750K	750	2 x 150BKB	HCPK4	–	1
	CS1-4-1000K	1000	2 x 200BKB	HCPK4	–	1

Mold sealing compound (MSC) will be required if surface is uneven.

- Stranded conductor
- Solid circular conductor

—  
CS2 cable to steel surface and pipe – For flat surfaces

Diagrams	Cat. no.	Wire size (A) AWG or kcmil	Welding powder size	Handle clamp type	Sleeve	Std. ctn.
	CS2-4-1/0	1/0	90BKB	HCPK4	–	1
	CS2-4-2/0	2/0	115BKB	HCPK4	–	1
	CS2-4-3/0	3/0	115BKB	HCPK4	–	1
	CS2-4-4/0	4/0	150BKB	HCPK4	–	1
	CS2-4-250K	250	150BKB	HCPK4	–	1
	CS2-4-300K	300	200BKB	HCPK4	–	1
	CS2-4-350K	350	250BKB	HCPK4	–	1
	CS2-5-500K	500	2 x 150BKB	HCPK4	–	1


Mold sealing compound (MSC) will be required if surface is uneven.

## Exothermic welding system

CS3 cable to steel surface and pipe – For flat surfaces

- Stranded conductor
- Solid circular conductor

**CS3 cable to steel surface and pipe – For flat surfaces**

Diagram	Cat. no.	Wire size (A) AWG or kcmil	Welding powder size	Handle clamp type	Sleeve	Std. ctn.
	CS3-4-#6	#6	45BKB	HCPK4	Sleeve#6	1
	CS3-4-#4	#4	45BKB	HCPK4	–	1
	CS3-4-#2S	#2 solid	45BKB	HCPK4	–	1
	CS3-4-#2	#2	45BKB	HCPK4	–	1
	CS3-4-#1	#1	65BKB	HCPK4	–	1
	CS3-4-1/0	1/0	90BKB	HCPK4	–	1
	CS3-4-2/0	2/0	90BKB	HCPK4	–	1
	CS3-4-3/0	3/0	115BKB	HCPK4	–	1
	CS3-4-4/0	4/0	115BKB	HCPK4	–	1
	CS3-4-250K	250	115BKB	HCPK4	–	1
	CS3-4-300K	300	150BKB	HCPK4	–	1
	CS3-4-350K	350	200BKB	HCPK4	–	1
	CS3-4-500K	500	200BKB	HCPK4	–	1
	CS3-5-750K	750	2 X 150BKB	HCPK5	–	1
	CS3-5-1000K	1000	2 X 200BKB	HCPK5	–	1


Mold sealing compound (MSC) will be required if surface is uneven.

## Exothermic welding system

CS3 cable to steel surface and pipe – For pipes

- Stranded conductor
- Solid circular conductor

**CS3 cable to steel surface and pipe – For pipes**

Diagram	Cat. no.	Wire size (A) AWG or kcmil	Pipe size (B) in.	Welding powder size	Handle clamp type	Sleeve	Std. ctn.
	CS3-4-#4C	#4	1½ - 2¾	45BKB	HCPK4	-	1
	CS3-4-#4D		2¾ - 6½	45BKB	HCPK4	-	1
	CS3-4-#4F		6½ - 10	45BKB	HCPK4	-	1
	CS3-4-#4G		10 - 14	45BKB	HCPK4	-	1
	CS3-4-#2SC	#2 solid	1½ - 2¾	45BKB	HCPK4	-	1
	CS3-4-#2SD		2¾ - 6½	45BKB	HCPK4	-	1
	CS3-4-#2SF		6½ - 10	45BKB	HCPK4	-	1
	CS3-4-#2SG		10 - 14	45BKB	HCPK4	-	1
	CS3-4-#2C	#2	1½ - 2¾	45BKB	HCPK4	-	1
	CS3-4-#2D		2¾ - 6½	45BKB	HCPK4	-	1
	CS3-4-#2F		6½ - 10	45BKB	HCPK4	-	1
	CS3-4-#2G		10 - 14	45BKB	HCPK4	-	1
	CS3-4-#1C	#1	1½ - 2¾	65BKB	HCPK4	-	1
	CS3-4-#1D		2¾ - 6½	65BKB	HCPK4	-	1
	CS3-4-#1F		6½ - 10	65BKB	HCPK4	-	1
	CS3-4-#1G		10 - 14	65BKB	HCPK4	-	1
	CS3-4-#1/0C	1/0	1½ - 2¾	90BKB	HCPK4	-	1
	CS3-4-#1/0D		2¾ - 6½	90BKB	HCPK4	-	1
	CS3-4-#1/0F		6½ - 10	90BKB	HCPK4	-	1
	CS3-4-#1/0G		10 - 14	90BKB	HCPK4	-	1
	CS3-4-#2/0C	2/0	1½ - 2¾	90BKB	HCPK4	-	1
	CS3-4-#2/0D		2¾ - 6½	90BKB	HCPK4	-	1
	CS3-4-#2/0F		6½ - 10	90BKB	HCPK4	-	1
	CS3-4-#2/0G		10 - 14	90BKB	HCPK4	-	1
	CS3-4-#3/0C	3/0	1½ - 2¾	115BKB	HCPK4	-	1
	CS3-4-#3/0D		2¾ - 6½	115BKB	HCPK4	-	1
	CS3-4-#3/0F		6½ - 10	115BKB	HCPK4	-	1
	CS3-4-#3/0G		10 - 14	115BKB	HCPK4	-	1
	CS3-4-#4/0C	4/0	1½ - 2¾	115BKB	HCPK4	-	1
	CS3-4-#4/0D		2¾ - 6½	115BKB	HCPK4	-	1
	CS3-4-#4/0F		6½ - 10	115BKB	HCPK4	-	1
	CS3-4-#4/0G		10 - 14	115BKB	HCPK4	-	1

Over 14": use CS3 for flat surface.

Use mold sealing compound (MSC) to ensure effective sealing.


## Exothermic welding system

CS4 cable to steel surface and pipe – For flat surfaces

- Stranded conductor
- Solid circular conductor

**CS4 cable to steel surface and pipe – For flat surfaces**

Diagram	Cat. no.	Wire size (A) AWG or kcmil	Welding powder size	Handle clamp type	Sleeve	Std. ctn.
	CS4-4-#6	#6	90BKB	HCPK4	Sleeve #6	1
	CS4-4-#4	#4	90BKB	HCPK4	–	1
	CS4-4-#2S	#2 solid	115BKB	HCPK4	–	1
	CS4-4-#2	#2	115BKB	HCPK4	–	1
	CS4-4-#1	#1	115BKB	HCPK4	–	1
	CS4-5-1/0	1/0	200BKB	HCPK5	–	1
	CS4-5-2/0	2/0	200BKB	HCPK5	–	1
	CS4-5-3/0	3/0	250BKB	HCPK5	–	1
	CS4-5-4/0	4/0	250BKB	HCPK5	–	1
	CS4-5-250K	250	250BKB	HCPK5	–	1



Mold sealing compound (MSC) will be required if surface is uneven.

## Exothermic welding system

CS4 cable to steel surface and pipe – For pipes


- Stranded conductor
- Solid circular conductor

CS4 cable to steel surface and pipe – For pipes

Diagram	Cat. no.	Wire size (A) AWG or kcmil	Pipe size (B) in.	Welding powder size	Handle clamp type	Sleeve	Std. ctn.
	CS4-4-#4C	#4	1½ - 2¾	90BKB	HCPK4	–	1
	CS4-4-#4D		2¾ - 6½	90BKB	HCPK4	–	1
	CS4-4-#4F		6½ - 10	90BKB	HCPK4	–	1
	CS4-4-#4G		10 - 14	90BKB	HCPK4	–	1
	CS4-4-#2SC	#2 solid	1½ - 2¾	115BKB	HCPK4	–	1
	CS4-4-#2SD		2¾ - 6½	115BKB	HCPK4	–	1
	CS4-4-#2SF		6½ - 10	115BKB	HCPK4	–	1
	CS4-4-#2SG		10 - 14	115BKB	HCPK4	–	1
	CS4-4-#2C	#2	1½ - 2¾	115BKB	HCPK4	–	1
	CS4-4-#2D		2¾ - 6½	115BKB	HCPK4	–	1
	CS4-4-#2F		6½ - 10	115BKB	HCPK4	–	1
	CS4-4-#2G		10 - 14	115BKB	HCPK4	–	1
	CS4-4-#1C	#1	1½ - 2¾	115BKB	HCPK4	–	1
	CS4-4-#1D		2¾ - 6½	115BKB	HCPK4	–	1
	CS4-4-#1F		6½ - 10	115BKB	HCPK4	–	1
	CS4-4-#1G		10 - 14	115BKB	HCPK4	–	1
	CS4-5-1/0C	1/0	1½ - 2¾	200BKB	HCPK5	–	1
	CS4-5-1/0D		2¾ - 6½	200BKB	HCPK5	–	1
	CS4-5-1/0F		6½ - 10	200BKB	HCPK5	–	1
	CS4-5-1/0G		10 - 14	200BKB	HCPK5	–	1
	CS4-5-2/0C	2/0	1½ - 2¾	200BKB	HCPK5	–	1
	CS4-5-2/0D		2¾ - 6½	200BKB	HCPK5	–	1
	CS4-5-2/0F		6½ - 10	200BKB	HCPK5	–	1
	CS4-5-2/0G		10 - 14	200BKB	HCPK5	–	1
	CS4-5-3/0C	3/0	1½ - 2¾	250BKB	HCPK5	–	1
	CS4-5-3/0D		2¾ - 6½	250BKB	HCPK5	–	1
	CS4-5-3/0F		6½ - 10	250BKB	HCPK5	–	1
	CS4-5-3/0G		10 - 14	250BKB	HCPK5	–	1
	CS4-5-4/0C	4/0	1½ - 2¾	250BKB	HCPK5	–	1
	CS4-5-4/0D		2¾ - 6½	250BKB	HCPK5	–	1
	CS4-5-4/0F		6½ - 10	250BKB	HCPK5	–	1
	CS4-5-4/0G		10 - 14	250BKB	HCPK5	–	1

Over 14": use CS4 for flat surface.

Use mold sealing compound (MSC) – ensure effective sealing.



A

## Exothermic welding system


CS7 cable to steel surface and pipe – For flat surfaces

- Stranded conductor
- Solid circular conductor

**CS7 cable to steel surface and pipe – For flat surfaces**

Diagram	Cat. no.	Wire size (A) AWG or kcmil	Welding powder size	Handle clamp type	Sleeve	Std. ctn.
	CS7-4-#4	#4	65BKB	HCPK4	–	1
	CS7-4-#2S	#2 solid	65BKB	HCPK4	–	1
	CS7-4-#2	#2	65BKB	HCPK4	–	1
	CS7-4-#1	#1	90BKB	HCPK4	–	1
	CS7-4-1/0	1/0	90BKB	HCPK4	–	1
	CS7-4-2/0	2/0	150BKB	HCPK4	–	1
	CS7-5-3/0	3/0	200BKB	HCPK4	–	1
	CS7-5-4/0	4/0	200BKB	HCPK4	–	1
	CS7-5-250K	250	200BKB	HCPK4	–	1
	CS7-5-300K	300	250BKB	HCPK4	–	1
	CS7-6-350K	350	2 X 150BKB	HCPK5	–	1
	CS7-6-500K	500	2 X 200BKB	HCPK5	–	1

Use mold sealing compound (MSC) to ensure effective sealing.



## Exothermic welding system

CS7 cable to steel surface and pipe – For pipes


- Stranded conductor
- Solid circular conductor

CS7 cable to steel surface and pipe – For pipes

Diagram	Cat. no.	Wire size (A) AWG	Pipe size (B) in.	Welding powder size	Handle clamp type	Sleeve	Std. ctn.
	CS7-4-#4C	#4	1½ - 2¾	65BKB	HCPK4	–	1
	CS7-4-#4D		2¾ - 6½	65BKB	HCPK4	–	1
	CS7-4-#4F		6½ - 10	65BKB	HCPK4	–	1
	CS7-4-#4G		10 - 14	65BKB	HCPK4	–	1
	CS7-4-#2SC	#2 solid	1½ - 2¾	65BKB	HCPK4	–	1
	CS7-4-#2SD		2¾ - 6½	65BKB	HCPK4	–	1
	CS7-4-#2SF		6½ - 10	65BKB	HCPK4	–	1
	CS7-4-#2SG		10 - 14	65BKB	HCPK4	–	1
	CS7-4-#2C	#2	1½ - 2¾	65BKB	HCPK4	–	1
	CS7-4-#2D		2¾ - 6½	65BKB	HCPK4	–	1
	CS7-4-#2F		6½ - 10	65BKB	HCPK4	–	1
	CS7-4-#2G		10 - 14	65BKB	HCPK4	–	1
	CS7-4-#1C	#1	1½ - 2¾	90BKB	HCPK4	–	1
	CS7-4-#1D		2¾ - 6½	90BKB	HCPK4	–	1
	CS7-4-#1F		6½ - 10	90BKB	HCPK4	–	1
	CS7-4-#1G		10 - 14	90BKB	HCPK4	–	1
	CS7-4-1/0C	1/0	1½ - 2¾	90BKB	HCPK4	–	1
	CS7-4-1/0D		2¾ - 6½	90BKB	HCPK4	–	1
	CS7-4-1/0F		6½ - 10	90BKB	HCPK4	–	1
	CS7-4-1/0G		10 - 14	90BKB	HCPK4	–	1
	CS7-4-2/0C	2/0	1½ - 2¾	150BKB	HCPK4	–	1
	CS7-4-2/0D		2¾ - 6½	150BKB	HCPK4	–	1
	CS7-4-2/0F		6½ - 10	150BKB	HCPK4	–	1
	CS7-4-2/0G		10 - 14	150BKB	HCPK4	–	1
	CS7-5-3/0C	3/0	1½ - 2¾	200BKB	HCPK4	–	1
	CS7-5-3/0D		2¾ - 6½	200BKB	HCPK4	–	1
	CS7-5-3/0F		6½ - 10	200BKB	HCPK4	–	1
	CS7-5-3/0G		10 - 14	200BKB	HCPK4	–	1
	CS7-5-4/0C	4/0	1½ - 2¾	200BKB	HCPK4	–	1
	CS7-5-4/0D		2¾ - 6½	200BKB	HCPK4	–	1
	CS7-5-4/0F		6½ - 10	200BKB	HCPK4	–	1
	CS7-5-4/0G		10 - 14	200BKB	HCPK4	–	1

Over 14": use CS7 for flat surface.

Use mold sealing compound (MSC) to ensure effective sealing.





## Exothermic welding system

CS8 and CS9 cable to steel surface and pipe – For flat surfaces

- Stranded conductor
- Solid circular conductor

### CS8 cable to steel surface and pipe – For flat surfaces

	Cat. no.	Wire size (A) AWG	Welding powder size	Handle clamp type	Sleeve	Std. ctn.
Diagrams	CS8-2-#6	#6	45BKB	HCPK2	Sleeve #6	1
	CS8-2-#4	#4	45BKB	HCPK2	–	1
	CS8-2-#2S	#2 solid	45BKB	HCPK2	–	1
	CS8-2-#2	#2	45BKB	HCPK2	–	1
	CS8-2-#1	#1	65BKB	HCPK2	–	1





Use mold sealing compound (MSC) to ensure effective sealing.

- Stranded conductor
- Solid circular conductor

### CS9 cable to steel surface and pipe – For flat surfaces

	Cat. no.	Wire size (A) AWG	Welding Powder size	Handle clamp type	Sleeve	Std. ctn.
Diagrams	CS9-2-#6	#6	45BKB	HCPK2	Sleeve #6	1
	CS9-2-#4	#4	45BKB	HCPK2	–	1
	CS9-2-#2S	#2 solid	45BKB	HCPK2	–	1
	CS9-2-#2	#2	45BKB	HCPK2	–	1
	CS9-2-#1	#1	65BKB	HCPK2	–	1



Use mold sealing compound (MSC) to ensure effective sealing.


## Exothermic welding system

CS25 cable to steel surface and pipe – For flat surfaces

- Stranded conductor
- Solid circular conductor

**CS25 cable to steel surface and pipe – For flat surfaces**

Diagram	Cat. no.	Wire size (A) AWG or kcmil	Welding powder size	Handle clamp type	Sleeve	Std. ctn.
	CS25-4-#4	#4	65BKB	HCPK4	–	1
	CS25-4-#2S	#2 solid	65BKB	HCPK4	–	1
	CS25-4-#2	#2	65BKB	HCPK4	–	1
	CS25-4-#1	#1	90BKB	HCPK4	–	1
	CS25-4-1/0	1/0	115BKB	HCPK4	–	1
	CS25-4-2/0	2/0	115BKB	HCPK4	–	1
	CS25-4-3/0	3/0	150BKB	HCPK4	–	1
	CS25-4-4/0	4/0	150BKB	HCPK4	–	1
	CS25-4-250K	250	200BKB	HCPK4	–	1
	CS25-4-300K	300	200BKB	HCPK4	–	1
	CS25-4-350K	350	250BKB	HCPK4	–	1
	CS25-4-500K	500	250BKB	HCPK4	–	1



Use mold sealing compound (MSC) to ensure effective sealing.

## Exothermic welding system

CS25 cable to steel surface and pipe – For pipes


- Stranded conductor
- Solid circular conductor

CS25 cable to steel surface and pipe – For pipes

Diagram	Cat. no.	Wire size (A) AWG	Pipe size (B) in.	Welding powder size	Handle clamp type	Sleeve	Std. ctn
	CS25-4-#4C	#4	1½ – 2¾	65BKB	HCPK4	–	1
	CS25-4-#4D		2¾ – 6½	65BKB	HCPK4	–	1
	CS25-4-#4F		6½ – 10	65BKB	HCPK4	–	1
	CS25-4-#4G		10 – 14	65BKB	HCPK4	–	1
	CS25-4-#2SC	#2 solid	1½ – 2¾	65BKB	HCPK4	–	1
	CS25-4-#2SD		2¾ – 6½	65BKB	HCPK4	–	1
	CS25-4-#2SF		6½ – 10	65BKB	HCPK4	–	1
	CS25-4-#2SG		10 – 14	65BKB	HCPK4	–	1
	CS25-4-#2C	#2	1½ – 2¾	65BKB	HCPK4	–	1
	CS25-4-#2D		2¾ – 6½	65BKB	HCPK4	–	1
	CS25-4-#2F		6½ – 10	65BKB	HCPK4	–	1
	CS25-4-#2G		10 – 14	65BKB	HCPK4	–	1
	CS25-4-#1C	#1	1½ – 2¾	90BKB	HCPK4	–	1
	CS25-4-#1D		2¾ – 6½	90BKB	HCPK4	–	1
	CS25-4-#1F		6½ – 10	90BKB	HCPK4	–	1
	CS25-4-#1G		10 – 14	90BKB	HCPK4	–	1
	CS25-4-1/0C	1/0	1½ – 2¾	90BKB	HCPK4	–	1
	CS25-4-1/0D		2¾ – 6½	90BKB	HCPK4	–	1
	CS25-4-1/0F		6½ – 10	90BKB	HCPK4	–	1
	CS25-4-1/0G		10 – 14	90BKB	HCPK4	–	1
	CS25-4-2/0C	2/0	1½ – 2¾	150BKB	HCPK4	–	1
	CS25-4-2/0D		2¾ – 6½	150BKB	HCPK4	–	1
	CS25-4-2/0F		6½ – 10	150BKB	HCPK4	–	1
	CS25-4-2/0G		10 – 14	150BKB	HCPK4	–	1
	CS25-4-3/0C	3/0	1½ – 2¾	200BKB	HCPK4	–	1
	CS25-4-3/0D		2¾ – 6½	200BKB	HCPK4	–	1
	CS25-4-3/0F		6½ – 10	200BKB	HCPK4	–	1
	CS25-4-3/0G		10 – 14	200BKB	HCPK4	–	1
	CS25-4-4/0C	4/0	1½ – 2¾	200BKB	HCPK4	–	1
	CS25-4-4/0D		2¾ – 6½	200BKB	HCPK4	–	1
	CS25-4-4/0F		6½ – 10	200BKB	HCPK4	–	1
	CS25-4-4/0G		10 – 14	200BKB	HCPK4	–	1

Over 14": use CS7 for flat surface.

Use mold sealing compound (MSC) to ensure effective sealing.



## Exothermic welding system


CS27 cable to steel surface and pipe – For flat surfaces

- Stranded conductor
- Solid circular conductor

**CS27 cable to steel surface and pipe – For flat surfaces**

Diagram	Cat. no.	Wire size (A) AWG or kcmil	Welding powder size	Handle clamp type	Sleeve	Std. ctn.
	CS27-4-#6	#6	45BKB	HCPK4	Sleeve#6	1
	CS27-4-#4	#4	45BKB	HCPK4	-	1
	CS27-4-#2S	#2 solid	45BKB	HCPK4	-	1
	CS27-4-#2	#2	45BKB	HCPK4	-	1
	CS27-4-#1	#1	65BKB	HCPK4	-	1
	CS27-4-1/0	1/0	115BKB	HCPK4	-	1
	CS27-4-2/0	2/0	115BKB	HCPK4	-	1
	CS27-4-3/0	3/0	150BKB	HCPK4	-	1
	CS27-4-4/0	4/0	150BKB	HCPK4	-	1
	CS27-4-250K	250	150BKB	HCPK4	-	1

Use mold sealing compound (MSC) to ensure effective sealing.



## Exothermic welding system

CS27 cable to steel surface and pipe – For pipes

- Stranded conductor
- Solid circular conductor

CS27 cable to steel surface and pipe – For pipes

Diagram	Cat. no.	Wire size (A) AWG	Pipe size (B) in.	Welding powder size	Handle clamp type	Sleeve	Std. ctn
	CS27-4-#4C	#4	1½ – 2¾	45BKB	HCPK4	–	1
	CS27-4-#4D		2¾ – 6½	45BKB	HCPK4	–	1
	CS27-4-#4F		6½ – 10	45BKB	HCPK4	–	1
	CS27-4-#4G		10 – 14	45BKB	HCPK4	–	1
	CS27-4-#2SC	#2 solid	1½ – 2¾	45BKB	HCPK4	–	1
	CS27-4-#2SD		2¾ – 6½	45BKB	HCPK4	–	1
	CS27-4-#2SF		6½ – 10	45BKB	HCPK4	–	1
	CS27-4-#2SG		10 – 14	45BKB	HCPK4	–	1
	CS27-4-#2C	#2	1½ – 2¾	45BKB	HCPK4	–	1
	CS27-4-#2D		2¾ – 6½	45BKB	HCPK4	–	1
	CS27-4-#2F		6½ – 10	45BKB	HCPK4	–	1
	CS27-4-#2G		10 – 14	45BKB	HCPK4	–	1
	CS27-4-#1C	#1	1½ – 2¾	65BKB	HCPK4	–	1
	CS27-4-#1D		2¾ – 6½	65BKB	HCPK4	–	1
	CS27-4-#1F		6½ – 10	65BKB	HCPK4	–	1
	CS27-4-#1G		10 – 14	65BKB	HCPK4	–	1
	CS27-4-110C	1/0	1½ – 2¾	115BKB	HCPK4	–	1
	CS27-4-110D		2¾ – 6½	115BKB	HCPK4	–	1
	CS27-4-110F		6½ – 10	115BKB	HCPK4	–	1
	CS27-4-110G		10 – 14	115BKB	HCPK4	–	1
	CS27-4-210C	2/0	1½ – 2¾	115BKB	HCPK4	–	1
	CS27-4-210D		2¾ – 6½	115BKB	HCPK4	–	1
	CS27-4-210F		6½ – 10	115BKB	HCPK4	–	1
	CS27-4-210G		10 – 14	115BKB	HCPK4	–	1
	CS27-4-310C	3/0	1½ – 2¾	150BKB	HCPK4	–	1
	CS27-4-310D		2¾ – 6½	150BKB	HCPK4	–	1
	CS27-4-310F		6½ – 10	150BKB	HCPK4	–	1
	CS27-4-310G		10 – 14	150BKB	HCPK4	–	1
	CS27-4-410C	4/0	1½ – 2¾	150BKB	HCPK4	–	1
	CS27-4-410D		2¾ – 6½	150BKB	HCPK4	–	1
	CS27-4-410F		6½ – 10	150BKB	HCPK4	–	1
	CS27-4-410G		10 – 14	150BKB	HCPK4	–	1

Over 14": use CS7 for flat surface.


Use mold sealing compound (MSC) to ensure effective sealing.

## Exothermic welding system

CS31 cable to steel surface and pipe – For flat surfaces

- Stranded conductor
- Solid circular conductor

**CS31 cable to steel surface and pipe – For flat surfaces**

Diagram	Cat. no.	Wire size (A) AWG or kcmil	Welding powder size	Handle clamp type	Sleeve	Std. ctn.
	CS31-4-#6	#6	45BKB	HCPK4	Sleeve#6	1
	CS31-4-#4	#4	45BKB	HCPK4	-	1
	CS31-4-#2S	#2 solid	45BKB	HCPK4	-	1
	CS31-4-#2	#2	45BKB	HCPK4	-	1
	CS31-4-#1	#1	65BKB	HCPK4	-	1
	CS31-4-1/0	1/0	90BKB	HCPK4	-	1
	CS31-4-2/0	2/0	90BKB	HCPK4	-	1
	CS31-4-3/0	3/0	115BKB	HCPK4	-	1
	CS31-4-4/0	4/0	115BKB	HCPK4	-	1
	CS31-4-250K	250	115BKB	HCPK4	-	1
	CS31-4-300K	300	150BKB	HCPK4	-	1
	CS31-4-350K	350	200BKB	HCPK4	-	1
	CS31-4-500K	500	200BKB	HCPK4	-	1

Add "R" or "L" to denote wire exiting left or right. (Example: CS31-6-#6r for #6 wire exiting on the right.)

Use mold sealing compound (MSC) to ensure effective sealing.

## Exothermic welding system

CS31 cable to steel surface and pipe – For pipes

- Stranded conductor
- Solid circular conductor


CS31 cable to steel surface and pipe – For pipes

Diagram	Cat. no.	Wire size (A) AWG	Pipe size (B) in.	Welding powder size	Handle clamp type	Sleeve	Std. ctn.
	CS31-4-#4C	#4	1½ – 2¾	45BKB	HCPK4	–	1
	CS31-4-#4D		2¾ – 6½	45BKB	HCPK4	–	1
	CS31-4-#4F		6½ – 10	45BKB	HCPK4	–	1
	CS31-4-#4G		10 – 14	45BKB	HCPK4	–	1
	CS31-4-#2SC	#2 solid	1½ – 2¾	45BKB	HCPK4	–	1
	CS31-4-#2SD		2¾ – 6½	45BKB	HCPK4	–	1
	CS31-4-#2SF		6½ – 10	45BKB	HCPK4	–	1
	CS31-4-#2SG		10 – 14	45BKB	HCPK4	–	1
	CS31-4-#2C	#2	1½ – 2¾	45BKB	HCPK4	–	1
	CS31-4-#2D		2¾ – 6½	45BKB	HCPK4	–	1
	CS31-4-#2F		6½ – 10	45BKB	HCPK4	–	1
	CS31-4-#2G		10 – 14	45BKB	HCPK4	–	1
	CS31-4-#1C	#1	1½ – 2¾	65BKB	HCPK4	–	1
	CS31-4-#1D		2¾ – 6½	65BKB	HCPK4	–	1
	CS31-4-#1F		6½ – 10	65BKB	HCPK4	–	1
	CS31-4-#1G		10 – 14	65BKB	HCPK4	–	1
	CS31-4-1/0C	1/0	1½ – 2¾	90BKB	HCPK4	–	1
	CS31-4-1/0D		2¾ – 6½	90BKB	HCPK4	–	1
	CS31-4-1/0F		6½ – 10	90BKB	HCPK4	–	1
	CS31-4-1/0G		10 – 14	90BKB	HCPK4	–	1
	CS31-4-2/0C	2/0	1½ – 2¾	90BKB	HCPK4	–	1
	CS31-4-2/0D		2¾ – 6½	90BKB	HCPK4	–	1
	CS31-4-2/0F		6½ – 10	90BKB	HCPK4	–	1
	CS31-4-2/0G		10 – 14	90BKB	HCPK4	–	1
	CS31-4-3/0C	3/0	1½ – 2¾	115BKB	HCPK4	–	1
	CS31-4-3/0D		2¾" to 6½	115BKB	HCPK4	–	1
	CS31-4-3/0F		6½ – 10	115BKB	HCPK4	–	1
	CS31-4-3/0G		10 – 14	115BKB	HCPK4	–	1
	CS31-4-4/0C	4/0	1½ – 2¾	115BKB	HCPK4	–	1
	CS31-4-4/0D		2¾ – 6½	115BKB	HCPK4	–	1
	CS31-4-4/0F		6½ – 10	115BKB	HCPK4	–	1
	CS31-4-4/0G		10 – 14	115BKB	HCPK4	–	1

Over 14": use CS31 for flat surface.

Add "R" or "L" to denote wire exiting left or right. (Example: cs31-6-#6r for #6 wire exiting on the right.)

Use mold sealing compound (MSC) to ensure effective sealing.




## Exothermic welding system

CS32 cable to steel surface and pipe – For pipes

- Stranded conductor

**CS32 cable to steel surface and pipe – For pipes**

Diagram	Cat. no.	Wire size (A) AWG	Pipe size (B) in.	Welding powder size	Handle clamp type	Sleeve	Std. ctn.
	CS32-2-#4C	#4	1½ - 2¾	45BKB	HCPK2	–	1
	CS32-2-#4D		2¾ - 6½	45BKB	HCPK2	–	1
	CS32-2-#4F		6½ - 10	45BKB	HCPK2	–	1
	CS32-2-#4G		10 - 14	45BKB	HCPK2	–	1
	CS32-2-#2SC	#2 solid	1½ - 2¾	45BKB	HCPK2	–	1
	CS32-2-#2SD		2¾ - 6½	45BKB	HCPK2	–	1
	CS32-2-#2SF		6½ - 10	45BKB	HCPK2	–	1
	CS32-2-#2SG		10 - 14	45BKB	HCPK2	–	1
	CS32-2-#2C	#2	1½ - 2¾	45BKB	HCPK2	–	1
	CS32-2-#2D		2¾ - 6½	45BKB	HCPK2	–	1
	CS32-2-#2F		6½ - 10	45BKB	HCPK2	–	1
	CS32-2-#2G		10 - 14	45BKB	HCPK2	–	1
	CS32-2-#1D	#1	2¾ - 6½	65BKB	HCPK2	–	1
	CS32-2-#1F		6½ - 10	65BKB	HCPK2	–	1
	CS32-2-#1G		10 - 14	65BKB	HCPK2	–	1
<b>Over 14": use CS8 for flat surface.</b>							
	CS32-4-#1/OD	1/0	2¾ - 6½	90BKB	HCPK4	–	1
	CS32-4-#1/OF		6½ - 10	90BKB	HCPK4	–	1
	CS32-4-#1/OG		10 - 14	90BKB	HCPK4	–	1
	CS32-4-#2/OD	2/0	2¾ - 6½	90BKB	HCPK4	–	1
	CS32-4-#2/OF		6½ - 10	90BKB	HCPK4	–	1
	CS32-4-#2/OG		10 - 14	90BKB	HCPK4	–	1
	CS32-4-#3/OD	3/0	2¾ - 6½	90BKB	HCPK4	–	1
	CS32-4-#3/OF		6½ - 10	90BKB	HCPK4	–	1
	CS32-4-#3/OG		10 - 14	90BKB	HCPK4	–	1
	CS32-4-#4/OD	4/0	2¾ - 6½	90BKB	HCPK4	–	1
	CS32-4-#4/OF		6½ - 10	90BKB	HCPK4	–	1
	CS32-4-#4/OG		10 - 14	90BKB	HCPK4	–	1

Over 14": use CS1 for flat surface.

Add "R" or "L" to denote wire exiting left or right. (Example: CS31-6-#6R for #6 wire exiting on the right.)


Use mold sealing compound (MSC) to ensure effective sealing.

## Exothermic welding system

CS34 cable to steel surface and pipe – For pipes

- Stranded conductor

**CS34 cable to steel surface and pipe – For pipes**

Diagram	Cat. no.	Wire size (A) AWG	Pipe size (B) in.	Welding powder size	Handle clamp type	Sleeve	Std. ctn.
	CS34-2-#4C	#4	1½ – 2¾	45BKB	HCPK2	–	1
	CS34-2-#4D		2¾ – 6½	45BKB	HCPK2	–	1
	CS34-2-#4F		6½ – 10	45BKB	HCPK2	–	1
	CS34-2-#4G		10 – 14	45BKB	HCPK2	–	1
	CS34-2-#2SC	#2S	1½ – 2¾	45BKB	HCPK2	–	1
	CS34-2-#2SD		2¾ – 6½	45BKB	HCPK2	–	1
	CS34-2-#2SF		6½ – 10	45BKB	HCPK2	–	1
	CS34-2-#2SG		10 – 14	45BKB	HCPK2	–	1
	CS34-2-#2C	#2	1½ – 2¾	45BKB	HCPK2	–	1
	CS34-2-#2D		2¾ – 6½	45BKB	HCPK2	–	1
	CS34-2-#2F		6½ – 10	45BKB	HCPK2	–	1
	CS34-2-#2G		10 – 14	45BKB	HCPK2	–	1
	CS34-2-#1D	#1	2¾ – 6½	65BKB	HCPK2	–	1
	CS34-2-#1F		6½ – 10	65BKB	HCPK2	–	1
	CS34-2-#1G		10 – 14	65BKB	HCPK2	–	1
<b>Over 14": use CS8 for flat surface.</b>							
	CS34-4-#1/0D	1/0	2¾ – 6½	90BKB	HCPK4	–	1
	CS34-4-#1/0F		6½ – 10	90BKB	HCPK4	–	1
	CS34-4-#1/0G		10 – 14	90BKB	HCPK4	–	1
	CS34-4-#2/0D	2/0	2¾ – 6½	115BKB	HCPK4	–	1
	CS34-4-#2/0F		6½ – 10	115BKB	HCPK4	–	1
	CS34-4-#2/0G		10 – 14	115BKB	HCPK4	–	1
	CS34-4-#3/0D	3/0	2¾ – 6½	115BKB	HCPK4	–	1
	CS34-4-#3/0F		6½ – 10	115BKB	HCPK4	–	1
	CS34-4-#3/0G		10 – 14	115BKB	HCPK4	–	1
	CS34-4-#4/0D	4/0	2¾ – 6½	150BKB	HCPK4	–	1
	CS34-4-#4/0F		6½ – 10	150BKB	HCPK4	–	1
	CS34-4-#4/0G		10 – 14	150BKB	HCPK4	–	1

Over 14": use CS1 for flat surface

Use mold sealing compound (MSC) to ensure effective sealing.


## Exothermic welding system

### Cable to bar quick reference


—  
01 CB1  
See page 45

—  
02 CB4  
See page 46


—  
03 CB29  
See page 47



—  
01



—  
02




—  
03

## Exothermic welding system

CB1 cable to bar – For pipes

- Stranded conductor
- Solid circular conductor
- Rectangular tape or bar

**CB1 cable to bar – For pipes**

Diagrams	Cat. no.	Wire size (A) AWG or kcmil	Bar size (B) in.	Welding powder size	Handle clamp type	Sleeve	Std. ctn.
	CB1-4-#4181	#4	1/8 x 1	45BKB	HCPK4	–	1
	CB1-4-#2181	#2 solid	1/8 x 1	45BKB	HCPK4	–	1
	CB1-4-#2181	#2	1/8 x 1	45BKB	HCPK4	–	1
	CB1-4-#1181	#1	1/8 x 1	45BKB	HCPK4	–	1
	CB1-4-1/0181	1/0	1/8 x 1	45BKB	HCPK4	–	1
	CB1-4-1/03161		3/16 x 1	65BKB	HCPK4	–	1
	CB1-4-1/0141		1/4 x 1	65BKB	HCPK4	–	1
	CB1-4-2/0181	2/0	1/8 x 1	65BKB	HCPK4	–	1
	CB1-4-2/03161		3/16 x 1	65BKB	HCPK4	–	1
	CB1-4-2/0141		1/4 x 1	65BKB	HCPK4	–	1
	CB1-4-3/018	3/0	1/8 x 1	65BKB	HCPK4	–	1
	CB1-4-3/0161		3/16 x 1	90BKB	HCPK4	–	1
	CB1-4-3/0141		1/4 X 1	90BKB	HCPK4	–	1
	CB1-4-4/03161	4/0	3/16 x 1	90BKB	HCPK4	–	1
	CB1-4-4/0141		1/4 x 1	90BKB	HCPK4	–	1
	CB1-4-4/014112		1/4 x 1½	90BKB	HCPK4	–	1
	CB1-4-4/0142		1/4 x 2	90BKB	HCPK4	–	1
	CB1-4-4/0143		1/4 x 3	90BKB	HCPK4	–	1
	CB1-4-250K3161	250	3/16 x 1	90BKB	HCPK4	–	1
	CB1-4-250K141		1/4 x 1	90BKB	HCPK4	–	1
	CB1-4-250K14112		1/4 x 1½	90BKB	HCPK4	–	1
	CB1-4-250K142		1/4 x 2	90BKB	HCPK4	–	1
	CB1-4-250K143		1/4 x 3	90BKB	HCPK4	–	1
	CB1-4-300K141	300	1/4 x 1	90BKB	HCPK4	–	1
	CB1-4-300K14112		1/4 x 1½	90BKB	HCPK4	–	1
	CB1-4-300K142		1/4 x 2	90BKB	HCPK4	–	1
	CB1-4-300K143		1/4 x 3	90BKB	HCPK4	–	1
	CB1-4-350K141	350	1/4 x 1	115BKB	HCPK4	–	1
	CB1-4-350K14112		1/4 x 1½	115BKB	HCPK4	–	1
	CB1-4-350K142		1/4 x 2	115BKB	HCPK4	–	1
	CB1-4-350K143		1/4 x 3	115BKB	HCPK4	–	1
	CB1-4-500K14112	500	1/4 x 1½	200BKB	HCPK4	–	1
	CB1-4-500K142		1/4 x 2	200BKB	HCPK4	–	1
	CB1-4-500K143		1/4 x 3	200BKB	HCPK4	–	1
	CB1-4-500K38112		3/8 x 1½	200BKB	HCPK4	–	1
	CB1-5-750K142	750	1/4 x 2	2 x 150BKB	HCPK5	–	1
	CB1-5-750K143		1/4 x 3	2 x 150BKB	HCPK5	–	1
	CB1-5-750K38112		3/8 x 1½	2 x 150BKB	HCPK5	–	1
	CB1-5-750K382		3/8 x 2	2 x 150BKB	HCPK5	–	1
	CB1-5-750K383		3/8 x 3	2 x 150BKB	HCPK5	–	1
	CB1-5-1000K143	1000	1/4 x 3	2 x 200BKB	HCPK5	–	1
	CB1-5-1000K382		3/8 x 2	2 x 200BKB	HCPK5	–	1
	CB1-5-1000K383		3/8 x 3	2 x 200BKB	HCPK5	–	1
	CB1-5-1000K122		1/2 x 2	2 x 200BKB	HCPK5	–	1
	CB1-5-1000K123		1/2 x 3	2 x 200BKB	HCPK5	–	1

## Exothermic welding system

CB4 cable to bar – For flat surfaces

- Stranded conductor
- Solid circular conductor
- Rectangular tape or bar

**CB4 cable to bar – For flat surfaces**

Diagram	Cat. no.	Bar size (A) in.	Wire size (B) AWG or kcmil	Welding powder size	Handle clamp type	Sleeve	Std. ctn.
	CB4-4-#2S14112	1/4 x 1½ and wider	#2 solid	45BKB	HCPK4	–	1
	CB4-4-214112		#2	45BKB	HCPK4	–	1
	CB4-4-1/014112		1/0	90BKB	HCPK4	–	1
	CB4-4-2/014112		2/0	90BKB	HCPK4	–	1
	CB4-4-3/014112		3/0	90BKB	HCPK4	–	1
	CB4-4-4/014112		4/0	90BKB	HCPK4	–	1
	CB4-4-250K14112		250	115BKB	HCPK4	–	1
	CB4-4-300K14112		300	115BKB	HCPK4	–	1
	CB4-4-350K14112		350	150BKB	HCPK4	–	1
	CB4-4-500K14111		500	200BKB	HCPK4	–	1
	CB4-4-#2S38112	5/8 x 1½ and wider	#2 solid	65BKB	HCPK4	–	1
	CB4-4-#238112		#2	65BKB	HCPK4	–	1
	CB4-4-1/038112		1/0	90BKB	HCPK4	–	1
	CB4-4-2/038112		2/0	90BKB	HCPK4	–	1
	CB4-4-4/038112		4/0	115BKB	HCPK4	–	1
	CB4-4-250K38112		250	150BKB	HCPK4	–	1
	CB4-4-300K38112		300	150BKB	HCPK4	–	1
	CB4-4-350K38112		350	200BKB	HCPK4	–	1
	CB4-4-500K38112		500	250BKB	HCPK4	–	1
	CB4-5-750K38112		750	2 x 150BKB	HCPK5	–	1
	CB4-5-1000K38112		1000	2 x 200BKB	HCPK5	–	1
	CB4-4-#2S12112	1/2 x 1½ and wider	#2 solid	90BKB	HCPK4	–	1
	CB4-4-#212112		#2	90BKB	HCPK4	–	1
	CB4-4-1/012112		1/0	115BKB	HCPK4	–	1
	CB4-4-2/012112		2/0	115BKB	HCPK4	–	1
	CB4-4-3/012112		3/0	150BKB	HCPK4	–	1
	CB4-4-4/012112		4/0	150BKB	HCPK4	–	1
	CB4-4-250K12112		250	200BKB	HCPK4	–	1
	CB4-4-300K12112		300	200BKB	HCPK4	–	1
	CB4-4-350K12112		350	250BKB	HCPK4	–	1
	CB4-5-500K12112		500	2 x 150BKB	HCPK5	–	1
	CB4-5-750K12112		750	2 x 200BKB	HCPK5	–	1
	CB4-5-1000K12112		1000	2 x 250BKB	HCPK5	–	1

## Exothermic welding system

CB29 cable to bar – For flat surfaces

CB29 cable to bar – For flat surfaces


Diagram	Cat. no.	Bar Size (A) in.	Wire Size (B) AWG or kcmil	Welding Powder size	Handle clamp type	Sleeve	Std. ctn.
	CB29-9-#2S142	1/4 x 2 and wider	#2 solid	250BKB	HCPK4	–	1
	CB29-9-#2142		#2	250BKB	HCPK4	–	1
	CB29-10-#1142		#1	2 x 150BKB	HCPK5	–	1
	CB29-10-1/0142		1/0	2 x 200BKB	HCPK5	–	1
	CB29-10-2/0142		2/0	2 x 200BKB	HCPK5	–	1
	CB29-10-4/0142		4/0	2 x 250BKB	HCPK5	–	1
	CB29-10-250K142		250	2 x 250BKB	HCPK5	–	1
	CB29-10-500K142		500	2 x 250BKB	HCPK5	–	1
	CB29-10-750K142		750	3 x 200BKB	HCPK5	–	1
	CB29-9-#2S382	3/8 x 2 and wider	#2 solid	250BKB	HCPK4	–	1
	CB29-9-#2382		#2 solid	250BKB	HCPK4	–	1
	CB29-10-#1382		#1	2 x 150BKB	HCPK5	–	1
	CB29-10-1/0382		1/0	2 x 200BKB	HCPK5	–	1
	CB29-10-2/0382		2/0	2 x 200BKB	HCPK5	–	1
	CB29-10-4/0382		4/0	2 x 250BKB	HCPK5	–	1
	CB29-10-250K382		250	2 x 250BKB	HCPK5	–	1
	CB29-10-500K382		500	2 x 250BKB	HCPK5	–	1
	CB29-10-750K382		750	3 x 200BKB	HCPK5	–	1
	CB29-10-#2S122	1/2 x 2 and wider	#2 solid	2 x 150BKB	HCPK5	–	1
	CB29-10-#2122		#2	2 x 150BKB	HCPK5	–	1
	CB29-10-#1122		#1	2 x 200BKB	HCPK5	–	1
	CB29-10-1/0122		1/0	2 x 250BKB	HCPK5	–	1
	CB29-10-2/0122		2/0	2 x 250BKB	HCPK5	–	1
	CB29-10-4/0122		4/0	3 x 200BKB	HCPK5	–	1
	CB29-10-250K122		250	3 x 200BKB	HCPK5	–	1
	CB29-10-500K122		500	3 x 200BKB	HCPK5	–	1
	CB29-10-750K		750	3 x 250BKB	HCPK5	–	1

Use mold sealing compound (MSC) to ensure effective sealing.


## Exothermic welding system

### Bar to bar quick reference


- 01 BB1  
See page 49
- 02 BB2  
See page 50
- 03 BB3  
See page 51
- 04 BB7  
See page 52
- 05 BB14  
See page 53




01




02



03



04




05

## Exothermic welding system

BB1 bar to bar – For flat surfaces

### BB1 bar to bar – For flat surfaces

Diagram	Cat. no.	Bar size (A) in.	Welding powder size	Handle clamp type	Sleeve	Std. ctn.
	BB1-4-181	1/8 x 1	45BKB	HCPK4	–	1
	BB1-4-18112	1/8 x 1½	65BKB	HCPK4	–	1
	BB1-4-182	1/8 x 2	90BKB	HCPK4	–	1
	BB1-4-183	1/8 x 3	200BKB	HCPK4	–	1
	BB1-4-184	1/8 x 4	250BKB	HCPK4	–	1
	BB1-4-3161	3/16 x 1	65BKB	HCPK4	–	1
	BB1-4-3162	3/16 x 2	115BKB	HCPK4	–	1
	BB1-4-141	1/4 x 1	90BKB	HCPK4	–	1
	BB1-4-14114	1/4 x 1½	115BKB	HCPK4	–	1
	BB1-4-14112	1/4 x 2	150BKB	HCPK4	–	1
	BB1-4-142	1/4 x 2	200BKB	HCPK4	–	1
	BB1-4-14212	1/4 x 2½	250BKB	HCPK4	–	1
	BB1-5-143	1/4 x 3	2 x 200BKB	HCPK5	–	1
	BB1-5-144	1/4 x 4	2 x 250BKB	HCPK5	–	1
	BB1-4-381	3/8 x 1	150BKB	HCPK5	–	1
	BB1-4-38112	3/8 x 1½	250BKB	HCPK4	–	1
	BB1-5-382	3/8 x 2	2 x 150BKB	HCPK5	–	1
	BB1-5-383	3/8 x 3	2 x 250BKB	HCPK5	–	1
	BB1-5-384	3/8 x 4	3 x 200BKB	HCPK5	–	1
	BB1-4-121	1/2 x 1	200BKB	HCPK4	–	1
	BB1-5-122	1/2 x 2	2 x 200BKB	HCPK5	–	1




## Exothermic welding system

BB2 bar to bar – For flat surfaces

### BB2 bar to bar – For flat surfaces

Diagram	Cat. no.	Bar size (A) in.	Welding powder size	Handle clamp type	Sleeve	Std. ctn.
	BB2-4-181	$\frac{1}{8} \times 1$	45BKB	HCPK4	–	1
	BB2-4-18112	$\frac{1}{8} \times 1\frac{1}{2}$	65BKB	HCPK4	–	1
	BB2-4-182	$\frac{1}{8} \times 2$	90BKB	HCPK4	–	1
	BB2-4-183	$\frac{1}{8} \times 3$	200BKB	HCPK4	–	1
	BB2-4-184	$\frac{1}{8} \times 4$	250BKB	HCPK4	–	1
	BB2-4-3161	$\frac{3}{16} \times 1$	65BKB	HCPK4	–	1
	BB2-4-3162	$\frac{3}{16} \times 2$	115BKB	HCPK4	–	1
	BB2-4-141	$\frac{1}{4} \times 1$	90BKB	HCPK4	–	1
	BB2-4-14114	$\frac{1}{4} \times 1\frac{1}{4}$	115BKB	HCPK4	–	1
	BB2-4-14112	$\frac{1}{4} \times 1\frac{1}{2}$	150BKB	HCPK4	–	1
	BB2-4-142	$\frac{1}{4} \times 2$	200BKB	HCPK4	–	1
	BB2-4-14212	$\frac{1}{4} \times 2\frac{1}{2}$	250BKB	HCPK4	–	1
	BB2-5-143	$\frac{1}{4} \times 3$	2 x 200BKB	HCPK5	–	1
	BB2-5-144	$\frac{1}{4} \times 4$	2 x 250BKB	HCPK5	–	1
	BB2-4-381	$\frac{3}{8} \times 1$	150BKB	HCPK5	–	1
	BB2-4-38112	$\frac{3}{8} \times 1\frac{1}{2}$	250BKB	HCPK4	–	1
	BB2-5-382	$\frac{3}{8} \times 2$	2 x 150BKB	HCPK5	–	1
	BB2-5-383	$\frac{3}{8} \times 3$	2 x 250BKB	HCPK5	–	1
	BB2-5-384	$\frac{3}{8} \times 4$	3 x 200BKB	HCPK5	–	1
	BB2-4-121	$\frac{1}{2} \times 1$	200BKB	HCPK4	–	1
	BB2-5-122	$\frac{1}{2} \times 2$	2 x 200BKB	HCPK5	–	1




## Exothermic welding system

BB3 bar to bar – For flat surfaces

**BB3 bar to bar – For flat surfaces**

Diagram	Cat. no.	Bar size (A) in.	Welding powder size	Handle clamp type	Sleeve	Std. ctn.
	BB3-4-181	1/8 x 1	45BKB	HCPK4	–	1
	BB3-4-18112	1/8 x 1½	65BKB	HCPK4	–	1
	BB3-4-182	1/8 x 2	90BKB	HCPK4	–	1
	BB3-4-183	1/8 x 3	200BKB	HCPK4	–	1
	BB3-4-184	1/8 x 4	250BKB	HCPK4	–	1
	BB3-4-3161	3/16 x 1	65BKB	HCPK4	–	1
	BB3-4-3162	3/16 x 2	115BKB	HCPK4	–	1
	BB3-4-141	1/4 x 1	90BKB	HCPK4	–	1
	BB3-4-14114	1/4 x 1¼	115BKB	HCPK4	–	1
	BB3-4-14112	1/4 x 1½	150BKB	HCPK4	–	1
	BB3-4-142	1/4 x 2	200BKB	HCPK4	–	1
	BB3-4-14212	1/4 x 2½	250BKB	HCPK4	–	1
	BB3-5-143	1/4 x 3	2 x 200BKB	HCPK5	–	1
	BB3-5-144	1/4 x 4	2 x 250BKB	HCPK5	–	1
	BB3-4-381	3/8 x 1	150BKB	HCPK5	–	1
	BB3-4-38112	3/8 x 1½	250BKB	HCPK4	–	1
	BB3-5-382	3/8 x 2	2 x 150BKB	HCPK5	–	1
	BB3-5-383	3/8 x 3	2 x 250BKB	HCPK5	–	1
	BB3-5-384	3/8 x 4	3 x 200BKB	HCPK5	–	1
	BB3-4-121	1/2 x 1	200BKB	HCPK4	–	1
	BB3-5-122	1/2 x 2	2 x 200BKB	HCPK5	–	1




## Exothermic welding system

BB7 bar to bar – For flat surfaces

### BB7 bar to bar – For flat surfaces

Diagram	Cat. no.	Bar size (A) in.	Welding powder size	Handle clamp type	Sleeve	Std. ctn.
	BB7-4-181	$\frac{1}{8} \times 1$	45BKB	HCPK4	–	1
	BB7-4-18112	$\frac{1}{8} \times 1\frac{1}{2}$	65BKB	HCPK4	–	1
	BB7-4-182	$\frac{1}{8} \times 2$	90BKB	HCPK4	–	1
	BB7-4-183	$\frac{1}{8} \times 3$	200BKB	HCPK4	–	1
	BB7-4-184	$\frac{1}{8} \times 4$	250BKB	HCPK4	–	1
	BB7-4-3161	$\frac{3}{16} \times 1$	65BKB	HCPK4	–	1
	BB7-4-3162	$\frac{3}{16} \times 2$	115BKB	HCPK4	–	1
	BB7-4-141	$\frac{1}{4} \times 1$	90BKB	HCPK4	–	1
	BB7-4-14114	$\frac{1}{4} \times 1\frac{1}{4}$	115BKB	HCPK4	–	1
	BB7-4-14112	$\frac{1}{4} \times 1\frac{1}{2}$	150BKB	HCPK4	–	1
	BB7-4-142	$\frac{1}{4} \times 2$	200BKB	HCPK4	–	1
	BB7-4-14212	$\frac{1}{4} \times 2\frac{1}{2}$	250BKB	HCPK4	–	1
	BB7-5-143	$\frac{1}{4} \times 3$	2 x 200BKB	HCPK5	–	1
	BB7-5-144	$\frac{1}{4} \times 4$	2 x 250BKB	HCPK5	–	1
	BB7-4-381	$\frac{3}{8} \times 1$	150BKB	HCPK5	–	1
	BB7-4-38112	$\frac{3}{8} \times 1\frac{1}{2}$	250BKB	HCPK4	–	1
	BB7-5-382	$\frac{3}{8} \times 2$	2 x 150BKB	HCPK5	–	1
	BB7-5-383	$\frac{3}{8} \times 3$	2 x 250BKB	HCPK5	–	1
	BB7-5-384	$\frac{3}{8} \times 4$	3 x 200BKB	HCPK5	–	1
	BB7-4-121	$\frac{1}{2} \times 1$	200BKB	HCPK4	–	1
	BB7-5-122	$\frac{1}{2} \times 2$	2 x 200BKB	HCPK5	–	1




## Exothermic welding system

BB14 bar to bar – For flat surfaces

**BB14 bar to bar – For flat surfaces**

Diagram	Cat. no.	Bar size (A) in.	Welding powder size	Handle clamp type	Sleeve	Std. ctn.
	BB14-4-181	$\frac{1}{8} \times 1$	45BKB	HCPK4	–	1
	BB14-4-18112	$\frac{1}{8} \times 1\frac{1}{2}$	65BKB	HCPK4	–	1
	BB14-4-182	$\frac{1}{8} \times 2$	90BKB	HCPK4	–	1
	BB14-4-183	$\frac{1}{8} \times 3$	200BKB	HCPK4	–	1
	BB14-4-184	$\frac{1}{8} \times 4$	250BKB	HCPK4	–	1
	BB14-4-3161	$\frac{3}{16} \times 1$	65BKB	HCPK4	–	1
	BB14-4-3162	$\frac{3}{16} \times 2$	115BKB	HCPK4	–	1
	BB14-4-141	$\frac{1}{4} \times 1$	90BKB	HCPK4	–	1
	BB14-4-14114	$\frac{1}{4} \times 1\frac{1}{4}$	115BKB	HCPK4	–	1
	BB14-4-14112	$\frac{1}{4} \times 1\frac{1}{2}$	150BKB	HCPK4	–	1
	BB14-4-142	$\frac{1}{4} \times 2$	200BKB	HCPK4	–	1
	BB14-4-14212	$\frac{1}{4} \times 2\frac{1}{2}$	250BKB	HCPK4	–	1
	BB14-5-143	$\frac{1}{4} \times 3$	2 x 200BKB	HCPK5	–	1
	BB14-5-144	$\frac{1}{4} \times 4$	2 x 250BKB	HCPK5	–	1
	BB14-4-381	$\frac{3}{8} \times 1$	150BKB	HCPK5	–	1
	BB14-4-38112	$\frac{3}{8} \times 1\frac{1}{2}$	250BKB	HCPK4	–	1
	BB14-5-382	$\frac{3}{8} \times 2$	2 x 150BKB	HCPK5	–	1
	BB14-5-383	$\frac{3}{8} \times 3$	2 x 250BKB	HCPK5	–	1
	BB14-5-384	$\frac{3}{8} \times 4$	3 x 200BKB	HCPK5	–	1
	BB14-4-121	$\frac{1}{2} \times 1$	200BKB	HCPK4	–	1
	BB14-5-122	$\frac{1}{2} \times 2$	2 x 200BKB	HCPK5	–	1



## Exothermic welding system

### Bar to steel surface quick reference


—  
01 BS1  
See page 55

—  
02 BS2  
See page 55


—  
03 BS3  
See page 56

—  
04 BS4  
See page 56


—  
05 BS5  
See page 57




—  
01




—  
02



—  
03



—  
04



—  
05

## Exothermic welding system

BS1 and BS2 bar to steel surface – For flat surfaces

- Rectangular tape or bar

### BS1 bar to steel surface – For flat surfaces

	Cat. no.	Bar size (A) in.	Welding powder size	Handle clamp type	Sleeve	Std. ctn.
Diagrams	BS1-4-181	$\frac{1}{8} \times 1$	115BKB	HCPK4	4	1
	BS1-4-18112	$\frac{1}{8} \times 1\frac{1}{2}$	150BKB	HCPK4	4	1
	BS1-4-182	$\frac{1}{8} \times 2$	200BKB	HCPK4	4	1
	BS1-4-3161	$\frac{3}{16} \times 1$	150BKB	HCPK4	4	1
	BS1-4-316112	$\frac{3}{16} \times 1\frac{1}{2}$	200BKB	HCPK4	4	1
	BS1-4-3162	$\frac{3}{16} \times 2$	250BKB	HCPK4	4	1
	BS1-4-141	$\frac{1}{4} \times 1$	150BKB	HCPK4	4	1
	BS1-4-14114	$\frac{1}{4} \times 1\frac{1}{4}$	200BKB	HCPK4	4	1
	BS1-4-14112	$\frac{1}{4} \times 1\frac{1}{2}$	250BKB	HCPK4	4	1
	BS1-5-142	$\frac{1}{4} \times 2$	2 x 150BKB	HCPK4	4	1
	BS1-4-381	$\frac{3}{8} \times 1$	200BKB	HCPK5	4	1
	BS1-4-38112	$\frac{3}{8} \times 1\frac{1}{2}$	250BKB	HCPK4	4	1
	BS1-5-382	$\frac{3}{8} \times 2$	2 x 200BKB	HCPK5	5	1
	BS1-4-121	$\frac{1}{2} \times 1$	250BKB	HCPK4	4	1
	BS1-5-12112	$\frac{1}{2} \times 1\frac{1}{2}$	2 x 200BKB	HCPK5	5	1
	BS1-5-122	$\frac{1}{2} \times 2$	2 x 250BKB	HCPK5	5	1

Mold sealing compound (MSC) will be required if surface is uneven.

### BS2 bar to steel surface – For flat surfaces

	Cat. no.	Bar size (A) in.	Welding powder size	Handle clamp type	Sleeve	Std. ctn.
Diagram	BS2-4-181	$\frac{1}{8} \times 1$	115BKB	HCPK4	-	1
	BS2-4-18112	$\frac{1}{8} \times 1\frac{1}{2}$	150BKB	HCPK4	-	1
	BS2-4-182	$\frac{1}{8} \times 2$	200BKB	HCPK4	-	1
	BS2-4-3161	$\frac{3}{16} \times 1$	150BKB	HCPK4	-	1
	BS2-4-316112	$\frac{3}{16} \times 1\frac{1}{2}$	200BKB	HCPK4	-	1
	BS2-4-3162	$\frac{3}{16} \times 2$	250BKB	HCPK4	-	1
	BS2-4-141	$\frac{1}{4} \times 1$	150BKB	HCPK4	-	1
	BS2-4-14114	$\frac{1}{4} \times 1\frac{1}{4}$	200BKB	HCPK4	-	1
	BS2-4-14112	$\frac{1}{4} \times 1\frac{1}{2}$	250BKB	HCPK4	-	1
	BS2-5-142	$\frac{1}{4} \times 2$	2 X 150BKB	HCPK4	-	1
	BS2-4-381	$\frac{3}{8} \times 1$	200BKB	HCPK5	-	1
	BS2-4-38112	$\frac{3}{8} \times 1\frac{1}{2}$	250BKB	HCPK4	-	1
	BS2-5-382	$\frac{3}{8} \times 2$	2 X 200BKB	HCPK5	-	1
	BS2-4-121	$\frac{1}{2} \times 1$	250BKB	HCPK4	-	1
	BS2-5-12112	$\frac{1}{2} \times 1\frac{1}{2}$	2 X 200BKB	HCPK5	-	1
	BS2-5-122	$\frac{1}{2} \times 2$	2 X 250BKB	HCPK5	-	1

Mold sealing compound (MSC) will be required if surface is uneven.

## Exothermic welding system

BS3 and BS4 bar to steel surface – For flat surfaces

- Rectangular tape or bar

### BS3 bar to steel surface – For flat surfaces

Diagram	Cat. no.	Bar size (A) in.	Welding powder size	Handle clamp type	Sleeve	Std. ctn.
	BS3-4-181	$\frac{1}{8} \times 1$	115BKB	HCPK4	–	1
	BS3-4-18112	$\frac{1}{8} \times 1\frac{1}{2}$ and wider	150BKB	HCPK4	–	1
	BS3-4-3161	$\frac{3}{16} \times 1$	150BKB	HCPK4	–	1
	BS3-4-316112	$\frac{3}{16} \times 1\frac{1}{2}$ and wider	200BKB	HCPK4	–	1
	BS3-4-141	$\frac{1}{4} \times 1$	150BKB	HCPK4	–	1
	BS3-4-14114	$\frac{1}{4} \times 1\frac{1}{4}$	200BKB	HCPK4	–	1
	BS3-4-14112	$\frac{1}{4} \times 1\frac{1}{2}$ and wider	250BKB	HCPK4	–	1
	BS3-4-381	$\frac{3}{8} \times 1$	200BKB	HCPK5	–	1
	BS3-4-38112	$\frac{3}{8} \times 1\frac{1}{2}$ and wider	250BKB	HCPK4	–	1
	BS3-4-121	$\frac{1}{2} \times 1$	250BKB	HCPK4	–	1
	BS3-5-12112	$\frac{1}{2} \times 1\frac{1}{2}$ and wider	2 x 200BKB	HCPK5	–	1

Mold sealing compound (MSC) will be required if surface is uneven.

- Rectangular tape or bar

### BS4 bar to steel surface – For flat surfaces

Diagram	Cat. no.	Bar size (A) in.	Welding powder size	Handle clamp type	Sleeve	Std. ctn.
	BS4-4-181	$\frac{1}{8} \times 1$	115BKB	HCPK4	–	1
	BS4-4-18112	$\frac{1}{8} \times 1\frac{1}{2}$	150BKB	HCPK4	–	1
	BS4-4-182	$\frac{1}{8} \times 2$	200BKB	HCPK4	–	1
	BS4-4-3161	$\frac{3}{16} \times 1$	150BKB	HCPK4	–	1
	BS4-4-316112	$\frac{3}{16} \times 1\frac{1}{2}$	200BKB	HCPK4	–	1
	BS4-4-3162	$\frac{3}{16} \times 2$	250BKB	HCPK4	–	1
	BS4-4-141	$\frac{1}{4} \times 1$	150BKB	HCPK4	–	1
	BS4-4-14114	$\frac{1}{4} \times 1\frac{1}{4}$	200BKB	HCPK4	–	1
	BS4-4-14112	$\frac{1}{4} \times 1\frac{1}{2}$	250BKB	HCPK4	–	1
	BS4-5-142	$\frac{1}{4} \times 2$	2 x 150BKB	HCPK4	–	1
	BS4-4-381	$\frac{3}{8} \times 1$	200BKB	HCPK5	–	1
	BS4-4-38112	$\frac{3}{8} \times 1\frac{1}{2}$	250BKB	HCPK4	–	1
	BS4-5-382	$\frac{3}{8} \times 2$	2 x 200BKB	HCPK5	–	1
	BS4-4-121	$\frac{1}{2} \times 1$	250BKB	HCPK4	–	1
	BS4-5-12112	$\frac{1}{2} \times 1\frac{1}{2}$	2 x 200BKB	HCPK5	–	1
	BS4-5-122	$\frac{1}{2} \times 2$	2 x 250BKB	HCPK5	–	1

Mold sealing compound (MSC) will be required if surface is uneven.


## Exothermic welding system

BS5 bar to steel surface – For flat surfaces

### BS5 bar to steel surface – For flat surfaces

Diagram	Cat. no.	Bar size (A) in.	Welding powder size	Handle clamp type	Sleeve	Std. ctn.
	BS5-4-181	$\frac{1}{8} \times 1$	115BKB	HCPK4	–	1
	BS5-4-18112	$\frac{1}{8} \times 1\frac{1}{2}$	150BKB	HCPK4	–	1
	BS5-4-182	$\frac{1}{8} \times 2$ and wider	200BKB	HCPK4	–	1
	BS5-4-3161	$\frac{3}{16} \times 1$	150BKB	HCPK4	–	1
	BS5-4-316112	$\frac{3}{16} \times 1\frac{1}{2}$	200BKB	HCPK4	–	1
	BS5-4-3162	$\frac{3}{16} \times 2$ and wider	250BKB	HCPK4	–	1
	BS5-4-141	$\frac{1}{4} \times 1$	150BKB	HCPK4	–	1
	BS5-4-14114	$\frac{1}{4} \times 1\frac{1}{4}$	200BKB	HCPK4	–	1
	BS5-4-14112	$\frac{1}{4} \times 1\frac{1}{2}$	250BKB	HCPK4	–	1
	BS5-5-142	$\frac{1}{4} \times 2$ and wider	2 x 150BKB	HCPK5	–	1
	BS5-4-381	$\frac{3}{8} \times 1$	200BKB	HCPK5	–	1
	BS5-4-38112	$\frac{3}{8} \times 1\frac{1}{2}$	250BKB	HCPK4	–	1
	BS5-5-382	$\frac{3}{8} \times 2$ and wider	2 x 200BKB	HCPK5	–	1
	BS5-4-121	$\frac{1}{2} \times 1$	250BKB	HCPK4	–	1
	BS5-5-12112	$\frac{1}{2} \times 1\frac{1}{2}$	2 x 200BKB	HCPK5	–	1
	BS5-5-122	$\frac{1}{2} \times 2$ and wider	2 x 250BKB	HCPK5	–	1

Mold sealing compound (MSC) will be required if surface is uneven.




## Exothermic welding system

### Tools and accessories

#### Tools and accessories

Cat. no.	Description	Applications	Std. ctn.
WWB1	Cable cleaning brush	Cleaning of stranded and other circular section conductors	6
WRB1	Replacement elements (pair)	—	3
BFC	Card cloth brush	Cleaning of conductors and surfaces	10
FGUN	Flint igniter gun	Starting powder ignition	10
BCM	Mold cleaning brush	Soft brush for mold cleaning	10
STM1-TB	Mold scraper tool	Break up and removal of slag in mold crucible	10
MSC	Mold sealing compound	Mold sealing on uneven surfaces, and general mold sealing	5
PACK-A	Packing	Mold sealing on rebar surfaces	50
SLEEVE#6	Sleeve for #6 wire	Prevents burning of small section wire	100
SLEEVE#6S	Sleeve for #6S wire	Prevents burning of small section wire	100
SLEEVE#8	Sleeve for #8 wire	Prevents burning of small section wire	100
SLEEVE#8S	Sleeve for #8s wire	Prevents burning of small section wire	100
SHIM	Copper shim	For sealing around undersize conductors	100

#### Diagrams



STM1-TB

FGUN

BFC

BCM


## Exothermic welding system

### Handle clamps


#### Handle clamps

Cat. no.	Description	Applications	Std. ctn.
HCPK1	Price key 1 handle	For use on price key 1 molds	1
HCPK2	Price key 2 handle	For use on price key 2 molds	1
HCPK3	Price key 3 handle clamp	For use on price key 3 molds	1
HCPK3A	Price key 3A handle clamp	Type 3A molds (connections to vertical rebars)	1
HCPK3B	Price key 3B handle clamp	Type 3B molds (connections to horizontal rebars)	1
HCPK3BMOD	Price key3B modified clamp	Type 3B molds (cross connections to horizontal rebars)	1
HCPK4	Price key 4 handle clamp	For use on price key 4 molds	1
HCPK5	Price key 5 handle clamp	For use on price key 5 molds	1
HCPK7	Price key 7 handle clamp	For use on price key 7 molds	1
HCPK8	Price key 8 handle clamp	For use on price key 8 molds	1
FRAME1	Price key 9 frame	For use with HCPK4 on price key 9 molds	1
FRAME2	Price key 10 frame	For use with HCPK5 on price key 10 molds	1


#### Diagrams




HCPK3



HCPK4



HCPK2



Frame 1

# Exothermic welding system

## Sure Shot® welding mold for conductor to copper ground rod

Quick, easy and disposable – no maintenance required!

- Fast and simple to use
- Maintenance-free disposable molds
- Packaged with everything necessary to make a connection
- Biodegradable ceramic mold can be left underground
- Ergonomic hexagonal shape allows easy handling, even with gloves

For the ultimate in speedy, convenient connections, try the Sure Shot Welding Mold, an extension of the Blackburn® line of exothermic welding products.




Sure Shot molds come packaged with all of the components you need to make a connection. The mold's hexagonal shape makes it easy to pick up and hold without removing your safety gloves and also ensures that it won't roll away while you're preparing the connection.

To make a connection, simply position the Sure Shot mold, add the weld powder and starting powder and ignite with a flint gun. It's that easy.

Since Sure Shot molds are disposable, there's no need to clean them after use. In fact, you don't even have to remove the molds from underground installations, because they're made of "earth-friendly" biodegradable ceramic.



### Dimensions



## Exothermic welding system

### Wire positioning

#### Wire positioning




	Cat. no.	Ground rod size (in.)	Solid	Conductor size (AWG)
	Blackburn® Type SCR1			
Diagram SCR1	SCR1-58-6808	5/8	6, 8	8
	SCR1-58-3446	5/8	3, 4	4, 6
	SCR1-58-1223	5/8	1, 2	2, 3
	SCR1-58-2010	5/8	2/0, 1/0	1/0, 1
	SCR1-58-0020	5/8	-	2/0
	SCR1-34-6808	3/4	6, 8	8
	SCR1-34-3446	3/4	3, 4	4, 6
	SCR1-34-1223	3/4	1, 2	2, 3
	SCR1-34-2010	3/4	2/0, 1/0	1/0, 1
	SCR1-34-0020	3/4	-	2/0
	SCR1-34-0040	3/4	-	4/0
	Blackburn Type SCR2			
Diagram SCR2	SCR2-58-6808	5/8	6, 8	8
	SCR2-58-3446	5/8	3, 4	4, 6
	SCR2-58-1223	5/8	1, 2	2, 3
	SCR2-58-2010	5/8	2/0, 1/0	1/0, 1
	SCR2-58-0020	5/8	-	2/0
	SCR2-34-6808	3/4	6, 8	8
	SCR2-34-3446	3/4	3, 4	4, 6
	SCR2-34-1223	3/4	1, 2	2, 3
	SCR2-34-2010	3/4	2/0, 1/0	1/0, 1
	SCR2-34-0020	3/4	-	2/0
	SCR2-34-0040	3/4	-	4/0
	Blackburn Type SCR17			
Diagram SCR17	SCR17-58-6808	5/8	6, 8	8
	SCR17-58-3446	5/8	3, 4	4, 6
	SCR17-58-1223	5/8	1, 2	2, 3
	SCR17-34-6808	3/4	6, 8	8
	SCR17-34-3446	3/4	3, 4	4, 6
	SCR17-34-1223	3/4	1, 2	2, 3

\* The weight per 100 is 20 lbs. And the standard carton/outer pack is six for all catalog numbers.

## Exothermic welding system

### Wire positioning (continued)

#### Wire positioning

	Cat. no.	Ground rod size (in.)	Solid	Conductor size (AWG)
	Blackburn® Type SCR24			
<b>Diagram</b>	SCR24-58-6808	5/8	6, 8	8
	SCR24-58-3446	5/8	3, 4	4, 6
SCR24	SCR24-58-1223	5/8	1, 2	2, 3
	SCR24-34-6808	3/4	6, 8	8
	SCR24-34-3446	3/4	3, 4	4, 6
	SCR24-34-1223	3/4	1, 2	2, 3
	Blackburn Type SCR25			
<b>Diagram</b>	SCR25-58-6808	5/8	6, 8	8
	SCR25-58-3446	5/8	3, 4	4, 6
SCR25	SCR25-58-1223	5/8	1, 2	2, 3
	SCR25-34-6808	3/4	6, 8	8
	SCR25-34-3446	3/4	3, 4	4, 6
	SCR25-34-1223	3/4	1, 2	2, 3
	Blackburn Type SCR27			
<b>Diagram</b>	SCR27-58-6808	5/8	6, 8	8
	SCR27-58-3446	5/8	3, 4	4, 6
SCR27	SCR27-34-6808	3/4	6, 8	8
	SCR27-34-3446	3/4	3, 4	4, 6
	SCR27-34-1223	3/4	1, 2	2, 3

\* The weight per 100 is 20 lbs. And the standard carton/outer pack is six for all catalog numbers.

## Exothermic welding system

### Cross reference

Cadweld cat. no.	Thermoweld cat. no.	Blackburn cat. no.
BAC-JE	M-1135	BB1-4-121
BAC-EE	M-1122	BB1-4-141
BAC-EG	M-1124	BB1-4-14112
BAC-EF	M-1123	BB1-4-14114
BAC-EH	M-1125	BB1-4-142
BAC-EJ	M-6346	BB1-4-14212
BAC-CE	M-1118	BB1-4-181
BAC-CG	M-2557	BB1-4-18112
BAC-CH	M-1119	BB1-4-182
BAC-CK	M-6298	BB1-4-183
BAD-CM	M-5315	BB1-4-184
BAC-DE	M-1120	BB1-4-3161
BAC-DH	M-1121	BB1-4-3162
BAC-GE	M-1130	BB1-4-381
BAC-GG	M-1131	BB1-4-38112
BAD-JH	M-1136	BB1-5-122
BAD-EK	M-1126	BB1-5-143
BAD-EM	M-1127	BB1-5-144
BAD-GH	M-1132	BB1-5-382
BAD-GK	M-1133	BB1-5-38
BAD-GM	M-1134	BB1-5-384
EPC-JE	M-1247	BB2-4-121
EPC-EE	M-1234	BB2-4-141
EPC-EG	M-1236	BB2-4-14112
EPC-EF	M-1235	BB2-4-14114
EPC-EH	M-1237	BB2-4-142
EPC-EJ	M-6352	BB2-4-14212
EPC-CE	M-1230	BB2-4-181
EPC-CG	M-6347	BB2-4-18112
EPC-CH	M-1231	BB2-4-182
EPC-CK	M-6348	BB2-4-183
EPD-CM	M-6351	BB2-4-184
EPC-DE	M-1232	BB2-4-3161
EPC-DH	M-1233	BB2-4-3162
EPC-GE	M-1242	BB2-4-381
EPC-GG	M-1243	BB2-4-38112
EPD-JH	M-1248	BB2-5-122
EPD-EK	M-1238	BB2-5-143
EPD-EM	M-1239	BB2-5-144
EPD-GH	M-1244	BB2-5-382
EPD-GK	M-1245	BB2-5-383
EPD-GM	M-1246	BB2-5-384
BQC-EEEE	M-1102	BB3-4-141
BQC-EGEG	M-1104	BB3-4-14112
BQC-EFEF	M-1103	BB3-4-14114
BQC-CECE	M-1098	BB3-4-181
BQC-CHCH	M-1099	BB3-4-182
BQC-DEDE	M-1100	BB3-4-3161
BQC-DHDH	M-1101	BB3-4-3162
BQC-GEGE	M-1108	BB3-4-381
BQD-JEJE	M-1113	BB3-5-121

Cadweld cat. no.	Thermoweld cat. no.	Blackburn cat. no.
BQD-JHJH	M-1114	BB3-5-122
BQD-EHEH	M-1105	BB3-5-142
BQD-GGGG	M-1109	BB3-5-38112
BQD-GHGH	M-1110	BB3-5-382
BQF-EKEK	M-1106	BB3-6-143
BQF-GKGK	M-1111	BB3-6-383
BWC-JE	M-1051	BS1-4-121
BWC-EE	M-1045	BS1-4-141
BWC-EG	M-1047	BS1-4-14112
BWC-EF	M-1046	BS1-4-14114
BWC-CE	M-1043	BS1-4-181
BWC-CG	M-6354	BS1-4-18112
BWC-CH	M-1044	BS1-4-182
BWC-DE	M-6056	BS1-4-3161
BWC-DG	M-6355	BS1-4-316112
BWC-DH	M-6356	BS1-4-3162
BWC-GE	M-1049	BS1-4-381
BWC-GG	M-6357	BS1-4-38112
BWD-JG	M-6358	BS1-5-12112
BWD-JH	M-1052	BS1-5-122
BWD-EH	M-1048	BS1-5-142
BWD-GH	M-1050	BS1-5-382
CGC-JE	M-1084	BS2-4-121
CGC-EE	M-1077	BS2-4-141
CGC-EG	M-1079	BS2-4-14112
CGC-EF	M-1078	BS2-4-14114
CGC-CE	M-1072	BS2-4-181
CGC-CG	M-1073	BS2-4-18112
CGC-CH	M-1074	BS2-4-182
CGC-DE	M-1075	BS2-4-3161
CGC-DG	M-6359	BS2-4-316112
CGC-DH	M-1076	BS2-4-3162
CGC-GE	M-1081	BS2-4-381
CGC-GG	M-1082	BS2-4-38112
CGD-JG	M-1085	BS2-5-12112
CGD-JH	M-1086	BS2-5-122
CGD-EH	M-1080	BS2-5-142
CGD-GH	M-1083	BS2-5-382
CHC-JE	M-1095	BS3-4-121
CHC-EE	M-1090	BS3-4-141
CHC-EG	M-1092	BS3-4-14112
CHC-EF	M-1091	BS3-4-14114
CHC-CE	M-1088	BS3-4-181
CHC-CG	M-1089	BS3-4-18112
CHC-DE	M-6353	BS3-4-3161
CHC-DG	M-7163	BS3-4-316112
CHC-GE	M-1093	BS3-4-381
CHC-GG	M-1094	BS3-4-38112
CHD-JG	M-1096	BS3-5-12112
CCC-JE	M-1060	BS4-4-121
CCC-EE	M-1056	BS4-4-141

## Exothermic welding system

### Cross reference

Cadweld cat. no.	Thermoweld cat. no.	Blackburn cat. no.
CCC-EG	M-6369	BS4-4-14112
CCC-EF	M-5566	BS4-4-14114
CCC-CE	M-1054	BS4-4-181
CCC-CG	M-6360	BS4-4-18112
CCC-CH	M-1055	BS4-4-182
CCC-DE	M-6361	BS4-4-3161
CCC-DG	M-6362	BS4-4-316112
CCC-DH	M-6367	BS4-4-3162
CCC-GE	M-1058	BS4-4-381
CCC-GG	M-6370	BS4-4-38112
CCD-JG	M-6372	BS4-5-12112
CCD-JH	M-1061	BS4-5-122
CCD-EH	M-1057	BS4-5-142
CCD-GH	M-1059	BS4-5-382
CFC-JE	M-1069	BS5-4-121
CFC-EE	M-1065	BS5-4-141
CFC-EG	M-6379	BS5-4-14112
CFC-EF	M-6377	BS5-4-14114
CFC-CE	M-1063	BS5-4-181
CFC-CF	M-6373	BS5-4-18112
CFC-CH	M-1064	BS5-4-182
CFC-DE	M-6374	BS5-4-3161
CFC-DG	M-6375	BS5-4-316112
CFC-DH	M-6376	BS5-4-3162
CFC-GE	M-1067	BS5-4-381
CFC-GG	M-6382	BS5-4-38112
CFD-JG	M-6383	BS5-5-12112
CFD-JH	M-1070	BS5-5-122
CFD-EH	M-1066	BS5-5-142
CFD-GH	M-1068	BS5-5-382
LAC-1YCE	M-977	CB1-4-#1181
LAC-1VCE	M-975	CB1-4-#2181
LAC-1TCE	-	CB1-4-#2S181
LAC-1LCE	M-971	CB1-4-#4181
LAC-2CEE	M-979	CB1-4-1/0141
LAC-2CCE	M-978	CB1-4-1/0181
LAC-2CDE	M-6075	CB1-4-1/03161
LAC-2GEE	M-981	CB1-4-2/0141
LAC-2GCE	M-980	CB1-4-2/0181
LAC-2GDE	M-6579	CB1-4-2/03161
LAC-2VEE	M-988	CB1-4-250K141
LAC-2VEG	M-990	CB1-4-250K14112
LAC-2VEH	M-8784	CB1-4-250K142
LAC-2VEK	M-1916	CB1-4-250K143
LAC-2VDE	M-8277	CB1-4-250K3161
LAC-2LEE	M-983	CB1-4-3/0141
LAC-2LCE	M-6284	CB1-4-3/0181
LAC-2LDE	M-982	CB1-4-3/03161
LAC-3AEE	M-991	CB1-4-300K141
LAC-3AEG	M-993	CB1-4-300K14112
LAC-3AEH	M-6288	CB1-4-300K142

Cadweld cat. no.	Thermoweld cat. no.	Blackburn cat. no.
LAC-3AEK	M-1917	CB1-4-300K143
LAC-3DEE	M-994	CB1-4-350K141
LAC-3DEG	M-996	CB1-4-350K1412
LAC-3DEH	M-6289	CB1-4-350K142
LAC-3DEK	M-1918	CB1-4-350K143
LAC-2QEE	M-985	CB1-4-4/0141
LAC-2QEG	M-987	CB1-4-4/01412
LAC-2QEHE	M-5657	CB1-4-4/0142
LAC-2QEKE	M-1915	CB1-4-4/0143
LAC-2QDE	M-984	CB1-4-4/03161
LAC-3QEG	M-1001	CB1-4-500K14112
LAC-3QEHE	M-1002	CB1-4-500K142
LAC-3QEKE	M-1920	CB1-4-500K143
LAC-3QGG	M-1004	CB1-4-500K38112
LAD-4YJH	M-1011	CB1-5-1000K122
LAD-4YJK	M-6295	CB1-5-1000K123
LAD-4YEK	M-6292	CB1-5-1000K143
LAD-4YGH	M-1009	CB1-5-1000K382
LAD-4YGK	M-1922	CB1-5-1000K383
LAD-4LEH	M-1006	CB1-5-750K142
LAD-4LEK	M-1921	CB1-5-750K143
LAD-4LGG	M-1007	CB1-5-750K38112
LAD-4LGH	M-1008	CB1-5-750K382
LAD-4LGK	M-6291	CB1-5-750K383
LQJ-JH1Y	-	CB29-10-#1122
LQJ-EH1Y	-	CB29-10-#1142
LQJ-GH1Y	-	CB29-10-#1382
LQJ-JH1V	-	CB29-10-#2122
LQJ-JH1T	-	CB29-10-#2S122
LQJ-JH2C	-	CB29-10-1/0122
LQJ-EH2C	-	CB29-10-1/0142
LQJ-GH2C	-	CB29-10-1/0382
LQJ-JH2G	-	CB29-10-2/0122
LQJ-EH2G	-	CB29-10-2/0142
LQJ-GH2G	-	CB29-10-2/0382
LQJ-JH2V	-	CB29-10-250K122
LQJ-EH2V	-	CB29-10-250K142
LQJ-GH2V	-	CB29-10-250K382
LQJ-JH2Q	-	CB29-10-4/0122
LQJ-EH2Q	-	CB29-10-4/0142
LQJ-GH2Q	-	CB29-10-4/0382
LQJ-JH3Q	-	CB29-10-500K122
LQJ-EH3Q	-	CB29-10-500K142
LQJ-GH3Q	-	CB29-10-500K382
LQJ-JH4L	-	CB29-10-750K122
LQJ-EH4L	-	CB29-10-750K142
LQJ-GH4L	-	CB29-10-750K382
LQE-EH1V	-	CB29-9-#2142
LQE-GH1V	-	CB29-9-#2382
LQE-EH1T	-	CB29-9-#2S142
LQE-GH1T	-	CB29-9-#2S382

## Exothermic welding system

### Cross reference

Cadweld cat. no.	Thermoweld cat. no.	Blackburn cat. no.
LJC-JG1V	-	CB4-4-#212112
LJC-EG1V	-	CB4-4-#214112
LJC-GG1V	-	CB4-4-#238112
LJC-JG1T	-	CB4-4-#2S12112
LJC-EG1T	-	CB4-4-#2S14112
LJC-GG1T	-	CB4-4-#2S38112
LJC-JG2C	M-1671	CB4-4-1/012112
LJC-EG2C	M-1651	CB4-4-1/014112
LJC-GG2C	M-1660	CB4-4-1/038112
LJC-JG2G	M-1672	CB4-4-2/012112
LJC-EG2G	M-1652	CB4-4-2/014112
LJC-GG2G	M-1661	CB4-4-2/038112
LJC-JG2V	M-1675	CB4-4-250K12112
LJC-EG2V	M-1655	CB4-4-250K14112
LJC-GG2V	M-1664	CB4-4-250K38112
LJC-JG2L	M-1673	CB4-4-3/012112
LJC-EG2L	M-1653	CB4-4-3/014112
LJC-GG2L	M-1662	CB4-4-3/038112
LJC-JG3A	M-1676	CB4-4-300K12112
LJC-EG3A	M-1656	CB4-4-300K14112
LJC-GG3A	M-1665	CB4-4-300K38112
LJC-JG3D	M-1677	CB4-4-350K12112
LJC-EG3D	M-1657	CB4-4-350K14112
LJC-GG3D	M-1666	CB4-4-350K38112
LJC-JG2Q	M-1674	CB4-4-4/012112
LJC-EG2Q	M-1654	CB4-4-4/014112
LJC-GG2Q	M-1663	CB4-4-4/038112
LJC-EG3Q	M-1659	CB4-4-500K14112
LJC-GG3Q	M-1668	CB4-4-500K38112
LJD-JG4Y	M-1681	CB4-5-1000K12112
LJD-GG4Y	M-1670	CB4-5-1000K38112
LJD-JG3Q	M-1679	CB4-5-500K12112
LJD-JG4L	M-1680	CB4-5-750K12112
LJD-GG4L	M-1669	CB4-5-750K38112
XBC-1Y1Y	M-2691	CC11-7-#1#1
XBC-1Y1V	M-2692	CC11-7-#1#2
XBC-1Y1L	M-2693	CC11-7-#1#4
XBC-1V1V	M-2689	CC11-7-#2#2
XBC-1V1L	M-2690	CC11-7-#2#4
XBC-1T1T	M-2689-S	CC11-7-#2S#2S
XBC-1L1L	M-2687	CC11-7-#4#4
XBP-1H1H	M-5432	CC11-7-#6#6
XBP-1G1G	M-5432-S	CC11-7-#6S#6S
XBM-2C1Y	M-2695	CC11-7-1/0#1
XBM-2C1V	M-2696	CC11-7-1/0#2
XBM-2C1L	M-2697	CC11-7-1/0#4
XBM-2C2C	M-2694	CC11-7-1/01/0
XBM-2G1Y	M-2700	CC11-7-2/0#1
XBM-2G1V	M-2701	CC11-7-2/0#2
XBM-2G2C	M-2699	CC11-7-2/01/0
XBM-2G2G	M-2698	CC11-7-2/02/0

Cadweld cat. no.	Thermoweld cat. no.	Blackburn cat. no.
XBM-2V1Y	M-2718	CC11-7-250K#1
XBM-2V1V	M-2719	CC11-7-250K#2
XBM-2V2C	M-2717	CC11-7-250K1/0
XBM-2V2G	M-2716	CC11-7-250K2/0
XBM-2V2V	M-2713	CC11-7-250K250K
XBM-2V2L	M-2715	CC11-7-250K3/0
XBM-2V2Q	M-2714	CC11-7-250K4/0
XBM-2L1Y	M-2705	CC11-7-3/0#1
XBM-2L1V	M-2706	CC11-7-3/0#2
XBM-2L2C	M-2704	CC11-7-3/01/0
XBM-2L2G	M-2703	CC11-7-3/02/0
XBM-2L2L	M-2702	CC11-7-3/03/0
XBM-3A1Y	M-2726	CC11-7-300K#1
XBM-3A1V	M-2727	CC11-7-300K#2
XBM-3A2C	M-2725	CC11-7-300K1/0
XBM-3A2G	M-2724	CC11-7-300K2/0
XBM-3A2L	M-2723	CC11-7-300K3/0
XBM-3A2Q	M-2722	CC11-7-300K4/0
XBM-3D1Y	M-2735	CC11-7-350K#1
XBM-3D1V	M-2736	CC11-7-350K#2
XBM-3D2C	M-2734	CC11-7-350K1/0
XBM-3D2G	M-2733	CC11-7-350K2/0
XBM-2Q1Y	M-2711	CC11-7-4/0#1
XBM-2Q1V	M-2712	CC11-7-4/0#2
XBM-2Q2C	M-2710	CC11-7-4/01/0
XBM-2Q2G	M-2709	CC11-7-4/02/0
XBM-2Q2L	M-2708	CC11-7-4/03/0
XBM-2Q2Q	M-2707	CC11-7-4/04/0
XBM-3Q2C	M-2755	CC11-7-500K1/0
XBV-3A2V	M-2721	CC11-8-300K250K
XBV-3A3A	M-2720	CC11-8-300K300K
XBV-3D2V	M-2730	CC11-8-350K250K
XBV-3D2L	M-2732	CC11-8-350K3/0
XBV-3D3A	M-2729	CC11-8-350K300K
XBV-3D3D	M-2728	CC11-8-350K350K
XBV-3D2Q	M-2731	CC11-8-350K4/0
XBV-3Q2G	M-2754	CC11-8-500K2/0
XBV-3Q2V	M-2751	CC11-8-500K250K
XBV-3Q2L	M-2753	CC11-8-500K3/0
XBV-3Q3A	M-2750	CC11-8-500K300K
XBV-3Q3D	M-2749	CC11-8-500K350K
XBV-3Q2Q	M-2752	CC11-8-500K4/0
XBV-3Q3Q	M-2747	CC11-8-500K500K
SST-1Y	M-5626	CC1-3-#1
SST-1X	M-5626-S	CC1-3-#1S
SST-1V	M-5625	CC1-3-#2
SST-1T	M-5625-S	CC1-3-#2S
SST-1Q	M-5624	CC1-3-#3
-	-	CC1-4-#2
SSC-2C	M-205	CC1-4-1/0
SSC-2B	M-205-S	CC1-4-1/0S

## Exothermic welding system

### Cross reference

Cadweld cat. no.	Thermoweld cat. no.	Blackburn cat. no.
SSC-2G	M-206	CC1-4-2/0
SSC-2V	M-209	CC1-4-250K
SSC-2L	M-207	CC1-4-3/0
SSC-3A	M-210	CC1-4-300K
SSC-3D	M-211	CC1-4-350K
SSC-2Q	M-208	CC1-4-4/0
SSC-2P	M-208-S	CC1-4-4/0S
SSC-3Q	M-213	CC1-4-500K
SSD-4Y	M-215	CC1-5-1000K
SSD-4L	M-214	CC1-5-750K
TAC-1Y1Y	M-225	CC2-4-#1#1
TAC-1Y1V	M-226	CC2-4-#1#2
TAC-1Y1T	M-5879	CC2-4-#1#2S
TAC-1Y1L	M-227	CC2-4-#1#4
TAC-1V1V	M-223	CC2-4-#2#2
TAC-1V1T	M-5869	CC2-4-#2#2S
TAC-1T1L	M-224	CC2-4-#2#4
TAC-1V1L	M-5859	CC2-4-#2#4
TAC-1T1V	M-5856	CC2-4-#2S#2
TAC-1T1T	M-223-S	CC2-4-#2S#2S
TAC-1L1L	M-221	CC2-4-#4#4
TAC-2C1Y	M-229	CC2-4-1/0#1
TAC-2C1V	M-230	CC2-4-1/0#2
TAC-2C1T	M-5311	CC2-4-1/0#2S
TAC-2C1L	M-231	CC2-4-1/0#4
TAC-2C2C	M-228	CC2-4-1/01/0
TAC-4Y2C	M-308	CC2-4-1000K1/0
TAC-4Y2G	M-307	CC2-4-1000K2/0
TAC-4Y2V	M-305	CC2-4-1000K250K
TAC-4Y3A	M-304	CC2-4-1000K300K
TAC-4Y3D	M-303	CC2-4-1000K350K
TAC-4Y2Q	M-306	CC2-4-1000K4/0
TAC-2G1Y	M-234	CC2-4-2/0#1
TAC-2G1V	M-235	CC2-4-2/0#2
TAC-2G1T	M-8093	CC2-4-2/0#2S
TAC-2G1L	M-5475	CC2-4-2/0#4
TAC-2G2C	M-233	CC2-4-2/01/0
TAC-2G2G	M-232	CC2-4-2/02/0
TAC-2V1Y	M-252	CC2-4-250K#1
TAC-2V1V	M-253	CC2-4-250K#2
TAC-2V1T	M-5889	CC2-4-250K#2S
TAC-2V1L	M-5425	CC2-4-250K#4
TAC-2V2C	M-251	CC2-4-250K1/0
TAC-2V2G	M-250	CC2-4-250K2/0
TAC-2V2V	M-247	CC2-4-250K250K
TAC-2V2L	M-249	CC2-4-250K3/0
TAC-2V2Q	M-248	CC2-4-250K4/0
TAC-2L1Y	M-239	CC2-4-3/0#1
TAC-2L1V	M-240	CC2-4-3/0#2
TAC-2L1T	M-5884	CC2-4-3/0#2S
TAC-2L1L	M-5574	CC2-4-3/0#4

Cadweld cat. no.	Thermoweld cat. no.	Blackburn cat. no.
TAC-2L2C	M-238	CC2-4-3/01/0
TAC-2L2G	M-237	CC2-4-3/02/0
TAC-2L2L	M-236	CC2-4-3/03/0
TAC-3A1Y	M-260	CC2-4-300K#1
TAC-3A1V	M-261	CC2-4-300K#2
TAC-3A1T	M-5903	CC2-4-300K#2S
TAC-3A1L	M-6397	CC2-4-300K#4
TAC-3A2C	M-259	CC2-4-300K1/0
TAC-3A2G	M-258	CC2-4-300K2/0
TAC-3A2V	M-255	CC2-4-300K250K
TAC-3A2L	M-257	CC2-4-300K3/0
TAC-3A3A	M-254	CC2-4-300K300K
TAC-3A2Q	M-256	CC2-4-300K4/0
TAC-3D1Y	M-269	CC2-4-350K#1
TAC-3D1V	M-270	CC2-4-350K#2
TAC-3D1L	M-6398	CC2-4-350K#4
TAC-3D2C	M-268	CC2-4-350K1/0
TAC-3D2G	M-267	CC2-4-350K2/0
TAC-3D2V	M-264	CC2-4-350K250K
TAC-3D2L	M-266	CC2-4-350K3/0
TAC-3D3A	M-263	CC2-4-350K300K
TAC-3D3D	M-262	CC2-4-350K350K
TAC-3D2Q	M-265	CC2-4-350K4/0
TAC-2Q1Y	M-245	CC2-4-4/0#1
TAC-2Q1V	M-246	CC2-4-4/0#2
TAC-2Q1T	M-5348	CC2-4-4/0#2S
TAC-2Q1L	M-5021	CC2-4-4/0#4
TAC-2Q2C	M-244	CC2-4-4/01/0
TAC-2Q2G	M-243	CC2-4-4/02/0
TAC-2Q2L	M-242	CC2-4-4/03/0
TAC-2Q2Q	M-241	CC2-4-4/04/0
TAC-3Q1Y	M-288	CC2-4-500K#1
TAC-3Q1V	M-289	CC2-4-500K#2
TAC-3Q1L	M-8113	CC2-4-500K#4
TAC-3Q2C	M-287	CC2-4-500K1/0
TAC-3Q2G	M-286	CC2-4-500K2/0
TAC-3Q2V	M-284	CC2-4-500K250K
TAC-3Q3A	M-283	CC2-4-500K300K
TAC-3Q3D	M-282	CC2-4-500K350K
TAC-3Q2Q	M-285	CC2-4-500K4/0
TAC-3Q3Q	M-280	CC2-4-500K500K
TAC-4L2C	M-298	CC2-4-750K1/0
TAC-4L2G	M-297	CC2-4-750K2/0
TAC-4L2V	M-295	CC2-4-750K250K
TAC-4L3A	M-294	CC2-4-750K300K
TAC-4L3D	M-293	CC2-4-750K350K
TAC-4L2Q	M-296	CC2-4-750K4/0
TAD-4Y4Y	M-299	CC2-5-1000K1000K
TAD-4Y3Q	M-301	CC2-5-1000K500K
TAD-4Y4L	M-300	CC2-5-1000K750K
TAD-4L3Q	M-291	CC2-5-750K500K

## Exothermic welding system

### Cross reference

Cadweld cat. no.	Thermoweld cat. no.	Blackburncat. no.
TAD-4L4L	M-290	CC2-5-750K750K
-	-	CC2HD-4-4/04/0
XAC-1Y1Y	M-427	CC4-4-#1#1
XAC-1Y1V	M-428	CC4-4-#1#2
XAC-1Y1L	M-429	CC4-4-#1#4
XAC-1V1V	-	CC4-4-#2#2
XAC-1V1L	-	CC4-4-#2#4
XAC-1T1T	-	CC4-4-#2S#2S
XAC-1L1L	-	CC4-4-#4#4
XAC-2C1Y	M-431	CC4-4-1/0#1
XAC-2C1V	M-432	CC4-4-1/0#2
XAC-2C1L	M-433	CC4-4-1/0#4
XAC-2C2C	M-430	CC4-4-1/01/0
XAC-2G1Y	M-436	CC4-4-2/0#1
XAC-2G1V	M-437	CC4-4-2/0#2
XAC-2G2C	M-435	CC4-4-2/01/0
XAC-2G2G	M-434	CC4-4-2/02/0
XAC-2V1Y	M-454	CC4-4-250K#1
XAC-2V1V	M-455	CC4-4-250K#2
XAC-2V2C	M-453	CC4-4-250K1/0
XAC-2V2G	M-452	CC4-4-250K2/0
XAC-2V2V	M-449	CC4-4-250K250K
XAC-2V2L	M-451	CC4-4-250K3/0
XAC-2V2Q	M-450	CC4-4-250K4/0
XAC-2L1Y	M-441	CC4-4-3/0#1
XAC-2L1V	M-442	CC4-4-3/0#2
XAC-2L2C	M-440	CC4-4-3/01/0
XAC-2L2G	M-439	CC4-4-3/02/0
XAC-2L2L	M-438	CC4-4-3/03/0
XAC-3A1Y	M-462	CC4-4-300K#1
XAC-3A1V	M-463	CC4-4-300K#2
XAC-3A2C	M-461	CC4-4-300K1/0
XAC-3A2G	M-460	CC4-4-300K2/0
XAC-3A2V	M-457	CC4-4-300K250K
XAC-3A2L	M-459	CC4-4-300K3/0
XAC-3A3A	M-456	CC4-4-300K300K
XAC-3A2Q	M-458	CC4-4-300K4/0
XAC-3D1Y	M-471	CC4-4-350K#1
XAC-3D1V	M-472	CC4-4-350K#2
XAC-3D2C	M-470	CC4-4-350K1/0
XAC-3D2G	M-469	CC4-4-350K2/0
XAC-3D2V	M-466	CC4-4-350K250K
XAC-3D2L	M-468	CC4-4-350K3/0
XAC-3D3A	M-465	CC4-4-350K300K
XAC-3D3D	M-464	CC4-4-350K350K
XAC-3D2Q	M-467	CC4-4-350K4/0
XAC-2Q1Y	M-447	CC4-4-4/0#1
XAC-2Q1V	M-448	CC4-4-4/0#2
XAC-2Q2C	M-446	CC4-4-4/01/0
XAC-2Q2G	M-445	CC4-4-4/02/0
XAC-2Q2L	M-444	CC4-4-4/03/0

Cadweld cat. no.	Thermoweld cat. no.	Blackburn cat. no.
XAC-2Q2Q	M-443	CC4-4-4/04/0
XAC-3Q2C	M-491	CC4-4-500K1/0
XAC-3Q2G	M-490	CC4-4-500K2/0
XAD-3Q2V	M-487	CC4-5-500K250K
XAD-3Q2L	M-489	CC4-5-500K3/0
XAD-3Q3A	M-486	CC4-5-500K300K
XAD-3Q3D	M-485	CC4-5-500K350K
XAD-3Q2Q	M-488	CC4-5-500K4/0
XAD-3Q3Q	M-483	CC4-5-500K500K
PCC-1Y1V	M-1282	CC6-4-#1#2
PCC-1Y1L	M-1283	CC6-4-#1#4
PCC-1Y1H	M-1284	CC6-4-#1#6
PCC-1Y1G	M-1285	CC6-4-#1#6S
PCC-1Y1D	M-1286	CC6-4-#1#8S
PCC-1V1V	M-1276	CC6-4-#2#2
PCC-1V1L	M-1277	CC6-4-#2#4
PCC-1V1H	M-1278	CC6-4-#2#6
PCC-1V1G	M-1279	CC6-4-#2#6S
PCC-1V1D	M-1280	CC6-4-#2#8S
PCC-1T1V	-	CC6-4-#2S#2
PCC-1T1T	-	CC6-4-#2S#2S
PCC-1T1H	-	CC6-4-#2S#6
PCC-1T1G	-	CC6-4-#2S#6S
PCC-1T2C	-	CC6-4-#2S1/0
PCC-1T2G	-	CC6-4-#2S2/0
PCC-1L1L	-	CC6-4-#4#4
PCC-1L1H	-	CC6-4-#4#6
PCC-1L1G	-	CC6-4-#4#6S
PCC-1L1D	-	CC6-4-#4#8S
PCC-2C1V	M-1289	CC6-4-1/0#2
PCC-2C1L	M-1290	CC6-4-1/0#4
PCC-2C1H	M-1291	CC6-4-1/0#6
PCC-2C1G	M-1292	CC6-4-1/0#6S
PCC-2C1D	M-1293	CC6-4-1/0#8S
PCC-2G1V	M-1297	CC6-4-2/0#2
PCC-2G1L	M-1298	CC6-4-2/0#4
PCC-2G1H	M-1299	CC6-4-2/0#6
PCC-2G1G	M-1300	CC6-4-2/0#6S
PCC-2G1D	M-1301	CC6-4-2/0#8S
-	-	CC6-4-2/02/0
PCC-2Q1Y	M-1305	CC6-4-4/0#1
PCC-2Q1V	M-1306	CC6-4-4/0#2
PCC-2Q1L	M-1307	CC6-4-4/0#4
PCC-2Q1H	M-1308	CC6-4-4/0#6
PCC-2Q1G	M-1309	CC6-4-4/0#6S
PCC-2Q1D	M-1310	CC6-4-4/0#8S
-	-	CC6-4-4/02/0
-	-	CC6-4-4/04/0
PTC-1Y1Y	M-1315	CC7-4-#1#1
PTC-1Y1X	M-6013	CC7-4-#1#S
PTC-1Y1V	M-1316	CC7-4-#1#2

## Exothermic welding system

### Cross reference

Cadweld cat. no.	Thermoweld cat. no.	Blackburn cat. no.
PTC-1Y1T	M-6017	CC7-4-#1#2S
PTC-1Y1L	M-1317	CC7-4-#1#4
PTC-1Y1H	M-5636	CC7-4-#1#6
PTC-1Y1G	M-5637	CC7-4-#1#6S
PTC-1Y1E	M-5638	CC7-4-#1#8
PTC-1Y1D	M-5639	CC7-4-#1#8S
PTC-1X1Y	M-5998	CC7-4-#1S#1
PTC-1X1V	M-6001	CC7-4-#1S#2
PTC-1X1T	M-1316-S	CC7-4-#1S#2S
PTC-1X1L	M-6008	CC7-4-#1S#4
PTC-1X1H	M-6010	CC7-4-#1S#6
PTC-1X1G	M-5636-S	CC7-4-#1S#6S
PTC-1X1E	M-6012	CC7-4-#1S#8
PTC-1X1D	M-5638-S	CC7-4-#1S#8S
PTC-1V1V	M-1313	CC7-4-#2#2
PTC-1V1L	M-1314	CC7-4-#2#4
PTC-1V1H	M-5631	CC7-4-#2#6
PTC-1V1G	M-5632	CC7-4-#2#6S
PTC-1V1E	M-5634	CC7-4-#2#8
PTC-1V1D	M-5635	CC7-4-#2#8S
PTC-1T1V	M-5973	CC7-4-#2S#2
PTC-1T1T	M-1313-S	CC7-4-#2S#2S
PTC-1T1L	M-5987	CC7-4-#2S#4
PTC-1T1H	M-5989	CC7-4-#2S#6
PTC-1T1G	M-5631-S	CC7-4-#2S#6S
PTC-1T1E	M-5993	CC7-4-#2S#8
PTC-1T1D	M-5634-S	CC7-4-#2S#8S
PTC-1L1L	M-1311	CC7-4-#4#4
PTC-1L1H	M-5627	CC7-4-#4#6
PTC-1L1G	M-8882	CC7-4-#4#6S
PTC-1L1E	M-5629	CC7-4-#4#8
PTC-1L1D	M-5630	CC7-4-#4#8S
PTC-2C1Y	M-1319	CC7-4-1/0#1
PTC-2C1X	M-6036	CC7-4-1/0#1S
PTC-2C1V	M-1320	CC7-4-1/0#2
PTC-2C1T	M-6044	CC7-4-1/0#2S
PTC-2C1L	M-1321	CC7-4-1/0#4
PTC-2C1H	M-5642	CC7-4-1/0#6
PTC-2C1G	M-1208	CC7-4-1/0#6S
PTC-2C1E	M-5644	CC7-4-1/0#8
PTC-2C1D	M-5645	CC7-4-1/0#8S
PTC-2C2C	M-1318	CC7-4-1/01/0
PTC-2C2B	M-6035	CC7-4-1/01/0S
PTC-2B1Y	M-6019	CC7-4-1/0S#1
PTC-2B1X	M-1319-S	CC7-4-1/0S#1S
PTC-2B1V	M-6023	CC7-4-1/0S#2
PTC-2B1T	M-1320-S	CC7-4-1/0S#2S
PTC-2B1L	M-6026	CC7-4-1/0S#4
PTC-2B1H	M-6806	CC7-4-1/0S#6
PTC-2B1G	M-5462-S	CC7-4-1/0S#6S
PTC-2B1E	M-6028	CC7-4-1/0S#8

Cadweld cat. no.	Thermoweld cat. no.	Blackburn cat. no.
PTC-2B1D	M-5644-S	CC7-4-1/0S#8S
PTC-2B2C	M-6227	CC7-4-1/0S1/0
PTC-2B2B	M-1318-S	CC7-4-1/0S1/0S
PTC-2G1Y	M-1324	CC7-4-2/0#1
PTC-2G1X	M-6052	CC7-4-2/0#1S
PTC-2G1V	M-1325	CC7-4-2/0#2
PTC-2G1L	M-5659	CC7-4-2/0#4
PTC-2G1H	M-5342	CC7-4-2/0#6
PTC-2G1G	M-5652	CC7-4-2/0#6S
PTC-2G1E	M-5668	CC7-4-2/0#8
PTC-2G1D	M-5943	CC7-4-2/0#8S
PTC-2G2C	M-1323	CC7-4-2/01/0
PTC-2G2B	M-6047	CC7-4-2/01/0S
PTC-2G2G	M-1322	CC7-4-2/02/0
PTC-2L1Y	M-1329	CC7-4-3/0#1
PTC-2L1X	M-6064	CC7-4-3/0#1S
PTC-2L1V	M-1330	CC7-4-3/0#2
PTC-2L1T	M-6065	CC7-4-3/0#2S
PTC-2L1L	M-6046	CC7-4-3/0#4
PTC-2L1H	M-5676	CC7-4-3/0#6
PTC-2L1G	M-5679	CC7-4-3/0#6S
PTC-2L1E	M-5680	CC7-4-3/0#8
PTC-2L1D	M-5682	CC7-4-3/0#8S
PTC-2L2C	M-1328	CC7-4-3/01/0
PTC-2L2B	M-6062	CC7-4-3/01/0S
PTC-2L2G	M-1327	CC7-4-3/02/0
PTC-2L2L	M-1326	CC7-4-3/03/0
PTC-2Q1Y	M-1335	CC7-4-4/0#1
PTC-2Q1X	M-6804	CC7-4-4/0#1S
PTC-2Q1V	M-1336	CC7-4-4/0#2
PTC-2Q1T	M-6805	CC7-4-4/0#2S
PTC-2Q1L	M-5340	CC7-4-4/0#4
PTC-2Q1H	M-5684	CC7-4-4/0#6
PTC-2Q1G	M-6552	CC7-4-4/0#6S
PTC-2Q1E	M-5686	CC7-4-4/0#8
PTC-2Q1D	M-5688	CC7-4-4/0#8S
PTC-2Q2C	M-1334	CC7-4-4/01/0
PTC-2Q2B	M-2551	CC7-4-4/01/0S
PTC-2Q2G	M-1333	CC7-4-4/02/0
PTC-2Q2L	M-1332	CC7-4-4/03/0
PTC-2Q2Q	M-1331	CC7-4-4/04/0
PTC-2Q2P	M-6803	CC7-4-4/04/0S
PTC-2P1Y	M-6089	CC7-4-4/0S#1
PTC-2P1X	M-1335-S	CC7-4-4/0S#1S
PTC-2P1V	M-6090	CC7-4-4/0S#2
PTC-2P1T	M-1336-S	CC7-4-4/0S#2S
PTC-2P1L	M-6109	CC7-4-4/0S#4
PTC-2P1H	M-6111	CC7-4-4/0S#6
PTC-2P1G	M-5684-S	CC7-4-4/0S#6S
PTC-2P1E	M-6112	CC7-4-4/0S#8
PTC-2P1D	M-5686-S	CC7-4-4/0S#8S

## Exothermic welding system

### Cross reference

Cadweld cat. no.	Thermoweld cat. no.	Blackburn cat. no.
PTC-2P2C	M-6085	CC7-4-4/0S1/0
PTC-2P2B	M-1334-S	CC7-4-4/0S1/0S
PTC-2P2G	M-6082	CC7-4-4/0S2/0
PTC-2P2L	M-6081	CC7-4-4/0S3/0
PTC-2P2Q	M-6071	CC7-4-4/0S4/0
PTC-2P2P	M-1331-S	CC7-4-4/0S4/0S
GRT-14A1V	-	CR1-3-500#2
GRT-14A1T	-	CR1-3-500#2S
GRT-14A1L	M-8403	CR1-3-500#4
GRT-14A1K	M-8403-S	CR1-3-500#4S
GRT-14A1H	M-8402	CR1-3-500#6
GRT-14A1G	M-8402-S	CR1-3-500#6S
GRT-14B1V	-	CR1-3-500L#2
GRT-14B1T	-	CR1-3-500L#2S
GRT-14B1L	M-8403-T	CR1-3-500L#4
GRT-14B1K	M-8403-ST	CR1-3-500L#4S
GRT-14B1H	M-8402-T	CR1-3-500L#6
GRT-14B1G	M-8402-ST	CR1-3-500L#6S
GRT-161L	M-8415	CR1-3-625#4
GRT-161K	M-8415-S	CR1-3-625#4S
GRT-161H	M-8414	CR1-3-625#6
GRT-161G	M-8414-S	CR1-3-625#6S
GRP-181L	M-8426	CR1-3-750#4
GRP-181K	M-8426-S	CR1-3-750#4S
GRT-181H	M-8422	CR1-3-750#6
GRT-181G	M-8422-S	CR1-3-750#6S
GRC-151Y	M-496	CR1-4-500#1
GRC-152C	M-497	CR1-4-5001/0
GRC-152B	M-497-S	CR1-4-5001/0S
GRC-152G	M-498	CR1-4-5002/0
GRC-152V	M-501	CR1-4-500250K
GRC-152L	M-499	CR1-4-5003/0
GRC-153A	M-502	CR1-4-500300K
GRC-152Q	M-500	CR1-4-5004/0
GRC-141Y	M-496-T	CR1-4-500L#1
GRC-142C	M-497-T	CR1-4-500L1/0
GRC-142B	M-497-ST	CR1-4-500L1/0S
GRC-142G	M-498-T	CR1-4-500L2/0
GRC-142V	M-501-T	CR1-4-500L250K
GRC-142L	M-499-T	CR1-4-500L3/0
GRC-143A	M-502-T	CR1-4-500L300K
GRC-142Q	M-500-T	CR1-4-500L4/0
GRC-161Y	M-504	CR1-4-625#1
GRC-161V	M-503	CR1-4-625#2
GRT-161V	-	CR1-4-625#2
GRC-161T	-	CR1-4-625#2S
GRT-161T	-	CR1-4-625#2S
GRC-162C	M-505	CR1-4-6251/0
GRC-162B	M-505-S	CR1-4-6251/0S
GRC-162G	M-506	CR1-4-6252/0
GRC-162V	M-509	CR1-4-625250K

Cadweld cat. no.	Thermoweld cat. no.	Blackburn cat. no.
GRC-162L	M-507	CR1-4-6253/0
GRC-163A	M-510	CR1-4-625300K
GRC-163D	M-511	CR1-4-625350K
GRC-162Q	M-508	CR1-4-6254/0
GRC-163Q	M-513	CR1-4-625500K
GRC-181Y	M-514	CR1-4-750#1
GRC-181V	M-5781	CR1-4-750#2
GRC-181T	-	CR1-4-750#2S
GRC-182C	M-515	CR1-4-7501/0
GRC-182B	M-515-S	CR1-4-7501/0S
GRC-182G	M-516	CR1-4-7502/0
GRC-182V	M-519	CR1-4-750250K
GRC-182L	M-517	CR1-4-7503/0
GRC-183A	M-520	CR1-4-750300K
GRC-183D	M-521	CR1-4-750350K
GRC-182Q	M-518	CR1-4-7504/0
GRC-183Q	M-523	CR1-4-750500K
-	-	CR17-4-7504/0
GTT-14A1L	M-8435	CR2-3-500#4
GTT-14A1K	M-8435-S	CR2-3-500#4S
GTT-14A1H	M-8434	CR2-3-500#6
GTT-14A1G	M-8434-S	CR2-3-500#6S
GTT-14B1L	M-8435-T	CR2-3-500L#4
GTT-14B1K	M-8435-ST	CR2-3-500L#4S
GTT-14B1H	M-8434-T	CR2-3-500L#6
GTT-14B1G	M-8434-ST	CR2-3-500L#6S
GTT-161L	M-8442	CR2-3-625#4
GTT-161K	M-8442-S	CR2-3-625#4S
GTT-161H	M-8441	CR2-3-625#6
GTT-161G	M-8441-S	CR2-3-625#6S
GTP-181L	M-8454	CR2-3-750#4
GTP-181K	M-8454-S	CR2-3-750#4S
GTP-181H	M-8452	CR2-3-750#6
GTP-181G	M-8452-S	CR2-3-750#6S
GTC-151Y	M-538	CR2-4-500#1
GTC-151V	M-537	CR2-4-500#2
GTC-151T	-	CR2-4-500#2S
GTC-152C	M-539	CR2-4-5001/0
GTC-152B	M-539-S	CR2-4-5001/0S
GTC-152G	M-540	CR2-4-5002/0
GTC-152V	M-543	CR2-4-500250K
GTC-152L	M-541	CR2-4-5003/0
GTC-153A	M-544	CR2-4-500300K
GTC-152Q	M-542	CR2-4-5004/0
GTC-141Y	M-538-T	CR2-4-500L#1
GTC-141V	M-537-T	CR2-4-500L#2
GTC-141T	-	CR2-4-500L#2S
GTC-142C	M-539-T	CR2-4-500L1/0
GTC-142B	-	CR2-4-500L1/0S
GTC-142G	M-540-T	CR2-4-500L2/0
GTC-142V	M-543-T	CR2-4-500L250K

## Exothermic welding system

### Cross reference

Cadweld cat. no.	Thermoweld cat. no.	Blackburn cat. no.
GTC-142L	M-541-T	CR2-4-500L3/0
GTC-143A	M-544-T	CR2-4-500L300K
GTC-142Q	M-542-T	CR2-4-500L4/0
GTC-161Y	M-546	CR2-4-625#1
GTC-161V	M-545	CR2-4-625#2
GTC-161T	-	CR2-4-625#2S
GTC-162C	M-547	CR2-4-6251/0
GTC-162B	M-547-S	CR2-4-6251/0S
GTC-162G	M-548	CR2-4-6252/0
GTC-162V	M-551	CR2-4-625250K
GTC-162L	M-549	CR2-4-6253/0
GTC-163A	M-552	CR2-4-625300K
GTC-163D	M-553	CR2-4-625350K
GTC-162Q	M-550	CR2-4-6254/0
GTC-163Q	M-555	CR2-4-625500K
GTC-181Y	M-557	CR2-4-750#1
GTC-181V	M-556	CR2-4-750#2
GTC-181T	-	CR2-4-750#2S
GTC-182C	M-558	CR2-4-7501/0
GTC-182B	M-558-S	CR2-4-7501/0S
GTC-182G	M-559	CR2-4-7502/0
GTC-182V	M-562	CR2-4-750250K
GTC-182L	M-560	CR2-4-7503/0
GTC-183A	M-563	CR2-4-750300K
GTC-183D	M-564	CR2-4-750350K
GTC-182Q	M-561	CR2-4-7504/0
GTC-183Q	M-566	CR2-4-750500K
GYJ-163Q	M-1593	CR3-10-625500K
GYJ-183D	M-1599	CR3-10-750350K
GYJ-183Q	M-1601	CR3-10-750500K
GYE-152C	M-1581	CR3-9-5001/0
GYE-152B	M-1581-S	CR3-9-5001/0S
GYE-152G	M-1582	CR3-9-5002/0
GYE-152V	M-1584	CR3-9-500250K
GYE-152L	M-6267	CR3-9-5003/0
GYE-153A	M-1585	CR3-9-500300K
GYE-152Q	M-1583	CR3-9-5004/0
GYE-142C	M-1581-T	CR3-9-500L1/0
GYE-142B	M-1581-ST	CR3-9-500L1/0S
GYE-142G	M-1582-T	CR3-9-500L2/0
GYE-142V	M-1584-T	CR3-9-500L250K
GYE-142L	M-6267-T	CR3-9-500L3/0
GYE-143A	M-1585-T	CR3-9-500L300K
GYE-142Q	M-1583-T	CR3-9-500L4/0
-	-	CR3-9-625#2
GYE-162C	M-1586	CR3-9-6251/0
GYE-162B	M-1586-S	CR3-9-6251/0S
GYE-162G	M-1587	CR3-9-6252/0
GYE-162V	M-1589	CR3-9-625250K
GYE-162L	M-8305	CR3-9-6253/0
GYE-163A	M-1590	CR3-9-625300K

Cadweld cat. no.	Thermoweld cat. no.	Blackburn cat. no.
GYE-163D	M-1591	CR3-9-625350K
GYE-162Q	M-1588	CR3-9-6254/0
GYE-182C	M-1594	CR3-9-7501/0
GYE-182B	M-1594-S	CR3-9-7501/0S
GYE-182G	M-1595	CR3-9-7502/0
GYE-182V	M-1597	CR3-9-750250K
GYE-182L	M-6608	CR3-9-7503/0
GYE-183A	-	CR3-9-750300K
GYE-182Q	M-1596	CR3-9-7504/0
RR	-	CRE1-3-#1Y
RR	-	CRE1-3-#1Z
RR	-	CRE1-3-#2SY
RR	-	CRE1-3-#2SZ
RR	-	CRE1-3-#2Y
RR	-	CRE1-3-#2Z
RR	-	CRE1-3-#4Y
RR	-	CRE1-3-#4Z
RR	-	CRE1-3-1/0Y
RR	-	CRE1-3-1/0Z
RR	-	CRE1-3-2/0Y
RR	-	CRE1-3-2/0Z
RR	-	CRE1-3-3/0Y
RR	-	CRE1-3-3/0Z
RR	-	CRE1-3-4/0Y
RR	-	CRE1-3-4/0Z
RRC-511Y	M-7503	CRE1-4-#13R
RRC-511V	M-7502	CRE1-4-#23R
RRC-511T	-	CRE1-4-#2S3R
RRC-511L	M-7501	CRE1-4-#43R
RRC-512C	M-7504	CRE1-4-1/03R
RRC-512G	M-7505	CRE1-4-2/03R
RRC-512L	M-7506	CRE1-4-3/03R
RRC-512Q	M-7507	CRE1-4-4/03R
RC	-	CRE3-3-#2SY
RC	-	CRE3-3-#2SZ
RC	-	CRE3-3-#2Y
RC	-	CRE3-3-#2Z
RC	-	CRE3-3-#4Y
RC	-	CRE3-3-#4Z
-	-	CRE3-3-1/0Y
-	-	CRE3-3-1/0Z
-	-	CRE3-3-2/0Y
-	-	CRE3-3-2/0Z
-	-	CRE3-3-4-#1Y
RC	-	CRE3-4-#1Z
RC	-	CRE3-4-1/0Y
RC	-	CRE3-4-1/0Z
RC	-	CRE3-4-2/0Y
RC	-	CRE3-4-2/0Z
RC	-	CRE3-4-3/0Y
RC	-	CRE3-4-3/0Z

## Exothermic welding system

### Cross reference

Cadweld cat. no.	Thermoweld cat. no.	Blackburn cat. no.
RC	—	CRE3-4-4/0Y
RC	—	CRE3-4-4/0Z
RD	—	CRE4-3-#1Y
RD	—	CRE4-3-#1Z
RD	—	CRE4-3-#2SY
RD	—	CRE4-3-#2SZ
RD	—	CRE4-3-#2Y
RD	—	CRE4-3-#2Z
RD	—	CRE4-3-#4Y
RD	—	CRE4-3-#4Z
RD	—	CRE4-3-1/0Y
RD	—	CRE4-3-1/0Z
RD	—	CRE4-3-2/0Y
RD	—	CRE4-3-2/0Z
RD	—	CRE4-3-3/0Y
RD	—	CRE4-3-3/0Z
RD	—	CRE4-3-4/0Y
RD	—	CRE4-3-4/0Z
RJ	—	CRE6-3-#1Y
RJ	—	CRE6-3-#1Z
RJ	—	CRE6-3-#2SY
RJ	—	CRE6-3-#2SZ
RJ	—	CRE6-3-#2Y
RJ	—	CRE6-3-#2Z
RJ	—	CRE6-3-#4Y
RJ	—	CRE6-3-#4Z
RJ	—	CRE6-4-1/0Y
RJ	—	CRE6-4-1/0Z
RJ	—	CRE6-4-2/0Y
RJ	—	CRE6-4-2/0Z
RJ	—	CRE6-4-3/0Y
RJ	—	CRE6-4-3/0Z
RJ	—	CRE6-4-4/0Y
RJ	—	CRE6-4-4/0Z
HSC-2C	M-644	CS1-4-1/0
HSD-4Y	M-654	CS1-4-1000K
HSC-2G	M-645	CS1-4-2/0
HSC-2V	M-648	CS1-4-250K
HSC-2L	M-646	CS1-4-3/0
HSC-3A	M-649	CS1-4-300K
HSC-3D	M-650	CS1-4-350K
HSC-2Q	M-647	CS1-4-4/0
HSC-3Q	M-652	CS1-4-500K
HSD-4L	M-653	CS1-4-750K
HTC-2C	M-616	CS2-4-1/0
HTC-2G	M-617	CS2-4-2/0
HTC-2V	M-620	CS2-4-250K
HTC-2L	M-618	CS2-4-3/0
HTC-3A	M-621	CS2-4-300K
HTC-3D	M-622	CS2-4-350K
HTC-2Q	M-619	CS2-4-4/0

Cadweld cat. no.	Thermoweld cat. no.	Blackburn cat. no.
VBC-1Y	M-5361	CS25-4-#1
VBC-1Y-V3	—	CS25-4-#1C
VBC-1Y-V5	—	CS25-4-#1D
VBC-1Y-V8	—	CS25-4-#1F
VBC-1Y-V21C	—	CS25-4-#1G
VBC-1V	M-2781	CS25-4-#2
VBC-1V-V3	—	CS25-4-#2C
VBC-1V-V5	—	CS25-4-#2D
VBC-1V-V8	—	CS25-4-#2F
VBC-1V-V21C	—	CS25-4-#2G
VBC-1T	—	CS25-4-#2S
VBC-1T-V3	—	CS25-4-#2SC
VBC-1T-V5	—	CS25-4-#2SD
VBC-1T-V8	—	CS25-4-#2SF
VBC-1T-V21	—	CS25-4-#2SG
VBC-1L	M-5359	CS25-4-#4
VBC-1L-V3	—	CS25-4-#4C
VBC-1L-V5	—	CS25-4-#4D
VBC-1L-V8	—	CS25-4-#4F
VBC-1L-V21	—	CS25-4-#4G
VBC-2C	M-2189	CS25-4-1/0
VBC-2C-V3	—	CS25-4-1/0C
VBC-2C-V5	—	CS25-4-1/0D
VBC-2C-V8	—	CS25-4-1/0F
VBC-2C-V20	—	CS25-4-1/0G
VBC-2G	M-2540	CS25-4-2/0
VBC-2G-V3	—	CS25-4-2/0C
VBC-2G-V5	—	CS25-4-2/0D
VBC-2G-V8	—	CS25-4-2/0F
VBC-2G-V20	—	CS25-4-2/0G
VBC-2V	M-8165	CS25-4-250K
VBC-2L	M-5362	CS25-4-3/0
VBC-2L-V3	—	CS25-4-3/0C
VBC-2L-V5	—	CS25-4-3/0D
VBC-2L-V8	—	CS25-4-3/0F
VBC-2L-V20	—	CS25-4-3/0G
VBC-3A	M-5363	CS25-4-300K
VBC-3D	M-9029	CS25-4-350K
VBC-2Q	M-8718	CS25-4-4/0
VBC-2Q-V3	—	CS25-4-4/0C
VBC-2Q-V5	—	CS25-4-4/0D
VBC-2Q-V8	—	CS25-4-4/0F
VBC-2Q-V20	—	CS25-4-4/0G
VBR-3Q	M-8512	CS25-4-500K
HTD-3Q	M-624	CS2-5-500K
VGC-1Y	M-6279	CS27-4-#1
VGC-1Y-V3	—	CS27-4-#1C
VGC-1Y-V5	—	CS27-4-#1D
VGC-1Y-V8	—	CS27-4-#1F
VGC-1Y-V21C	—	CS27-4-#1G
VGC-1V	M-5822	CS27-4-#2

## Exothermic welding system

### Cross reference

Cadweld cat. no.	Thermoweld cat. no.	Blackburn cat. no.
VGC-1V-V3	-	CS27-4-#2C
VGC-1V-V5	-	CS27-4-#2D
VGC-1V-V8	-	CS27-4-#2F
VGC-1V-V21C	-	CS27-4-#2G
VGC-1T	-	CS27-4-#2S
VGC-1T-V3	-	CS27-4-#2SC
VGC-1T-V5	-	CS27-4-#2SD
VGC-1T-V8	-	CS27-4-#2SF
VGC-1T-V21	-	CS27-4-#2SG
VGC-1H	M-5245	CS27-4-#4
VGC-1L	M-5816	CS27-4-#4
VGC-1L-V3	-	CS27-4-#4C
VGC-1L-V5	-	CS27-4-#4D
VGC-1L-V8	-	CS27-4-#4F
VGC-1L-V21	-	CS27-4-#4G
VGC-2C	M-1168	CS27-4-1/0
VGC-2C-V3	-	CS27-4-1/0C
VGC-2C-V5	-	CS27-4-1/0D
VGC-2C-V8	-	CS27-4-1/0F
VGC-2C-V20	-	CS27-4-1/0G
VGC-2G	M-9242	CS27-4-2/0
VGC-2G-V3	-	CS27-4-2/0C
VGC-2G-V5	-	CS27-4-2/0D
VGC-2G-V8	-	CS27-4-2/0F
VGC-2G-V20	-	CS27-4-2/0G
VGC-2V	M-2520	CS27-4-250K
VGC-2L	M-6195	CS27-4-3/0
VGC-2L-V3	-	CS27-4-3/0C
VGC-2L-V5	-	CS27-4-3/0D
VGC-2L-V8	-	CS27-4-3/0F
VGC-2L-V20	-	CS27-4-3/0G
VGC-2Q	M-2177	CS27-4-4/0
VGC-2Q-V3	-	CS27-4-4/0C
VGC-2Q-V5	-	CS27-4-4/0D
VGC-2Q-V8	-	CS27-4-4/0F
VGC-2Q-V20	-	CS27-4-4/0G
VNC-1Y	M-6060	CS31-4-#1
VGC-1Y-V3	-	CS31-4-#1C
VGC-1Y-V5	-	CS31-4-#1D
VGC-1Y-V8	-	CS31-4-#1F
VGC-1Y-V21C	-	CS31-4-#1G
VNC-1V	M-2569	CS31-4-#2
VGC-1V-V3	-	CS31-4-#2C
VGC-1V-V5	-	CS31-4-#2D
VGC-1V-V8	-	CS31-4-#2F
VGC-1V-V21C	-	CS31-4-#2G
VNC-1T	-	CS31-4-#2S
VGC-1T-V3	-	CS31-4-#2SC
VGC-1T-V5	-	CS31-4-#2SD
VGC-1T-V8	-	CS31-4-#2SF
VGC-1T-V21	-	CS31-4-#2SG

Cadweld cat. no.	Thermoweld cat. no.	Blackburn cat. no.
VNC-1L	M-2761	CS31-4-#4
VGC-1L-V3	-	CS31-4-#4C
VGC-1L-V5	-	CS31-4-#4D
VGC-1L-V8	-	CS31-4-#4F
VGC-1L-V21	-	CS31-4-#4G
VNC-1H	M-5910	CS31-4-#6
VNC-2C	M-5419	CS31-4-1/0
VGC-2C-V3	-	CS31-4-1/0C
VGC-2C-V5	-	CS31-4-1/0D
VGC-2C-V8	-	CS31-4-1/0F
VGC-2C-V20	-	CS31-4-1/0G
VNC-2G	M-2567	CS31-4-2/0
VGC-2G-V3	-	CS31-4-2/0C
VGC-2G-V5	-	CS31-4-2/0D
VGC-2G-V8	-	CS31-4-2/0F
VGC-2G-V20	-	CS31-4-2/0G
VNC-2V	M-2568	CS31-4-250K
VNC-2L	M-6072	CS31-4-3/0
VGC-2L-V3	-	CS31-4-3/0C
VGC-2L-V5	-	CS31-4-3/0D
VGC-2L-V8	-	CS31-4-3/0F
VGC-2L-V20	-	CS31-4-3/0G
VNC-3A	M-6061	CS31-4-300K
VNC-3D	M-6067	CS31-4-350K
VNC-2Q	M-9253	CS31-4-4/0
VGC-2Q-V3	-	CS31-4-4/0C
VGC-2Q-V5	-	CS31-4-4/0D
VGC-2Q-V8	-	CS31-4-4/0F
VGC-2Q-V20	-	CS31-4-4/0G
VNC-3Q	M-8359	CS31-4-500K
HAA-1Y-325C	M-6269	CS32-2-#1D
HAA-1Y-7C	M-6270	CS32-2-#1F
HAA-1Y-11C	M-6271	CS32-2-#1G
HAA-1V-162C	M-6016	CS32-2-#2C
HAA-1V-350C	M-2576	CS32-2-#2D
HAA-1V-7C	M-2514	CS32-2-#2F
HAA-1V-11C	M-2515	CS32-2-#2G
HAA-1T-162C	-	CS32-2-#2SC
HAA-1T-350C	-	CS32-2-#2SD
HAA-1T-7C	-	CS32-2-#2SF
HAA-1T-11C	-	CS32-2-#2SG
HAA-1L-162C	M-8014	CS32-2-#4C
HAA-1L-350C	M-8015	CS32-2-#4D
HAA-1L-7C	M-2516	CS32-2-#4F
HAA-1L-11C	M-2517	CS32-2-#4G
HAH-2C-350C	M-8504	CS32-4-1/0D
HAH-2C-8C	M-8505	CS32-4-1/0F
HAH-2C-20C	M-6272	CS32-4-1/0G
HAH-2G-350C	M-2776	CS32-4-2/0D
HAH-2G-8C	M-6273	CS32-4-2/0F
HAH-2G-20C	M-6274	CS32-4-2/0G

## Exothermic welding system

### Cross reference

Cadweld cat. no.	Thermoweld cat. no.	Blackburn cat. no.
HAH-2L-350C	M-6275	CS32-4-3/0D
HAH-2L-8C	M-6276	CS32-4-3/0F
HAH-2L-20C	M-6278	CS32-4-3/0G
HAH-2Q-350C	M-9236	CS32-4-4/0D
HAH-2Q-8C	M-9237	CS32-4-4/0F
HAH-2Q-20C	M-9238	CS32-4-4/0G
VSC-1Y	M-589	CS3-4-#1
VSC-1Y-V3C	M-2482	CS3-4-#1C
VSC-1Y-V5C	M-2483	CS3-4-#1D
VSC-1Y-V8C	M-2484	CS3-4-#1F
VSC-1Y-V21C	M-2485	CS3-4-#1G
VSC-1V	M-588	CS3-4-#2
VSC-1V-V3C	M-9233	CS3-4-#2C
VSC-1V-V5C	M-2480	CS3-4-#2D
VSC-1V-V8C	M-2583	CS3-4-#2F
VSC-1V-V21C	M-2481	CS3-4-#2G
VSC-1T	-	CS3-4-#2S
VSC-1T-V3C	-	CS3-4-#2SC
VSC-1T-V5C	-	CS3-4-#2SD
VSC-1T-V8C	-	CS3-4-#2SF
VSC-1T-V21C	-	CS3-4-#2SG
VSC-1L	M-586	CS3-4-#4
VSC-1L-V3C	M-2476	CS3-4-#4C
VSC-1L-V5C	M-2477	CS3-4-#4D
VSC-1L-V8C	M-2478	CS3-4-#4F
VSC-1L-V21C	M-2479	CS3-4-#4G
VSC-1H	M-585	CS3-4-#6
VSC-2C	M-590	CS3-4-1/0
VSC-2C-V3C	M-2486	CS3-4-1/0C
VSC-2C-V5C	M-2487	CS3-4-1/0D
VSC-2C-V8C	M-2488	CS3-4-1/0F
VSC-2C-V21C	M-2489	CS3-4-1/0G
HCA-1Y-350C	-	CS34-2-#1D
HCA-1Y-7C	-	CS34-2-#1F
HCA-1Y-11C	-	CS34-2-#1G
HCA-1V-162C	-	CS34-2-#2C
HCA-1V-350C	-	CS34-2-#2D
HCA-1V-7C	-	CS34-2-#2F
HCA-1V-11C	-	CS34-2-#2G
HCA-1T-162C	-	CS34-2-#2SC
HCA-1T-350C	-	CS34-2-#2SD
HCA-1T-7C	-	CS34-2-#2SF
HCA-1T-11C	-	CS34-2-#2SG
HCA-1L-162C	-	CS34-2-#4C
HCA-1L-350C	-	CS34-2-#4D
HCA-1L-7C	-	CS34-2-#4F
HCA-1L-11C	-	CS34-2-#4G
VSC-2G	M-591	CS3-4-2/0
VSC-2G-V3C	M-8833	CS3-4-2/0C
VSC-2G-V5C	M-2490	CS3-4-2/0D
VSC-2G-V8C	M-2491	CS3-4-2/0F

Cadweld cat. no.	Thermoweld cat. no.	Blackburn cat. no.
VSC-2G-V21C	M-2492	CS3-4-2/0G
VSC-2V	M-594	CS3-4-250K
VSC-2L	M-592	CS3-4-3/0
VSC-2L-V3C	M-2493	CS3-4-3/0C
VSC-2L-V5C	M-2494	CS3-4-3/0D
VSC-2L-V8C	M-2495	CS3-4-3/0F
VSC-2L-V21C	M-2496	CS3-4-3/0G
VSC-3A	M-595	CS3-4-300K
VSC-3D	M-596	CS3-4-350K
VSC-2Q	M-593	CS3-4-4/0
VSC-2Q-V3C	M-9021	CS3-4-4/0C
VSC-2Q-V5C	M-2497	CS3-4-4/0D
VSC-2Q-V8C	M-2498	CS3-4-4/0F
VSC-2Q-V21C	M-2499	CS3-4-4/0G
HTC-2C-350C	-	CS34-4-1/0D
HTC-2C-8C	-	CS34-4-1/0F
HTC-2C-20C	-	CS34-4-1/0G
HTC-2G-350C	-	CS34-4-2/0D
HTC-2G-8C	-	CS34-4-2/0F
HTC-2G-20C	-	CS34-4-2/0G
HTC-2L-350C	-	CS34-4-3/0D
HTC-2L-8C	-	CS34-4-3/0F
HTC-2L-20C	-	CS34-4-3/0G
HTC-2Q-350C	-	CS34-4-4/0D
HTC-2Q-8C	-	CS34-4-4/0F
HTC-2Q-20C	-	CS34-4-4/0G
VSC-3Q	M-598	CS3-4-500K
VSD-4Y	M-600	CS3-5-1000K
VSD-4L	M-599	CS3-5-750K
VVC-1Y	M-1219	CS4-4-#1
VVC-1Y-V3	-	CS4-4-#1C
VVC-1Y-V5	-	CS4-4-#1D
VVC-1Y-V8	-	CS4-4-#1F
VVC-1Y-V21	-	CS4-4-#1G
VVC-1V	M-1218	CS4-4-#2
VVC-1V-V3	-	CS4-4-#2C
VVC-1V-V5	-	CS4-4-#2D
VVC-1V-V8	-	CS4-4-#2F
VVC-1V-V21	-	CS4-4-#2G
VVC-1T	-	CS4-4-#2S
VVC-1T-V3	-	CS4-4-#2SC
VVC-1T-V5	-	CS4-4-#2SD
VVC-1T-V8	-	CS4-4-#2SF
VVC-1T-V21	-	CS4-4-#2SG
VVC-1L	M-1216	CS4-4-#4
VVC-1L-V3	-	CS4-4-#4C
VVC-1L-V5	-	CS4-4-#4D
VVC-1L-V8	-	CS4-4-#4F
VVC-1L-V21	-	CS4-4-#4G
VVC-1H	M-1215	CS4-4-#6
VVR-2C	M-1220	CS4-5-1/0

## Exothermic welding system

### Cross reference

Cadweld cat. no.	Thermoweld cat. no.	Blackburn cat. no.
VVR-2C-V3		CS4-5-1/0C
VVR-2C-V5		CS4-5-1/0D
VVR-2C-V8		CS4-5-1/0F
VVR-2C-V20		CS4-5-1/0G
VVR-2G	M-1221	CS4-5-2/0
VVR-2G-V3		CS4-5-2/0C
VVR-2G-V5		CS4-5-2/0D
VVR-2G-V8		CS4-5-2/0F
VVR-2G-V20		CS4-5-2/0G
VVR-2V	M-1224	CS4-5-250K
VVR-2L	M-1222	CS4-5-3/0
VVR-2L-V3		CS4-5-3/0C
VVR-2L-V5		CS4-5-3/0D
VVR-2L-V8		CS4-5-3/0F
VVR-2L-V20		CS4-5-3/0G
VVR-2Q	M-1223	CS4-5-4/0
VVR-2Q-V3		CS4-5-4/0C
VVR-2Q-V5		CS4-5-4/0D
VVR-2QV8		CS4-5-4/0F
VVR-2Q-V20		CS4-5-4/0G
VFC-1Y	M-1639	CS7-4-#1
VFC-1Y-V3		CS7-4-#1C
VFC-1Y-V5		CS7-4-#1D
VFC-1Y-V8		CS7-4-#1F
VFC-1Y-V21		CS7-4-#1G
VFC-1V	M-1638	CS7-4-#2
VFC-1V-V3		CS7-4-#2C
VFC-1V-V5		CS7-4-#2D
VFC-1V-V8		CS7-4-#2F
VFC-1V-V21		CS7-4-#2G
VFC-1T		CS7-4-#2S
VFC-1T-V3		CS7-4-#2SC
VFC-1T-V5		CS7-4-#2SD
VFC-1T-V8		CS7-4-#2SF
VFC-1T-V21		CS7-4-#2SG
VFC-1L	M-1636	CS7-4-#4
VFC-1L-V3		CS7-4-#4C
VFC-1L-V5		CS7-4-#4D
VFC-1L-V8		CS7-4-#4F
VFC-1L-V21		CS7-4-#4G
VFC-2C	M-1640	CS7-4-1/0
VFC-2C-V3		CS7-4-1/0C
VFC-2C-V5		CS7-4-1/0D
VFC-2C-V8		CS7-4-1/0F
VFC-2C-V20		CS7-4-1/0G
VFC-2G	M-1641	CS7-4-2/0
VFC-2G-V3		CS7-4-2/0C
VFC-2G-V5		CS7-4-2/0D
VFC-2G-V8		CS7-4-2/0F
VFC-2G-V20		CS7-4-2/0G
VFR-2V	M-1644	CS7-5-250K

Cadweld cat. no.	Thermoweld cat. no.	Blackburn cat. no.
VFR-2L		M-1642 CS7-5-3/0
VFR-2L-V3		— CS7-5-3/0C
VFR-2L-V5		— CS7-5-3/0D
VFR-2L-V8		— CS7-5-3/0F
VFR-2L-V20		— CS7-5-3/0G
VFR-3A		M-1645 CS7-5-300K
VFR-2Q		M-1643 CS7-5-4/0
VFR-2Q-V3		— CS7-5-4/0C
VFR-2Q-V5		— CS7-5-4/0D
VFR-2Q-V8		— CS7-5-4/0F
VFR-2Q-V20		— CS7-5-4/0G
VFF-3D		M-1646 CS7-6-350K
VFF-3Q		M-1648 CS7-6-500K
HAA-1Y		M-631 CS8-2-#1
HAA-1V		M-630 CS8-2-#2
HAA-1T		— CS8-2-#2S
HAA-1L		M-629 CS8-2-#4
HAA-1H		M-628 CS8-2-#6
HCA-1Y		M-605 CS9-2-#1
HCA-1V		M-604 CS9-2-#2
HCA-1T		— CS9-2-#2S
HCA-1L		M-603 CS9-2-#4
HCA-1H		M-602 CS9-2-#6
15		15 15BKB
25		25 25BKB
32		32 32BKB
45		45 45BKB
65		65 65BKB
90		90 90BKB
115		115 115BKB
150		150 150BKB
200		200 200BKB
250		250 250BKB
L160		40-0106-00 HCPK4
L159		40-0107-00 HCPK5
T314		38-0135-00 WWB1
T314A		38-0135-01 WRB1
T313		38-0306-00 BFC
T320		38-0309-00 FGUN
T394		38-3922-00 BCM
B136A/B		40-0319-01/3/5/6 STM1
T403		38-4129-00 MSC
B144A/B/C/E		38-4061/2/3/4-00 PACK-A

## Exothermic welding system

### Cross reference

#### Sure Shot® cross reference – Type CR1

Ground rod size (in.)	Conductor size (AWG)		Cadweld cat. no. Type GR (CR1)	Thermoweld cat. no. Type CR-1	Blackburn cat. no. Type CR1
	Solid	Stranded			
$\frac{1}{2}$	6, 8	8	GR1-141G	–	–
	3, 4	4, 6	GR1-141L	–	–
	1, 2	2, 3	GR1-141V	–	–
$\frac{5}{8}$	6, 8	8	GR1-161G	M-2012	SCR1-58-6808
	3, 4	4, 6	GR1-161L	M-2013	SCR1-58-3446
	1, 2	2, 3	GR1-161V	M-2014	SCR1-58-1223
	2/0, 1/0	1/0, 1	GR1-162C	M-2015	SCR1-58-2010
	–	2/0	GR1-162G	M-2016	SCR1-58-0020
$\frac{3}{4}$	6, 8	8	GR1-181G	M-2017	SCR1-34-6808
	3, 4	4, 6	GR1-181L	M-2018	SCR1-34-3446
	1, 2	2, 3	GR1-181V	M-2019	SCR1-34-1223
	2/0, 1/0	1/0, 1	GR1-182C	M-2020	SCR1-34-2010
	–	2/0	GR1-182G	M-2021	SCR1-34-0020
	–	4/0	GR1-182Q	–	SCR1-34-0040

#### Sure Shot® cross reference – Type CR2

Ground rod size (in.)	Conductor size (AWG)		Cadweld cat. no. Type GR (CR2)	Thermoweld cat. no. Type CR-2	Blackburn cat. no. Type CR1
	Solid	Stranded			
$\frac{1}{2}$	6, 8	8	GT1-141G	–	–
	3, 4	4, 6	GT1-141L	–	–
	1, 2	2, 3	GT1-141V	–	–
$\frac{5}{8}$	6, 8	8	GT1-161G	M-2027	SCR2-58-6808
	3, 4	4, 6	GT1-161L	M-2028	SCR2-58-3446
	1, 2	2, 3	GT1-161V	M-2029	SCR2-58-1223
	2/0, 1/0	1/0, 1	GT1-162C	M-2030	SCR2-58-2010
	–	2/0	–	–	SCR2-58-0020*
$\frac{3}{4}$	6, 8	8	GT1-181G	M-2031	SCR2-34-6808
	3, 4	4, 6	GT1-181L	M-2032	SCR2-34-3446
	1, 2	2, 3	GT1-181V	M-2033	SCR2-34-1223
	2/0, 1/0	1/0, 1	GT1-182C	M-2034	SCR2-34-2010
	–	2/0	–	–	SCR2-34-0020*
	–	4/0	–	–	SCR2-34-0040*

\* Future development.

Cadweld is a trademark of Erico International Corporation. Thermoweld is a trademark of Continental Industries.

## Exothermic welding system

### Cross reference

#### Sure Shot® cross reference – Type CR17

Ground rod size (in.)	Conductor size (AWG)		Cadweld cat. no. Type GR (CR17)	Thermoweld cat. no. –	Blackburn cat. no. Type CR1
	Solid	Stranded			
$\frac{1}{2}$	6, 8	8	NT1-141G	–	–
	3, 4	4, 6	NT1-141L	–	–
	1, 2	2, 3	–	–	–
$\frac{5}{8}$	6, 8	8	NT1-161G	–	SCR17-58-6808
	3, 4	4, 6	NT1-161L	–	SCR17-58-3446
	1, 2	2, 3	NT1-161V	–	SCR17-58-1223
	2/0, 1/0	1/0, 1	–	–	SCR17-58-2010*
	–	2/0	–	–	SCR17-58-0020*
$\frac{3}{4}$	6, 8	8	NT1-181G	–	SCR17-34-6808
	3, 4	4, 6	NT1-181L	–	SCR17-34-3446
	1, 2	2, 3	NT1-181V	–	SCR17-34-1223
	2/0, 1/0	1/0, 1	–	–	SCR17-34-2010*
	–	2/0	–	–	SCR17-34-0020*
	–	4/0	–	–	SCR17-34-0040*

\* Future development.

#### Sure Shot cross reference – Type CR24

Ground rod size (in.)	Conductor size (AWG)		Cadweld cat. no. Type NX (CR24)	Thermoweld cat. no. Type CR-24	Blackburn cat. no. Type CR24
	Solid	Stranded			
$\frac{1}{2}$	6, 8	8	NX1-141G	–	–
	3, 4	4, 6	NX1-141L	–	–
	1, 2	2, 3	–	–	–
$\frac{5}{8}$	6, 8	8	NX1-161G	–	SCR24-58-6808
	3, 4	4, 6	NX1-161L	–	SCR24-58-3446
	1, 2	2, 3	NX1-161V	–	SCR24-58-1223
	2/0, 1/0	1/0, 1	–	–	SCR24-58-2010*
	–	2/0	–	–	SCR24-58-0020*
$\frac{3}{4}$	6, 8	8	NX1-181G	–	SCR24-34-6808
	3, 4	4, 6	NX1-181L	–	SCR24-34-3446
	1, 2	2, 3	NX1-181V	–	SCR24-34-1223
	2/0, 1/0	1/0, 1	–	–	SCR24-34-2010*

#### Sure Shot cross reference – Type CR25

Ground rod size (in.)	Conductor size (AWG)		Cadweld cat. no. –	Thermoweld cat. no. Type CR-25	Blackburn cat. no. Type CR25
	Solid	Stranded			
$\frac{5}{8}$	6, 8	8	–	M-2006	–
	3, 4	4, 6	–	M-2007	–
	1, 2	2, 3	–	M-2008	–
$\frac{3}{4}$	2/0, 1/0	1/0, 1	–	M-2023	SCR17-58-6808
	6, 8	8	–	M-2068	SCR17-58-3446
	3, 4	4, 6	–	M-2069	SCR17-58-1223

\* Future development.

Cadweld is a trademark of Erico International Corporation. Thermoweld is a trademark of Continental Industries.

## Exothermic welding system

### Conductor properties

#### Conductor properties

Size (AWG or kcmil)	Area	Conductors						Direct current resistance at 75 °C (167 °F)							
		Stranding			Overall			Uncoated		Copper		Aluminum			
		Quantity	Diameter mm	Diameter in.	mm	in.	Area mm <sup>2</sup>	Area in. <sup>2</sup>	ohm/ km	ohm/ kft	ohm/ km	ohm/ kft	ohm/ km	ohm/ kft	
18	0.823	1620	1	—	—	1.02	0.040	0.823	0.001	25.5	7.77	26.5	8.08	42.0	12.8
18	0.823	1620	7	0.39	0.015	1.16	0.046	1.06	0.002	26.1	7.95	27.7	8.45	42.8	13.1
16	1.31	2580	1	—	—	1.29	0.051	1.31	0.002	16.0	4.89	16.7	5.08	26.4	8.05
16	1.31	2580	7	0.49	0.019	1.46	0.058	1.68	0.003	16.4	4.99	17.3	5.29	26.9	8.21
14	2.08	4110	1	—	—	1.63	0.064	2.08	0.003	10.1	3.07	10.4	3.19	16.6	5.06
14	2.08	4110	7	0.62	0.024	1.85	0.073	2.68	0.004	10.3	3.14	10.7	3.26	16.9	5.17
12	3.31	6530	1	—	—	2.05	0.081	3.31	0.005	6.34	1.93	6.57	2.01	10.45	3.18
12	3.31	6530	7	0.78	0.030	2.32	0.092	4.25	0.006	6.50	1.98	6.73	2.05	10.69	3.25
10	5.261	10380	1	—	—	2.588	0.102	5.26	0.008	3.984	1.21	4.148	1.26	6.561	2.00
10	5.261	10380	7	0.98	0.038	2.95	0.116	6.76	0.011	4.070	1.24	4.226	1.29	6.679	2.04
8	8.367	16510	1	—	—	3.264	0.128	8.37	0.013	2.506	0.764	2.579	0.786	4.125	1.26
8	8.367	16510	7	1.23	0.049	3.71	0.146	10.76	0.017	2.551	0.778	2.653	0.809	4.204	1.28
6	13.30	26240	7	1.56	0.061	4.67	0.184	17.09	0.027	1.608	0.491	1.671	0.510	2.652	0.808
4	21.15	41740	7	1.96	0.077	5.89	0.232	27.19	0.042	1.010	0.308	1.053	0.321	1.666	0.508
3	26.67	52620	7	2.20	0.087	6.60	0.260	34.28	0.053	0.802	0.245	0.833	0.254	1.320	0.403
2	33.62	66360	7	2.47	0.097	7.42	0.292	43.23	0.067	0.634	0.194	0.661	0.201	1.045	0.319
1	42.41	83690	19	1.69	0.066	8.43	0.332	55.80	0.087	0.505	0.154	0.524	0.160	0.829	0.253
1/0	53.49	105600	19	1.89	0.074	9.45	0.372	70.41	0.109	0.399	0.122	0.415	0.127	0.660	0.201
2/0	67.43	133100	19	2.13	0.084	10.62	0.418	88.74	0.137	0.3170	0.0967	0.329	0.101	0.523	0.159
3/0	85.01	167800	19	2.39	0.094	11.94	0.470	111.9	0.173	0.2512	0.0766	0.2610	0.0797	0.413	0.126
4/0	107.2	211600	19	2.68	0.106	13.41	0.528	141.1	0.219	0.1996	0.0608	0.2050	0.0626	0.328	0.100
250	—	—	37	2.09	0.082	14.61	0.575	168	0.260	0.1687	0.0515	0.1753	0.0535	0.2778	0.0847
300	—	—	37	2.29	0.090	16.00	0.630	201	0.312	0.1409	0.0429	0.1463	0.0446	0.2318	0.0707
350	—	—	37	2.47	0.097	17.30	0.681	235	0.364	0.1205	0.0367	0.1252	0.0382	0.1984	0.0605
400	—	—	37	2.64	0.104	18.49	0.728	268	0.416	0.1053	0.0321	0.1084	0.0331	0.1737	0.0529
500	—	—	37	2.95	0.116	20.65	0.813	336	0.519	0.0845	0.0258	0.0869	0.0265	0.1391	0.0424
600	—	—	61	2.52	0.099	22.68	0.893	404	0.626	0.0704	0.0214	0.0732	0.0223	0.1159	0.0353
700	—	—	61	2.72	0.107	24.49	0.964	471	0.730	0.0603	0.0184	0.0622	0.0189	0.0994	0.0303
750	—	—	61	2.82	0.111	25.35	0.998	505	0.782	0.0563	0.0171	0.0579	0.0176	0.0927	0.0282
800	—	—	61	2.91	0.114	26.16	1.030	538	0.834	0.0528	0.0161	0.0544	0.0166	0.0868	0.0265
900	—	—	61	3.09	0.122	27.79	1.094	606	0.940	0.0470	0.0143	0.0481	0.0147	0.0770	0.0235
1000	—	—	61	3.25	0.128	29.26	1.152	673	1.042	0.0423	0.0129	0.0434	0.0132	0.0695	0.0212

FPN: the construction information is per NEMA WC8-1992 or ANSI/UL 1581-1998. The resistance is calculated per national bureau of standards handbook 100, dated 1966, and handbook 109, dated 1972.

70–625 Tables

National Electrical Code®, 2002 edition. NEC and National Electrical Code are registered trademarks of the National Fire Protection Association, Inc.

## Exothermic welding system

Table B.310.1

**Table B.310.1**

Ampacities of two or three insulated conductors, rated 0 through 2000 V, within an overall covering

(multiconductor cable), in raceway in free air based on ambient air temperature of 30 °C (86 °F)

Temperature rating of conductor (see Table 310.13)

Size (AWG or kcmil)	60 °C (140 °F)		75 °C (167 °F)		90 °C (194 °F)		60 °C (140 °F)		75 °C (167 °F)		90 °C (194 °F)			
	Types TW, UF	Types RHW, THHW, THW, THWN, XHHW, ZW	Types THHN, THHW, THW-2, THWN-2, RHH, RWH-2, USE-2, XHHN, XHHW-2, ZW-2		Type TW	Types RHW, THHW, THW, THWN, XHHW	Types THHN, THHW, THW-2, THWN-2, RHH, RWH-2, USE-2, XHHW, XHHW-2, ZW-2		Size (AWG or kcmil)					
			Copper				Aluminum or copper-clad aluminum							
14	16*	18*		21*	—	—		—	—	—	—	14		
12	20*	24*		27*	16*	18*		18*	—	21*	21*	12		
10	27*	33*		36*	21*	25*		25*	—	28*	28*	10		
8	36	43		48	28	33		33	—	37	37	8		
6	48	58		65	38	45		45	—	51	51	6		
4	66	79		89	51	61		61	—	69	69	4		
3	76	90		102	59	70		70	—	79	79	3		
2	88	105		119	69	83		83	—	93	93	2		
1	102	121		137	80	95		95	—	106	106	1		
1/0	121	145		163	94	113		113	—	127	127	1/0		
2/0	138	166		186	108	129		129	—	146	146	2/0		
3/0	158	189		214	124	147		147	—	167	167	3/0		
4/0	187	223		253	147	176		176	—	197	197	4/0		
250	205	245		276	160	192		192	—	217	217	250		
300	234	281		317	185	221		221	—	250	250	300		
350	255	305		345	202	242		242	—	273	273	350		
400	274	328		371	218	261		261	—	295	295	400		
500	315	378		427	254	303		303	—	342	342	500		
600	343	413		468	279	335		335	—	378	378	600		
700	376	452		514	310	371		371	—	420	420	700		
750	387	466		529	321	384		384	—	435	435	750		
800	397	479		543	331	397		397	—	450	450	800		
900	415	500		570	350	421		421	—	477	477	900		
1000	448	542		617	382	460		460	—	521	521	1000		

### Correction factors

Ambient temp. (°C)	For ambient temperatures other than 30 °C (86 °F), multiply the ampacities shown above by the appropriate factor shown below.						Ambient temp. (°F)
21–25	1.08	1.05	1.04	1.08	1.05	—	1.04 70–77
26–30	1.00	1.00	1.00	1.00	1.00	—	1.00 79–86
31–35	0.91	0.94	0.96	0.91	0.94	—	0.96 88–95
36–40	0.82	0.88	0.91	0.82	0.88	—	0.91 97–104
41–45	0.71	0.82	0.87	0.71	0.82	—	0.87 106–113
46–50	0.58	0.75	0.82	0.58	0.75	—	0.82 115–122
51–55	0.41	0.67	0.76	0.41	0.67	—	0.76 124–131
56–60	—	0.58	0.71	—	0.58	—	0.71 133–140
61–70	—	0.33	0.58	—	0.33	—	0.58 142–158
71–80	—	—	0.41	—	—	—	0.41 160–176

\* Unless otherwise specifically permitted elsewhere in this code, the overcurrent protection for these conductor types shall not exceed 15 A for 14 AWG, 20 A for 12 AWG, and 30 A for 10 AWG copper; or 15 A for 12 AWG and 25 A for 10 AWG aluminum and copper-clad aluminum. National Electrical Code®, 2002 Edition. NEC and National Electrical Code are registered trademarks of the National Fire Protection Association, Inc.

## Exothermic welding system

Table B.310.1 (continued)

### Metric conductors

Wire size mm <sup>2</sup>	AWG	Circ mils	# of strands	Strand diameter	Diameter mm	Diameter in.	Color code	Die code
10	8	19,730	1	3.57	3.57	0.140	Red	21
10	8	19,730	7	1.35	4.05	0.159	Red	21
16	6	31,558	1	4.50	4.50	0.177	Blue	24
16	6	31,558	7	1.70	5.10	0.200	Blue	24
25	2	49,325	7	2.14	6.42	0.253	Gray	29
25	2	49,325	19	1.35	6.75	0.266	Brown	33
35	1	69,055	19	1.53	7.65	0.300	Green	37
50	1/0	98,650	19	1.78	8.90	0.350	Pink	42
70	2/0	138,110	19	2.14	10.70	0.421	Black	45
95	3/0	187,500	19	2.52	12.60	0.496	Orange	50
95	3/0	187,500	37	1.78	12.46	0.490	Orange	50
120	250	236,760	37	2.03	14.21	0.560	Purple	54
150	300	295,950	37	2.25	15.75	0.620	White	66
185	-	365,000	61	2.52	17.64	0.695	Red	71
240	500	473,500	61	2.25	20.25	0.797	Brown	87
300	-	591,900	61	2.52	22.68	0.893	Green	94
400	-	789,200	61	2.85	25.65	1.000	Black	106
400	-	789,200	91	2.36	25.96	1.022	Black	106
500	-	986,500	61	3.20	28.80	1.134	-	125
500	-	986,500	91	2.65	29.15	1.148	-	-
630	-	1,243,000	127	2.52	32.76	1.290	-	-
800	-	1,578,400	127	2.85	37.05	1.459	-	-
1000	-	1,973,000	127	3.20	41.60	1.638	-	-

## Exothermic welding system

Table C1

**Conductors**

Type	Conductor Size (AWG/ kcmil)	Metric designator (trade size)									
		16 ( $\frac{1}{2}$ )	21 ( $\frac{3}{4}$ )	27 (1)	35 ( $1\frac{1}{4}$ )	41 ( $1\frac{1}{2}$ )	53 (2)	63 ( $2\frac{1}{2}$ )	78 (3)	91 ( $3\frac{1}{2}$ )	103 (4)
RHH,	14	4	7	11	20	27	46	80	120	157	201
RHW,	12	3	6	9	17	23	38	66	100	131	167
RHW-2	10	2	5	8	13	18	30	53	81	105	135
	8	1	2	4	7	9	16	28	42	55	70
	6	1	1	3	5	8	13	22	34	44	56
	4	1	1	2	4	6	10	17	26	34	44
	3	1	1	1	4	5	9	15	23	30	38
	2	1	1	1	3	4	7	13	20	26	33
	1	0	1	1	1	3	5	9	13	17	22
1/0	0	1	1	1	2	4	7	11	15	19	
2/0	0	1	1	1	2	4	6	10	13	17	
3/0	0	0	1	1	1	3	5	8	11	14	
4/0	0	0	1	1	1	3	5	7	9	12	
250	0	0	0	1	1	1	3	5	7	9	
300	0	0	0	1	1	1	3	5	6	8	
350	0	0	0	1	1	1	3	4	6	7	
400	0	0	0	1	1	1	2	4	5	7	
500	0	0	0	0	1	1	2	3	4	6	
600	0	0	0	0	1	1	1	3	4	5	
700	0	0	0	0	0	1	1	2	3	4	
750	0	0	0	0	0	1	1	2	3	4	
800	0	0	0	0	0	1	1	1	1	3	
900	0	0	0	0	0	1	1	1	1	3	
1000	0	0	0	0	0	1	1	1	2	3	
TW,	14	8	15	25	43	58	96	168	254	332	424
THHW,	12	6	11	19	33	45	74	129	195	255	326
THW,	10	5	8	14	24	33	55	96	145	190	243
THW-2	8	2	5	8	13	18	30	53	81	105	135
RHH*,	14	6	10	6	28	39	64	112	169	221	282
RHW*,	12	4	8	13	23	31	51	90	136	177	227
RHW-2*	10	3	6	10	18	24	40	70	106	138	177
	8	1	4	6	10	14	24	42	63	83	106

**Table C1**

Maximum number of conductors or fixture wires in electrical metallic tubing (emt) (based on Table 1, Chapter 9)

**Conductors**

Type	Conductor Size (AWG/ kcmil)	Metric designator (trade size)									
		16 ( $\frac{1}{2}$ )	21 ( $\frac{3}{4}$ )	27 (1)	35 ( $1\frac{1}{4}$ )	41 ( $1\frac{1}{2}$ )	53 (2)	63 ( $2\frac{1}{2}$ )	78 (3)	91 ( $3\frac{1}{2}$ )	103 (4)
RHH*,	6	1	3	4	8	11	18	32	48	63	81
RHW*,	4	1	1	3	6	8	13	24	36	47	60
RHW-2*,	3	1	1	3	5	7	12	20	31	40	52
TW, THW,	2	1	1	2	4	6	10	17	26	34	44
THHW,	1	1	1	1	3	4	7	12	18	24	31
THW-2	1/0	0	1	1	2	3	6	10	16	20	26
	2/0	0	1	1	1	3	5	9	13	17	22
	3/0	0	1	1	1	2	4	7	11	15	19
	4/0	0	0	1	1	1	3	6	9	12	16
	250	0	0	1	1	1	3	5	7	10	13
	300	0	0	1	1	1	2	4	6	8	11
	350	0	0	0	1	1	1	4	6	7	10
	400	0	0	0	1	1	1	3	5	7	9
	500	0	0	0	1	1	1	3	4	6	7
	600	0	0	0	1	1	1	2	3	4	6
	700	0	0	0	0	1	1	1	3	4	5
	750	0	0	0	0	1	1	1	3	4	5
	800	0	0	0	0	1	1	1	3	3	5
	900	0	0	0	0	0	1	1	2	3	4
	1000	0	0	0	0	0	1	1	2	3	4
THHN,	14	12	22	35	61	84	138	241	364	476	608
THWN,	12	9	16	26	45	61	101	176	266	347	443
THWN-2	10	5	10	16	28	38	63	111	167	219	279
	8	3	6	9	16	22	36	64	96	126	161
	6	2	4	7	12	16	26	46	69	91	116
	4	1	2	4	7	10	16	28	43	56	71
	3	1	1	3	6	8	13	24	36	47	60
	2	1	1	3	5	7	11	20	30	40	51
	1	1	1	1	4	5	8	15	22	29	37
	1/0	1	1	1	3	4	7	12	19	25	32
	2/0	0	1	1	2	3	6	10	16	20	26
	3/0	0	1	1	1	3	5	8	13	17	22
	4/0	0	1	1	1	2	4	7	11	14	18
	250	0	0	1	1	1	3	6	9	11	15
	300	0	0	1	1	1	2	4	6	9	11
	350	0	0	1	1	1	2	4	6	9	11
	400	0	0	0	1	1	1	4	6	8	10
	500	0	0	0	1	1	1	3	5	6	8
	600	0	0	0	1	1	1	2	4	5	7
	700	0	0	0	1	1	1	2	3	4	6
	750	0	0	0	0	1	1	1	3	4	5
	800	0	0	0	0	1	1	1	3	4	5
	900	0	0	0	0	1	1	1	3	3	4
	1000	0	0	0	0	1	1	1	2	3	4

National Electrical Code®, 2002 Edition. NEC and National Electrical Code are registered trademarks of the National Fire Protection Association, Inc.

## Exothermic welding system

Table C4

### Conductors

Type	Conductor Size (AWG/ kcmil)	Metric designator (trade size)									
		16 ( $\frac{1}{8}$ )	21 ( $\frac{3}{16}$ )	27 (1)	35 ( $\frac{1}{4}$ )	41 ( $\frac{1}{2}$ )	53 (2)	63 ( $\frac{2}{3}$ )	78 (3)	91 ( $\frac{3}{4}$ )	103 (4)
RHH,	14	4	8	13	22	30	49	70	108	144	186
RHW,	12	4	6	11	18	25	41	58	89	120	154
RHW-2											
RHH,	10	3	5	8	15	20	33	47	72	97	124
RHW,	8	1	3	4	8	10	17	24	38	50	65
RHW-2	6	1	1	3	6	8	14	19	30	40	52
	4	1	1	3	5	6	11	15	23	31	41
	3	1	1	2	4	6	9	13	21	28	36
	2	1	1	1	3	5	8	11	18	24	31
	1	0	1	1	2	3	5	7	12	16	20
	1/0	0	1	1	1	3	4	6	10	14	18
	2/0	0	1	1	1	2	4	6	9	12	15
	3/0	0	0	1	1	1	3	5	7	10	13
	4/0	0	0	1	1	1	3	4	6	9	11
	250	0	0	1	1	1	3	5	6	8	
	300	0	0	0	1	1	1	3	4	6	7
	350	0	0	0	1	1	1	2	4	5	7
	400	0	0	0	1	1	1	2	3	5	6
	500	0	0	0	1	1	1	3	4	5	5
	600	0	0	0	0	1	1	1	1	3	4
	700	0	0	0	0	0	1	1	1	2	3
	800	0	0	0	0	0	1	1	1	2	3
	900	0	0	0	0	0	1	1	1	2	3
	1000	0	0	0	0	0	0	1	1	1	3
TW,	14	10	17	27	47	64	104	147	228	304	392
THHW,	12	7	13	21	36	49	80	113	175	234	301
THW,	10	5	9	15	27	36	59	84	130	174	224
THW-2	8	3	5	8	15	20	33	47	72	97	124
RHH*, RHW*, RHW-2*	14	6	11	18	31	42	69	98	151	202	261
RHH*, RHW*, RHW-2*	12	5	9	14	25	34	56	79	122	163	209
RHH*, RHW*, RHW-2*	10	4	7	11	19	26	43	61	95	127	163
RHH*, RHW*, RHW-2*	8	2	4	7	12	16	26	37	57	76	98
RHH*, RHW*, RHW-2*	6	1	3	5	9	12	20	28	43	58	75
RHH*, RHW*, RHW-2*	4	1	2	4	6	9	15	21	32	43	56

Note: This table is for concentric stranded conductors only. For compact stranded conductors, Table C4(A) should be used. \* Types RHH, RHW, and RHW-2 without outer covering. National Electrical Code®, 2002 Edition. NEC and National Electrical Code are registered trademarks of the National Fire Protection Association, Inc.

Table C4

Maximum number of conductors or fixture wires in intermediate metal conduit (imc) (based on Table 1, Chapter 9)

### Conductors

Type	Conductor Size (AWG/ kcmil)	Metric designator (trade size)									
		16 ( $\frac{1}{8}$ )	21 ( $\frac{3}{16}$ )	27 (1)	35 ( $\frac{1}{4}$ )	41 ( $\frac{1}{2}$ )	53 (2)	63 ( $\frac{2}{3}$ )	78 (3)	91 ( $\frac{3}{4}$ )	103 (4)
TW, THW,	3	1	1	3	6	8	13	18	28	37	48
THHW, THW-2	2	1	1	3	5	6	11	15	23	31	41
	1	1	1	1	3	4	7	11	16	22	28
	1/0	1	1	1	3	4	6	9	14	19	24
	2/0	0	1	1	2	3	5	8	12	16	20
	3/0	0	1	1	1	3	4	6	10	13	17
	4/0	0	1	1	1	2	4	5	8	11	14
	250	0	0	1	1	1	3	4	7	9	12
	300	0	0	1	1	1	2	4	6	8	10
	350	0	0	1	1	1	2	3	5	7	9
	400	0	0	0	1	1	1	3	4	6	8
	500	0	0	0	1	1	1	2	4	5	7
	600	0	0	0	1	1	1	1	3	4	5
	700	0	0	0	0	1	1	1	2	3	4
	800	0	0	0	0	1	1	1	2	3	4
	900	0	0	0	0	1	1	1	2	3	4
	1000	0	0	0	0	0	1	1	1	3	3
THHN, THWN, THWN-2	14	14	24	39	68	91	149	211	326	436	562
	12	10	17	29	49	67	109	154	238	318	410
	10	6	11	18	31	42	68	97	150	200	258
	8	3	6	10	18	24	39	56	86	115	149
	6	2	4	7	13	17	28	40	62	83	107
	4	1	3	4	8	10	17	25	38	51	66
	3	1	2	4	6	9	15	21	32	43	56
	2	1	1	3	5	7	12	17	27	36	47
	1	1	1	2	4	5	9	13	20	27	35
	1/0	1	1	1	3	4	8	11	17	23	29
	2/0	1	1	1	3	4	6	9	14	19	24
	3/0	0	1	1	2	3	5	7	12	16	20
	4/0	0	1	1	1	2	4	6	9	13	17
	250	0	0	1	1	1	3	5	8	10	13
	300	0	0	1	1	1	3	4	7	9	12
	350	0	0	1	1	1	2	4	6	8	10
	400	0	0	1	1	1	2	3	5	7	9
	500	0	0	0	1	1	1	3	4	6	7
	600	0	0	0	1	1	1	2	3	5	6
	700	0	0	0	1	1	1	1	3	4	5
	750	0	0	0	1	1	1	1	3	4	5
	800	0	0	0	0	1	1	1	1	3	4
	900	0	0	0	0	1	1	1	2	3	4
	1000	0	0	0	0	1	1	1	1	2	3

## Exothermic welding system

Table C8

**Table C8**

Maximum number of conductors or fixture wires  
in rigid metal conduit (RMC) (Based on Table 1,  
Chapter 9)

### Conductors

Type	Conductor Size (AWG/ kcmil)	Metric designator (trade size)											
		16 ( $\frac{1}{2}$ )	21 ( $\frac{3}{4}$ )	27 (1)	35 (1 $\frac{1}{4}$ )	41 (1 $\frac{1}{2}$ )	53 (2)	63 (2 $\frac{1}{4}$ )	78 (3)	91 (3 $\frac{1}{4}$ )	103 (4)	129 (5)	155 (6)
RHH,	14	4	7	12	21	28	46	66	102	136	176	276	398
RHW,	12	3	6	10	17	23	38	55	85	113	146	229	330
RHW-2	10	3	5	8	14	19	31	44	68	91	11w8	185	267
	8	1	2	4	7	10	16	23	36	48	61	97	139
	6	1	1	3	6	8	13	18	29	38	49	77	112
	4	1	1	2	4	6	10	14	22	30	38	60	87
	3	1	1	2	4	5	9	12	19	26	34	53	76
	2	1	1	1	3	4	7	11	17	23	29	46	66
	1	0	1	1	1	3	5	7	11	15	19	30	44
	1/0	0	1	1	1	2	4	6	10	13	17	26	38
	2/0	0	1	1	1	2	4	5	8	11	14	23	33
	3/0	0	0	1	1	1	3	4	7	10	12	20	28
	4/0	0	0	1	1	1	3	4	6	8	11	17	24
	250	0	0	0	1	1	1	3	4	6	8	13	18
	300	0	0	0	1	1	1	2	4	5	7	11	16
	350	0	0	0	1	1	1	2	4	5	6	10	15
	400	0	0	0	1	1	1	1	3	4	6	9	13
	500	0	0	0	1	1	1	1	3	4	5	8	11
	600	0	0	0	0	1	1	1	2	3	4	6	9
	700	0	0	0	0	1	1	1	1	3	4	6	8
	750	0	0	0	0	0	1	1	1	3	3	5	8
	800	0	0	0	0	0	1	1	1	2	3	5	7
	900	0	0	0	0	0	1	1	1	2	3	5	7
	1000	0	0	0	0	0	1	1	1	1	3	4	6
TW,	14	9	15	25	44	59	98	140	216	288	370	581	839
THHW,	12	7	12	19	33	45	75	107	165	221	284	446	644
THW,	10	5	9	14	25	34	56	80	123	164	212	332	480
THW-2*	8	3	5	8	14	19	31	44	68	91	118	185	267
RHH*, RHW*, RHW-2*	14	6	10	17	29	39	65	93	143	191	246	387	558
RHH*, RHW*, RHW-2*	12	5	8	13	23	32	52	75	115	154	198	311	448
RHH*, RHW*, RHW-2*	10	3	6	10	18	25	41	58	90	120	154	242	350
RHH*, RHW*, RHW-2*	8	1	4	6	11	15	24	35	54	72	92	145	209

## Exothermic welding system

Table C8 (continued)

### Conductors

Type	Conductor Size (AWG/ kcmil)	Metric designator (trade size)											
		16 ( $\frac{1}{2}$ )	21 ( $\frac{3}{4}$ )	27 (1)	35 (1 $\frac{1}{4}$ )	41 (1 $\frac{1}{2}$ )	53 (2)	63 (2 $\frac{1}{4}$ )	78 (3)	91 (3 $\frac{1}{4}$ )	103 (4)	129 (5)	155 (6)
RHH*	6	1	3	5	8	11	18	27	41	55	71	111	160
RHW*	4	1	1	3	6	8	14	20	31	41	53	83	120
RHW-2*	3	1	1	3	5	7	12	17	26	35	45	71	103
TW,	2	1	1	2	4	6	10	14	22	30	38	60	87
THW,	1	1	1	1	3	4	7	10	15	21	27	42	61
THHW,	1/0	0	1	1	2	3	6	8	13	18	23	36	52
THW-2	2/0	0	1	1	2	3	5	7	11	15	19	31	44
	3/0	0	1	1	1	2	4	6	9	13	16	26	37
	4/0	0	0	1	1	1	3	5	8	10	14	21	31
	250	0	0	1	1	1	3	4	6	8	11	17	25
	300	0	0	1	1	1	2	3	5	7	9	15	22
	350	0	0	0	1	1	1	3	5	6	8	13	19
	400	0	0	0	1	1	1	3	4	6	7	12	17
	500	0	0	0	1	1	1	2	3	5	6	10	14
	600	0	0	0	1	1	1	1	3	4	5	8	12
	700	0	0	0	0	1	1	1	2	3	4	7	10
	750	0	0	0	0	1	1	1	2	3	4	7	10
	800	0	0	0	0	1	1	1	2	3	4	6	9
	900	0	0	0	0	1	1	1	1	3	4	6	8
	1000	0	0	0	0	0	1	1	1	2	3	5	8
THHN,	14	13	22	36	63	85	140	200	309	412	531	833	1202
THWN,	12	9	16	26	46	62	102	146	225	301	387	608	877
THWN-2	10	6	10	17	29	39	64	92	142	189	244	383	552
	8	3	6	9	16	22	37	53	82	109	140	221	318
	6	2	4	7	12	16	27	38	59	79	101	159	230
	4	1	2	4	7	10	16	23	36	48	62	98	141
	3	1	1	3	6	8	14	20	31	41	53	83	120
	2	1	1	3	5	7	11	17	26	34	44	70	100
	1	1	1	1	4	5	8	12	19	25	33	51	74
	1/0	1	1	1	3	4	7	10	16	21	27	43	63
	2/0	0	1	1	2	3	6	8	13	18	23	36	52
	3/0	0	1	1	1	3	5	7	11	15	19	30	43
	4/0	0	1	1	1	2	4	6	9	12	16	25	36
	250	0	0	1	1	1	3	5	7	10	13	20	29
	300	0	0	1	1	1	3	4	6	8	11	17	25
	350	0	0	1	1	1	2	3	5	7	10	15	22
	400	0	0	1	1	1	2	3	5	7	8	13	20
	500	0	0	0	1	1	1	2	4	5	7	11	16
	600	0	0	0	1	1	1	1	3	4	6	9	13
	700	0	0	0	1	1	1	1	3	4	5	8	11
	750	0	0	0	0	1	1	1	3	4	5	7	11
	800	0	0	0	0	1	1	1	2	3	4	7	10
	900	0	0	0	0	1	1	1	2	3	4	6	9
	1000	0	0	0	0	1	1	1	1	3	4	6	8

Note: This table is for concentric stranded conductors only. For compact stranded conductors, Table C8(A) should be used.

\* Types RHH, RHW, and RHW-2 without outer covering.

National Electrical Code®, 2002 Edition. NEC and National Electrical Code are registered trademarks of the National Fire Protection Association, Inc.

## Appendix

### Part number index

Cat. no.	Page	Cat. no.	Page	Cat. no.	Page	Cat. no.	Page
BB1-4-121	49	BB2-4-183	50	BB7-5-382	52	BS4-4-14114	56
BB1-4-141	49	BB2-4-184	50	BB7-5-383	52	BS4-4-181	56
BB1-4-14112	49	BB2-4-3161	50	BB7-5-384	52	BS4-4-18112	56
BB1-4-14114	49	BB2-4-3162	50	BCM	58	BS4-4-182	56
BB1-4-142	49	BB2-4-381	50	BFC	58	BS4-4-3161	56
BB1-4-14212	49	BB2-4-38112	50	BS1-4-121	55	BS4-4-316112	56
BB1-4-181	49	BB2-5-122	50	BS1-4-141	55	BS4-4-3162	56
BB1-4-18112	49	BB2-5-143	50	BS1-4-14112	55	BS4-4-381	56
BB1-4-182	49	BB2-5-144	50	BS1-4-14114	55	BS4-4-38112	56
BB1-4-183	49	BB2-5-382	50	BS1-4-181	55	BS4-5-12112	56
BB1-4-184	49	BB2-5-383	50	BS1-4-18112	55	BS4-5-122	56
BB1-4-3161	49	BB2-5-384	50	BS1-4-182	55	BS4-5-142	56
BB1-4-3162	49	BB3-4-121	51	BS1-4-3161	55	BS4-5-382	56
BB1-4-381	49	BB3-4-141	51	BS1-4-316112	55	BS5-4-121	57
BB1-4-38112	49	BB3-4-14112	51	BS1-4-3162	55	BS5-4-141	57
BB14-4-121	53	BB3-4-14114	51	BS1-4-381	55	BS5-4-14112	57
BB14-4-141	53	BB3-4-142	51	BS1-4-38112	55	BS5-4-14114	57
BB14-4-14112	53	BB3-4-14212	51	BS1-5-12112	55	BS5-4-181	57
BB14-4-14114	53	BB3-4-181	51	BS1-5-122	55	BS5-4-18112	57
BB14-4-142	53	BB3-4-18112	51	BS1-5-142	55	BS5-4-182	57
BB14-4-14212	53	BB3-4-182	51	BS1-5-382	55	BS5-4-3161	57
BB14-4-181	53	BB3-4-183	51	BS2-4-121	55	BS5-4-316112	57
BB14-4-18112	53	BB3-4-184	51	BS2-4-141	55	BS5-4-3162	57
BB14-4-182	53	BB3-4-3161	51	BS2-4-14112	55	BS5-4-381	57
BB14-4-183	53	BB3-4-3162	51	BS2-4-14114	55	BS5-4-38112	57
BB14-4-184	53	BB3-4-381	51	BS2-4-181	55	BS5-5-12112	57
BB14-4-3161	53	BB3-4-38112	51	BS2-4-18112	55	BS5-5-122	57
BB14-4-3162	53	BB3-5-122	51	BS2-4-182	55	BS5-5-142	57
BB14-4-381	53	BB3-5-143	51	BS2-4-3161	55	BS5-5-382	57
BB14-4-38112	53	BB3-5-144	51	BS2-4-316112	55	CB1-4-#1181	45
BB14-5-122	53	BB3-5-382	51	BS2-4-3162	55	CB1-4-#2181	45
BB14-5-143	53	BB3-5-383	51	BS2-4-381	55	CB1-4-#4181	45
BB14-5-144	53	BB3-5-384	51	BS2-4-38112	55	CB1-4-1/0141	45
BB14-5-382	53	BB7-4-121	52	BS2-5-12112	55	CB1-4-1/0181	45
BB14-5-383	53	BB7-4-141	52	BS2-5-122	55	CB1-4-1/03161	45
BB14-5-384	53	BB7-4-14112	52	BS2-5-142	55	CB1-4-2/0141	45
BB1-5-122	49	BB7-4-14114	52	BS2-5-382	55	CB1-4-2/0181	45
BB1-5-143	49	BB7-4-142	52	BS3-4-121	56	CB1-4-2/03161	45
BB1-5-144	49	BB7-4-14212	52	BS3-4-141	56	CB1-4-250K141	45
BB1-5-382	49	BB7-4-181	52	BS3-4-14112	56	CB1-4-250K14112	45
BB1-5-383	49	BB7-4-18112	52	BS3-4-14114	56	CB1-4-250K142	45
BB1-5-384	49	BB7-4-182	52	BS3-4-181	56	CB1-4-250K143	45
BB2-4-121	50	BB7-4-183	52	BS3-4-18112	56	CB1-4-250K3161	45
BB2-4-141	50	BB7-4-184	52	BS3-4-3161	56	CB1-4-3/0141	45
BB2-4-14112	50	BB7-4-3161	52	BS3-4-316112	56	CB1-4-3/0161	45
BB2-4-14114	50	BB7-4-3162	52	BS3-4-381	56	CB1-4-3/018	45
BB2-4-142	50	BB7-4-381	52	BS3-4-38112	56	CB1-4-300K141	45
BB2-4-14212	50	BB7-4-38112	52	BS3-5-12112	56	CB1-4-300K14112	45
BB2-4-181	50	BB7-5-122	52	BS4-4-121	56	CB1-4-300K142	45
BB2-4-18112	50	BB7-5-143	52	BS4-4-141	56	CB1-4-300K143	45
BB2-4-182	50	BB7-5-144	52	BS4-4-14112	56	CB1-4-350K141	45

## Appendix

### Part number index

Cat. no.	Page	Cat. no.	Page	Cat. no.	Page	Cat. no.	Page
CB1-4-350K14112	45	CB4-4-#2S12112	46	CC11-7-250K2/0	19	CC1-4-350K	11
CB1-4-350K142	45	CB4-4-#2S14112	46	CC11-7-250K250K	19	CC1-4-4/0	11
CB1-4-350K143	45	CB4-4-#2S38112	46	CC11-7-250K3/0	19	CC1-4-4/OS	11
CB1-4-4/0141	45	CB4-4-1/012112	46	CC11-7-250K4/0	19	CC1-4-500K	11
CB1-4-4/014112	45	CB4-4-1/014112	46	CC11-7-3/0#1	19	CC1-5-1000K	11
CB1-4-4/0142	45	CB4-4-1/038112	46	CC11-7-3/0#2	19	CC1-5-750K	11
CB1-4-4/0143	45	CB4-4-2/012112	46	CC11-7-3/01/0	19	CC2-4-#1#1	12
CB1-4-4/03161	45	CB4-4-2/014112	46	CC11-7-3/02/0	19	CC2-4-#1#2	12
CB1-4-500K14112	45	CB4-4-2/038112	46	CC11-7-3/03/0	19	CC2-4-#1#2S	12
CB1-4-500K142	45	CB4-4-214112	46	CC11-7-300K#1	19	CC2-4-#1#4	12
CB1-4-500K143	45	CB4-4-250K12112	46	CC11-7-300K#2	19	CC2-4-#2#2	12
CB1-4-500K38112	45	CB4-4-250K14112	46	CC11-7-300K1/0	19	CC2-4-#2#2S	12
CB1-5-1000K122	45	CB4-4-250K38112	46	CC11-7-300K2/0	19	CC2-4-#2#4	12
CB1-5-1000K123	45	CB4-4-3/012112	46	CC11-7-300K3/0	19	CC2-4-#2S#2	12
CB1-5-1000K143	45	CB4-4-3/014112	46	CC11-7-300K4/0	19	CC2-4-#2S#2S	12
CB1-5-1000K382	45	CB4-4-300K12112	46	CC11-7-350K#1	19	CC2-4-#2S#4	12
CB1-5-1000K383	45	CB4-4-300K14112	46	CC11-7-350K#2	19	CC2-4-#4#4	12
CB1-5-750K142	45	CB4-4-300K38112	46	CC11-7-350K1/0	19	CC2-4-1/0#1	12
CB1-5-750K143	45	CB4-4-350K12112	46	CC11-7-350K2/0	19	CC2-4-1/0#2	12
CB1-5-750k38112	45	CB4-4-350K14112	46	CC11-7-4/0#1	19	CC2-4-1/0#2S	12
CB1-5-750k382	45	CB4-4-350K38112	46	CC11-7-4/0#2	19	CC2-4-1/0#4	12
CB1-5-750K383	45	CB4-4-4/012112	46	CC11-7-4/01/0	19	CC2-4-1/01/0	12
CB29-10-#1122	47	CB4-4-4/014112	46	CC11-7-4/02/0	19	CC2-4-1000K1/0	13
CB29-10-#1142	47	CB4-4-4/038112	46	CC11-7-4/03/0	19	CC2-4-1000K2/0	13
CB29-10-#1382	47	CB4-4-500K1411	46	CC11-7-4/04/0	19	CC2-4-1000K250K	13
CB29-10-#2122	47	CB4-4-500K38112	46	CC11-8-300K250K	19	CC2-4-1000K300K	13
CB29-10-#2S122	47	CB4-5-1000K12112	46	CC11-8-300K300K	19	CC2-4-1000K350K	13
CB29-10-1/0122	47	CB4-5-1000K38112	46	CC11-8-350K250K	19	CC2-4-1000K4/0	13
CB29-10-1/0142	47	CB4-5-500K12112	46	CC11-8-350K3/0	19	CC2-4-2/0#1	12
CB29-10-1/0382	47	CB4-5-750K12112	46	CC11-8-350K300K	19	CC2-4-2/0#2	12
CB29-10-2/0122	47	CB4-5-750K38112	46	CC11-8-350K350K	19	CC2-4-2/0#2S	12
CB29-10-2/0142	47	CC11-7-#1#1	19	CC11-8-350K4/0	19	CC2-4-2/0#4	12
CB29-102/0382	47	CC11-7-#1#2	19	CC11-8-500K1/0	19	CC2-4-2/01/0	12
CB29-10-250K122	47	CC11-7-#1#4	19	CC11-8-500K2/0	19	CC2-4-2/02/0	12
CB29-10-250K142	47	CC11-7-#2#2	19	CC11-8-500K250K	19	CC2-4-250K#1	12
CB29-10-250K382	47	CC11-7-#2#4	19	CC11-8-500K3/0	19	CC2-4-250K#2	12
CB29-10-4/0122	47	CC11-7-#2S#2S	19	CC11-8-500K300K	19	CC2-4-250K#2S	12
CB29-10-4/0142	47	CC11-7-#4#4	19	CC11-8-500K350K	19	CC2-4-250K#4	12
CB29-104/0382	47	CC11-7-#6#6	19	CC11-8-500K4/0	19	CC2-4-250K1/0	12
CB29-10-500K122	47	CC11-7-#6S#6S	19	CC11-8-500K500K	19	CC2-4-250K2/0	12
CB29-10-500K142	47	CC11-7-1/0#1	19	CC1-3-#1	11	CC2-4-250K250K	12
CB29-10-500K382	47	CC11-7-1/0#2	19	CC1-3-#1S	11	CC2-4-250K4/0	12
CB29-10-750K	47	CC11-7-1/0#4	19	CC1-3-#2	11	CC2-4-3/0#1	12
CB29-10-750K142	47	CC11-7-1/01/0	19	CC1-3-#2S	11	CC2-4-3/0#2	12
CB29-10-750K382	47	CC11-7-2/0#1	19	CC1-3-#3	11	CC2-4-3/0#2S	12
CB29-9-#2142	47	CC11-7-2/0#2	19	CC1-4-1/0	11	CC2-4-3/0#4	12
CB29-9-#2382	47	CC11-7-2/01/0	19	CC1-4-1/0S	11	CC2-4-3/01/0	12
CB29-9-#2S142	47	CC11-7-2/02/0	19	CC1-4-2/0	11	CC2-4-3/02/0	12
CB29-9-#2S382	47	CC11-7-250K#1	19	CC1-4-250K	11	CC2-4-3/03/0	12
CB4-4-#212112	46	CC11-7-250K#2	19	CC1-4-3/0	11	CC2-4-300K#1	13
CB4-4-#238112	46	CC11-7-250K1/0	19	CC1-4-300K	11	CC2-4-300K#2	13

## Appendix

### Part number index

Cat. no.	Page	Cat. no.	Page	Cat. no.	Page	Cat. no.	Page
CC2-4-300K#2S	13	CC4-4-#2#2	14	CC4-5-500K350K	15	CC7-4-#1#1S	17
CC2-4-300K#4	13	CC4-4-#2#4	14	CC4-5-500K4/0	15	CC7-4-#1#2	17
CC2-4-300K1/0	13	CC4-4-#2S#2S	14	CC4-5-500K500K	15	CC7-4-#1#2S	17
CC2-4-300K2/0	13	CC4-4-#4#4	14	CC6-4-#1#1	16	CC7-4-#1#4	17
CC2-4-300K250K	13	CC4-4-1/0#1	14	CC6-4-#1#2	16	CC7-4-#1#6	17
CC2-4-300K3/0	13	CC4-4-1/0#2	14	CC6-4-#1#4	16	CC7-4-#1#6S	17
CC2-4-300K300K	13	CC4-4-1/0#4	14	CC6-4-#2#2	16	CC7-4-#1#8	17
CC2-4-300K4/0	13	CC4-4-1/01/0	14	CC6-4-#2#4	16	CC7-4-#1#8S	17
CC2-4-350K#1	13	CC4-4-2/0#1	14	CC6-4-#2S#2S	16	CC7-4-#1S#1	17
CC2-4-350K#2	13	CC4-4-2/0#2	14	CC6-4-#4#4	16	CC7-4-#1S#2	17
CC2-4-350K#4	13	CC4-42/01/0	14	CC6-4-1/0#1	16	CC7-4-#1S#2S	17
CC2-4-350K1/0	13	CC4-4-2/02/0	14	CC6-4-1/0#2	16	CC7-4-#1S#4	17
CC2-4-350K2/0	13	CC4-4-250K#1	14	CC6-4-1/0#4	16	CC7-4-#1S#6	17
CC2-4-350K250K	13	CC4-4-250K#2	14	CC6-4-1/01/0	16	CC7-4-#1S#6S	17
CC2-4-350K3/0	13	CC4-4-250K1/0	14	CC6-4-2/0#1	16	CC7-4-#1S#8	17
CC2-4-350K300K	13	CC4-4-250K2/0	14	CC6-4-2/0#2	16	CC7-4-#1S#8S	17
CC2-4-350K350K	13	CC4-4-250K250K	14	CC6-42/01/0	16	CC7-4-#2#2	17
CC2-4-350K4/0	13	CC4-4-250K3/0	14	CC6-4-2/02/0	16	CC7-4-#2#4	17
CC2-4-4/0#1	12	CC4-4-250K4/0	14	CC6-4-250K#1	16	CC7-4-#2#6	17
CC2-4-4/0#2	12	CC4-4-3/0#1	14	CC6-4-250K#2	16	CC7-4-#2#6S	17
CC2-4-4/0#2S	12	CC4-4-3/0#2	14	CC6-4-250K1/0	16	CC7-4-#2#8	17
CC2-4-4/0#4	12	CC4-4-3/01/0	14	CC6-4-250K2/0	16	CC7-4-#2#8S	17
CC2-4-4/01/0	12	CC4-4-3/02/0	14	CC6-4-250K250K	16	CC7-4-#2S#2	17
CC2-4-4/02/0	12	CC4-4-3/03/0	14	CC6-4-250K3/0	16	CC7-4-#2S#2S	17
CC2-4-4/03/0	12	CC4-4300K#1	15	CC6-4-250K4/0	16	CC7-4-#2S#4	17
CC2-4-4/04/0	12	CC4-4-300K#2	15	CC6-4-3/0#1	16	CC7-4-#2S#6	17
CC2-4-500K#1	13	CC4-4-300K1/0	15	CC6-4-3/0#2	16	CC7-4-#2S#6S	17
CC2-4-500K#2	13	CC4-4-300K2/0	15	CC6-4-3/01/0	16	CC7-4-#2S#8	17
CC2-4-500K#4	13	CC4-4-300K250K	15	CC6-4-3/02/0	16	CC7-4-#2S#8S	17
CC2-4-500K1/0	13	CC4-4-300K3/0	15	CC6-4-3/03/0	16	CC7-4-#4#4	17
CC2-4-500K2/0	13	CC4-4-300K300K	15	CC6-4300K#1	16	CC7-4-#4#6	17
CC2-4-500K250K	13	CC4-4-300K4/0	15	CC6-4-300K#2	16	CC7-4-#4#6S	17
CC2-4-500K300K	13	CC4-4-350K#1	15	CC6-4-300K1/0	16	CC7-4-#4#8	17
CC2-4-500K350K	13	CC4-4-350K#2	15	CC6-4-300K2/0	16	CC7-4-1/0#1	17
CC2-4-500K4/0	13	CC4-4-350K1/0	15	CC6-4-300K250K	16	CC7-4-1/0#1S	17
CC2-4-500K500K	13	CC4-4-350K3/0	15	CC6-4-300K3/0	16	CC7-4-1/0#2	17
CC2-4-750K1/0	13	CC4-4-350K300K	15	CC6-4-300K300K	16	CC7-4-1/0#2S	17
CC2-4-750K2/0	13	CC4-4-350K350K	15	CC6-4-300K4/0	16	CC7-4-1/0#4	17
CC2-4-750K250K	13	CC4-4-350K4/0	15	CC6-4-350K2/0	16	CC7-4-1/0#6	17
CC2-4-750K300K	13	CC4-4-4/0#1	14	CC6-4-350K3/0	16	CC7-4-1/0#6S	17
CC2-4-750K350K	13	CC4-4-4/0#2	14	CC6-4-350K300K	16	CC7-4-1/0#8	17
CC2-4-750K4/0	13	CC4-4-4/01/0	14	CC6-4-350K350K	16	CC7-4-1/0#8S	18
CC2-5-1000K1000K	13	CC4-4-4/02/0	14	CC6-4-350K4/0	16	CC7-4-1/01/0	17
CC2-5-1000K500K	13	CC4-4-4/03/0	14	CC6-4-4/0#1	16	CC7-4-1/01/OS	17
CC2-5-1000K750K	13	CC4-4-4/04/0	14	CC6-4-4/0#2	16	CC7-4-1/0S#1	17
CC2-5-750K500K	13	CC4-4-4350K250K	15	CC6-4-4/01/0	16	CC7-4-1/0S#1S	17
CC2-5-750K750K	13	CC4-4-500K1/0	15	CC6-4-4/02/0	16	CC7-4-1/0S#2	17
CC4-350K2/0	15	CC4-4-500K2/0	15	CC6-4-4/03/0	16	CC7-4-1/0S#2S	17
CC4-4-#1#1	14	CC4-5-500K250K	15	CC6-4-4/04/0	16	CC7-4-1/0S#4	17
CC4-4-#1#2	14	CC4-5-500K3/0	15	CC6-4-4-4350K250K	16	CC7-4-1/0S#6	17
CC4-4-#1#4	14	CC4-5-500K300K	15	CC7-4-#1#1	17	CC7-4-1/0S#6S	17

## Appendix

### Part number index

Cat. no.	Page						
CC7-4-1/0S#8	17	CC7-4-4/0S#8S	18	CR1-4-625300K	21	CR2-4-500L4/0	22
CC7-4-1/0S#8S	17	CC7-4-4/0S1/0	18	CR1-4-625350K	21	CR2-4-625#1	22
CC7-4-1/0S1/0	17	CC7-4-4/0S1/OS	18	CR1-4-6254/0	21	CR2-4-625#2	22
CC7-4-1/0S1/OS	17	CC7-4-4/0S2/0	18	CR1-4-625500K	21	CR2-4-625#2S	22
CC7-4-2/0#1	18	CC7-4-4/0S3/0	18	CR1-4-750#1	21	CR2-4-6251/0	22
CC7-4-2/0#1S	18	CC7-4-4/0S4/0	18	CR1-4-750#2	21	CR2-4-6251/0S	22
CC7-4-2/0#2	18	CC7-4-4/0S4/OS	18	CR1-4-750#2S	21	CR2-4-6252/0	22
CC7-4-2/0#4	18	CR1-3-500#2	21	CR1-4-7501/0	21	CR2-4-625250K	22
CC7-4-2/0#6	18	CR1-3-500#2S	21	CR1-4-7501/OS	21	CR2-4-6253/0	22
CC7-4-2/0#6S	18	CR1-3-500#4	21	CR1-4-7502/0	21	CR2-4-625300K	22
CC7-4-2/0#8	18	CR1-3-500#4S	21	CR1-4-750250K	21	CR2-4-625350K	22
CC7-4-2/0#8S	18	CR1-3-500#6	21	CR1-4-7503/0	21	CR2-4-6254/0	22
CC7-4-2/01/0	18	CR1-3-500#6S	21	CR1-4-750300K	21	CR2-4-625500K	22
CC7-4-2/01/0S	18	CR1-3-500L#2	21	CR1-4-750350K	21	CR2-4-750#1	22
CC7-4-2/02/0	18	CR1-3-500L#2S	21	CR1-4-7504/0	21	CR2-4-750#2	22
CC7-4-3/0#1	18	CR1-3-500L#4	21	CR1-4-750500K	21	CR2-4-750#2S	22
CC7-4-3/0#1S	18	CR1-3-500L#4S	21	CR2-3-500#4	22	CR2-4-7501/0	22
CC7-4-3/0#2	18	CR1-3-500L#6	21	CR2-3-500#4S	22	CR2-4-7501/0S	22
CC7-4-3/0#2S	18	CR1-3-500L#6S	21	CR2-3-500#6	22	CR2-4-7502/0	22
CC7-4-3/0#4	18	CR1-3-625#4	21	CR2-3-500#6S	22	CR2-4-750250K	22
CC7-4-3/0#6	18	CR1-3-625#4S	21	CR2-3-500L#4	22	CR2-4-7503/0	22
CC7-4-3/0#6S	18	CR1-3-625#6	21	CR2-3-500L#4S	22	CR2-4-750300K	22
CC7-4-3/0#8	18	CR1-3-625#6S	21	CR2-3-500L#6	22	CR2-4-750350K	22
CC7-4-3/0#8S	18	CR1-3-750#4	21	CR2-3-500L#6S	22	CR2-4-7504/0	22
CC7-4-3/01/0	18	CR1-3-750#4S	21	CR2-3-625#4	22	CR2-4-750500K	22
CC7-4-3/01/0S	18	CR1-3-750#6	21	CR2-3-625#4S	22	CR3-10-625500K	23
CC7-4-3/02/0	18	CR1-3-750#6S	21	CR2-3-625#6	22	CR3-10-750350K	23
CC7-4-3/03/0	18	CR1-4-500#1	21	CR2-3-625#6S	22	CR3-10-750500K	23
CC7-4-4/0#1	18	CR1-4-5001/0	21	CR2-3-750#4	22	CR3-9-5001/0	23
CC7-4-4/0#1S	18	CR1-4-5001/OS	21	CR2-3-750#4S	22	CR3-9-5001/0S	23
CC7-4-4/0#2	18	CR1-4-5002/0	21	CR2-3-750#6	22	CR3-9-5002/0	23
CC7-4-4/0#2S	18	CR1-4-500250K	21	CR2-3-750#6S	22	CR3-9-500250K	23
CC7-4-4/0#4	18	CR1-4-5003/0	21	CR2-4-500#1	22	CR3-9-5003/0	23
CC7-4-4/0#6	18	CR1-4-500300K	21	CR2-4-500#2	22	CR3-9-500300K	23
CC7-4-4/0#6S	18	CR1-4-5004/0	21	CR2-4-500#2S	22	CR3-9-5004/0	23
CC7-4-4/0#8	18	CR1-4-500L#1	21	CR2-4-5001/0	22	CR3-9-500L1/0	23
CC7-4-4/0#8S	18	CR1-4-500L1/0	21	CR2-4-5001/OS	22	CR3-9-500L1/0S	23
CC7-4-4/01/0	18	CR1-4-500L1/OS	21	CR2-4-5002/0	22	CR3-9-500L2/0	23
CC7-4-4/01/0S	18	CR1-4-500L2/0	21	CR2-4-500250K	22	CR3-9-500L250K	23
CC7-4-4/02/0	18	CR1-4-500L250K	21	CR2-4-5003/0	22	CR3-9-500L3/0	23
CC7-4-4/03/0	18	CR1-4-500L3/0	21	CR2-4-500300K	22	CR3-9-500L4/0	23
CC7-4-4/04/0	18	CR1-4-500L300K	21	CR2-4-5004/0	22	CR3-9-6251/0	23
CC7-4-4/04/0S	18	CR1-4-500L4/0	21	CR2-4-500L#1	22	CR3-9-6251/0S	23
CC7-4-4/0S#1	18	CR1-4-625#1	21	CR2-4-500L#2	22	CR3-9-6252/0	23
CC7-4-4/0S#1S	18	CR1-4-625#2	21	CR2-4-500L#2S	22	CR3-9-625250K	23
CC7-4-4/0S#2	18	CR1-4-625#2S	21	CR2-4-500L1/0	22	CR3-9-6253/0	23
CC7-4-4/0S#2S	18	CR1-4-6251/0	21	CR2-4-500L1/OS	22	CR3-9-625300K	23
CC7-4-4/0S#4	18	CR1-4-6251/OS	21	CR2-4-500L2/0	22	CR3-9-625350K	23
CC7-4-4/0S#6	18	CR1-4-6252/0	21	CR2-4-500L250K	22	CR3-9-6254/0	23
CC7-4-4/0S#6S	18	CR1-4-625250K	21	CR2-4-500L3/0	22	CR3-9-7501/0	23
CC7-4-4/0S#8	18	CR1-4-6253/0	21	CR2-4-500L300K	22	CR3-9-7501/0S	23

## Appendix

### Part number index

Cat. no.	Page	Cat. no.	Page	Cat. no.	Page	Cat. no.	Page
CR3-9-7502/0	23	CRE4-3-#4Z	26	CS25-4-#2G	37	CS27-4-#4	38
CR3-9-750250K	23	CRE4-3-1/OY	26	CS25-4-#2S	36	CS27-4-#4C	39
CR3-9-7503/0	23	CRE4-3-1/OZ	26	CS25-4-#2SC	37	CS27-4-#4D	39
CR3-9-750300K	23	CRE4-3-2/OY	26	CS25-4-#2SD	37	CS27-4-#4F	39
CR3-9-7504/0	23	CRE4-3-2/OZ	26	CS25-4-#2SF	37	CS27-4-#4G	39
CRE1-3-#1Y	25	CRE4-3-3/OY	26	CS25-4-#2SG	37	CS27-4-#6	38
CRE1-3-#1Z	25	CRE4-3-3/OZ	26	CS25-4-#4	36	CS27-4-1/0	38
CRE1-3-#2SY	25	CRE4-3-4/OY	26	CS25-4-#4C	37	CS27-4-110C	39
CRE1-3-#2SZ	25	CRE4-3-4/OZ	26	CS25-4-#4D	37	CS27-4-110D	39
CRE1-3-#2Y	25	CRE6-3-#1Y	26	CS25-4-#4F	37	CS27-4-110F	39
CRE1-3-#2Z	25	CRE6-3-#1Z	26	CS25-4-#4G	37	CS27-4-110G	39
CRE1-3-#4Y	25	CRE6-3-#2SY	26	CS25-4-1/0	36	CS27-4-2/0	38
CRE1-3-#4Z	25	CRE6-3-#2SZ	26	CS25-4-1/0C	37	CS27-4-210C	39
CRE1-3-1/OY	25	CRE6-3-#2Y	26	CS25-4-1/0D	37	CS27-4-210D	39
CRE1-3-1/OZ	25	CRE6-3-#2Z	26	CS25-4-1/0F	37	CS27-4-210F	39
CRE1-3-2/OY	25	CRE6-3-#4Y	26	CS25-4-1/0G	37	CS27-4-210G	39
CRE1-3-2/OZ	25	CRE6-3-#4Z	26	CS25-4-2/0	36	CS27-4-250K	38
CRE1-3-3/OY	25	CRE6-4-1/OY	26	CS25-4-2/0C	37	CS27-4-3/0	38
CRE1-3-3/OZ	25	CRE6-4-1/OZ	26	CS25-4-2/0D	37	CS27-4-310C	39
CRE1-3-4/OY	25	CRE6-4-2/OY	26	CS25-4-2/0F	37	CS27-4-310D	39
CRE1-3-4/OZ	25	CRE6-4-2/OZ	26	CS25-4-2/0G	37	CS27-4-310F	39
CRE1-4-#13R	25	CRE6-4-3/OY	26	CS25-4-250K	36	CS27-4-310G	39
CRE1-4-#23R	25	CRE6-4-3/OZ	26	CS25-4-3/0	36	CS27-4-4/0	38
CRE1-4-#2S3R	25	CRE6-4-4/OY	26	CS25-4-3/0C	37	CS27-4-410C	39
CRE1-4-#43R	25	CRE6-4-4/OZ	26	CS25-4-3/0D	37	CS27-4-410D	39
CRE1-4-1/03R	25	CS1-4-1/0	28	CS25-4-3/0F	37	CS27-4-410F	39
CRE1-4-2/03R	25	CS1-4-1000K	28	CS25-4-3/0G	37	CS27-4-410G	39
CRE1-4-3/03R	25	CS1-4-2/0	28	CS25-4-300K	36	CS31-4-#1	40
CRE3-3-#2SY	25	CS1-4-250K	28	CS25-4-350K	36	CS31-4-#1C	41
CRE3-3-#2SZ	25	CS1-4-3/0	28	CS25-4-4/0	36	CS31-4-#1D	41
CRE3-3-#2Y	25	CS1-4-300K	28	CS25-4-4/0C	37	CS31-4-#1F	41
CRE3-3-#2Z	25	CS1-4-350K	28	CS25-4-4/0D	37	CS31-4-#1G	41
CRE3-3-#4Y	25	CS1-4-4/0	28	CS25-4-4/0F	37	CS31-4-#2	40
CRE3-3-#4Z	25	CS1-4-500K	28	CS25-4-4/0G	37	CS31-4-#2C	41
CRE3-4-#1Y	25	CS1-4-750K	28	CS25-4-500K	36	CS31-4-#2D	41
CRE3-4-#1Z	25	CS2-4-1/0	28	CS2-5-500K	28	CS31-4-#2F	41
CRE3-4-1/OY	25	CS2-4-2/0	28	CS27-4-#1	38	CS31-4-#2G	41
CRE3-4-1/OZ	25	CS2-4-250K	28	CS27-4-#1C	39	CS31-4-#2S	40
CRE3-4-2/OY	25	CS2-4-3/0	28	CS27-4-#1D	39	CS31-4-#2SC	41
CRE3-4-2/OZ	25	CS2-4-300K	28	CS27-4-#1F	39	CS31-4-#2SD	41
CRE3-4-3/OY	25	CS2-4-350K	28	CS27-4-#1G	39	CS31-4-#2SF	41
CRE3-4-3/OZ	25	CS2-4-4/0	28	CS27-4-#2	38	CS31-4-#2SG	41
CRE3-4-4/OY	25	CS25-4-#1	36	CS27-4-#2C	39	CS31-4-#4	40
CRE3-4-4/OZ	25	CS25-4-#1C	37	CS27-4-#2D	39	CS31-4-#4C	41
CRE4-3-#1Y	26	CS25-4-#1D	37	CS27-4-#2F	39	CS31-4-#4D	41
CRE4-3-#1Z	26	CS25-4-#1F	37	CS27-4-#2G	39	CS31-4-#4F	41
CRE4-3-#2SY	26	CS25-4-#1G	37	CS27-4-#2S	38	CS31-4-#4G	41
CRE4-3-#2SZ	26	CS25-4-#2	36	CS27-4-#2SC	39	CS31-4-#6	40
CRE4-3-#2Y	26	CS25-4-#2C	37	CS27-4-#2SD	39	CS31-4-1/0	40
CRE4-3-#2Z	26	CS25-4-#2D	37	CS27-4-#2SF	39	CS31-4-1/0C	41
CRE4-3-#4Y	26	CS25-4-#2F	37	CS27-4-#2SG	39	CS31-4-1/0D	41

## Appendix

### Part number index

Cat. no.	Page	Cat. no.	Page	Cat. no.	Page	Cat. no.	Page
CS31-4-1/0F	41	CS3-4-#1/0F	30	CS3-4-250K	29	CS4-5-250K	31
CS31-4-1/0G	41	CS3-4-#1/0G	30	CS3-4-3/0	29	CS4-5-3/0	31
CS31-4-2/0	40	CS3-4-#1C	30	CS3-4-300K	29	CS4-5-3/0C	32
CS31-4-2/0C	41	CS3-4-#1D	30	CS3-4-350K	29	CS4-5-3/0D	32
CS31-4-2/0D	41	CS3-4-#1F	30	CS34-4-#1/0D	43	CS4-5-3/0F	32
CS31-4-2/0F	41	CS3-4-#1G	30	CS34-4-#1/0F	43	CS4-5-3/0G	32
CS31-4-2/0G	41	CS3-4-#2	29	CS34-4-#1/0G	43	CS4-5-4/0	31
CS31-4-250K	40	CS3-4-#2/0C	30	CS34-4-#2/0D	43	CS4-5-4/0C	32
CS31-4-3/0	40	CS3-4-#2/0D	30	CS34-4-#2/0F	43	CS4-5-4/0D	32
CS31-4-3/0C	41	CS3-4-#2/0F	30	CS34-4-#2/0G	43	CS4-5-4/0F	32
CS31-4-3/0D	41	CS3-4-#2/0G	30	CS34-4-#3/0D	43	CS4-5-4/0G	32
CS31-4-3/0F	41	CS3-4-#2C	30	CS34-4-#3/0F	43	CS7-4-#1	33
CS31-4-3/0G	41	CS3-4-#2D	30	CS34-4-#3/0G	43	CS7-4-#1C	34
CS31-4-300K	40	CS3-4-#2F	30	CS34-4-#4/0D	43	CS7-4-#1D	34
CS31-4-350K	40	CS3-4-#2G	30	CS34-4-#4/0F	43	CS7-4-#1F	34
CS31-4-4/0	40	CS3-4-#2S	29	CS34-4-#4/0G	43	CS7-4-#1G	34
CS31-4-4/0C	41	CS3-4-#2SC	30	CS3-4-4/0	29	CS7-4-#2	33
CS31-4-4/0D	41	CS3-4-#2SD	30	CS3-4-500K	29	CS7-4-#2C	34
CS31-4-4/0F	41	CS3-4-#2SF	30	CS3-5-1000K	29	CS7-4-#2D	34
CS31-4-4/0G	41	CS3-4-#2SG	30	CS3-5-750K	29	CS7-4-#2F	34
CS31-4-500K	40	CS3-4-#3/0C	30	CS4-4-#1	31	CS7-4-#2G	34
CS32-2-#1D	42	CS3-4-#3/0D	30	CS4-4-#1C	32	CS7-4-#2S	33
CS32-2-#1F	42	CS3-4-#3/0F	30	CS4-4-#1D	32	CS7-4-#2SC	34
CS32-2-#1G	42	CS3-4-#3/0G	30	CS4-4-#1F	32	CS7-4-#2SD	34
CS32-2-#2C	42	CS3-4-#4	29	CS4-4-#1G	32	CS7-4-#2SF	34
CS32-2-#2D	42	CS3-4-#4/0C	30	CS4-4-#2	31	CS7-4-#2SG	34
CS32-2-#2F	42	CS3-4-#4/0D	30	CS4-4-#2C	32	CS7-4-#4	33
CS32-2-#2G	42	CS3-4-#4/0F	30	CS4-4-#2D	32	CS7-4-#4C	34
CS32-2-#2SC	42	CS3-4-#4/0G	30	CS4-4-#2F	32	CS7-4-#4D	34
CS32-2-#2SD	42	CS3-4-#4C	30	CS4-4-#2G	32	CS7-4-#4F	34
CS32-2-#2SF	42	CS3-4-#4D	30	CS4-4-#2S	31	CS7-4-#4G	34
CS32-2-#2SG	42	CS3-4-#4F	30	CS4-4-#2SC	32	CS7-4-1/0	33
CS32-2-#4C	42	CS3-4-#4G	30	CS4-4-#2SD	32	CS7-4-1/0C	34
CS32-2#4D	42	CS3-4-#6	29	CS4-4-#2SF	32	CS7-4-1/0D	34
CS32-2#4F	42	CS3-4-1/0	29	CS4-4-#2SG	32	CS7-4-1/0F	34
CS32-2#4G	42	CS34-2-#1D	43	CS4-4-#4	31	CS7-4-1/0G	34
CS32-4-#1/0D	42	CS34-2-#1F	43	CS4-4-#4C	32	CS7-4-2/0	33
CS32-4-#1/0F	42	CS34-2-#1G	43	CS4-4-#4D	32	CS7-4-2/0C	34
CS32-4-#1/0G	42	CS34-2-#2C	43	CS4-4-#4F	32	CS7-4-2/0D	34
CS32-4-#2/0D	42	CS34-2-#2D	43	CS4-4-#4G	32	CS7-4-2/0F	34
CS32-4-#2/0F	42	CS34-2-#2F	43	CS4-4-#6	31	CS7-4-2/0G	34
CS32-4-#2/0G	42	CS34-2-#2G	43	CS4-5-1/0	31	CS7-5-250K	33
CS32-4-#3/0D	42	CS34-2-#2SC	43	CS4-5-1/0C	32	CS7-5-3/0	33
CS32-4-#3/0F	42	CS34-2-#2SD	43	CS4-5-1/0D	32	CS7-5-3/0C	34
CS32-4-#3/0G	42	CS34-2-#2SF	43	CS4-5-1/0F	32	CS7-5-3/0D	34
CS32-4-#4/0D	42	CS34-2-#2SG	43	CS4-5-1/0G	32	CS7-5-3/0F	34
CS32-4-#4/0F	42	CS34-2-#4C	43	CS4-5-2/0	31	CS7-5-3/0G	34
CS32-4-#4/0G	42	CS34-2-#4D	43	CS4-5-2/0C	32	CS7-5-300K	33
CS3-4-#1	29	CS34-2-#4F	43	CS4-5-2/0D	32	CS7-5-4/0	33
CS3-4-#1/0C	30	CS34-2-#4G	43	CS4-5-2/0F	32	CS7-5-4/0C	34
CS3-4-#1/0D	30	CS34-2-#4	29	CS4-5-2/0G	32	CS7-5-4/0D	34

## Appendix

### Part number index

Cat. no.	Page	Cat. no.	Page
CS7-5-4/0F	34	SCR1-58-3446	61
CS7-5-4/0G	34	SCR1-58-6808	61
CS7-6-350K	33	SCR17-34-1223	61
CS7-6-500K	33	SCR17-34-3446	61
CS8-2-#1	35	SCR17-34-6808	61
CS8-2-#2	35	SCR17-58-1223	61
CS8-2-#2S	35	SCR17-58-3446	61
CS8-2-#4	35	SCR17-58-6808	61
CS8-2-#6	35	SCR2-34-0020	61
CS9-2-#1	35	SCR2-34-0040	61
CS9-2-#2	35	SCR2-34-1223	61
CS9-2-#2S	35	SCR2-34-2010	61
CS9-2-#4	35	SCR2-34-3446	61
CS9-2-#6	35	SCR2-34-6808	61
FGUN	58	SCR24-34-1223	62
FRAME1	59	SCR24-34-3446	62
FRAME2	59	SCR24-34-6808	62
GPC100	9	SCR24-58-1223	62
GPC101	9	SCR24-58-3446	62
GPC105	9	SCR24-58-6808	62
GPC106	9	SCR25-34-1223	62
GPC110	9	SCR25-34-3446	62
GPC111	9	SCR25-34-6808	62
GPC115	9	SCR25-58-1223	62
GPC116	9	SCR25-58-3446	62
GPC120	9	SCR25-58-6808	62
GPC121	9	SCR2-58-0020	61
GPC125	9	SCR2-58-1223	61
GPC126	9	SCR2-58-2010	61
GRX005	9	SCR2-58-3446	61
HCPK1	59	SCR2-58-6808	61
HCPK2	59	SCR27-34-1223	62
HCPK3	59	SCR27-34-3446	62
HCPK3A	59	SCR27-34-6808	62
HCPK3B	59	SCR27-58-3446	62
HCPK3BMOD	59	SCR27-58-6808	62
HCPK4	59	SHIM	58
HCPK5	59	SLEEVE#6	58
HCPK7	59	SLEEVE#6S	58
HCPK8	59	SLEEVE#8	58
MSC	58	SLEEVE#8S	58
PACK-A	58	STM1-TB	58
SCR1-34-0020	61	WRB1	58
SCR1-34-0040	61	WWB1	58
SCR1-34-1223	61		
SCR1-34-2010	61		
SCR1-34-3446	61		
SCR1-34-6808	61		
SCR1-58-0020	61		
SCR1-58-1223	61		
SCR1-58-2010	61		

## Notes

## Notes

## Notes

**Additional information**

We reserve the right to make technical changes or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB AG does not accept any responsibility whatsoever for potential errors or possible lack of information in this document.

We reserve all rights in this document and in the subject matter and illustrations contained therein. Any reproduction, disclosure to third parties or utilization of its contents – in whole or in parts – is forbidden without prior written consent of ABB AG.





—  
**US**

ABB Installation Products  
Electrification business  
860 Ridge Lake Blvd.  
Memphis, TN 38120  
+1 901-252-5000

**[tnb.abb.com](http://tnb.abb.com)**