Data Sheet DS/268HS/NS-EN Rev. J

Model 268HS Gauge Model 268NS Absolute

ABB 2600T Series Engineered solutions for all applications



TÜV SIL2 certified to IEC 61508

- the smart solution in Safety loop application

Best in Class Safety protection for your plants

- Safe Failure Fraction (SFF): 98.6%
- Diagnostic Coverage (DC): 97.7%
- Undetected Dangerous Failures λDU: 11 FIT

In-situ hardware redundancy (HFT=1)

- a guarantee of true protection

SIL3 capability in redundant architecture (1002)

 Software and hardware development process certified by TÜV

Reduced maintenance costs thanks to the longest proof test interval of 10 years for SIL2 in 1001 architecture

Base accuracy: ±0.075%

Span limits

- 0.27 to 16000kPa; 1.08inH₂O to 2320psi
- 1.1 to 16000kPa abs; 8mmHg to 2320psia

Hardware and software redundancy with MTBF of over 100 years

Full compliance with PED Category IV

- suitable for safety accessory application



General Description

Model 268 is the IEC 61508 TÜV certified Safety 2600T transmitter for SIS and critical applications where safety and performances are the main requirement.

The transmitters detailed in this datasheets have been designed and manufactured according to a certified process which lead to a product specifically suitable for critical applications.

Thanks to the internal software and hardware redundancy, the 268 models have got the IEC 61508 certifications which not only allows installation in conformance with SIL2 (1001) but also to SIL3 in a 1002 architecture.

The 2600T Safety transmitter exceeds the IEC 61508 requirements for SIL2 with a Hardware Fault Tolerance of 1 (HFT = 1) and a Safe Failure Fraction of 98%.

In addition the following requirements of IEC 61508 have been assessed as part of the certification process:

- functional safety (hardware and software) testing;
- electrical safety testing;
- EMC testing;
- environmental testing;
- Quality Assurance in production and product maintenance;
- verification of the product development process.

Furthermore, with a very low Probability of Dangerous Undetected Failures ($\lambda_{DU} = 11$ FIT), the 2600T safety transmitters allow to extend the Proof Test Interval reducing maintenance costs by 50%.

Functional Specifications

Range and span limits

Sensor	Upper Range	Lower Range Limit (LRL)	Minim	um span
Code	Limit (URL)	for 268HS	268HS gauge	268NS absolute
E	16kPa 160mbar 64inH ₂ O	–16kPa –160mbar –64inH2O	0.27kPa 2.7mbar 1.08inH ₂ O	
G	65kPa	-65kPa	0.65kPa	1.1kPa
	650mbar	-650mbar	6.5mbar	11mbar
	260inH ₂ O	-260inH₂O	2.6inH ₂ O	8mmHg
н	160kPa	0.07kPa abs (§)	1.6kPa	2.67kPa
	1600mbar	0.7mbar abs (§)	16mbar	26.7mbar
	642inH ₂ O	0.5mmHg (§)	6.4inH ₂ O	20mmHg
M	600kPa	0.07kPa abs (§)	6kPa	10kPa
	6bar	0.7mbar abs (§)	0.06bar	0.1bar
	87psi	0.5mmHg (§)	0.87psi	1.45psi
P	2400kPa	0.07kPa abs (§)	24kPa	40kPa
	24bar	0.7mbar abs (§)	0.24bar	0.4bar
	348psi	0.5mmHg (§)	3.5psi	5.8psi
Q	8000kPa	0.07kPa abs (§)	80kPa	134kPa
	80bar	0.7mbar abs (§)	0.8bar	1.34bar
	1160psi	0.5mmHg (§)	11.6psi	19.4psi
S	16000kPa	0.07kPa abs (§)	160kPa	267kPa
	160bar	0.7mbar abs (§)	1.6bar	2.67bar
	2320psi	0.5mmHg (§)	23.2psi	38.7psi

Lower Range Limit for 268NS is 0.07kPa abs, 0.7mbar abs, 0.5mmHg for all ranges.

(§) Lower Range Limit is 0.135kPa abs, 1.35mbar abs, 1mmHg for inert Galden or 0.4kPa abs, 4mbar abs, 3mmHg for inert Halocarbon.

Span limits

Maximum span = URL

IT IS RECOMMENDED TO SELECT THE TRANSMITTER SENSOR CODE PROVIDING THE TURNDOWN VALUE AS LOWEST AS POSSIBLE TO OPTIMIZE PERFORMANCE CHARACTERISTICS.

Zero suppression and elevation

Zero and span can be adjusted to any value within the range limits detailed in the table as long as:

- calibrated span ≥ minimum span

Damping

Selectable time constant: 0, 0.25, 0.5, 1, 2, 4, 8 or 16s. This is in addition to sensor response time

Turn on time

Operation within specification in less than 5s with minimum damping.

Insulation resistance

 $> 100 M\Omega$ at 1000VDC (terminals to earth)

4kV

Operative limits

Model 268HS, 268NS

Temperature limits °C (°F):

Ambient (is the operating temperature)

Filling	Model 268HS	Model 268NS
Cilicopo oil	oil	-40 and +85
Silicone oil (-4	(-40 and +185)	(-40 and +185)
Inert-Galden	-20 and +85	-10 and +65
li lei t-Galdei i	(-4 and +185)	(+14 and +150)
Inert-Halocarbon		-10 and +65
linert-haiocarbori	(-4 and +185)	(+14 and +150)

Lower ambient limit for LCD indicators: -20°C (-4°F)

Upper ambient limit for LCD indicators: +70°C (+158°F)

Note: For Hazardous Atmosphere applications see the temperature range specified on the certificate/approval relevant to the aimed type of protection

Process

Lower limit

- refer to lower ambient limits

Upper limit

- Silicone oil: 121°C (250°F) (1) - Inert fluid: 100°C (212°F) (2)

100°C (212°F) for application below atmospheric pressure (1)

65°C (150°F) for application below atmospheric pressure

Storage

Lower limit: -50°C (-58°F): -40°C (-40°F) for LCD indicators Upper limit: +85°C (+185°F)

Pressure limits

Overpressure limits (without damage to the transmitter)

0.07kPa abs, 0.7mbar abs, 0.01psia (0.135kPa abs, 1.35mbar abs, 1mmHg for inert Galden or 0.4kPa abs, 4mbar abs, 3mmHg for inert Halocarbon) to:

- 14MPa, 140bar, 2030psi for sensor codes E, G, H, M
- 21MPa, 210bar, 3045psi for sensor codes P, Q, S

Proof pressure

The transmitter can be exposed without leaking to line pressure of up to:

- 28MPa, 280bar, 4060psi for sensor codes E, G, H, M
- 40MPa, 400bar, 5800psi for sensor codes P, Q, S

Meet ANSI/ISA-S 82.03 hydrostatic test requirements .

Environmental limits

Electromagnetic compatibility (EMC)

Comply with EN 61000-6-3 for emission and EN 61000-6-2 for immunity requirements and test;

Radiated electromagnetic immunity level: 30V/m

(according to IEC 1000-4-3, EN61000-4-3)

Conducted electromagnetic immunity level: 10V (according to IEC 1000-4-6, EN 61000-4-6)

Surge immunity level (with surge protector):

(according to IEC 1000-4-5 EN 61000-4-5)

Fast transient (Burst) immunity level: 4kV

(according to IEC 1000-4-4 EN 61000-4-4)

Pressure equipment directive (PED)

Comply with 97/23/EEC Category IV Modules D and B.

Humidity

Relative humidity: up to 100% annual average

Condensing, icing: admissible

Vibration resistance

Accelerations up to 2g at frequency up to 1000Hz (according to IEC 60068-2-6)

Shock resistance

Acceleration: 50g Duration: 11ms (according to IEC 60068-2-27)

Wet and dust-laden atmospheres

The transmitter is dust and sand tight and protected against immersion effects as defined by EN 60529 (1989) to IP 67 (IP 68 on request) or by NEMA to 4X or by JIS to C0920. IP65 with Harting Han connector.

Hazardous atmospheres

With or without output meter

- INTRINSIC SAFETY and EXPLOSION PROOF/ATEX:

ZELM approval

II 1G Ex ia IIC T6 and II 1/2G Ex ia IIC T6 and

II 1D Ex iaD 20 T95°C and II 1/2D Ex iaD 21 T95°C resp. II 1/2G Ex d IIC T6 and II 1/2D Ex tD A21 IP67 T85°C

EXPLOSION PROOF/IECEx:

ZELM approval

Ex d IIC T6 Ga/Gb resp.

Ex tb IIIC T85°C Da/Db (-40°C < Ta < +75°C)

- CANADIAN STANDARD ASSOCIATION and FACTORY MUTUAL:
- Explosionproof: Class I, Div. 1, Groups A, B, C, D
- Dust ignitionproof: Class II, Div. 1, Groups E, F, G
- Suitable for : Class II, Div. 2, Groups F, G; Class III, Div. 1, 2
- Nonincendive: Class I, Div. 2, Groups A, B, C, D
- Intrinsically safe: Class I, II, III, Div. 1, Groups A, B, C, D, E, F, G AEx ia IIC T6/T4, Zone 0 (FM)
- GOST (Russia), GOST (Kazakhstan), Inmetro (Brazil pending) based on ATEX

Electrical Characteristics and Options

HART digital communication and 4 to 20mA output

Power Supply


The transmitter operates from 10.5 to 42VDC with no load and is protected against reverse polarity connection (additional load allows operations over 42VDC).

For EEx ia and other intrinsically safe approval power supply must not exceed 30VDC.

Ripple

20mV max on a 250 $\!\Omega$ load as per HART specifications

MINIMUM OPERATING VOLTAGES



Load limitations

4 to 20mA and HART total loop resistance :

$$R(k\Omega) = \frac{\text{Supply voltage - min. operating voltage (VDC)}}{22.5}$$

A minimum of 250Ω is required for HART communication.

Optional indicators

Output meter

CoMeter and Prometer LCD:

5-digit (±99999 counts) programmable with 7.6mm. high (3in), 7-segment numeric characters plus sign and digital point for digital indication of output value in percentage, current or engineer unit;

10-segment bargraph display (10% per segment) for analog indication of output in percentage;

7-digit with 6mm. high (2.3in), 14-segment alphanumeric characters, for engineer units and configuration display

Analog: 36mm (1.4in) scale on 90°.

Optional surge protection

Up to 4kV

- voltage 1.2 µs rise time / 50 µs delay time to half value
- current 8µs rise time / 20µs delay time to half value

Output signal

Two-wire 4 to 20mA, user-selectable for linear or 5th order or two 2nd order switching point selectable programmable polynomial output.

HART® communication provides digital process variable (%, mA or engineering units) superimposed on 4 to 20mA signal, with protocol based on Bell 202 FSK standard.

Output current limits (to NAMUR standard)

Low saturation: 3.8mA (field configurable from 3.5 to 4mA)
High saturation: 20.5mA (field configurable from 20 to 22.5mA)

Alarm current

Low alarm current: 3.7mA (field configurable from 3.5 to 4mA)

High alarm current: 22mA (field configurable from 20 to 22.5mA)

Factory setting: high alarm current

Model 268HS, 268NS DS/268HS/NS-EN Rev. J

Performance specifications

Stated at reference condition to IEC 60770 ambient temperature of 20°C (68°F), relative humidity of 65%, atmospheric pressure of 1013hPa (1013mbar), zero based range for transmitter with isolating diaphragms in AISI 316 L ss or Hastelloy and silicone oil fill and digital trim values equal to span end points, in linear mode.

Unless otherwise specified, errors are quoted as % of span.

Some performance data are affected by the actual turndown (TD) as ratio between Upper Range Limit (URL) and calibrated span.

IT IS RECOMMENDED TO SELECT THE TRANSMITTER SENSOR CODE PROVIDING THE TURNDOWN VALUE AS LOWEST AS POSSIBLE TO OPTIMIZE PERFORMANCE CHARACTERISTICS.

Dynamic performance (according to IEC 61298-1 definition)

Dead time: 40ms

Time constant (63.2% of total step change):

- sensor M to S: ≤ 70ms - sensor H: 100ms - sensor G: 130ms

Response time (total) = dead time + time constant

Accuracy rating

% of calibrated span, including combined effects of terminal based linearity, hysteresis and repeatability.

Model 268HS

 $-\pm0.075\%$ for TD from 1:1 to 15:1 (to 10:1 for sensor code E)

$$-\pm0.005\%$$
 x $\frac{URL}{Span}$ for TD from 15:1 to 60:1

(
$$\pm 0.0075\%$$
 x $\frac{URL}{Span}$ for sensor code E for TD from 10:1 to 30:1)

Model 268NS

- ±0.075% for TD from 1:1 to 10:1

$$-\pm0.0075\%$$
 x URL for TD from 10:1 to 20:1

Operating influences

Ambient temperature

per 20K (36°F) change between the limits of –20°C to +65°C (–4 to +150°F) :

Model	Sensor Code	for TD up to	
268HS	Е	10:1	± (0.04% URL + 0.065% span)
200113	G to S	15:1	1± (0.04 % ONL + 0.003 % Spail)
268NS	G to S	10:1	± (0.04% URL + 0.065% span)

Optional CoMeter and ProMeter ambient temperature

Total reading error per 20K (36°F) change between the ambient limits of -20 and +70°C (-4 and +158°F) :

±0.15% of max span (16mA).

Supply voltage

Within voltage/load specified limits the total effect is less than 0.005% of URL per volt.

Load

Within load/voltage specified limits the total effect is negligible.

Electromagnetic field

Total effect: less than 0.10% of span from 20 to 1000MHz and for field strengths up to 30V/m when tested with shielded conduit and grounding, with or without meter.

Common mode interference

No effect from 100Vrms @ 50Hz, or 50VDC

Mounting position

No effect

Stability

±0.15% of URL over a ten years period (for 268HS) ±0.15% of URL over a five years period (for 268NS)

Vibration effect

±0.10% of URL (according to IEC 61298-3)

Model 268HS, 268NS DS/268HS/NS-EN Rev. J

Physical Specification

(Refer to ordering information sheets for variant availability related to specific model or versions code)

Materials

Process isolating diaphragms (*)

AISI 316 L ss; AISI 316 L ss gold plated; Monel 400™; Tantalum; Hastelloy C276™; Hastelloy C276™ on AISI 316 L ss gasket seat.

Process connection (*)

AISI 316 L ss; Hastelloy C276™; Monel 400™.

Sensor fill fluid

Silicone oil (DC200™); inert fill (Halocarbon™ 4.2 or Galden™);.

Mounting bracket (**)

Zinc plated carbon steel with chrome passivation;

AISI 316 L ss.

Sensor housing

AISI 316 L ss.

Electronic housing and covers (Barrel version)

- Aluminium alloy with baked epoxy finish;
- Copper-free content aluminium alloy with baked epoxy finish;
- AISI 316 L ss.

Covers O-ring

Buna N.

Local zero and span adjustments:

Glass filled polycarbonate plastic (removable).

Tagging

AISI 316ss data plate attached to the electronics housing.

Calibration

Standard: at maximum span, zero based range, ambient temperature and pressure;

Optional: at specified range and ambient conditions.

Optional extras

Mounting brackets

For 60mm. (2in) pipes or wall mounting.

Output indicator

plug-in rotatable type, LCD or analog.

Supplemental customer tag

AISI 316 ss tag screwed/fastened to the transmitter for customer's tag data up to a maximum of 20 characters and spaces on one line for tag number and tag name, and up to a maximum of 3 spaced strings of 10 characters each for calibration details (lower and upper values plus unit). Special typing evaluated on request for charges.

Surge protection

Cleaning procedure for oxygen service

Test Certificates (test, design, calibration, material traceability)

Tag and manual language

Communication connectors

- (*) Wetted parts of the transmitter.
- (**) U-bolt material: AISI 400 ss; screws material: high-strength alloy steel or AISI 316 ss.

Process connections

 $^{1}/_{2}$ – 14 NPT female or male; DIN EN837–1 G $^{1}/_{2}$ B; adapter straight (180°) entry; adapter angle (90°) entry.

fixing threads on adapter entries: $^{7}\!/_{16}$ – 20 UNF at 41.3mm centre distance.

Electrical connections

Two $^{1}\!/_{2}-14$ NPT or M20x1.5 or PG 13.5 or $^{1}\!/_{2}$ GK threaded conduit entries, direct on housing.

Special communication connector (on request)

- HART: straight or angle Harting Han connector and one plug.

Terminal block

HART version: three terminals for signal/external meter wiring up to 2.5mm² (14AWG) and three connection points for test and communication purposes.

Grounding

Internal and external $6 \text{mm}^2 (10 \text{AWG})$ ground termination points are provided.

Mounting position

Transmitter can be mounted in any position.

Electronics housing may be rotated to any position. A positive stop prevents over travel.

Mass (without options)

1.7kg approx (4lb); add 1.5kg (3.4lb) for AISI housing. Add 650g (1.5lb) for packing.

Packing

Carton 26 x 26 x 18cm approx (10 x 10 x 7in).

Configuration

Transmitter with HART communication and 4 to 20 mA

Standard configuration

Transmitters are factory calibrated to customer's specified range. Calibrated range and tag number are stamped on the tag plate. If a calibration range and tag data are not specified, the transmitter will be supplied with the plate left blank and configured as follows:

Engineering Unit kPa 4 mA Zero

20 mA Upper Range Limit (URL)

Output Linear
Damping 1 sec.
Transmitter failure mode Upscale
Software tag (8 characters max) Blank

Optional LCD indicator/display 0 to 100.0% linear

Any or all the above configurable parameters, including Lower range–value and Upper range-value which must be the same unit of measure, can be easily changed using the HART hand–held communicator or by a PC running the configuration software SMART VISION with DTM for 2600T. The transmitter database is customized with specified flange type and material, O–ring and drain/vent materials and meter code option.

Custom configuration (option)

The following data may be specified in addition to the standard configuration parameters:

Descriptor 16 alphanumeric characters Message 32 alphanumeric characters

Date Day, month, year

For any protocol available engineering units of pressure measure are :

Pa, kPa, MPa

inH₂O@4°C, mmH₂O@4°C, psi


inH₂O@20°C, ftH₂O@20°C, mmH₂O@20°C

inHg, mmHg, Torr g/cm², kg/cm², atm


mbar, bar

MOUNTING DIMENSIONS (not for construction unless certified) – dimensions in mm (in)


Transmitter with barrel housing on bracket for 60mm (2in) pipe mounting




¹/₂ – 14 NPT female connection




DIN-EN837-1 G 1/2 B connection



1/2 - 14 NPT male connection




Adapter straight (180°) entry connection (7/16 - 20 UNF drilling)



Adapter angle (90°) entry connection (7/16 – 20 UNF drilling)

Electrical connections

HART Version



BASIC ORDERING INFORMATION model 268HS Safety Gauge Pressure Transmitter

Select one character or set of characters from each category and specify complete catalog number.

Refer to additional ordering information code and specify one or more codes for each transmitter if additional options are required.

ASE MODEL - 1st to 5th characters			2 6 8	H S X	Х	X Z	X
Safety Gauge Pressure Transmitter – BASE ACCURAC	Y 0.075%						
ENSOR - Span limits – 6 th character				_			
0.27 and 16kPa 2.7 and 160mbar	1.08 and 64inH ₂ O			E			
0.65 and 65kPa 6.5 and 650mbar	2.6 and 260inH2O			G			
1.6 and 160kPa 16 and 1600mbar	6.4 and 642inH ₂ O			Н			
6 and 600kPa 0.06 and 6bar	0.87 and 87psi			M			
24 and 2400kPa 0.24 and 24bar	3.5 and 348psi			Р			
80 and 8000kPa	11.6 and 1160psi			Q			
160 and 16000kPa 1.6 and 160bar	23.2 and 2320psi			S			
iaphragm material / Fill fluid (wetted parts) - 7th cha							
AISI 316 L ss	Silicone oil				S		
Hastelloy C276™ (on AISI seat)	Silicone oil			NACE	Н		
Hastelloy C276™	Silicone oil			NACE	K		
Monel 400™	Silicone oil			NACE			
AISI 316 L ss gold plated	Silicone oil	(Note 11)		NACE	8		
Tantalum	Silicone oil			NACE	T		
AISI 316 L ss	Inert fluid - Galden	(Note 1)			Α		
Hastelloy C276™ (on AISI seat)	Inert fluid - Galden	(Note 1)		NACE	В		
Hastelloy C276™	Inert fluid - Galden	(Note 1)		NACE	F		
Monel 400™	Inert fluid - Galden	(Note 1)		NACE	С		
AISI 316 L ss gold plated	Inert fluid - Galden	(Notes 1, 11)		NACE	9		
Tantalum	Inert fluid - Galden	(Note 1)		NACE	D		
AISI 316 L ss	Inert fluid - Halocarbon	(Note 1)			L		
Hastelloy C276™ (on AISI seat)	Inert fluid - Halocarbon	(Note 1)		NACE	Q		
Hastelloy C276™	Inert fluid - Halocarbon	(Note 1)		NACE	Р		
Monel 400 TM	Inert fluid - Halocarbon	(Note 1)		NACE	4		
AISI 316 L ss gold plated	Inert fluid - Halocarbon	(Notes 1, 11)		NACE	i		
Tantalum	Inert fluid - Halocarbon	(Note 1)		NACE	5		
rocess connection material (wetted parts) - 8th cha			(NI=+= O)	NIAOE			
AISI 316 L ss	1/2 – 14 NPT female		(Note 2)	NACE		В	
AISI 316 L ss	1/2 - 14 NPT male		(Note 2)	NACE		T P	
AISI 316 L ss	DIN EN837–1 G ¹ / ₂ B		(Note 2)	NACE			
AISI 316 L ss	Adapter straight (180°) entry (Not	available with bracket)	(Note 2)	NACE		A	
AISI 316 L ss	Adapter angle (90°) entry		(Note 2)	NACE		N	
Hastelloy C276™	1/2 - 14 NPT female		(Note 3)	NACE		E	
Hastelloy C276™	1/2 - 14 NPT male		(Note 3)	NACE		K	
Hastelloy C276™	DIN EN837-1 G ¹ / ₂ B		(Note 3)	NACE		D	
Hastelloy C276™	Adapter straight (180°) entry (Not	available with bracket)	(Note 3)	NACE		F	
Hastelloy C276™	Adapter angle (90°) entry		(Note 3)	NACE		C	
Monel 400™	1/2 - 14 NPT female		(Note 4)	NACE		1	
Monel 400™	1/2 - 14 NPT male		(Note 4)	NACE		2	
Monel 400™	DIN EN837-1 G ¹ / ₂ B		(Note 4)	NACE		3	
ousing material and electrical connection – 9th char	acter						
Aluminium alloy (Barrel version)	1/2 - 14 NPT						Α
Aluminium alloy (Barrel version)	M20 x 1.5 (CM 20)						В
Aluminium alloy (Barrel version)	Pg 13.5						D
Aluminium alloy (Barrel version)	1/2 GK						С
Aluminium alloy (Barrel version)	Harting Han connector	(general purpose o	naly)	(Note 5)			E
	•	(general purpose c	n ny)	(14016.2)			Н
Aluminium alloy copper-free (Barrel version)	1/2 – 14 NPT M20 v 1.5 (CM 20)						
Aluminium alloy copper-free (Barrel version)	M20 x 1.5 (CM 20)						L
Aluminium alloy copper-free (Barrel version)	Pg 13.5						N
Aluminium alloy copper-free (Barrel version)	1/2 GK	,	1.	(b.) . =:			М
Aluminium alloy copper-free (Barrel version)	Harting Han connector	(general purpose o	niy)	(Note 5)			Р
AISI 316 L ss (Barrel version)	1/2 – 14 NPT						S
AISI 316 L ss (Barrel version)	M20 x 1.5 (CM20)						Т
AISI 316 L ss (Barrel version)	Pg 13.5						٧
AISI 316 L ss (Barrel version)	¹ / ₂ GK					I	U
utput/Additional options – 10th character							
LIADT 1: 11 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1	No additional options			(Note 6)			
HART digital communication and 4 to 20mA (SIL 2)							

ADDITIONAL ORDERING INFORMATION for model 268HS

Add one or more 2-digit code(s) after the basic ordering information to select all required options

			XX	xx	XX	XX	хх	хх	XX	хх	XX	хх	хх	хх	XX
Drain/vent valve (wetted parts)]												
AISI 316 L ss	(Note 7)	NACE	VA												
Hastelloy C276™ Monel 400™	(Note 8) (Note 9)	NACE NACE	VB VC												
Electrical certification	(Note 9)	NACL	VO	1											
ATEX Group II Category 1G and 1/2G, Category 1D and	l 1/2D - Intrinsic Safety Ex ia			E1											
ATEX Group II Category 1/2 GD – Explosion Proof Ex d Canadian Standard Association (CSA) (only 1/2–14NPT, I	M20 and Pa 12 5 plactrical a	oppostion)		E2 E4											
Factory Mutual (FM) approval (only with 1/2–14NPT, M20				E6											
IECEx IIC T6 Ga/Gb resp. Ex tb IIIC T85° C Da/Db (only	9	,		E9											
GOST (Russia) EEx ia GOST (Russia) EEx d				W1 W2											
GOST (Russia) EEX d GOST (Kazakistan) EEx ia				W3											
GOST (Kazakistan) EEx d				W4											
Inmetro (Brazil) EEx ia (pending)				W5											
Inmetro (Brazil) EEx d (pending) Inmetro (Brazil) EEx nL (pending)				W6 W7											
Metrologic (Russia)				WC											
Metrologic (Kazakhstan)				WD											
Output meter															
ProMeter, Standard calibration					D1										
ProMeter, Special calibration Analog output indicator linear 0-100% scale					D2 D3										
Analog output indicator, special graduation (to be specif	ied for linear scale)				D5										
Programmable signal meter and HART configurator (Col	Meter)				D7										
Programmable signal meter and HART configurator (Col	Meter – customer configuration	on)			D8										
Mounting bracket (shape and material)						D0									
For pipe mounting (Not suitable for AISI housing) For pipe mounting	Carbon steel AISI 316 L ss					B6 B7									
Surge	7 1101 0 10 2 00					<u></u>	l								
Surge/Transient Protector							S1								
							01								
Operating manual								N 4 +							
German Italian								M1 M2							
French								M4							
Labels & tag language															
German									T1						
Italian Specials									T2 T3						
Spanish French									T4						
Additional tag plate															
Laser printing of tag on stainless steel plate										12					
Configuration											l				
Standard – Pressure = inH2O/psi at 20° C; Temperature	e = dea. F										N2				
Standard – Pressure = inH2O/psi at 4° C; Temperature :											N3				
Standard - Pressure = inH2O/psi at 20° C; Temperature											N4				
Standard – Pressure = inH2O/psi at 4° C; Temperature : Custom	= deg. C										N5 N6				
Preparation procedure											140	I			
Oxygen service cleaning (only available with inert fill) – Pr	max = 12MPa for Galden or 91	MPa for Halocarbon	; Tma	x = 60)° C/	140	° F					P1			
Certificates															
Inspection certificate EN 10204–3.1 of calibration (9-point	nt)												C1		
Certificate of compliance with the order EN 10204–2.1 of													C6		
Material traceability															
Certificate of compliance with the order EN 10204-2.1 c	of process wetted parts													Н1	
Inspection certificate EN 10204-3.1 of process wetted p	parts													НЗ	
Connector															
Harting Han – straight entry		(Note 10)													U3
Harting Han – angle entry		(Note 10)													U4

	O 11 1 1	-		
Note 1:	Suitable	tor	OVVIGOR	CONJICO
INOLE I.	Juliable	IUI	OVACELL	SCI VICE

- Note 2: Not available with diaphragm code K, M, T, F, C, D, P, 4, 5
- Note 3: Not available with diaphragm code M, 8, A, B, C, 9, L, Q, 4, I
- Note 4: Not available with diaphragm code S, H, K, T, A, B, F, D, L, Q, P, 5, 8, 9, I
- Note 5: Select type in additional ordering code
- Note 6: Not available with Electronic Housing code P, E
- Note 7: Not available with Process connection code E, K, D, F, C, 1, 2, 3
- Note 8: Not available with Process connection code B, T, A, P, N, 1, 2, 3
- Note 9: Not available with Process connection code E, K, D, F, C, B, T, A, P, N
- Note 10: Not available with Electronic housing code U, S, T, V, H, M, L, N, D, C, A, B
- Note 11: Not available with sensor code E

Standard delivery items (can be differently specified by additional ordering code)

- No drain/vent valve
- General purpose (no electrical certification)
- No meter/display, no mounting bracket, no surge protection
- English manual and labels
- Configuration with kPa and deg. C units
- No test, inspection or material traceability certificates

THE SELECTION OF SUITABLE WETTED PARTS AND FILLING FLUID FOR COMPATIBILITY WITH THE PROCESS MEDIA IS A CUSTOMER'S RESPONSIBILITY, IF NOT OTHERWISE NOTIFIED BEFORE MANUFACTURING.

BASIC ORDERING INFORMATION model 268NS Safety Absolute Pressure Transmitter

Select one character or set of characters from each category and specify complete catalog number.

Refer to additional ordering information code and specify one or more codes for each transmitter if additional options are required.

BASE MODEL - 1st to 5th o	characters			2	6	8	N	SX	X	Х	X	X
Safety Absolute Pressure	Transmitter - BASE ACCURA	ACY 0.075%										
SENSOR - Span limits -	6 th character											
1.1 and 65kPa	11 and 650mbar	8 and 480mmHg						G				
2.67 and 160kPa	26.7 and 1600mbar	20 and 1200mmHg						Н				
10 and 600kPa	0.1 and 6bar	1.45 and 87psi						M				
40 and 2400kPa	0.4 and 24bar	5.8 and 348psi						P				
134 and 8000kPa	1.34 and 80bar	19.4 and 1160psi						Q				
267 and 16000kPa	2.67 and 160bar	38.7 and 2320psi						S				
	fluid (wetted parts) - 7th cha											
AISI 316 L ss		Silicone oil							S			
Hastelloy C276™ (on AIS	I seat)	Silicone oil						NACE	Н			
Hastelloy C276™		Silicone oil						NACE	K			
AISI 316 L ss		Inert fluid - Galden	(Note 1)						Α			
Hastelloy C276™ (on AlS	SI seat)	Inert fluid - Galden	(Note 1)					NACE	В			
Hastelloy C276™		Inert fluid - Galden	(Note 1)					NACE	F			
AISI 316 L ss		Inert fluid - Halocarbon	(Note 1)						L			
Hastelloy C276™ (on Als	SI seat)	Inert fluid - Halocarbon	(Note 1)					NACE	Q			
Hastelloy C276™	,	Inert fluid - Halocarbon	(Note 1)					NACE	Р			
rocess connection mate	erial (wetted parts) - 8th cha	racter								_		
AISI 316 L ss		1/2 - 14 NPT female		(Note	2)			NACE		В		
AISI 316 L ss		1/2 - 14 NPT male		(Note	e 2)			NACE		Т		
AISI 316 L ss		DIN EN837-1 G 1/2 B		(Note	,			NACE		Р		
AISI 316 L ss		Adapter straight (180°) entry (Not availab	ole with bracket)	(Note	,			NACE		Α		
AISI 316 L ss		Adapter angle (90°) entry	,	(Note				NACE		Ν		
Hastelloy C276™		1/2 - 14 NPT female		(Note	3)			NACE		Ε		
Hastelloy C276™		1/2 - 14 NPT male		(Note				NACE		Κ		
Hastelloy C276™		DIN EN837-1 G 1/2 B		(Note				NACE		D		
Hastelloy C276™		Adapter straight (180°) entry (Not availab	ole with bracket)	(Note	,			NACE		F		
Hastelloy C276™		Adapter angle (90°) entry	,	(Note				NACE		С		
lousing material and ele	ctrical connection – 9th char	acter										
Aluminium alloy (Barrel ve	ersion)	1/2 - 14 NPT									Α	
Aluminium alloy (Barrel ve	ersion)	M20 x 1.5 (CM 20)									В	
Aluminium alloy (Barrel ve		Pg 13.5									D	
Aluminium alloy (Barrel ve		1/2 GK									С	
Aluminium alloy (Barrel ve		Harting Han connector	(general purpose	only)				(Note 4	.)		Ε	
Aluminium alloy copper-fi	ree (Barrel version)	1/2 – 14 NPT									Н	
Aluminium alloy copper-fi		M20 x 1.5 (CM 20)									L	
Aluminium alloy copper-fi		Pg 13.5									Ν	
Aluminium alloy copper-fi	ree (Barrel version)	1/2 GK									Μ	
Aluminium alloy copper-fi		Harting Han connector	(general purpose	only)				(Note 4	.)		Ρ	
AISI 316 L ss (Barrel vers	sion)	1/2 - 14 NPT									S	
AISI 316 L ss (Barrel vers	sion)	M20 x 1.5 (CM20)									Т	
AISI 316 L ss (Barrel vers		Pg 13.5									V	
AISI 316 L ss (Barrel vers		1/2 GK									U	
Output/Additional option	s - 10 th character											_
HART digital communicat	tion and 4 to 20mA (SIL 2)	No additional options						(Note 5	5)			
	tion and 4 to 20mA (SIL 2)	Options requested (to be ordered by "Ad	Iditional ordering o	code")								

ADDITIONAL ORDERING INFORMATION for model 268NS

Add one or more 2-digit code(s) after the basic ordering information to select all required options

	XX	XX	хх	ХX	XX	xx	ХX	хх	хх	хх	хх	ХX	XX
Drain/vent valve (wetted parts)													
AISI 316 L ss (Note 6) NACE	VA												
Hastelloy C276 TM (Note 7) NACE	VB												
Electrical certification													
ATEX Group II Category 1G and 1/2G, Category 1D and 1/2D - Intrinsic Safety Ex ia		E1 E2											
ATEX Group II Category 1/2 GD - Explosion Proof Ex d Canadian Standard Association (CSA) (only 1/2-14NPT, M20 and Pg 13.5 electrical connection)		E2											
Factory Mutual (FM) approval (only with 1/2–14NPT, M20 and Pg 13.5 electrical connection)		E6											
IECEx IIC T6 Ga/Gb resp. Ex tb IIIC T85° C Da/Db (only with 1/2–14NPT and M20 electrical conn./Barrel)		E9											
GOST (Russia) EEx ia		W1											
GOST (Russia) EEx d		W2											
GOST (Kazakistan) EEx ia GOST (Kazakistan) EEx d		W3 W4											
Inmetro (Brazil) EEx ia (pending)		W5											
Inmetro (Brazil) EEx d (pending)		W6											
Inmetro (Brazil) EEx nL (pending)		W7											
Metrologic (Russia)		WC											
Metrologic (Kazakhstan) Output meter		WD											
			Г.										
ProMeter, Standard calibration ProMeter, Special calibration			D1 D2										
Analog output indicator linear 0-100% scale			D2										
Analog output indicator, special graduation (to be specified for linear scale)			D5										
Programmable signal meter and HART configurator (CoMeter)			D7										
Programmable signal meter and HART configurator (CoMeter – customer configuration)			D8										
Mounting bracket (shape and material)													
For pipe mounting (Not suitable for AISI housing) Carbon steel For pipe mounting AISI 316 L ss				B6 B7									
Surge													
Surge/Transient Protector					S1								
Operating manual													
German						M1							
Italian						M2							
French						M4	J						
Labels & tag language							т.						
German Italian							T1 T2						
Spanish							T3						
French							T4						
Additional tag plate								10					
Laser printing of tag on stainless steel plate								12					
Configuration													
Standard - Pressure = inH2O/psi at 20° C; Temperature = deg. F Standard - Pressure = inH2O/psi at 4° C; Temperature = deg. F									N2 N3				
Standard - Pressure = inH2O/psi at 4 °C, Temperature = deg.C									N4				
Standard – Pressure = inH2O/psi at 4° C; Temperature = deg. C Custom									N5 N6				
Preparation procedure										ı			
Oxygen service cleaning (only available with inert fill) - Pmax = 12MPa for Galden or 9MPa for Halocarbon	; Tmax	= 60	° C/1	140°	F					P1			
Certificates											,		
Inspection certificate EN 10204-3.1 of calibration (9-point) Certificate of compliance with the order EN 10204-2.1 of instrument design											C1 C6		
Material traceability													
Material traceability Certificate of compliance with the order EN 10204–2.1 of process wetted parts Inspection certificate EN 10204–3.1 of process wetted parts												H1 H3	
Certificate of compliance with the order EN 10204–2.1 of process wetted parts													
Certificate of compliance with the order EN 10204–2.1 of process wetted parts Inspection certificate EN 10204–3.1 of process wetted parts													U3

- Note 1: Suitable for oxygen service
- Note 2: Not available with diaphragm code K, F, P
- Note 3: Not available with diaphragm code S, H, A, B, L, Q
- Note 4: Select type in additional ordering code
- Note 5: Not available with Electronic Housing code P, E
- Note 6: Not available with Process connection code E, K, D, F, C Note 7: Not available with Process connection code B, T, A, P, N
- Note 8: Not available with Electronic housing code U, S, T, V, H, M, L, N, D, C, A, B

Standard delivery items (can be differently specified by additional ordering code)

- No drain/vent valve
- General purpose (no electrical certification)
- No meter/display, no mounting bracket, no surge protection
- English manual and labels
- Configuration with kPa and deg. C units
- No test, inspection or material traceability certificates

THE SELECTION OF SUITABLE WETTED PARTS AND FILLING FLUID FOR COMPATIBILITY WITH THE PROCESS MEDIA IS A CUSTOMER'S RESPONSIBILITY, IF NOT OTHERWISE NOTIFIED BEFORE MANUFACTURING.

[™] Hastelloy C276 is a Cabot Corporation trademark

[™] Monel is an International Nickel Co. trademark

[™] DC200 is a Dow Corning Corporation trademark

 $^{^{\}mathsf{TM}}$ Galden is a Montefluos trademark

[™] Halocarbon is a Halocarbon Products Co. trademark

Contact us

ABB Ltd.

Process Automation

Howard Road St. Neots Cambridgeshire PE19 8EU UK

Tel: +44 (0)1480 475321 Fax: +44 (0)1480 217948

ABB Inc.

Process Automation

125 E. County Line Road Warminster PA 18974 USA

Tel: +1 215 674 6000 Fax: +1 215 674 7183

ABB Automation Products GmbH

Process Automation

Schillerstr. 72 32425 Minden Germany

Tel: +49 551 905 534 Fax: +49 551 905 555

ABB S.p.A.

Process Automation

Via Statale 113 22016 Lenno (CO) Italy

Tel: +39 0344 58111 Fax: +39 0344 56278

www.abb.com

Note

We reserve the right to make technical changes or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB does not accept any responsibility whatsoever for potential errors or possible lack of information in this document.

We reserve all rights in this document and in the subject matter and illustrations contained therein. Any reproduction, disclosure to third parties or utilization of its contents - in whole or in parts - is forbidden without prior written consent of ABB.

Copyright© 2012 ABB All rights reserved

- ™ Hastelloy C276 is a Cabot Corporation trademark
- ™ Monel is an International Nickel Co. trademark
- ™ DC200 is a Dow Corning Corporation trademark
- ™ Galden is a Montefluos trademark
- ™ Halocarbon is a Halocarbon Products Co. trademark

