

ROBOTICS

Product Range

For the flexible and efficient
Factory of the Future




ABB Robotics is a pioneer in industrial and collaborative robots and advanced digital services. As one of the world's leading robotics suppliers, we are active in 53 countries and over 100 locations and have shipped over 300,000 robot solutions in a diverse range of industries and applications. We help our customers to improve flexibility, efficiency, safety and reliability, while moving towards the connected and collaborative factory of the future.

Index

04 – 05	The Factory of the Future
06 – 07	Robots: YuMi
08 – 09	Customer Service
10 – 15	Selection table, Robots
16 – 31	Robots
32 – 33	Press Automation Robots
34 – 35	Controllers
36 – 39	Body-in-White
40 – 41	Positioners
42 – 51	Application equipment
52 – 55	Paint robots
56 – 58	Painting equipment
59 – 62	Application equipment
63 – 65	Software products: RobotWare
66 – 68	Application software
69 – 71	Software products: RobotStudio

The Factory of the Future

Flexible for growth and efficient at every level

It is not easy to compete while the ground is shifting under your feet. In many industries ‘high mix low volume’ is the new normal, while automation becomes more complex and product cycles shorter. Is your business ready?



Powerful performance can be unlocked by connecting the virtual world with physical robots, systems and equipment in factories

Adapting to the realities of today’s manufacturing environment can carry unique pain points:

- Shop floor disruptions and higher engineering costs from more frequent line changes
- Managing increasingly complex automation processes and data
- Higher cost of downtime from shorter product lifecycles
- Lost productivity to maintain safety with the increased need for human and robot interaction

ABB is helping its customers make the journey to the factory of the future – one which is flexible for new growth opportunities and efficient through the entire automation lifecycle.

We combine the experience of 300,000 plus delivered robots with our deep domain expertise and first-mover advantage in digital to prepare our customers to meet tomorrow’s challenges, today.

ABB focuses on three building blocks for the factory of the future – Collaboration, Simplification and Digitalization.



SafeMove2 allows people to work closer to robots without unnecessary stoppages.

Collaboration

Collaboration is not only about safety or ‘co-bots,’ it means people and robots working close together with flexibility and productivity. Collaboration also means your robotic solutions are part of the manufacturing ecosystem, not separate islands of automation.



Lead through programming allows even untrained users to quickly setup robots.

Simplification

Robots that are easy to install, program and use is imperative to global enterprises and local manufacturing shops alike. As automation becomes more complex, it also becomes more critical to have intuitive dashboards that help people make better decisions.



ABB Ability™ Connected Services provides proactive intelligence that can reduce incidents by up to 25%.

Digitalization

Securely connecting robots to the digital world can improve the efficiency of each step of the automation lifecycle: engineering, commissioning, operations and maintenance.

Advanced analytics can help improve the performance and reliability of single robots, systems, or even entire fleets across several locations.



YuMi®: Creating an automated future together

You and Me

01 YuMi® assembles USB sticks at DEONET in the Netherlands.

02 YuMi® manufactures sockets at ABB's plant in the Czech Republic.

03 YuMi® makes electrical socket in Ede, the Netherlands.

The new era of robotic co-workers is here. YuMi® is the result of years of research and development, making collaboration between humans and robots a reality, but it is also much more.


ABB has developed a collaborative, dual arm, small parts assembly robot solution that includes flexible hands, parts feeding systems, camera-based part location and state-of-the-art robot control. YuMi® is a vision of the future. YuMi® will change the way we think about assembly automation. YuMi® is “you and me”, working together to create endless possibilities.

Human - robot collaboration


Innovative human - friendly dual arm robot with breakthrough functionality designed to unlock vast global additional automation potential in industry.


YuMi® is designed for a new era of automation, for example in small parts assembly, where people and robots work side-by-side on the same tasks. Safety is built into the functionality of the robot itself. YuMi® removes the barriers to collaboration by making fencing and cages a thing of the past.


At only 38 kg and approximately the size of a small human, YuMi® is quickly and easily installed on the production line to work hand-in-hand with a human colleague. Lead-through programming means YuMi® can be taught a process by being physically guided through it, eliminating the need for complex, time-consuming code-based instruction.


World's first
truly collaborative
human sized
dual-arm robot

Safe Integrated
collision detection,
soft padding and
eliminated
pinch
points 


Precise YuMi®
is accurate enough
to thread a
needle

Intuitive
lead-through
programming
requires no
special training or
programming skills 



Customer Service

Value-added services across the entire life cycle

At your service. Worldwide.

ABB Robotics Customer Service helps its customers to increase uptime, resolve issues faster and reduce lifetime ownership costs. This includes unlocking the full benefits of connected robots and advanced analytics.

ABB Robotics is an innovator in advanced, digital services, having introduced its Remote Services offering over a decade ago, long before 'the Internet of Things' was even coined. Today all ABB robots are delivered with embedded connectivity, and there are more than 6,000 ABB connected robots in 750+ customer sites in 40 countries.

This is part of the largest service offering and broadest service network in the industry, including over 1,600 service professionals in 53 countries and 24/7 global support through dedicated call centers for immediate response. ABB's comprehensive offering also includes parts and logistics, field service, training, and expert systems and application services based on ABB's experience from having sold more than 300,000 robots.


Robot Care Service Agreements

A Robot Care service agreement from ABB, ensures that unplanned stops are reduced to a minimum, and if they occur, ABB can deliver a fast response tailored to your needs, further supported via ABB Ability™ Connected Services.

Within the selectable options of our service agreement configuration tool, our experts stand ready to help you choose the service solution that suits your needs. In addition to our flexible service agreements, we offer four standardized Robot Care service agreement packages that are based on extensive experience and an understanding of customer needs.

Value-added life cycle services

For optimized return on equipment investment, you can depend on ABB Robotics' support during the four life cycle phases of your robot system.



—
01 ABB Robotics'
value-added life
cycle services

Start-up phase

During the installation Start-up phase, ABB ensures a fast ramp-up, the right operations, and guarantees the longest possible equipment lifetime. This is enabled by simulation and offline programming with RobotStudio®, as well as commissioning services, training, spare part packages and technical support.

Benefits:

- Faster ramp-up
- Risk reduction
- Secured long equipment lifetime

Production phase

For the Production phase, ABB ensures production continuity, increased uptime, availability and cost control. This is secured by our service agreements with ABB Ability Connected Services, Preventive Maintenance and Repair services.

Benefits:

- Production continuity
- Increased uptime
- Increased availability
- Cost control

Production Improvement phase

In the Production Improvement phase, ABB ensures reduced cycle time, improved productivity, increased production output and reduced costs. This is achieved by equipment upgrades, remanufacturing, and ABB Ability Connected Services.

Benefits:

- Reduced cycle time
- Improved productivity
- Increased production output
- Reduced costs

Lifetime Extension phase





Finally, during the Lifetime Extension phase, ABB ensures secured production, maximized Return On Investment for the equipment, the latest technology performance and safety. This is achieved with the fast and secure replacement of manipulator, controller and complete robot.

Benefits:




- Secured production
- Maximized Return On Investment
- Latest technology
- Safety




Selection table

Robots

PRODUCT		BASIC SPECIFICATIONS		
	Load (kg)	3		
	Reach (m)	0.58		
	Position repeatability (mm)	0.01		
	Protection	Std: IP30. Option: Cleanroom Class 5, certified by IPA. Food Grade Lubrication		
	Mounting	Floor, wall, inverted and tilted		
	Load (kg)	5	7	
	Reach (m)	0.90	0.70	
	Position repeatability (mm)	0.025	0.02	
	Protection	Std: IP40 Option: Foundry Plus 2, IP67, Cleanroom ISO 3, Food Grade Lubrication		
	Mounting	Any angle		
	Load (kg)	6		
	Reach (m)	0.81		
	Position repeatability (mm)	0.03		
	Protection	Std: IP67 Option: Cleanroom Class 6, Foundry Plus 2		
	Mounting	Floor, wall, inverted, and tilted angles		
	Load (kg)	5		
	Reach (m)	1.44		
	Position repeatability (mm)	0.02		
	Protection	-		
	Mounting	Floor		





PRODUCT	BASIC SPECIFICATIONS				
	Load (kg)	4			
	Reach (m)	1.50			
	Position repeatability (mm)	0.05			
	Protection	Std: IP40			
	Mounting	Floor, inverted			
	Load (kg)	6	6	10	10
	Reach (m)	1.20	1.45	1.20	1.45
	Position repeatability (mm)	0.02	0.02	0.02	0.05
	Protection	Std: IP54 Option: Foundry Plus 2 with IP67			
	Mounting	Floor, wall, inverted, tilted and shelf			
	Load (kg)	4	6		
	Reach (m)	1.55	1.55		
	Position repeatability (mm)	0.02	0.02		
	Protection	Std: IP40 (wrist IP67)			
	Mounting	Floor, wall, inverted and tilted			
	Load (kg)	12	20		
	Reach (m)	1.55	1.55		
	Position repeatability (mm)	0.03			
	Protection	Std: IP54 Option: Foundry Plus 2 with IP67			
	Mounting	Floor, inverted			





PRODUCT	BASIC SPECIFICATIONS					
	Load (kg)	8*	12	12	15*	20
	Reach (m)	2*	1.65	1.85	1.85*	1.65
	Position repeatability (mm)	0.02	0.04	0.04	0.02	0.04
	Protection	Std: IP67; IP54 (axis 4) Option: Foundry Plus 2				
	Mounting	Floor, wall, inverted, tilted and shelf				
	Load (kg)	10	60			
	Reach (m)	2.55	1.96			
	Position repeatability (mm)	0.05	0.05			
	Protection	Std: IP54 Option: IP67, Foundry Plus 2				
	Mounting	Floor				
	Load (kg)	20	40	45	60	
	Reach (m)	2.50	2.55	2.05	2.05	
	Position repeatability (mm)	0.05	0.06	0.05	0.06	
	Protection	Std: IP67 Option: Foundry Plus 2, Foundry Prime 2				
	Mounting	Floor, inverted, tilted and shelf				
	Load (kg)	150	150*			
	Reach (m)	2.20	1.90*			
	Position repeatability (mm)	0.10	0.10			
	Protection	Std: IP66 (linear axis) Option: Foundry Plus 2				
	Mounting	Floor, inverted, tilted and inverted*				
*On linear axis						




PRODUCT	BASIC SPECIFICATIONS			
	Load (kg)	235	185	
	Reach (m)	2.55	2.80	
	Position repeatability (mm)	0.05	0.05	
	Protection	Std: IP67 Option: Foundry Plus 2		
	Mounting	Floor		
	Load (kg)	90	125	200
	Reach (m)	3.90	3.50*	3.00*
	Position repeatability (mm)	0.13	0.13	0.14
	Protection	Std: IP67 Option: Foundry Plus 2, High pressure steam washable		
	Mounting	Shelf		
*Available with LeanID				
	Load (kg)	100	130	205
	Reach (m)	3.30	3.10	1.90
	Position repeatability (mm)	0.10	0.11	0.07
	Protection	Std: IP67 Option: Foundry Plus 2		
	Mounting	Floor		

Selection table

Robots

PRODUCT	BASIC SPECIFICATIONS									
	Load (kg)	150	155	175	200	205	235	245	300	
	Reach (m)	3.20	2.85	3.05	2.60	2.80	2.65	3.00	2.70	
	Position repeatability (mm)	0.10	0.10	0.10	0.10	0.10	0.10	0.10	0.10	
	Protection	Std: IP67 Option: Foundry Plus 2								
	Mounting	Floor								
*Available with LeanID										
	Load (kg)	245	300							
	Reach (m)	2.90	2.60							
	Position repeatability (mm)	0.06	0.05							
	Protection	Std: IP67. Option: Foundry Plus 2								
	Mounting	Inverted								
*Available with LeanID										
	Load (kg)	150	325	340	400	500				
	Reach (m)	3.50	3.10*	2.80*	2.55*	2.55				
	Position repeatability (mm)	0.19	0.10	0.27	0.19	0.08				
	Protection	Std: IP67 Option: Foundry Plus 2								
	Mounting	Floor								
*Available with LeanID										
	Load (kg)	550	800							
		The load is up to 1000 kg while the wrist is down								
	Reach (m)	4.20	3.50							
	Position repeatability (mm)	0.10	0.10							
	Protection	Std: IP67, Foundry Plus 2								
	Mounting	Floor								
*Available with LeanID										




PRODUCT	BASIC SPECIFICATIONS	
	Load (kg)	30
	Reach (m)	1.53
	Position repeatability (mm)	0.03
	Protection	Std: IP67
	Mounting	Floor
	Load (kg)	110
	Reach (m)	2.40
	Position repeatability (mm)	0.20
	Protection	Std: IP67
	Mounting	Floor
	Load (kg)	180 250
	Reach (m)	3.15 3.15
	Position repeatability (mm)	0.05 0.05
	Protection	Std: IP67
	Mounting	Floor
	Load (kg)	450
	Reach (m)	3.18
	Position repeatability (mm)	0.05
	Protection	Std: IP67
	Mounting	Floor

PRODUCT	BASIC SPECIFICATIONS					
	Load (kg)	1	1	3	6	8
	Reach (m)	1.13	1.60	1.13	1.60	1.13
	Position repeatability (mm)	0.10	0.10	0.10	0.10	0.10
	Protection	Std: IP54/67/IP69K				
	Option: Wash down, Stainless Cleanroom, ISO class 5–7, IRB 360-1/1130 certified by IPA					
	Load (kg)	3, max 6				
	Reach (m)	0.45	0.55	0.65		
	Position repeatability (mm)					
	Axis 1 + 2	±0.01	±0.01	±0.01		
	Axis 3	±0.01	±0.01	±0.01		
	Axis 4	±0.01 deg	±0.01 deg	±0.01 deg		
	Protection	Std: IP20				
	Mounting	Table				
	Load (kg)	0.50				
	Reach (m)	0.559				
	Position repeatability (mm)	0.02				
	Protection	Std: IP30				
	Mounting	Table				
	Safety	PL b Cat B				

PRODUCT	BASIC SPECIFICATIONS		PRESS AUTO-MATION ROBOT
	Load (kg)	75/50	
	Reach (m)	3.10 + 1.3/1.45	
	7th axis rotational	Offset 6th–7th axis: 1.30/1.45 m Height: 127 mm	
	Load (kg)	85/80	PRESS AUTO-MATION ROBOT
	Reach (m)	3.50 + 1.3/1.45	
	7th axis rotational	Offset 6th–7th axis: 1.30/1.45 m Height: 127 mm	
	Load (kg)	40	PRESS AUTO-MATION ROBOT
	Reach (m)	3.10 + 1.40	
	7th axis rotational	Stroke: ± 1.40 m Height: 130 mm Max. speed: 5 m Max. acceleration: 20 (m/s²)	
	Load (kg)	100	PRESS AUTO-MATION ROBOT
	Reach (m)	3.10 + 1.75	
	7th axis linear	Stroke: ± 1.75 m Height: 130 mm Max. speed: 5 m Max. acceleration: 18 (m/s²)	
	Load (kg)	150 (Crossbar, tooling and part)	PRESS AUTO-MATION ROBOT
	Reach (m)	3.10 + 1.75	
	Load (kg)	100	PRESS AUTO-MATION ROBOT
	Reach (m)	3.20 + 1.65	


Selection table

Robots



PRODUCT		BASIC SPECIFICATIONS		PAINT ROBOT
	Load (kg)	7		
	Reach (m)	1.20	1.45	
	Position repeatability (mm)	0.15		
	Protection	Std: IP67, Ex		
	Mounting	Floor mounted. Wall mounted and inverted are selectable		
IRB 580		Load (kg)	10 10	PAINT ROBOT
	Reach (m)	2.2	2.6	
	Position repeatability (mm)	0.30		
	Protection	Std: IP67, Ex		
	Mounting	Floor mounted		
IRB 580-13/14		Load (kg)	10	PAINT ROBOT
	Reach (m)	2.2	2.6, rail travel lengthh: 1 - 14	
	Position repeatability (mm)	0.30		
	Protection	Std: IP67, Ex		
	Mounting	Clean wall rail, In-booth rail		



PRODUCT		BASIC SPECIFICATIONS		PAINT ROBOT
	IRB 5400-12	Load (kg)	25	
	Slim arm	Reach (m)	3.10	
		Position repeatability (mm)	0.15	
		Protection	Std: IP67, Ex	
		Mounting	Floor mounted	
	IRB 5400-13/14	Load (kg)	25	PAINT ROBOT
	Slim arm	Reach (m)	3.10, rail travel length: 1 -14	
		Position repeatability (mm)	0.15	
		Protection	Std: IP67, Ex	
		Mounting	Clean wall rail, In-booth rail	
	IRB 5400-22	Load (kg)	25	PAINT ROBOT
	Process arm	Reach (m)	3.10	
		Position repeatability (mm)	0.15	
		Protection	Std: IP67, Ex	
		Mounting	Floor mounted	

PRODUCT	BASIC SPECIFICATIONS		PAINT ROBOT
IRB 5400-23/24 Process arm	Load (kg)	25	
	Reach (m)	3.10, rail travel length: 1 - 14	
	Position repeatability (mm)	0.15	
	Protection	Std: IP67, Ex	
	Mounting	Clean wall rail, In-booth rail	
IRB 5500-22 Process arm	Load (kg)	13	PAINT ROBOT
	Reach (m)	3	
	Position repeatability (mm)	0.15	
	Protection	Std: IP67, Ex	
	Mounting	Wall, floor, tilted, inverted	
IRB 5500-23 Process arm	Load (kg)	13	PAINT ROBOT
	Reach (m)	3	
	Rail travel length	1 - 14	
	Position repeatability (mm)	0.15	
	Protection	Std: IP67, Ex	
	Mounting	Clean-wall rail	





PRODUCT	BASIC SPECIFICATIONS		PAINT ROBOT
	Load (kg)	13	
	Reach (m)	3 rail travel length: 1- 14	
	Position repeatability (mm)	0.15	
	Protection	Std: IP67, Ex	
	Mounting	Elevated, Robot: tilted, upright and inverted	
	Load (kg)	5	
	Reach (m)	1.35, rail lengthh: 3 - 10	
	Position repeatability (mm)	0.15	
	Protection	Std: IP67, Ex	
	Mounting	Floor mounted, rail mounted	




Robots



IRB 120		
	IRB 120 and IRB 120T	
	Load (kg)	3
	Reach (m)	0.58
	Position repeatability (RP) (mm)	0.01
	Working range	
Protection/option		Std: IP30, Cleanroom Class 5. Option: Food Grade Lubrication
Mounting		Floor, wall, inverted and tilted angles
		Main applications
		Assembly
		Machine tending
		Material handling
		Packing/Dispensing
Certified by IPA		



IRB 140		
	IRB 140 and IRB 140T	
	Load (kg)	6
	Reach (m)	0.81
	Position repeatability (RP) (mm)	0.03
	Working range	
	Protection/option	Std: IP67, Cleanroom Class 6. Option: Foundry Plus 2
Mounting		Floor, wall, inverted and tilted angles
		Main applications
		Arc Welding
		Assembly
		Cleaning/Spraying
		Deburring
		Machine Tending
		Material Handling
		Packing

Certified by IPA



IRB 910SC				
IRB 910SC-3/0.45, IRB 910SC-3/0.55 and IRB 910SC-3/0.65		IRB910-3/0.45	IRB910-3/0.55	IRB910-3/0.65
	Load (kg)	3, max 6	3, max 6	3, max 6
	Reach (m)	0.45	0.55	0.65
	Position repeatability (RP) (mm)	Axis 1 + 2 ±0.01	±0.01	±0.01
		Axis 3 ±0.01	±0.01	±0.01
		Axis 4 ±0.01 deg	±0.01 deg	±0.01 deg
Working range				
Protection available		Std: IP20	Std: IP20	Std: IP20
Mounting		Table	Table	Table
Main applications				
Assembly				
Component Placement				
Machine Loading				
Machine Unloading				
Kitting				
Certified by IPA				



IRB 1200			
IRB 1200-5/0.9 and IRB 1200-7/0.7		5/0.9	7/0.7
	Load (kg)	5	7
	Reach (m)	0.90	0.70
	Position repeatability (RP) (mm)	0.025	0.02
	Working range		
	Protection /option	Std: IP40, Cleanroom Class 3. Option: IP67, Foundry Plus 2, Food Grade Lubrication	
Mounting		Any angle	Any angle
Main applications			
Machine Tending			
Material Handling			
Certified by IPA			



IRB 1410		
IRB 1410		Main applications
	Load (kg)	5
	Reach (m)	1.44
	Position repeatability (RP) (mm)	0.02
	Working range	
	Protection available	-
Mounting		Floor
Arc Welding		
Certified by IPA		



IRB 1520		
		Main applications
		Arc Welding
	Load (kg)	4
	Reach (m)	1.50
	Position repeatability (RP) (mm)	0.05
	Working range	
	Protection available	Std: IP40
Mounting	Floor, inverted	
Certified by IPA		

Robots



IRB 1600					
	IRB 1600-6/1.2 and IRB 1600-10/1.2		6/1.2	10/1.2	Main applications
	Load (kg)		6	10	Assembly
	Reach (m)		1.20	1.20	Cleaning/Spraying
	Position repeatability (RP) (mm)		0.02	0.02	Extraction
	Working range				Machine Tending
					Material Handling
					Packing
	Protection available		Std: IP54. Option: IP67 with Foundry Plus 2		
Mounting		Floor, wall, tilted, inverted, shelf			



IRB 1600				
	IRB 1600-6/1.45 and IRB 1600-10/1.45			
		6/1.45	10/1.45	Main applications
	Load (kg)	6	10	Arc Welding
	Reach (m)	1.45	1.45	Assembly
	Position repeatability (RP) (mm)	0.02	0.05	Cleaning/Spraying
	Working range			Cutting
	Machine Tending			
	Material Handling			
			Packing	
	Protection available	Std: IP54. Option: IP67 with Foundry Plus 2		
	Mounting	Floor, wall, tilted, inverted, shelf		



IRB 1660				
	IRB 1660ID-4/1.50 and IRB 1660ID-6/1.55			
	Load (kg)		4	6
	Reach (m)		1.55	1.55
	Position repeatability (RP) (mm)		0.02	0.02
	Working range			
	Protection available		Std: IP40	Std: IP 67 (base, lower arm, wrist), IP 54 (axis 4)
	Mounting		Floor, inverted, tilted	Floor, tilted, inverted, shelf
		Main applications		
		Arc Welding		
		Machine Tending		
		Material Handling		



IRB 2400			Main applications Cutting/Deburring Grinding/Polishing
	IRB 2400-10/1.55 and IRB 2400-16/1.55		
	Load (kg)	12 20	
	Reach (m)	1.55 1.55	
	Position repeatability (RP) (mm)	0.03 0.03	
	Working range		
			
Protection available	Std: IP54. Option: IP67 with Foundry Plus 2		
Mounting	Floor, inverted		



Robots



IRB 2600					
	IRB 2600-12/1.65 and IRB 2600-20/1.65		12/1.65	20/1.65	Main applications
	Load (kg)		12	20	Arc Welding
	Reach (m)		1.65	1.65	Assembly
	Position repeatability (RP) (mm)		0.04	0.04	Cleaning/Spraying
	Working range				Cutting
					Dispensing
					Machine Tending
					Material Handling
					Packing
Protection available		Standard: IP67. Option: Foundry Plus 2			
Mounting		Floor, wall, tilted, inverted, shelf			

IRB 2600		
	IRB 2600-12/1.85	
	Load (kg)	12
	Reach (m)	1.85
	Position repeatability (RP) (mm)	0.04
	Working range	
	Protection available	Standard: IP67. Option: Foundry Plus 2
	Mounting	Floor, wall, tilted, inverted, shelf
	Main applications	
Arc Welding		
Assembly		
Cleaning/Spraying		
Cutting		
Dispensing		
Machine Tending		
Material Handling		
Packing		




IRB 2600ID			
	IRB 2600ID-8/2.00		Main applications
	Load (kg)	8	Arc Welding
	Reach (m)	2.00	Dispensing
	Position repeatability (RP) (mm)	0.02	Machine Tending
	Working range		Material Handling
	Protection available	Standard: IP67 (base, lower arm, wrist), IP54 (axis 4)	
Mounting	Floor, wall, tilted, inverted, shelf		




IRB 2600ID			
	IRB 2600ID/1.85		Main applications
	Load (kg)	15	Arc Welding
	Reach (m)	1.85	Assembly
	Position repeatability (RP) (mm)	0.02	Dispensing
	Working range		Machine Tending
			Material Handling
	Protection available	Std: IP67 (base, lower arm and wrist), IP54 (axis 4)	
Mounting	Floor, wall, tilted, inverted, shelf		



IRB 4400		
	IRB 4400/L10	
	Load (kg)	10
	Reach (m)	2.55
	Position repeatability (RP) (mm)	0.05
	Working range	
	Protection available	Std: IP54. option: IP67, Foundry Plus 2
	Mounting	Floor
		Main applications
		Cutting/Deburring
		Die Spraying
		Dispensing
		Grinding/Polishing
		Measuring

IRB 4400			
	IRB 4400/L60		Main applications
	Load (kg)	60	Cutting/Deburring
	Reach (m)	1.96	Dispensing
	Position repeatability (RP) (mm)	0.05	Grinding/Polishing
	Working range		Measuring
	Protection available	Std: IP54. Option: IP67, steam washable - Foundry Plus 2	
	Mounting	Floor	

Robots



IRB 4600			
	IRB 4600-20/2.50 and IRB 4600-40/2.55		Main applications
	Load (kg)	20 40	Arc Welding
	Reach (m)	2.50 2.55	Assembly
	Position repeatability (RP) (mm)	0.05 0.06	Dispensing
	Working range	 	Laser Welding Machine Tending Material Handling Packing/Palletizing Press brake tending
	Protection available	Std: IP67. Option: Foundry Plus 2, Foundry Prime 2	
Mounting		Floor, tilted, inverted, shelf	




IRB 4600			
	IRB 4600-45/2.05 and IRB 4600-60/2.05		Main applications
	Load (kg)	45/2.05 60/2.05	Assembly
	Reach (m)	2.05 2.05	Deburring
	Position repeatability (RP) (mm)	0.05 0.06	Dispensing
	Working range	 	Machine Tending Material Handling Packing/Palletizing Press Brake Tending
	Protection available	Std: IP67. Option: Foundry Plus 2, Foundry Prime 2 (valid for 60 kg variant)	
Mounting		Floor, tilted, inverted, shelf Floor, tilted, inverted, shelf	

IRB 6620			
	IRB 6620		Main applications
	Load (kg)	150	Assembly
	Reach (m)	2.20	Cleaning/Spraying
	Position repeatability (RP) (mm)	0.10	Cutting/Deburring
	Working range		Dispensing Grinding/Polishing Machine Tending Material Handling Spot Welding
	Protection available	Std: IP54. Option: Foundry Plus 2	
	Mounting	Floor, tilted, inverted*	



*On linear axis



*On linear axis



	IRB 6620		Main applications	
	IRB 6620LX			Machine Tending
	Load (kg)	150		Material Handling
	Reach (m)	1.90		Powertrain Assembly
	Position repeatability (RP) (mm)	0.10		
	Working range			
				
Protection available		5-axis robot arm: Std IP54. Option: Foundry Plus 2 Std: IP66 (linear axis).		
Mounting		Wall, inverted		



IRB 6640			
	IRB 6640-235/2.55 and IRB 6640-185/2.80		Main applications
	Load (kg)	185/2.8 235/2.55	Material Handling
	Reach (m)	2.80 2.55	Machine Tending
	Position repeatability (RP) (mm)	0.05 0.05	Spot Welding
	Working range	 	
	Protection available	Std: IP67. Option: Foundry Plus 2	
Mounting		Floor Floor	



Robots



IRB 6650S					
	IRB 6650S-90/3.9, IRB 6650S-125/3.5 and IRB 6650S-200/3.0		90/3.9	125/3.5	200/190
	Load (kg)		90	125	200
	Reach (m)		3.90	3.50	3.00
	Position repeatability (RP)(mm)		0.13	0.13	0.14
	Working range				
	Protection available		Std: IP67. Option: Foundry Plus 2, High pressure steam washable		
Mounting		Shelf	Shelf	Shelf	
DressPack option			LeanID	LeanID	

IRB 6660					
	IRB 6660-100/3.3 and IRB 6660-130/3.1		100/3.3	130/3.1	
	Load (kg)		100	130	
	Reach (m)		3.30	3.10	
	Position repeatability (RP) (mm)		0.10	0.11	
	Working range				
	Protection available		Std: IP67. Option: Foundry Plus 2		
Mounting		Floor	Floor		



IRB 6660					
	IRB 6660-205/1.9				
	Load (kg)		205		
	Reach (m)		1.90		
	Position repeatability (RP) (mm)		0.07		
	Working range				
	Protection available		Std: IP67, incl Chip Protection. Option: Foundry Plus 2		
Mounting		Floor			



IRB 6700					
	IRB 6700-155/2.85 and IRB 6700-200/2.60		155/2.85	200/2.6	
	Load (kg)		155	200	
	Reach (m)		2.85	2.60	
	Position repeatability (RP) (mm)		0.10	0.10	
	Working range				
	Protection available		Std: IP67. Option: Foundry Plus 2		
Mounting		Floor	Floor		
DressPack option		LeanID	LeanID		



IRB 6700					
	IRB 6700-150/3.20, IRB 6700-175/3.05 , IRB 6700-205/2.80 and IRB 6700-235/2.65		150/3.20	175/3.05	205/2.80
	Load (kg)		150	175	205
	Reach (m)		3.20	3.05	2.80
	Position repeatability (RP) (mm)		0.10	0.10	0.10
	Working range				
	Protection available		Std: IP67. Option: Foundry Plus 2		
Mounting		Floor	Floor	Floor	Floor
DressPack option		LeanID	LeanID	LeanID	LeanID



IRB 6700					
	IRB 6700-245/3.00 and IRB 6700-300/2.70		245/3.00	300/2.70	
	Load (kg)		245	300	
	Reach (m)		3.00	2.70	
	Position repeatability (RP) (mm)		0.10	0.10	
	Working range				
	Protection available		Std: IP67. Option: Foundry Plus 2		
Mounting		Floor	Floor		
DressPack option		LeanID	LeanID		



Robots

IRB 6700				
	IRB 6700 Inverted-245,		245/2.9	300/2.6
	IRB 6700 Inverted-300			
	Load (kg)		245	300
	Reach (m)		2.90	2.60
	Position repeatability (RP) (mm)		0.06	0.05
	Working range			
	Protection available		Std: IP67. Option: Foundry Plus 2	
Mounting			Inverted	Inverted
DressPack option			LeanID	LeanID
				Main applications
				Assembly
				Cutting/Deburring
				Grinding/Polishing
				Machine Tending
				Material Handling
				Spraying
				Spot Welding



IRB 7600				
	IRB 7600-325/3.1 and		325/3.1	340/2.8
	IRB 7600-340/2.8			
	Load (kg)		325	340
	Reach (m)		3.10	2.80
	Position repeatability (RP) (mm)		0.10	0.27
	Working range			
	Protection available		Std: IP67. Option: Foundry Plus 2	
Mounting			Floor	Floor
DressPack option			LeanID	LeanID
				Main applications
				Assembly
				Cutting/Deburring
				Grinding/Polishing
				Machine Tending
				Material Handling
				Spot Welding



IRB 7600				
	IRB 7600-400/2.55 and		400/2.55	500/2.55
	IRB 7600-500/2.55			
	Load (kg)		400	500
	Reach (m)		2.55	2.55
	Position repeatability (RP) (mm)		0.19	0.08
	Working range			
	Protection available		Std: IP67. Option: Foundry Plus 2	
Mounting			Floor	Floor
DressPack option			LeanID	
				Main applications
				Assembly
				Cutting/Deburring
				Grinding/Polishing
				Machine Tending
				Material Handling
				Spot Welding

IRB 7600			
	IRB 7600-150/3.50		
	Load (kg)	150	
	Reach (m)	3.50	
	Position repeatability (RP) (mm)	0.19	
	Working range		
	Protection available	Std: IP67. Option: Foundry Plus 2	
	Mounting	Floor	
			Main applications
			Assembly
			Cutting/Deburring
			Grinding/Polishing
			Machine Tending
			Material Handling

IRB 8700				
	IRB 8700-550/4.20 and		550/4.20	800/3.50
	IRB 8700-800/3.50			
	Load (kg)		550	800
	Reach (m)		4.20	3.50
	Position repeatability (RP) (mm)		0.10	0.10
	Working range			
	Protection available		Std IP67, Foundry Plus 2	
Mounting			Floor	Floor
DressPack option			LeanID	LeanID
				Main applications
				Material Handling
				Machine Tending
				Machining
				Spot Welding

Robots

YuMi®			
IRB 14000-0.5/0.5			
	Load (kg)	0.50	Main applications
	Reach (m)	0.559	Small Parts Material
	Position repeatability (RP) (mm)	0.02	Handling
	Working range		Small Parts Assembly
	Protection available	Std: IP30	
	Mounting	Table	
	Functional saftey	PL b Cat B	

Grippers			
Small Parts Modular servo gripper			
	Weight (g)	215 - 280 depending on configuration	Main applications
	Load (g)	Up to 285	Small Parts Assembly
	Position repeatability (servo gripper) (mm)	0.05	Options
	Finger stroke (mm)	50	Five possible configurations using function modules:
	Stroke	 0-50 mm	1. Servo 2. Servo + Vacuum 3. Servo + Vacuum 1 + Vacuum 2 4. Servo + Vision 5. Servo + Vision + Vacuum
	Protection	Std: IP30	
	Mounting	YuMi® toolflange	
	Vacuum spec. (bar)	Input max 6, Vacuum max 0.050	

Small parts storage, feeding and presentation				
FlexFeeder™				
		FlexFeeder-Single	FlexFeeder-Double	Main applications
	Max. Feature Dimension	< 25	< 30	Small Parts
	Min. Feature Dimension	> 0.50	> 0.50	Presentation 3D to 2D
	Product Weight	< 0.1	< 0.1	Storage and Parts Handling
	Feeder Weight	27	40	
	Feeder Dimension (mm)	754x737x125	754x737x230	For intergration with 2D vision
	Illumination area dimension (mm)	90x160	200x160	



YuMi®




Servo gripper (hand) and one pneumatic, with camera





Servo gripper (hand) and two pneumatics with status lights





Press Automation Robots


Press Automation			
	IRB 6660RX (7-axis robot)		Main applications
	Load (kg)	75/50	Press Automation
	Reach (m)	3.10 + 1.3/1.45	Machine Tending
	7th axis rotational	Offset 6th–7th axis: 1.30/1.45 m Height: 127 mm	Material Handling

Press Automation			
	IRB 7600RX (7-axis robot)		Main applications
	Load (kg)	85/80	Press Automation
	Reach (m)	3.50 + 1.3/1.45	Machine Tending
	7th axis rotational	Offset 6th–7th axis: 1.30/1.45 m Height: 127 mm	Material Handling


Press Automation			
	IRB 6660FX (7-axis robot)		Main applications
	Load (kg)	40	Press Automation
	Reach (m)	3.10 + 1.40	Machine Tending
	7th axis linear	Stroke: ± 1.40 m Height: 130 mm Max. speed: 5 m Max. acceleration: 20 (m/s²)	Material Handling


Press Automation			
	IRB 7600FX (7-axis robot)		Main applications
	Load (kg)	100	Press Automation
	Reach (m)	3.10 + 1.75	Machine Tending
	7th axis linear	Stroke: ± 1.75 m Height: 130 mm Max. speed: 5 m Max. acceleration: 18 (m/s²)	Material Handling


Press Automation			
	IRB 760 Twin XB		Main applications
	Load (kg)	150 (Crossbar, tooling and part)	Press Automation
	Reach (m)	3.10 + 1.75	Material Handling


Press Automation			
	IRB 760FX		Main applications
	Load (kg)	100	Press Automation
	Reach (m)	3.20 + 1.65	Machine Tending
	7th axis linear	Stroke: 1.65 m Height: 175 mm	Material Handling
	Tilting module	+/- 30	


Controllers


IRC5 Single cabinet controller and Drive module			
		Single cabinet	Drive module
	Size H x W x D (mm)	970 x 725 x 710	720 x 725 x 710
	Electrical connections	200–600 V, 50–60 Hz	200–600 V, 50–60 Hz
	Protection	Std: IP54 (IP33 in rear compartment)	Std: IP54 (IP33 in rear compartment)
	IRB support	All robots except IRB 910 SC	All robots except IRB 910 SC
Based on advanced dynamic modelling, the IRC5 optimizes the performance of the robot for the physically shortest possible cycle time (QuickMove™) and precise path accuracy (TrueMove™).			


IRC5 Compact controller		
	Size H x W x D (mm)	320 x 449 x 490
	Electrical connections	220–230 V, 50–60 Hz, single phase
	Protection	Std: IP20
	IRB support	IRB 120, IRB 140, IRB 260, IRB 360, IRB 1200, IRB 1410, IRB 1600, IRB 910SC


IRC5 Panel mounted controller				
		Control module	Drive module small	Drive module large
	Size H x W x D (mm)	375 x 498 x 271	375 x 498 x 299	658 x 498 x 425
	Electrical connections	200–600 V, 50–60 Hz	200–600 V, 50–60 Hz	200–600 V, 50–60 Hz
	Protection	Std: IP20	Std: IP20	Std: IP20
	IRB support	IRB 140, IRB 260, IRB 360, IRB 1200, IRB 1600 (small drive unit), IRB 2400, IRB 2600, IRB 4400, IRB 4600, IRB 6620, IRB 6640, IRB 6650S, IRB 6700, IRB 7600, IRB 460, IRB 660, IRB 760 (large drive unit)		

Process module		
	Size H x W x D (mm)	Small 720 x 725 x 710 mm, Large 970 x 725 x 710
	Electrical connections	Empty cabinet
	Protection	Std: IP54


IRC5P Paint robot controller			
			
	Size H x W x D (mm)	1450 x 725 x 710 mm	
	Electrical connections	200–600 V, 50–60 Hz	
	Protection	Std: IP54 (IP33 in rear compartment)	
	IRB support	Paint robots	


FlexPendant		
	Size	6.5" color touch screen / 1 kg
	Protection	Std: IP54
	IRB support	Non-paint robots


FlexPaint Pendant		
	Protection	Std: IP54, EX protected
	IRB support	Paint robots


FPRC - FlexPendant Retractable Cable			
		Small	Large
	Size H x W x D (mm)	325 x 275 x 185 (mm)	450 x 361 x 195 (mm)
	S4C/S4C+ TPU	3HAC047665-001	3HAC047665-002
	IRC5 GTPU 1 & 2	3HAC047666-001	3HAC047666-002IRC5
	IRC5 GTPU 3	3HAC047724-001	3HAC047724-002

Body-in-White

Gate Framer		
	Strokes (mm)	3000
	Repeatability (mm)	+/- 0.1
	Max Tooling weight (Gate) (kg)	3000
	Max Speed	1.1 m/s for setters – 2.1 m/s for storages
	Cycle Time	18 second gate change (excluding tooling clamping and unclamping)
	Stiffness/Flexibility	S = 100 daN/mm
	Max Static Force in Y	300 daN for each side
	Lifetime	> 1 million cycles
	Weight	70 tons (6 models)

ModulFlex		
	Repeatability (mm)	X & Y : +/- 0.1 , Z : +/- 0.5
	Max Tooling weight (kg)	3000
	Max Speed	4 sec from storage to carriage
	Cycle Time	Tooling change within 12 seconds
	Stiffness	0.01 mm/daN
	Flexibility	Up to 6 models
	Robots in the Framer	4x SW, 2x MH
	Dimensions: 6 models	14x15m


Roller Hemming Head		
	Hemming force (typical)	60 to 100 daN for 0.8 mm panel
	Hemming force (maximum)	300 daN at air supply: 5 bars minimum 160 daN for C-push head
	Force variation speed	600 daN/s
	Flange angle	Up to 130°
	Heming stroke (mm)	Up to 20
	Roll-in (mm)	0.2
	Embedded rollers	2 rollers plus additional roller, blade or pointer


IRBT		
IRBT 2005		
	Max Speed (m/s)	2
	Protection available	Standard and covered version
	Mounting position	Floor
	Travel length (m)	0.80 – 19.80 (in steps of 1m)
	Acc/Ret (m/s²)	2.50 up to 4 depending on actual load
	Robot model	IRB 1520
		IRB 1600
		IRB 2600
		IRB 4600


IRBT				
IRBT 4004, IRBT 6004 and IRBT 7004		IRBT 4004	IRBT 6004	IRBT 7004
	Max Speed (m/s)	2.00	1.60	1.20
	Protection available	Std: Foundry, IP65	Std: Foundry, IP65	Std: Foundry, IP65
	Mounting position	Floor	Floor	Floor
	Travel length (m)	1.90–19.90 (in steps of 1m)	1.70–19.70m (in steps of 1m)	1.70–19.70 (in steps of 1m)
	Acc/Ret (m/s²)	2.50	2.00	1.80
	Robot model	IRB 4400-60	IRB 6620	IRB 7600
		IRB 4600	IRB 6640	
			IRB 6650S	
			IRB 6700	

FlexTrack					
IRT501-66, IRT501-66R, IRT501-90 and IRT501-90R		IRT501-66	IRT501-66R	IRT501-90	IRT501-90R
	Max Speed (m/s)	2	1.50	1.50	1.20
	Load (kg)	900	2000	2000	2950
	Travel length (m)	1-25	1-25	1-25	1-25
	Track length (m)	2.10-105	2.10-105	2.10-105	2.10-105
	Width (m)	0.66	0.66	0.90	0.90
	Acc/Ret (m/s²)	2	1.20	1.20	1
	Robot model	None (Material Handling track motion)			


Body-in-White


FlexLifter			
	IRL 100 and IRL 190		
		IRL 100	IRL 190
	Load (kg)	1000	500
	Lifting height (mm)	100	190
	Speed (mm/s)	40	76
	Lift time (sec)	2.50	2.50
	Rotation	Optional 360° rotation	Optional 360° rotation
	Mounting	Floor or FlexTrack, IRT501-66R, 90, 90R	Floor or FlexTrack, IRT501-66R, 90, 90R


FlexLifter		
	IRL 600	
	Load (kg)	600
	Lifting height (mm)	600
	Speed (mm/s)	200
	Lift time (sec)	3
	Rotation	
	Mounting	Floor or FlexTrack, IRT501-66,66R

FlexPLP				
	IRPLP220			
	Pos. repeatability	± 0.025 mm		
	Linear axis speed	200 mm/s		
	Dynamic Payload	220 kg		
		First horizontal axis (Ball Screw)	First horizontal axis (Rack & Pinion)*	Second horizontal axis
	Available strokes (mm)	190	990	190
		270	1150	270
		350	1630	350
		430	2110	430
		510		510
		590		590
		670		
	Number of axes**	1 to 3 (X, Y, Z, X+Y, X+Z, X+Y+Z)		


* Rack and pinion drive type for the first horizontal axis can have up to 2110mm stroke for a single carriage, and can be increased in steps of 480mm when multiple carriages are mounted.
**Additional carriages can be mounted on the floor axis. - 2 carriages max. on floor axis with ball screw drive type. - No limit on floor axis with rack and pinion drive type.


FlexPLP		
	IRPLP050, 1 axis horizontal	
		H300
		H400
	Repeatability (mm)	+/- 0.05
	Speed (mm/s)	200
	Stroke (mm)	300
	Dynamic load (kg)	50
	Static Load (kg)	150


FlexPLP		
	IRPLP050, 1 axis vertical	
		V200
	Repeatability (mm)	+/- 0.05
	Speed (mm/s)	100
	Stroke (mm)	200
	Dynamic load (kg)	50
	Static Load (kg)	150


FlexPLP		
	IRPLP050, 3 axis	
	Repeatability (mm)	+/- 0.05
	Speed (mm/s)	100
	Stroke (mm)	X = 400 Y = 300 Z = 200
	Dynamic load (kg)	30
	Static Load (kg)	150


Positioners


IRBP A				
	IRBP A-250, IRBP A-500, IRBP A-750	A-250	A-500	A-750
	Max handling capacity (kg)	250	500	750
	Max working envelope ø (mm)	1000	1450	1450
	Max length (mm)	900	950	950


IRBP B				
	IRBP B-250, IRBP B-500 and IRBP B-750	B-250	B-500	B-750
	Max handling capacity (kg)	250 (each side)	500 (each side)	750 (each side)
	Max working envelope ø (mm)	1000	1450	1450
	Max length (mm)	900	1000	1000

IRBP C			
	IRBP C-500 and IRBP C-1000	C-500	C-1000
	Max handling capacity (kg)	500 (each side)	1000 (each side)
	Max working envelope ø (mm)	-	-
	Max length (mm)	-	-

IRBP D		
	IRBP D-600	D-600
	Max handling capacity (kg)	600 (each side)
	Max working envelope ø (mm)	1200
	Max length (mm)	2000

IRBP K				
	IRBP K-300, IRBP K-600 and IRBP K-1000	K-300	K-600	K-1000
	Max handling capacity (kg)	300 (each side)	600 (each side)	1000 (each side)
	Max working envelope ø (mm)	1200	1400	1400
	Max length (mm)	4000	4000	4000


IRBP L						
	IRBP L-300, IRBP L-600, IRBP L-1000, IRBP L-2000 and IRBP L-5000	L-300	L-600	L-1000	L-2000	L-5000
	Max handling capacity (kg)	300	600	1000	2000	5000
	Max working envelope ø (mm)	1500	1500	1500	1500	2200
	Max length (mm)	4000	4000	4000	4000	5000

IRBP R				
	IRBP R-300, IRBP R-600 and IRBP R-1000	R-300	R-600	R-1000
	Max handling capacity (kg)	300 (each side)	600 (each side)	1000 (each side)
	Max working envelope ø (mm)	1000	1200	1200
	Max length (mm)	1600	2000	2000

Application equipment

Arc Welding


WeldGuide IV



WeldGuide IV is the most powerful robotic though-the arc joint seam tracker on the market. To perform accurate welding it is important not only to see the arc, but also to listen to the sound of the welding process. We had this in mind when developing the thru-the-arc tracking sensor WeldGuide. It uses two sensor inputs - the welding current and the arc voltage. Measurements are synchronized with the weave pattern of the robot along the weld seam and provides both vertical and horizontal correction signals to the robot controller, to ensure consistent location of the welding arc along the seam. The WeldGuide sensor reads the real values from the welding arc 25,000 times per second, which means it is up to 25 times faster than traditional tracking methods.

Arc Welding


Welding torches



We offer a wide range of welding torches from the leading brands for local installation. For delivery with the Esab AristoMig 5000i process equipment we offer the Binzel ABIROB A and ABIROB W torch packages with air and water cooling. For delivery with the RPC process equipment we offer the Binzel ABIROB A torch package (air cooling) for IRB 1520ID and the Esab PSF315 welding torch kit (air cooling) for IRB 1410.

Arc Welding

TSC Torch Service Center 2013




Our Torch Service Center is an integrated system for the mechanical removal of spatter from welding torches.

The robot control system operates and supervises the cleaning operation to ensure it does not start until the torch is clamped in the correct position. This guarantees that no vibrations or shocks reach the robot and the torch is locked in the same position every time for more precise cleaning and less wear on the parts being cleaned.

Arc Welding

Bull's Eye




The Bull's Eye provides the user with a fully automated tool center point calibration giving the highest possible level of utilization, quality and productivity from your robot station.

Customised pre-defined programs enable fully automatic tool centre point calibration during production execution, reducing down time to almost zero.

Arc Welding

Esab AristoMig 5000i




Voltage range (V)	8-60
Current range (A)	16-500
Permissible load at MIG/MAG	60% duty cycle: 500A/40V, 100 % duty cycle: 400A/36V
Process methods MIG/MAG	Short arc, Spray arc, Rapid arc, Pulse arc

Esab AristoMig 5000i process equipment standard packages with the Esab AristoMig integrated GUI. Available for IRB 1600, IRB 1600ID, IRB 2600 and IRB 2600ID.

Arc Welding

Power Source RPC S-400




Voltage range (V)	400 (-15%... + 20%)
Current range (A)	400 80% duty cycle
Welding mode	Synergic MIG/MAG

ABB RPC S-400 process equipment standard packages with the ABB RPC S integrated GUI. Available for IRB 1410 and IRB 1520ID. Only for the Asian market.

Arc Welding


GUIs



Available for Fronius, RPC, Esab, Lincoln and Miller power source packages. The easy-to-use FlexPendant GUI provides operators with a single point of programming, an overview of cell status and a display of important quality and production data. With just a few buttons, an intuitive and PC-like, multilingual interface, the operator can organize the welding operation with a minimum of training. By integrating the power source interface on the FlexPendant the operator can have full control over voltage, current, speed, gas flow, etc.


Arc Welding


Seam finder SmarTac





Search Speed (mm/s)	20–50 (depending on position accuracy required)
Search time per point/one dimension (sec)	2–6 (depending on workpiece complexity)
Accuracy (mm)	+/- 0.25 (with search speed 20 mm/sec)


Application equipment




Dispensing				
	Doser (single or double, heated or not heated)			
	Gross volume (cm3)	80	155	560
	Nominal flow (ml/s)	24	37.50	80
	Peak flow (ml/s)	28	44	96
	Nominal pressure / peak pressure (bar)	150/250	150/250	150/250
	Dimensions* (mm)	170x460x950	180x470x960	200x510x1390
*Max. envelope volume; not heated single doser, incl. inlet and outlet valves; no cabling.				


Dispensing				
	Pump (single or double barrel, heated or not heated)			
	Barrel size (l)	30	50	200
	Follower plate (ø) (mm)	280	355	571
	Pressure ratio	65:1	65:1	65:1
	Delivery volume per double stroke (cm3)	150	150	150
	Dimensions* (mm)	1070x700x 2350	1070x700x 2350	1070x700x 2350
*Width, depth, maximum height.				

Integrated Force Control	
	Integrated Force Control
	Conventional robotic solutions are controlled by predefined paths and speeds. However, with Integrated Force Control, the robot reacts to its surrounding and can deviate from its programmed path or speed based on feedback from the force sensor. It is possible to automate complex tasks which previously required skilled personnel and advanced fixed automation.



Integrated Force Control				
	Integrated Force Control			
	Capacity	Sensor 165	Sensor 660	Sensor 2500
	Fx, Fy	165 Nm	660 N	2500 N
	Fz	495 N	1980 N	6250 N
	Mx, My, Mz	15 Nm	60 Nm	400 Nm
	Dimensions			
	Height (mm)	40	40	62
	Diameter (ø mm)	104	104	168
Main applications				
Grinding				
Milling				
Polishing				
Deburring				
Assembly				
Product testing				




Integrated Vision	
	Integrated Vision
	Compact smart cameras that are easily programmed in RobotStudio® together with the robots makes vision guided robots viable for any user. The vision system is highly robust and proven in industrial solutions under tough conditions. The product comes complete with cables, filters, lenses, cameras and software.

Dispensing				
	Applicator			
	Gluing	SPA470 Sealing	SPA410 Sealing	Material Temperature Conditioning
		1 Nozzle*	3 Nozzles	Peltier 600W** Peltier 800W**
				
*Optional with nozzle changer. **Air- or watercooled.				




Machine Tending	
	Tool System TS 2600ID
	The Tools System for IRB 2600ID enables access to tight spaces while having full control of the DressPack by routing the cables and hoses through the robots upper arm. The manifold delivers air, power and signals to any gripper while the optional tool changer is suitable for automatic tool change increasing the flexibility of the tool system. This is giving added benefits of less wear and tear, no restrictions of the robots movement and increased prductivity.
Handling capacity (kg)	60
Max air pressure (bar)	10
Air connections	G 1/8"
Max Voltage (V)	60
Max Current (A)	3

Application equipment

Material Handling								
DressPack								
To support different production needs a family of DressPacks has been developed for Material Handling.								
Common features: <ul style="list-style-type: none">- Well documented solutions including training material, circuit diagram and CAD models.- Easy to maintain including spare part support.- Supports parallel signals as well as common fieldbus communication.								
Motor Units and Gear units								
Gear Units MTD / MID								
	Product/MTD and MID	MTD 250	MTD 500	MTD 750	MTD 2000	MTD 5000	MID 500	MID 1000
	Max handling capacity (kg)	300	600	1000	2000	5000	1300	3300
	Max continous torque (Nm)	350	650	900	3800	9000	1400	3800
	Max bend moment (Nm)	650	3300	5000	15000	60000	5000	15000
Motor Units and Gear units								
Motor Units MU								
	Product/MU	MU 100	MU 200	MU 250	MU 300	MU 400		
	Rated Speed (rpm)	3300	5000	4750	5000	4700		
	Max dynamic torque (Nm)	4.30	14	28	42.80	50		


Material Handling		
Integrated DressPack - LeanID		Robot model
	This type of DressPack creates flexibility for a variety of production demands. It is intended for production where there are high demands on flexibility and accessibility. For operations with many complex wrist movements and where the need for flexibility in changing products is high. No individual adjustment are needed for DressPack.	IRB 6700
		IRB 6650S
		IRB 7600
		IRB 8700
Material Handling		
External with retract arm function		Robot model
	External DressPack with a retract arm pulling the cables away from the wrist. Minor individual adjustment needed for DressPack.	IRB 6620
Material Handling		
External		Robot model
	External DressPack targeting production with basic needs for robot handled tool. Individual adjustment needed for DressPack.	IRB 6620
		IRB 6650S
		IRB 6700
		IRB 7600
		IRB 8700

Application equipment

Spot Welding		
Spot Welding DressPack		
To support different production needs a family of DressPacks has been developed for Spot Welding applications or when they are combined with Material Handling. Common features:		
<ul style="list-style-type: none">- Well documented solutions including training material, circuit diagram and CAD models.- Easy to maintain including spare part support.- Supports parallel signals as well as common fieldbus communication.- Supports pneumatic or servo welding guns.- Supports AC or MFDC welding application.		
Spot Welding		
Integrated DressPack - LeanID		Robot model
	This type of DressPack creates flexibility for a variety of production demands. It is intended for production where there are high demands on flexibility and accessibility. For operations with many complex wrist movements and where the need for flexibility in changing products is high. No individual adjustment is needed for DressPack.	IRB 6700
		IRB 6700 Inverted
		IRB 6650S
		IRB 7600
		IRB 8700
Spot Welding		
External with retract arm function		Robot model
	External DressPack with a retract arm pulling the cables away from the wrist. Minor individual adjustment needed for DressPack.	IRB 6620
Spot Welding		
Spot Welding cabinet		
	Dedicated controller cabinet for spot welding processes, including spot welding timer.	
	The cabinet supports different process needs, like:	
	<ul style="list-style-type: none">• MFDC welding technique.• Robot handled or stationary welding guns.• Servo controlled welding guns.	

Spot Welding

Water and Air Unit



A fully integrated water and air unit for spot welding processes.


The unit supports different process needs like:

– Robot handled or stationary welding guns.

– Servo controlled welding guns.

Spot Welding


FlexGun X Type



Type	X
Transformer	MFDC
Max stroke (mm)	245
Max force (daN)	757 (gun body capability)
Arm length (mm)	227-600
Weight (kg)	100-150
Key feature	Same body for both X and C gun


Spot Welding


FlexGun C/J Type





Type	CJ
Transformer	MFDC
Max stroke (mm)	245
Max force (daN)	757 (gun body capability)
Arm length (mm)	0-250
Weight (kg)	100-150
Key feature	Same body for both X and C gun


Application equipment

Palletizing		
FlexGripper – Claw		
	Handled products	1
	Max. weight per lift (kg)	50
	Gripper weight (kg)	70
	Finger pitch (mm)	75
	Bag dimensions	Finger pitch 80 mm Bag height range 120 - 240 mm Bag length range 300 - 750 mm Bag width range 250 - 450 mm
Main application		Bag palletizing



Palletizing		
FlexGripper – Clamp		
	Handled products	1-21-5
	Max. weight per lift (kg)	4060
	Gripper weight (kg)	4580
	Finger pitch (mm)	1-zone2-zone
	Bag dimensions (LxWxH range) (mm)	(200-650)x(200-500)x(150-330)(200-1200)x(200-500)x(150-330)
Main application		Case palletizing



Palletizing		
FlexGripper – Vacuum		
	Handled products	1-5
	Max. weight per lift (kg)	40
	Gripper weight (kg)	75
	Finger pitch (mm)	10
	Bag dimensions (LxWxH range) (mm)	Minimum product size (LxWxH) 200 x 200 x 10 mm
Main application		Case palletizing handled pallet types: GMA/AUS/EUR/ISO



Press Automation		
Carbon Fiber tooling		Main applications
	Our modular tooling concept combines carbon fiber for structural components (1 & 2) with aluminum components (3) for adaptation to each specific part.	Press Automation Material Handling
	Carbon fiber improves performance thanks to a dramatic reduction in deflection, vibrations and weight. Its design features a reduced height for optimum cycle time.	
	The carbon fiber boom (1) is an extension of the robot arm. With a length of 1450 mm, it has been dimensioned to handle up to 100kg. The carbon fiber gondola arm (2) is a common component for 6- and 7- axis robots. There are two length variants: 1000 and 1400 mm.	



Press Automation		
DDC - Dynamic Drive Chain (Press servotechnology)		
	DDC allows new and existing presses to take full advantage of servo technology with limited peak power, using a servo motor to open and close the press faster while performing the stamping process with the energy accumulated in the flywheel. It consists of a servo kit (gear motor plus drive) that is integrated in the same master control as the automation. The DDC line is capable of running 30% faster than common lines. Energy losses decrease thanks to regeneration capability of both motors.	



Paint robots



IRB 52			Main applications Painting
	IRB 52		
	Load (kg)	7	
	Reach (m)	1.20 1.45	
	Position repeatability (RP) (mm)	0.15	
	Working range		
		Protection available	Std: IP67, Ex
		Mounting	Floor mounted. Wall mounted and inverted are selectable

IRB 580			Main applications Painting
	IRB 580-12, 1220 mm		
	Load (kg)	10	
	Reach (m)	2.20	
	Position repeatability (RP) (mm)	0.30	
	Working range		
		Protection	Std: IP67, Ex
		Mounting	Floor mounted



IRB 580			Main applications Painting
	IRB 580-12, 1620 mm		
	Load (kg)	10	
	Reach (m)	2.60	
	Position repeatability (RP) (mm)	0.30	
	Working range		
		Protection available	Std: IP67, Ex
		Mounting	Floor mounted



IRB 580			Main applications Painting
	IRB 580-13/14		
	Load (kg)	10	
	Reach (m)	2.20 2.60, rail travel length: 1 - 14	
	Position repeatability (RP) (mm)	0.30	
	Working range		
		Protection available	Std: IP67, Ex
		Mounting	Clean wall rail, In-booth rail



IRB 5400			Main applications Painting
	IRB 5400-12 Slim arm		
	Load (kg)	25	
	Reach (m)	3.10	
	Position repeatability (RP) (mm)	0.15	
	Working range		
		Protection available	Std: IP67, Ex
		Mounting	Floor mounted

IRB 5400			Main applications Painting
	IRB 5400-13/14 Slim arm		
	Load (kg)	25	
	Reach (m)	3.10, rail travel length: 1 - 14	
	Position repeatability (RP) (mm)	0.15	
	Working range		
		Protection available	Std: IP67, Ex
		Mounting	Clean wall rail, In-booth rail



Paint robots

IRB 5400		
	IRB 5400-22 Process arm	Main applications
	Load (kg)	25
	Reach (m)	3.10
	Position repeatability (RP) (mm)	0.15
	Working range	
	Protection available	Std: IP67, Ex
	Mounting	Floor mounted
		Painting


IRB 5400		
	IRB 5400-23/24 Process arm	Main applications
	Load (kg)	25
	Reach (m)	3.10, rail travel length: 1 - 14
	Position repeatability (RP) (mm)	0.15
	Working range	
	Protection available	Std: IP67, Ex
	Mounting	Clean wall rail, In-booth rail
		Painting



IRB 5500		
	IRB 5500-22 Process arm	Main applications
	Load (kg)	13
	Reach (m)	3
	Position repeatability (RP) (mm)	0.15
	Working range	
	Protection available	Std: IP67, Ex
	Mounting	Wall, floor, tilted, inverted
		Painting

Bending backwards possibility on axis 3 (may be limited by the hose guiding on the robot)

IRB 5500		
	IRB 5500-23 Process arm	Main applications
	Load (kg)	13
	Reach (m)	3, rail travel length: 1 - 14
	Position repeatability (RP) (mm)	0.15
	Working range	
	Protection available	Std: IP67, Ex
	Mounting	Clean-wall rail
		Painting

Bending backwards possibility on axis 3 (may be limited by the hose guiding on the robot)

IRB 5500		
	IRB 5500-25 Elevated rail	Main applications
	Load (kg)	13
	Reach (m)	3, rail travel length: 1- 14
	Position repeatability (RP) (mm)	0.15
	Protection available	Std: IP67, Ex
	Mounting	Elevated. Robot: tilted, upright and inverted
		Painting





IRB 5350 Door Opener		
	5350 3-axis/4-axis	Main applications
	Load (kg)	5
	Reach (m)	1.35, rail length: 3 - 10
	Position repeatability (RP) (mm)	0.15
	Working range	
	Protection available	Std: IP66, Ex
	Mounting	Floor mounted, rail mounted
		Painting

Painting equipment





Color Change Unit	
Color Change Unit	<p>Our color change units are specifically designed for fast color change. The internal bores of the color change unit are without “dead-ends,” reducing the cleaning cycle to a minimum. Both plastic and steel versions are available, with or without recirculation. The ABB color change units are compatible with solvent based and water borne paint materials used in 1K and 2K systems.</p>
2K Mixer Unit	
2K Mixer Unit	<p>Our 2K mixers are specifically designed for precise mixing of two component fluids and optimized for fast material change. The 2K mixer unit is using the same fluid valves as in the color change unit (common parts). 2K mixer unit is designed and optimized to be used in combination with ABB's gear pumps (and IPS software).</p>
GearPump Unit	
GearPump Unit	<p>Our precision paint pump provides constant and consistent fluid regulation for automatic coating applications. It is specifically designed for fast color change. The ABB gear pumps can be used for paint, catalyst and clear coat and are available in sizes: 1.2 cc/rev, 3 cc/rev, 6 cc/rev and 9 cc/rev. The compact design uses light weight materials and is optimized for low material waste and color change time.</p>
M-PAC Color Change Module & Gear Pump Module	
M-PAC Color Change Module	<p>The modular concept of M-PAC paint application equipment makes it easy to combine the various components to build compact and light units for integration on the robot arms. This enables for the robots to use high acceleration and the application solution to have minimum material waste. The color change module can be mounted directly on a gear pump module for maximum paint savings and minimum color change time. This complete assembly is designed to be integrated in the robot with the shortest possible supply line to the atomizer (typically less than 650 mm).</p>
Compact CBS Unit	
Compact CBS Unit and C-CBS2	<p>The Compact CBS is an optimized solution for internal charge waterborne materials. This CBS unit is used to prepare and change the paint cartridges in the CBS bell atomizer which is handled and controlled by the ABB paint robot. It is a cost effective solution, prepared for 1 or 2 filling stations with flushable cartridges. Flushable cartridges are used when the cartridges are connected to a color change unit for changing the paint material in the same cartridge. Color change waste in a flushable cartridge is slightly more than with dedicated cartridges (< 30 ml).</p>
IRB 5320 Workpiece Positioner	
IRB 5320 Workpiece Positioner	<p>The IRB 5320 Workpiece Positioner is a manipulator that is integrated with a six-axis paint robot, simplifying the painting process. It operates with either one or three axes. The three-axis version of the IRB 5320 is used to precisely position workpieces for painting. The turntables are controlled by the fully-integrated robot servo unit alternating as the loading/unloading station and as the place where the robot paints the workpieces. This single-axis positioner is built, with precision and reliability, on the proven ABB robotics gear box and delivered in several thousand units prior to this introduction.</p>

IRB 5330 Paint External Axis Kit	
Paint External Axis Kit	<p>Our pre-engineered Paint External Axis Kit is for the control and positioning of ABB paint robots on linear or vertical axes solutions. This ex-certificated servo unit is specially designed to be used, together with customized track motion systems, as an engineering building block for paint application, extending possibilities for large object painting with the use of a standardized external axis solution.</p>
Air Control Unit	
Air Control Unit	<p>Our Air Control Unit (ACU) is a high performance, cost-efficient air flow controller typically used for high volume paint applications. This extremely accurate and reliable unit controls the air flow destined to a paint gun or paint bell and contains three different channels that control spray patterns, bell rotation and even paint flow for some applications.</p>
Atomizers (RB1000-SAD, -SSD)	
RB1000-SAD, -SSD	<p>The Robobel family of internal charged bells consist of highly efficient, high performance rotary atomizers for solvent borne paint, providing high finish quality and high transfer efficiency. It includes the popular 926 atomizer, the 951 with pattern control function, and the RB1000 high performance atomizer with up to 1000cc/min paint flow capacity.</p>
CBS Atomizers	
RB1000-WSC	<p>Our Cartridge Bell System (CBS) is the optimal solution for saving paint, both for water borne and solvent borne paints. Color changing is done by changing the paint cartridge, resulting in near zero paint-loss for dedicated color-cartridges. For efficient use of space and cost a flushable version is also available. Key features are: Pattern control for high transfer efficiency, and high flow capacity for high acceleration robots.</p>
Atomizers	
RB1000-EXT	<p>Our external charged bell is a highly efficient atomizer designed for waterborne paint. By utilizing the same air motor as the RB1000 series, the rotation speed performance is up to max 80,000 rpm with a paint flow of 700cc/min in primer. The atomizer is designed with an air heater-free system and has an newly designed electrodes, providing high transfer efficiency.</p>
Atomizers	
RB1000-CE	<p>The RB1000-CE has a small atomizer head with the ø30-mm bell cup and the compact COPES ring. This allows easy access to confined and narrow spaces such as automobile interiors while significantly increaseing painting performance.</p>

Painting equipment

Atomizers	
ROBOBEL031-PC	
	The 031-PC bell is easiest way for general industry customers to gain access to ABB's bell atomizer technology. The circle spray pattern and variable pattern control of ROBOBEL031-PC bring a lot of benefits to users that normally use spray gun. Since the 031-PC uses no high-voltage, not only both water-borne and solvent-borne but also coating materials can be used. There are widely line-up bell cup and selectable for suitable size.
Application package	
Paint Application Packages (PAP)	
	ABB's standardized paint application packages are complete solution designed to have your system up and running very quickly. They are pre-engineered and pre-connected to enable fast installation. They require less field tuning and come documented with standardized interfaces. The packages are flexible. You can choose between gun or bell, select the number of colors, pump sizes, cable length, etc.
Application package	
Simplified Robot Programming (SRP)	
	The ABB Simplified Robot Programming solution combines modern motion tracking technology, with smart software and a teaching handle (tracing device) which resembles a traditional spray gun. Recording mode is activated from the teaching tool and records paint commands along the motion path, visually guided by a line laser to see where the trigger on points are located on the object. Speed, accuracy and fluidness of motion are fully editable in RobView once the recording has stopped.
Feather duster	
Feather duster	
	Designed for the cleaning of car bodies preliminary to Painting, The FeatherDuster system advantageously replace purpose-built "tack off" machines with robotic technology that is incredibly flexible and built on well-established standards to achieve higher quality, efficiency and ease of use.

Application equipment

Machine Tool Tending	
FlexLoader™ SC 6000	
	A leader in the development of automation solutions, ABB's FlexLoader™ SC 6000 sets the standard in flexible machine tool tending. This robotic solution increases machine utilization by as much as 60%. The FlexLoader™ SC 6000 is available in two variants, with IRB 2600 robot (20kg/1.65m reach) and with IRB 4600 robot (60kg/2.05m reach). The FlexLoader™ SC 6000 is a pre-engineered, well-tested and reliable automation solution.
Machining	
FlexWasher	
	<p>2-in-1 process Our FlexWasher technology combines high pressure water de-burring (HPWD) and parts washing into one system. This system removes eyelash burrs and other foreign materials without removing parent material.</p> <p>Robotic Agility Our FlexWashers take advantage of the robot's agility to move the part around stationary HPWD tools or the HPWD tool around the part in a fixture. The result is a uniform and unsurpassed cleanliness of parts with simple as well as complex geometries.</p> <p>Green technology Our FlexWasher technology is different because it does not use heated water to remove burrs and debris. This results in significant lower energy consumption and operating costs. The patented closed loop water filtration system with best-in-class low water consumption also reduces waste handling costs.</p>
Palletizing	
PalletPack	
	PalletPack is a package of pre-engineered products to make end-of-line and bag palletizing solutions more accessible and easier to use. The package includes robot, gripper and easy-to-use wizard on Flexpendant for setting up different palletizing tasks. A PLC including safety is included for control of the complete line.
Packing	
RacerPack	
	RacerPack is a robot function package for packing of flow wrapped products. Receiving flow wraps on a high speed in feed conveyor, RacerPack distributes the products into an indexing belt from which the IRB 360 picks up the products and pack them into boxes. The product is modular and can be ordered with full configuration or modules depending on the need.

Application equipment


FlexArc™ standard arc welding cells

FlexArc cells deliver maximum performance while making optimum use of available space.

All equipment is installed on the common platform which provides for easy relocation within the production facilities. Complete cell is tested in production including welding test, therefore, customers obtains fully functioning solution without need for additional on-site commissioning. FlexArc features the FlexPendant GUI, which not only provides operators with an over-view of the status of the cell, but also important quality and production data.

Cells based on A-type positioners


FlexArc A



Robot	IRB 1520ID, IRB 1600(ID), IRB 2600(ID), IRB 4600
Number of robots	1-2
Positioners	IRBP A-250, IRBP A-500, IRBP A-750
Handling capacity	Max 750 kg
Process equipment package	Fronius, SKS, ESAB, Kemppi

Cells based on B-type positioners


FlexArc B



Robot	IRB 1520ID, IRB 1600(ID), IRB 2600(ID), IRB 4600
Number of robots	1-2
Positioners	IRBP B-250, IRBP B-500, IRBP B-750
Handling capacity	Max 750 kg
Process equipment package	Fronius, SKS, ESAB, Kemppi
Welding torch	Fronius, Dinse, Binzel, SKS
Safety equipment	Complete system of safety features – safety fencing, light curtains, laser scanner, roll doors, safety locks, safety PLC

Cells based on C-type positioners


FlexArc C



Robot	IRB 1520ID, IRB 1600(ID), IRB 2600(ID), IRB 4600
Number of robots	1–2 (up to 3 on request)
Positioners	IRBP C-500, IRBP C-1000
Handling capacity	Max 1000 kg
Process equipment package	Fronius, SKS, ESAB, Kemppi
Welding torch	Fronius, Dinse, Binzel, SKS
Safety equipment	Complete system of safety features – safety fencing, light curtains, laser scanner, roll doors, safety locks, safety PLC

Cells based on D-type positioners


FlexArc D



Robot	IRB 1520ID, IRB 1600(ID), IRB 2600(ID), IRB 4600
Number of robots	1–2 (up to 3 on request)
Positioners	IRBP D-300, IRBP D-600
Handling capacity	Max 600 kg
Process equipment package	Fronius, SKS, ESAB, Kemppi
Welding torch	Fronius, Dinse, Binzel, SKS
Safety equipment	Complete system of safety features – safety fencing, light curtains, laser scanner, roll doors, safety locks, safety PLC

Cells based on K-type positioners

FlexArc K




Robot	IRB 1520ID, IRB 1600(ID), IRB 2600(ID), IRB 4600
Number of robots	1–2 (up to 4 on request)
Positioners	IRBP K-300, IRBP K-600, IRBP K-1000
Handling capacity	Max 1000 kg
Process equipment package	Fronius, SKS, ESAB, Kemppi
Welding torch	Fronius, Dinse, Binzel, SKS
Safety equipment	Complete system of safety features – safety fencing, light curtains, laser scanner, roll doors, safety locks, safety PLC

Application equipment

FlexArc™ standard arc welding cells

Cells based on R-type positioners


FlexArc R



Robot	IRB 1520ID, IRB 1600(ID), IRB 2600(ID), IRB 4600
Number of robots	1–2 (up to 4 on request)
Positioners	IRBP R-300, IRBP R-600, IRBP R-1000
Handling capacity	Max 1000 kg
Process equipment package	Fronius, SKS, ESAB, Kemppi
Welding torch	Fronius, Dinse, Binzel, SKS
Safety equipment	Complete system of safety features – safety fencing, light curtains, laser scanner, roll doors, safety locks, safety PLC

Cells based on 2L-type positioners or fixed tables


FlexArc 2L



Robot	IRB 1520ID, IRB 1600(ID), IRB 2600(ID), IRB 4600
Number of robots	1–2 (up to 4 on request)
Positioners	IRBP R-300, IRBP R-600, IRBP R-1000
Handling capacity	Max 1000 kg
Process equipment package	Fronius, SKS, ESAB, Kemppi
Welding torch	Fronius, Dinse, Binzel, SKS
Safety equipment	Complete system of safety features – safety fencing, light curtains, laser scanner, roll doors, safety locks, safety PLC

Cells based on 2L-type positioners

FlexArc 2L



Robot	IRB 1520ID, IRB 1600(ID), IRB 2600(ID), IRB 4600
Number of robots	1–2 (up to 43on request)
Positioners	2 IRBP L
Handling capacity	Max 300 kg
Process equipment package	Fronius, SKS, ESAB, Kemppi
Welding torch	Fronius, Dinse, Binzel, SKS
Safety equipment	Complete system of safety features – safety fencing, light curtains, laser scanner, roll doors, safety locks, safety PLC

Software products

RobotWare

To boost your productivity and decrease your total cost of owning and operating a robot-based solution, ABB has developed a family of software products to support every stage of the robot life cycle.

RobotWare is a collection of robot software, which offers in its basic design – superior motion control and enables the quick integration of additional hardware. For RobotWare there are a number of options and specific application software available. They represent tools for robot users who need additional functionality, for example running multiple tasks, transfer information from file to robot, communicating with a PC and performing advanced motion tasks. For more information, please visit abb.com/robotics.

RobotWare – Features

QuickMove™ and TrueMove™



Based on advanced dynamic modelling, the IRC5 optimizes the performance of the robot for the physically shortest possible cycle time (QuickMove) and precise path accuracy (TrueMove). Together with a speed-independent path, predictable and high-performance behavior is delivered automatically, with no tuning required by the programmer. What you program is what you get.

RobotWare – Options

Communications



Several optional RobotWare functions are available for communication to and from the robot such as:

– FTP Client	– FlexPendant Interface	– File and Serial Channel Handling
– NFS Client	– Field bus Command Interface	– EtherNet/IP m/s
– PC Interface (including Socket Messaging)		– PROFINET SW, master/slave and slave only

IRC5 Options

I/O Communication



ABB Robotics has expanded the I/O communication capabilities of IRC5 and the I/O system are based on a compact modular design with big improvement in flexibility, easiness and reliability. The system consist of a base unit serving as the minimum configuration. It is equipped with industrial network connectivity, 16 digital inputs, and 16 digital outputs.

RobotWare – Options

AbsAcc




Absolute Accuracy (AbsAcc) is a calibration concept which ensures a TCP absolute accuracy of better than ±1mm in the entire working range with some limitation for “bending backwards” robots. The user is supplied with robot calibration data (compensation parameters saved on the manipulator SMB) and a certificate that shows the performance (“birth certificate”). The difference between an ideal robot and a real robot can typically be up to 10mm, resulting from mechanical tolerances and deflection in the robot structure. The Absolute Accuracy option is integrated in the controller algorithms for compensation of this difference, and does not require external position recalculation.

Software products

RobotWare

RobotWare – Options


SoftMove



SoftMove is a cartesian soft servo option that allows the robot to be compliant or floating to adjust to external forces or variations in work objects. SoftMove can lower the stiffness of the robot in a pre-defined cartesian direction (in relation to either the tool or the work object) while keeping the original behavior in the other directions. The basic behavior of the softness is mainly controlled by stiffness and damping parameters. With SoftMove, the robot is compliant in one direction only which facilitates high accuracy and reliability. The option reduces robot programming time and enables effective interaction between robot and machine, which reduces cycle time.

RobotWare – Options

SafeMove2



SafeMove2 is the latest generation of ABB’s safety certified robot monitoring solution. It delivers greater flexibility, space savings and cutting edge commissioning tools for greater productivity at a lower total investment cost. All this, combined with unsurpassed safety, enables closer collaboration between robots and factory workers. Like its predecessor, SafeMove2 includes a host of cutting-edge safety functions, including safe speed limits, safe standstill monitoring, safe axis ranges and position and orientation supervision.

RobotWare – Options

MultiMove™



A MultiMove system is a system where a common controller controls up to four robots, each equipped with its own drive module. MultiMove system exists in two different modes – Independent and Coordinated. With MultiMove Independent, the robots run independently of each other, i.e. controlled by separate RAPID tasks. It is also possible to run positioners independently (controlled by separate RAPID tasks).

The option MultiMove – Coordinated makes a robot system a MultiMove system with coordinated robots functionality. A MultiMove system is a system where a common controller controls up to four robots, each equipped with its own drive module. MultiMove exists in two different modes – Independent and Coordinated. With the MultiMove Coordinated option, a MultiMove system is able to work together on a common work piece and coordinated in a common workobject. MultiMove Coordinated also includes all MultiMove Independent functionality.

RobotWare – Options

Conveyor Tracking



Conveyor Tracking (also called line tracking) is the function which makes the robot follow a work object on a moving conveyor. While tracking the conveyor, the programmed TCP speed, relative to the work object, will be maintained even when the conveyor speed is changing slowly.

RobotWare – Options

Independent Axis

The Independent Axis option is used to make an external axis (linear or rotating) run independently of the other axes in the robot system.

Path Recovery

Path Recovery is used to store the current movement path, perform some robot movements and then restore the interrupted path. This is useful when an error or interrupt occurs during the path movement. An error handler or interrupt routine can perform a task and then recreate the path.

Path Offset

Path Offset (path corrections) changes the robot path according to the input from a sensor. The robot can thus follow/track a contour, such as an edge or a weld. The path corrections will take effect immediately when receiving data from the sensor.

Multitasking

The Multitasking option gives the possibility of executing up to 20 programs (tasks) in parallel, including the main program. Multitasking can be used to control peripheral equipment or other processes concurrently with robot motion.

Continuous Application Platform

Continuous Application Platform (CAP) is a software platform for time critical application, where a continuous process, for example arc welding, must be synchronized with the movement of the robot.

Discrete Application Platform

Discrete Application Platform (DAP) is a software platform for time critical application, where certain actions shall be performed at specific robot positions. Target users are advanced application software engineers and system integrators

Sensor Interface

The Sensor Interface option can be used to integrate sensor equipment for adaptive control, like path correction or process tuning. For communication between the sensor and the robot controller two different communication links are available: serial link (RS 232) and Ethernet.

Externally Guided Motion


Externally Guided Motion (EGM) is a fast low level interface to the robot controller’s path planning. It can be used to change the robot path with high responsiveness based on input from external devices. The function is designed for advanced users.

Application software

ABB offers a full range of easy-to-use software tools to help you to improve your process, optimize your production, increase productivity, reduce risks and maximize the return of investment of your robot systems.

Arc Welding

RobotWare Arc



RobotWare Arc comprises a large number of dedicated arc welding functions. It is a simple yet powerful program since both the positioning of the robot and the process control and monitoring are handled in one instruction.

Assembly

RobotWare Force Control



RobotWare Force Control will greatly facilitate the use of robots for tasks that needs “touch sensing”, like assembly, fixturing, product testing etc. The option is based on the force control concept, i.e. a robot control strategy where the robot movements are adapted to the feedback from a force sensor. Thus the robot can automatically search for the correct location, and assemble parts using intelligent force/torque motion without the risk for jamming or part damage.

Cutting

RobotWare Cutting



Modern ABB robots are used for high precision laser cutting. This is possible through a combination of ABB robot features and advanced cutting software products, RobotStudio Cutting PowerPac and RobotWare Cutting, developed specifically for robotic laser cutting. Using robots for laser cutting offers substantial cost benefits compared to using laser cutting machines. Robotic laser cutting reduces capital investment by up to 35 percent* and uses less floor space.

*An ABB robot based standard function package compared to a dedicated cutting machine.

Dispensing

RobotWare Dispense



RobotWare-Dispense can be used for different types of dispensing processes. It is a software option typically used for gluing, sealing, spraying and other similar processes, but can also be useful in a wide spectrum of other applications.

Machining

RobotWare Force Control



Enables easy teaching and automatic path generation of complex part surfaces and edges for machining processes like polishing, deburring, grinding. Forces are also controlled during the processing instead of the conventional position control of the robot which makes it more sensitive and increases the quality of the finished parts. Suitable function packages are available for various machining robots of ABB.

Machine Tending

RobotWare Machine Tending




An integrated set of software tools that uses ABB’s extensive experience in machine tending to reduce operational expenditure and increase productivity through easy and flexible programming, straightforward configuration and trouble free operation of ABB robots.

RobotWare Machine Tending is a flexible controller software for deployment and operation of ABB robots. It provides configurable and powerful tools, including an intuitive graphical user interface, that facilitates trouble-free and safe operation for everyone.




Picking and Packing

PickMaster 3



PickMaster is the tool for guiding robots in the packaging process. The PC based software product uses comprehensive graphical interfaces to configure powerful applications where up to eight robots may work in a team along conveying belts. PickMaster 3 includes advanced vision technique and tightly integrated conveyor tracking capability. The integrated vision system is advanced, however PickMaster 3 is also open to communicate with any external sensor. (line scanners, color vision, 3D, etc.).



Application software

Press Automation	
RobotWare StampApp	
	<p>RobotWare StampApp is the core value of StampPack, a Stamping Function Package, to facilitate the automation of different variety of Stamping cells. StampApp provides a friendly environment to integrate, program and operate robotic stamping cells. Its configuration tool brings an unprecedented flexibility for stamping processes.</p> <p>RobotWare StampApp includes:</p> <ul style="list-style-type: none">• Wizard to facilitate robot programming• HMI to easily interact with the robot• Basic pre-engineered interphase to connect robot with cell devices.• Configurator to edit (if required) production processes.
RobView	
RobView	
	<p>With RobView 5 you can manage your paint installation, whether it is one or many robots, visualize the complete paint process, and operate and supervise your paint robot cell. A basic version of RobView 5 is bundled with all IRC5P paint robots, free of charge*. It is an affordable graphical user interface for low budget installations. However, it is scalable and expandable with plug-in options for large and advanced installations.</p>
Spot Welding	
RobotWare Spot	
	<p>Dedicated software that simplifies the Spot Welding application. Advanced motion control for an electrical servo gun are built in features. RobotWare Spot is designed to be a general and flexible software platform offering both standard configurations as well as giving possibility to create customized solutions. All with the target to give easy to use function packages for different types of spot welding systems.</p>

Software products

RobotStudio®

Computer-based programming is the best way to maximize return on investment for robotic systems, resulting in lower costs, faster time to market and superior end products. RobotStudio allows programming to be done on a computer without committing to construction or disturbing existing production.

RobotStudio	
RobotStudio	
	<p>The computer-based system design in RobotStudio ensures you do it right the first time, with the ability to verify tooling, cycle times, work envelopes and product throughput before any construction begins in the real world.</p> <p>Achieving perfectly optimized solutions is made possible because you can quickly and easily try multiple configurations on your PC. You can be certain your system will work properly in the real world after seeing it work in the virtual world. The end result is greatly reduced risk.</p>
RobotStudio – PowerPacs	
RobotStudio ArcWelding PowerPac	
	<p>ArcWelding PowerPac is an add-in to RobotStudio that makes it fast and easy to program arc-welding applications. It includes VirtualArc, an expert system that makes it possible to determine the process parameters necessary to achieve a particular welding result. Use of ArcWelding PowerPac makes it easy to make sure that the optimum tool angles are always used, resulting in higher quality welds and shorter cycle-times.</p>

Software products

RobotStudio®

RobotStudio – PowerPacs

RobotStudio Painting PowerPac



The Painting PowerPac integrates paint programming knowledge and paint process tools into RobotStudio. It will speed up your programming and simulation of painting robots and painting equipment, and is a faster and more intuitive way to create paint programs. Paint strokes are easy to create and edit. Instructions for paint events are automatically added to your program and the event trigger axis automatically selected. Robot positions for the acceleration and deceleration distances are calculated automatically. Paint process performance parameters can be predicted off-line.

RobotStudio – PowerPacs


RobotStudio Machine Tending PowerPac



RobotStudio Machine Tending PowerPac – an add-on for RobotStudio, ABB’s powerful PC-based programming tool – provides a platform for quick, easy creation and editing of machine tending robot cells in a 3D virtual environment. RobotStudio Machine Tending PowerPac is seamlessly integrated with RobotWare Machine Tending.

RobotStudio – PowerPacs

RobotStudio Machining PowerPac



Machining PowerPac reduces programming complexity by 50% and optimizes machining tool path to improve product quality. The PowerPac guides the users in creating accurate targets and paths from surfaces and edges on an imported CAD model while having control of related process parameters in the simulation. In addition the PowerPac provides the possibility to convert CNC-Code to RAPID and customize conversion to match different machine setups. RobotStudio MachiningPowerPac not only supports the traditional position controlled processes but also supports force controlled processes and is seamlessly integrated with Robotware Machining FC.

RobotStudio – PowerPacs

RobotStudio Cutting PowerPac



RobotStudio Cutting PowerPac is an offline programming tool that allows operators to create, modify and verify cutting programs in an offline 3D simulation instead of on the factory floor. RobotStudio Cutting PowerPac is seamlessly integrated with RobotWare Cutting.

RobotStudio – PowerPacs


RobotStudio Palletizing PowerPac



RobotStudio Palletizing PowerPac makes programming robot palletizing systems easier than ever before. As no programming skills are required, RobotStudio Palletizing PowerPac software radically reduces programming times and creates fully tested simulations, and real robot system programs, in minutes.

RobotStudio – PowerPacs

RobotStudio Picking PowerPac



Picking PowerPac is an offline tool that simulates PickMaster 3 in picking applications. The PowerPac offers ease of use configuration of a picking application which can be simulated and fully optimized before being downloaded into PickMaster 3 for real production.

ABB AB
Robotics

Hydrovägen 10
SE-721 36 Västerås, Sweden
Phone: +46 21 325000

ABB Engineering (Shanghai) Ltd.
Robotics

No. 4528, Kangxin Highway,
Pudong New District,
Shanghai, 201319, China
Phone: +86 21 6105 6666

ABB Inc.

1250 Brown Road
Auburn Hills, MI 48326 USA
Phone: +1 248 391 9000

www.abb.com/robotics

Note:

We reserve the right to make technical changes or modify the contents of this document without prior notification. With regard to purchase orders, the agreed particulars shall prevail. ABB does not accept any responsibility whatsoever for potential errors or possible lack of information in this document.

We reserve all rights in this document and in the subject matter and illustrations contained therein. Any reproduction, disclosure to third parties or utilization of its contents – in whole or in part – is forbidden without prior written consent of ABB.



www.facebook.com/ABBRobotics



www.twitter.com/ABBRobotics



www.youtube.com/ABBRobotics



www.linkedin.com/showcase/13223282