

ABB MEASUREMENT & ANALYTICS | DATA SHEET

PUV3402

LED Process Photometer



Measurements for the hydrocarbon processing and chemical industry

Measurement made easy

PUV3402 LED

Overview

The ABB Multiwave PUV3402 LED process photometer is used in the hydrocarbon processing industry and the chemical industry for measurements that are used for process control, environmental compliance and safety measurements. The range of the measurements can be from ppm level to high percent levels and can be made in either vapor or liquid samples.

Features

The ABB PUV3402-LED builds from the successful PUV3402. The PUV3402 LED uses long life wavelength specific Light Emitting Diodes (LED) in the UV and Visible spectral regions to provide both the measure and reference wavelengths. This eliminates the traditional moving part of the filter wheel, which reduces the maintenance requirements of the analyzer. The LED source provides a UV analyzer with a low zero rate, and thus significantly extends the time between calibrations.

PUV3402 LED Multiwave Process Photometer

Applications for process control, environmental compliance and safety measurements

Specification

Environmental (Enclosure)

Protected from direct sunlight and rain: IP 52

Ambient Temperature

Range 0 to +45 °C (32 to 113 °F)

Humidity

95% relative humidity, non-condensing

Dimensions (W x D x H)

254 mm x 266.7 mm x 342.9 mm x 681.0 to

1665.0 mm L*

10.0 in. x 10.5 in. x 13.5 in. x 26.8 to 65.5 in L*)

* Dependent on cell pathlength

Weight

36.28 kg (80 lbs) (minimum, configuration

dependent)

Mounting

Wall

EMI/RFI Considerations

Conform to Class A industrial environment

Electrical Entries

Top and Bottom

Tube Fittings

Sample Inlet/Outlet

Size: 1/4" Standard Gyrolok (Swagelok optional)

Material: 316SS, Monel, Hastelloy C

Purge Inlet & Outlet

Size: 1/4" NPT-F Gyrolok

Material: 316 SS

Output Signals

Analog

4 ea. 4 to 20 mA isolated into 600 ohms max.

Contact Closures

2 each Relay, 3W at 0.25,

5 each Isolated solid state

Both Relay and solid state contact closures

N.O. or N.C.

Digital Outputs

4 ea. 110VDC, 25 watts each

Digital Inputs

8 ea. 2 ea. are dedicated

Power

Size

18 AWG, ¾" Conduit hub

Type

3 conductors each

Performance

Precision

± 1% of full scale

Noise

± 1% of full scale

Lineraity

± 2% of full scale

Zero drift

± 1% of full scale

Response time

Programmable

Ambient electronic stability

± 1% of full scale for 10 °C (18 °F) in 4 hours

Operating Specifications

Wavelength range

280 nm to 800 nm

Ambient temperature range

0 to +45 °C (32 to 113 °F)

Electronic cell heat maximum cell heat

150 °C (302 °F)

Power consumption

450 watts maximum

Sample flow rate

Typical for vapors - 20 to 500 cc/min

Typical for liquids - 5 to 120 cc/min

Sample pressure

0 to 500 psig (0 to 34 bar)

Voltage input variation

10% fluctuation without causing an output of variation of 0.05% of full scale

Safety area classification

NEC/NRTL

Class I, Division 2; Gas Groups B, C, D without enclosure purge

Class I, Division 1; Gas Groups B, C, D with Y type enclosure purge

CSA

Class I, Division 2; Gas Groups B, C, D with Z type enclosure purge

Class I, Division 1; Gas Groups B, C, D with X

type enclosure purge

ATEX

CE Zone 2: II3G, EEx pz IIIB+H2 T4 to T2

CE Zone 1 : II2G, EEx pd[ib] IIB+ H2 T4 to T2

(LCIE 03 ATEX 6007X)

Power

Voltage

100 to 240 VAC

Frequency

45 to 66 HZ

Power consumption

150 Watts maximum power consumption

600 Watts Maximum power consmption with

electric cell heat

Purge gases

Instrument air for enclosure purge

¼ inch tube, minimum

Supply pressure

40 to 80 psi (3 to 6 bars)

Flow rate

0.5 CFM (15 LPM)

Optical purge

Typically Nitrogen

Supply pressure

15 to 30 psi (1 to 2 bars)

Flow rate

10 to 15 cc / min



ABB Inc.

Measurement & Analytics

3567 Jefferson Street North Lewisburg, WV 24901 USA

Tel: +1 304 647 4358 Fax: +1 304 645 4236

Mail: analyzeit@us.abb.com

abb.com/measurement

